




RP73D1J73K2BTG Product Details



Fixed Resistors

RP 1J 73K2 0.1% 15PPM CUT LENGTH

RP73D1J73K2BTG

TE Internal Number: 1879747-7

Product Highlights

- Fixed Resistor
- Resistor Type = Precision Resistor
- Resistance Selection = K Ω
- Resistance = 73.2K Ω
- Power Rating = .10 W

Features

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Precision Resistor
Element	Thin Film

Electrical Characteristics

Resistance Selection (Ω)	K
Resistance (Ω)	73.2K
Power Rating (W)	0.10
Tolerance (%)	0.1

Termination Features

Termination Type	Solder
------------------	--------

Body Features

Mount Style	Surface Mount
Packaging Style	0603
Package, Component Size	1.6 x 0.8

Configuration Features

Number of Terminations	2
Number of Resistors	1

Industry Standards

RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Reflow solder capable to 245°C, Reflow solder capable to 260°C
RoHS/ELV Compliance History	Always was RoHS compliant

Conditions for Usage

Temperature Coefficient (ppm/°C)	±15
----------------------------------	-----

Operation/Application

Application	Precision
-------------	-----------

Packaging Features

Package Type	Taped and Reeled
--------------	------------------

Other

Series	RP73
Brand	Holsworthy