

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [06-66-0013](#)
Status: **Active**
Overview: [Pre-Crimped Leads](#)
Description: Pre-Crimped Lead PicoBlade™ Female-to-PicoBlade™ Female, 304mm, 28 AWG

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	666
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	PicoBlade™ Crimp Terminals
Overview	Pre-Crimped Leads
Product Name	PicoBlade™
UPC	800754232913

Physical

Cable Length	0.30m
Circuits (Loaded)	1
Color - Resin	Red
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.500/g
Packaging Type	Bag
Single Ended	No
Wire Size AWG	28
Wire/Cable Type	Discrete Wire

Material Info

EU RoHS

ELV and RoHS Compliant
REACH SVHC
Contains SVHC: Yes

China RoHS



Hydrazine
Tris(2-chloroethyl)phosphate (TCEP)
Dibutyl phthalate
Diarsenic pentaoxide
Diarsenic trioxide
Bis (2-ethyl(hexyl)phthalate) (DEHP)
Hexabromocyclododecane (HBCDD)
Triethyl arsenate
Benzyl butyl phthalate
2-Pyrrolidinone, 1-methyl
2,4-Dinitrotoluene
Trichloroethylene
Boric acid
Disodium tetraborate, anhydrous
Tetraboron disodium heptaoxide, hydrate
1,2,3-trichloropropane
1,2-Dichloroethane
[4-[4,4'-bis(dimethylamino)benzhydrylidene]cycl
1,2-bis(2-methoxyethoxy)ethane (TEGDME; triglyme
4,4'-bis(dimethylamino)-4''-(methylamino)trityl
Diboron trioxide
#,#-Bis[4-(dimethylamino)phenyl]-4(phenylamino)
4,4'-bis(dimethylamino)benzophenone (Michlers ke
N,N,N',N'-tetramethyl-4,4'-methylenedianiline (M
[4-[[4-anilino-1-naphthyl][4-(dimethylamino)phen
Formamide
Silicic acid, barium salt, lead-doped

4-(1,1,3,3-tetramethylbutyl)phenol,
ethoxylated
Heptacosafuorotetradecanoic
acid
1-bromopropane
Dinoseb
3-ethyl-2-methyl-2-(3-methylbutyl)-1,3-oxazolidi
Propylene oxide;
1,2-epoxypropane;
methyloxirane
Methoxy acetic acid
Furan
Henicosafuoroundecanoic
acid
1,2-Diethoxyethane
Diethyl sulphate
Methylhexahydrophthalic
anhydride
Diazene-1,2-dicarboxamide (C,C'-azodi(formamide)
N-methylacetamide
Pentacosafuorotridecanoic
acid
Tricosafuorododecanoic
acid
Trixylyl phosphate
Sodium perborate;
perboric acid, sodium
salt
Sodium
peroxometaborate

Low-Halogen Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

666Series

Mates With

50125 Crimp Terminal, [50133 Crimp Terminal](#)

Use With

PicoBlade™ Housings [51021](#)

This document was generated on 02/20/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION