

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [06-66-0015](#)  
**Status:** **Active**  
**Overview:** [Pre-Crimped Leads](#)  
**Description:** Pre-Crimped Lead Single-Ended PicoBlade™ Female, 304mm, 28 AWG

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	666
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	PicoBlade™ Crimp Terminals
Overview	<a href="#">Pre-Crimped Leads</a>
Product Name	PicoBlade™
UPC	800754232920

**Physical**

Cable Length	0.15m
Circuits (Loaded)	1
Color - Resin	Red
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.483/g
Packaging Type	Bag
Single Ended	Yes
Wire Size AWG	28
Wire/Cable Type	Discrete Wire

**Material Info**

**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Not Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[666Series](#)

**Mates With**

[50125](#) Crimp Terminal, [50133](#) Crimp Terminal

**Use With**

[PicoBlade™ Housings 51021](#)