

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [08-56-0124](#)  
**Status:** **Active**  
**Overview:** [KK® Interconnect System - Molex](#)  
**Description:** [KK® Trifurcon™ Crimp Terminal 7258, 22-26 AWG, Bag, Phosphor Bronze Gold\(Au\)](#)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-40-02 \(PDF\)](#)

**General**

|                         |   |
|-------------------------|---|
| Product Family          | Crimp Terminals                                 |
| Series                  | <a href="#">7258</a>                            |
| Application             | Power   |
| Crimp Quality Equipment | Yes   |
| Overview                | <a href="#">KK® Interconnect System - Molex</a> |
| Packaging Alternative   | <a href="#">08-56-0123 (Reel)</a>               |
| Product Name            | KK®, Trifurcon™                                 |
| UPC                     | 800754226677                                    |

**Physical**

|                                |                      |
|--------------------------------|----------------------|
| Gender                         | Female               |
| Material - Metal               | Phosphor Bronze      |
| Material - Plating Mating      | Gold                 |
| Material - Plating Termination | Nickel               |
| Net Weight                     | 0.159/g              |
| Packaging Type                 | Bag                  |
| Plating min - Mating           | 0.762µm              |
| Plating min - Termination      | 1.270µm              |
| Termination Interface: Style   | Crimp or Compression |
| Wire Insulation Diameter       | 1.65mm max.          |
| Wire Size AWG                  | 22, 24, 26           |
| Wire Size mm²                  | N/A                  |

**Material Info**

Old Part Number [7258-A\(P558\)L](#)

**Reference - Drawing Numbers**

|                       |                          |
|-----------------------|--------------------------|
| Product Specification | <a href="#">PS-40-02</a> |
| Sales Drawing         | <a href="#">SD-7258</a>  |



*image - Reference only*

**EU RoHS**

**ELV and RoHS  
Compliant**  
**REACH SVHC  
Contains SVHC: No**  
**Low-Halogen Status  
Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[7258Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

| Description                         | Product #                  |
|-------------------------------------|----------------------------|
| Hand Crimp Tool for Crimp Terminals | <a href="#">0638117400</a> |
| Extraction Tool                     | <a href="#">0011030016</a> |