

6.02116.53 BS 18 Li

18 Volt Cordless Drills / Screwdrivers BS 18 Li



- Integrated working light to illuminate the work site
- Ultra-M technology for highest performance, gentle charging, optimum energy utilisation and long service life.
- Battery packs with capacity display for checking the charge status
- 3-year battery pack warranty by means of Ultra-M technology

Comparative technical values

| | |
|--------------------------|--------|
| Type of battery pack | Li-ion |
| Battery pack voltage | 18 V |
| Capacity of battery pack | 2,0 Ah |

| | |
|---------------------------------|--------------------------|
| Maximum torque, soft | 24 Nm |
| Maximum torque, hard | 48 Nm |
| Adjustable torque | 0,8 - 5 Nm |
| - Drill diameter in | |
| - Steel | 10 mm |
| - Wood | 20 mm |
| Idle revolutions | 0 - 450 / 0 - 1.650 /min |
| Drill spindle thread | 1/2 " - 20 UNF |
| Chuck adapter | 1,5 - 13 mm |
| Weight (including battery pack) | 1,5 kg |

Scope of delivery

Quick-action keyless chuck, 2 Li-Power battery packs (18 V/2.0 Ah), Charger SC 60 Plus, Plastic carry case