

## Power It! 4-Outlet Power Strip, 10-ft. Cord with ABS Fire Retardant Plastic Casing

MODEL NUMBER: PS410



### Description

Tripp Lite's Power It! PS410 power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes 4 NEMA 5-15R outlets, 10-foot AC power cord.. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features ABS fire retardant plastic case to stand up to the most demanding environments, illuminated power switch and 15A integrated circuit breaker to prevent dangerous overloads.

INPUT/OUTPUT: Input: NEMA 5-15P/Output: 4 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: Corded power distribution strip

### Features

- Multi-outlet power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment
- Includes 4 NEMA 5-15R outlets
- Illuminated on/off switch provides one-touch power control for connected equipment
- 15A power handling capacity with integrated circuit breaker
- 120V AC, 50/60Hz electrical compatibility
- 10-foot AC power cord
- ABS fire retardant plastic case provides extra safety and durability
- UL certification

## Specifications

OVERVIEW	
Style	Strip

### Highlights

- 4 outlets
- Illuminated on/off switch with cover
- 15-amp circuit breaker
- 10 ft. power cord
- ABS fire retardant plastic

### Applications

- Offers a reliable, convenient and cost-effective method of power distribution for appliances, power tools, lighting and other electrical equipment in home, office or worksite.
- Unfiltered electrical pass-through makes the power strip ideal for distributing alternate waveform UPS or generator power to connected equipment.

### Package Includes

- PS410 power strip
- Warranty information
- Instruction manual



<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Outlet Orientation	Single row of 4
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	1.8
Input Cord Gauge Type	SJT 14AWG
Voltage Compatibility (VAC)	120
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	Illuminated on/off switch controls power to all outlets
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	12 x 5.8 x 1.8
Shipping Dimensions (hwd / cm)	30.5 x 14.7 x 4.6
Shipping Weight (lbs.)	1.2
Shipping Weight (kg)	.544
Unit Dimensions (hwd / in.)	1.2 x 1.85 x 8.1
Unit Dimensions (hwd / cm)	3 x 4.7 x 20.6
Unit Weight (lbs.)	1.4
Unit Weight (kg)	.6
Material of Construction	ABS Fire Retardant Plastic
Integrated Keyhole Mounting Tabs	Keyhole Slots
Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray
<b>CERTIFICATIONS</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Additional International Approvals	Complies with RoHS (Restriction of Hazardous Substances Directive)
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.