

## Protect It! 5-Outlet Surge Protector, Direct Plug-In, 1080 Joules, 1-Line RJ11 Protection

MODEL NUMBER: **SK5TEL-0**



### Highlights

- 5 outlets / direct plug-in
- 1080 joule rating
- Tel/DSL Surge Protection
- Diagnostic LEDs
- \$15,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

### Applications

- Ideal for any desktop, network or home computing application requiring AC power protection

### Package Includes

- SK5TEL-0 surge suppressor
- 6-ft phone cord

### Description

The SK5TEL-0 surge suppressor offers reliable surge and line noise protection. The compact direct plug-in design allows for easy portability and features 5 outlets and 1080 joules of surge energy absorption. Set of RJ11 telephone line suppression jacks protect dial-up and DSL modem lines, fax machines, cordless phones and more. Diagnostic LEDs alert you to potential wiring or protection faults before connected equipment is damaged. \$15,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

### Features

- 5 outlets / direct plug-in
- Surge suppression rating: 1080 joules
- 1 in/1 out Tel/DSL surge protection
- EMI/RFI noise filtering
- Diagnostic LEDs indicate Protected (green) & Grounded (red)
- \$15,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Specifications

OVERVIEW	
Style	Direct Plug-In
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(5) 5-15R
Output (Watts)	1875
Circuit Breaker (amps)	15



<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120v
Input Connection Type	NEMA 5-15P
Input Plug Features	120V, 15A
Input Cord Length (ft.)	0
Input Cord Details	Direct plug-in
Voltage Compatibility (VAC)	120
Maximum Surge Amps	72000
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	500, 500, 400
EMI / RFI Filtering	up to 45dB
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	Yes
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Unit Dimensions (hwd / in.)	5 x 3.5 x 2.1
Unit Dimensions (hwd / cm)	12.7 x 8.89 x 5.33
Unit Weight (lbs.)	.33
Unit Weight (kg)	.15
Material of Construction	Plastic
Housing Color	Light Gray
Receptacle Color	Light Gray
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
cUL / CSA (Canada)	cUL



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Approvals	RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$15,000 <a href="#">Ultimate Lifetime Insurance</a>

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.