


Item no.: 787-904
 Product description: POWER SUPPLY UNIT PRIMARY TRIGGERED WIDE INPUT VOLTAGE RANGE OUTPUT VOLTAGE INDICATION BY LED PFC (POWER FACTOR CORRECTION)



Produkt kann von Bild abweichen / product may differ

Packing unit 1 piece

RoHS compliant

Product group	6 (Electronics)
Peak start-up current	< 5 A
Input fuse	6.3 A slow
Function indication	LED green
max. power consumption	250 W
Output power	240 W
Nominal output current	10 A
Efficiency (AC 230 V)	88 %
Power - Factor - correction (AC 230V)	> 0,97
Deviation, static load change	350 mV
Deviation, dynamic load change 10-90%	2,6 - 3 V
PEAK-TO-AVERAGE RIPPLE FACTOR (%)	5 %
Residual wave	50 mV typ. acc. IEC/EN 61204
Switching peak 20 MHz	ca. 20 mV
Start-up time	700 ms
Output current limit	1 s ... 1,5 x IN / 1,0 ... 1,1 x IN
Mains failure hold up time	15 ms
Protection measurement	Overload- and short-circuit protection

Dielectric strength input-output (AC)
Normal operating method
Vibration resistance
Shock resistance

3 kV
100 % ED
5 g at 10 Hz ... 2 kHz
50 g



Surge capacity	25 g
Ambient operating temperature	-40°C ... +60°C
rel. Humidity	93 %, without condensation
Storage temperature	-40°C .. 100°C
Installation type	DIN-rail (EN 50022) vertical
Connection type	Modules with CAGE CLAMP®-connection 0,08 - 2,5 mm ² / AWG 28 - 14 (Series 236) Strip length 5 - 6 mm / 0.22 in
Standards	EN 60950, VDE 0805, EN 50081-1, EN 50081-2, EN 50082-2, EN 60555-2, EN 61000-3-2, EN 55011/55022, EN 61000-4-2,-3,-4,-5,-6,-11; IEC/En 61204, EN 60068; UL 1950, UL 508 Listed
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 14 AWG
Connection method	CAGE CLAMP® CONNECTION
Weight	1520 g
Color	black
Height	106.6 mm
Height	4.197 in
Width	103 mm
Width	4.055 in
Depth	138 mm
Depth	5.433 in
Strip length from	5 mm
Strip length to	6 mm
Strip length	0.22 in
Customs Tariff No.	85043121



Country of Origin
Mounting

Slowakei
TS 35

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected