

WAGO 890-132



Plug with strain relief housing 2-pole for cable diameter 3.8 - 8.2 mm

Product group	20 (WINSTA)
pole count	2
Cross section [mm ²]	0.25 - 1.5 mm ²
Cross section [AWG]	22 - 16 AWG
Connection method	CAGE CLAMP®S Connection
Measured voltage EN	250 V
Measured shock voltage	4 kV
Pollution degree	3
Current intensity EN	16 A
Weight	5.216 g
Color	white
No. of connection Points	2
No. of potentials	2
Height	13.2 mm
Height	0.52 in
Width	15.6 mm
Width	0.614 in
Depth	61.6 mm
Depth	2.425 in
Strip length from	9 mm
Strip length to	9 mm
Strip length	0.35 in
Customs Tariff No.	85366990
Country of Origin	Deutschland