

# WAGO 890-133



## Plug with strain relief housing 3-pole for cable diameter 4.5 - 10 mm

Product group	20 (WINSTA)
pole count	3
Cross section [mm <sup>2</sup> ]	0.25 - 1.5 mm <sup>2</sup>
Cross section [AWG]	22 - 16 AWG
Connection method	CAGE CLAMP®S Connection
Measured voltage EN	250 V
Measured shock voltage	4 kV
Pollution degree	3
Current intensity EN	16 A
Weight	6.835 g
Color	white
No. of connection Points	3
No. of potentials	3
Height	14 mm
Height	0.551 in
Width	17.9 mm
Width	0.705 in
Depth	63.6 mm
Depth	2.504 in
Strip length from	9 mm
Strip length to	9 mm
Strip length	0.35 in
Customs Tariff No.	85366990
Country of Origin	Deutschland