

smartentry



Wireless Video Doorphone

The smartentry is a wireless video doorphone that allows you to view visitors at your door while speaking to them before answering. Simply install the Door Entry Unit next to your front door so the camera can view your visitor. When the bell rings, you can view visitors on the Wireless Handset from anywhere in your home (up to 300m* away). Plus, using the extended range mode, you can switch to speak-only mode and speak to visitors up to 500m* away.

- Up to 500m* wireless range
- Open doors & gates
- Re-chargable battery
- See & speak to visitors
- Built-in tamper alarm
- 10 picture visitor memory
- 2.5" TFT LCD monitor
- Weatherproof outdoor camera
- 2m IR Night Vision

* Range can be up to 50% less through walls & other obstacles

CONTENTS



1x Wireless Handset



1x Wireless Door Entry Unit



1x Charging Station



2x Li-ion Battery



1x 1m USB A to USB Mini B Cable



1x 1m USB to Fly Lead



2x USB Plug Adaptors



4x Screws
4x Wall Plugs



1x User Manual

Optional Accessories:



1x 20m DC Extension Cable



1x 3m USB Extension Cable

SPECIFICATIONS

smartentry Indoor Monitor Specifications


External Power	5V 1000mA
Li-ion Battery Power	3.7v 1400mA
Shut Down Current	200mA
Average Working Current	260mA
Standby Current	4-8mA
Working Voltage	USB 5V (External Power) 3.7V-4.2V (Li-ion Battery Power)
Transmission Power	18-20dBm
Receiver Sensitivity	-100dBm
Charging Current	600mA
Charging Time	3 Hours
Operating Temperature	-20 ~ 70°C
Transmission Distance (Line of Sight)	500m (Audio) 300m (Video & Audio)

smartentry Outdoor Camera Specifications

External Power	5V 1000mA
Li-ion Battery Power	3.7v 1400mA
Shut Down Current	0mA
Average Working Current	340mA
Standby Current	15-18mA (External Power) 0mA (Li-ion Battery Power)
Working Voltage	DC 5V (External Power) 3.7V-4.2V (Li-ion Battery Power)
Transmission Power	18-20dBm
Receiver Sensitivity	-100dBm
Charging Current	600mA
Charging Time	3 Hours
Operating Temperature	-20 ~ 70°C
Transmission Distance (Line of Sight)	500m (Audio) 300m (Video & Audio)
Night Vision	2m IR Night Vision
Weatherproof	IP44

smartentry Charging Station Specifications

External Power	USB 5V
Charging Current	200mA
Operating Temperature	-20 ~ 70°C



Tel: +44 (0) 844 947 1000

Fax: +44 (0) 871 222 1431

Email: sales@smartwitness.com

Web: www.smartwitness.co.uk



Head Office: Unit 2, Valley Point, Beddington Farm Road, Croydon, Surrey CR0 4WP



Far East Office: Kyoung Am Building, 157-27 Samsung-dong, Kangnam-ku, 135 090. Seoul



USA: SmartWitness USA LLC, 1108 Lunt Avenue, Schaumburg, Chicago, Illinois, 60193, USA

© Copyright SmartWitness 2014. All trademarks acknowledged.