

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [112008-0014](#)
Status: **Active**
Overview: [Brad® Network Diagnostics Tools](#)
Description: NetMeter® Hand Held DeviceNet, Power Monitor, Term. Resistor and Carrying Case

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	112008
Approvals	CE, CUL, UL certified
Comments	NetMeter®, Power Monitor, Term. Resistor & Bag; Measures 667 Parameters
Communication Speed	125, 250, 500 Kbaud
I/O Connector	5-pole Micro-Change® (M12)
IP Rating	N/A
Overview	Brad® Network Diagnostics Tools
Product Literature Order No	987650-3281
Product Name	NetMeter®
Type	Hand Held Digital NetMeter®
UPC	78172506707

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	Yes
Diagnostics Port	Yes
Gender	N/A
Keyway	N/A
Material - Connector Body	N/A
Material - Contact	N/A
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Orientation	N/A
Poles	N/A
Temperature Range - Operating	0°C to +40°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	7-30V DC

Material Info

Old Part Number	DN-MTR-KIT(E)
-----------------	---------------

Reference - Drawing Numbers

Sales Drawing	E-112008-0014
---------------	---------------



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

112008Series