


RE520-LF


- Epoxy fibre-glass FR4 1.50 mm
- Single-sided 35 µm Cu
- Hot air leveling (HAL-leadfree)
- Hole spacing 2.54 x 2.54 mm
- 38 continuous strips with 61 holes
- Hole diameter 1.00 mm
- Size 100 x 160 mm



RE520-LF


- Epoxydglashartgewebe FR4 1,50 mm
- Einseitig 35 µm Cu
- Heißverzinnt (HAL-leadfree)
- Lochraster 2,54 x 2,54 mm
- 38 Leiterbahnen mit 61 Bohrungen
- Lochdurchmesser 1,00 mm
- Größe 100 x 160 mm

ver.20150130



RE520-LF

- Fibre de verre époxyde FR4 1,50 mm
- Simple face 35 µm Cu
- Étamé à chaud (HAL-leadfree)
- Pas 2,54 x 2,54 mm
- 38 pistes 61 perages
- Perforation 1,00 mm Ø
- Dimensions 100 x 160 mm



RE520-LF

- Fibra de vidrio epoxídica FR4 1,50 mm
- Por un lado 35 µm de Cu
- Estañado en caliente (HAL-leadfree)
- Trama de agujeros 2,54 x 2,54 mm
- 38 vías conductoras con 61 agujeros
- Diámetro de los agujeros 1,00 mm
- Tamaño 100 x 160 mm