


RE840-LF


- Epoxy fibre-glass FR4 1.50 mm
- Single-sided 35 µm Cu
- Hot air leveling (HAL-leadfree)
- Hole spacing 2.54 x 2.54 mm
- 53 x 89 soldering pads 2.20 mm Ø
- Hole diameter 1.00 mm
- Connector 32/64/96-channel DIN 41612 type C
- Size 160 x 233.40 mm



RE840-LF


- Epoxydglashartgewebe FR4 1,50 mm
- Einseitig 35 µm Cu
- Heißverzinkt (HAL-leadfree)
- Lochraster 2,54 x 2,54 mm
- 53 x 89 Lötinseln 2,20 mm Ø
- Lochdurchmesser 1,00 mm
- Steckverbinder 32/64/96-polig DIN 41612 Bauform C
- Größe 160 x 233,40 mm

ver.20150130



RE840-LF

- Fibre de verre époxyde FR4 1,50 mm
- Simple face 35 µm Cu
- Étamé à chaud (HAL-leadfree)
- Pas 2,54 x 2,54 mm
- 53 x 89 îlots de brasage 2,20 mm Ø
- Perforation 1,00 mm Ø
- Connecteur 32/64/96-pôles DIN 41612 type C
- Dimensions 160 x 233,40 mm



RE840-LF

- Fibra de vidrio epoxídica FR4 1,50 mm
- Por un lado 35 µm de Cu
- Estañado en caliente (HAL-leadfree)
- Trama de agujeros 2,54 x 2,54 mm
- 53 x 89 nodos de soldadura 2,20 mm Ø
- Diámetro de los agujeros 1,00 mm
- Conector enchufable 32/64/96 polos DIN 41612 modelo C
- Tamaño 160 x 233,40 mm