


#### RE1050


- Epoxy fibre-glass FR4 0.80 mm
- Single-sided 35 µm Cu
- Without holes
- Surface chem. Ni/Au
- 12 self-adhesive strips in pitch 0.65 mm
- Pre-scratched rated break point for the separation of individual modules from the board
- Size 90 x 100 mm



#### RE1050


- Epoxydglashartgewebe FR4 0,80 mm
- Einseitig 35 µm Cu
- Keine Bohrungen
- Oberfläche aus chem. Ni/Au
- 12 selbstklebende Kontakteleisten im Pitch 0,65 mm
- Vorgeritzte Sollbruchstellen
- Größe 90 x 100 mm

ver.20150130



#### RE1050

- Fibre de verre époxyde FR4 0,80 mm
- Simple face 35 µm Cu
- Sans trous
- Surface avec Ni/Au chimique
- 12 listeaux de contact autoadhésifs en pitch 0,65 mm
- Points destinés à la rupture
- Dimensions 90 x 100 mm



#### RE1050

- Fibra de vidrio epoxídica FR4 0,80 mm
  - Por dos lados 35 µm de Cu
  - Sin agujeros
  - Superficie terminal química de Ni/Au
  - 12 adaptadores autoadhesivos de pitch 0,65 mm
  - Punto de rotura controlada tallado
- Tamaño 90 x 100 mm