



#### RE1310-LF

- Epoxy fibre-glass FR4 0.80 mm
- Single-sided 35 µm Cu
- Without holes
- Hot air leveling (HAL-leadfree)
- 5 self-adhesive SM8-Adapters
- Pre-scratched rated break point for the separation of individual modules from the board
- Size 34.70 x 88.00 mm




#### RE1310-LF

- Epoxydglashartgewebe FR4 0,80 mm
- Einseitig 35 µm Cu
- Keine Bohrungen
- Heißverzinkt (HAL-leadfree)
- 5 selbstklebende SM8-Adapter
- Vorgeritzte Sollbruchstellen
- Größe 34,70 x 88,00 mm



#### RE1310-LF

- Fibre de verre époxyde FR4 0,80 mm
- Simple face 35 µm Cu
- Sans trous
- Étamée à chaud (HAL-leadfree)
- 5 adaptateurs SM8 autoadhésifs
- Points destinés à la rupture
- Dimensions 34,70 x 88,00 mm



#### RE1310-LF

- Fibra de vidrio epoxídica FR4 0,80 mm
- Por dos lados 35 µm de Cu
- Sin agujeros
- Estañado en caliente (HAL-leadfree)
- 5 adaptadores autoadhesivos tipo SM8
- Punto de rotura controlada tallado
- Tamaño 34,70 x 88,00 mm