



RE010-HP

- SRBP paper FR2 1.50 mm
- No Cu
- Hole spacing 2.54 x 2.54 mm
- 38 x 61 holes with 1.00 mm Ø
- Size 100 x 160 mm



RE010-HP

- Phenolharz-Hartpapier FR2 1,50 mm
- Kein Cu
- Lochraster 2,54 x 2,54 mm
- 38 x 61 Bohrungen mit 1,00 mm Ø
- Größe 100 x 160 mm



RE010-HP

- Résine phénolplaste FR2 1,50 mm
- Sans Cu
- Pas 2,54 x 2,54 mm
- 38 x 61 perforations 1,00 mm Ø
- Dimensions 100 x 160 mm



RE010-HP

- Papel endurecido con resina fenolada FR2 1,50 mm
- Sin Cu
- Trama de agujeros 2,54 x 2,54 mm
- 38 x 61 agujeros 1,00 mm Ø
- Tamaño 100 x 160 mm