

General Feature	Model No.	T1124
	Panel	10.1" TN
	Destination Country	UK
	Safty and Regulation	CE
	Cabinet Color	Front:White/Black Back:White/Black
	Aspect Ratio	16:9
	Max. Resolution	1024x600
	Touch Module	Capacitive
	multitouch	10 point
	OS	Andriod 4.2.2
	CPU	RK3168 CORTEX-A9 dual Core 1.2GHz
	GPU	PowerVR SGX54X
	Storage	N/A
	ROM FLASH	8GB Nand Flash
	RAM	1GB
	Camera	0.3MP Front 2.0MP Back
	Audio	N/A
	G-sensor	Gravity acceleration sensor
	Speaker	8Ω/1W speaker
	MIC	Yes
	Bluetooth	N/A
	WIFI	802.11b/g/n
	GPS	N/A
	3G	N/A
	DVD	N/A
LAN	N/A	
Connectors	VGA-IN	N/A
	HDMI-IN	N/A
	HDMI-OUT	MINI HDMI
	USB	USB 2.0 (Micro USB)
	RJ45	N/A
	RF-IN(TV)	N/A
	MIC-IN	YES x 1
	AUDIO-OUT	N/A
	AV-IN	N/A
	Headphone	YES x 1
	Memory card socket	SD Card , up to 32GB
	DC connector	YES x 1
	SIM Card Socker	N/A
	Others	N/A
	Photo Viewer	JPG, JPEG, GIF, BMP, PNG

Multi Media	Video Format	MPEG-1/2 MP , MPEG-4 SP/ASP level 5 , H.263 , H.264 BP/MP/HP level 4.2 , AVS , VC-1 SP/MP/AP level 3 , RV8/9/10 , VP6/8 , Sorenson Spark , MVC
	Audio Format	MP3,WMA,OGG,APE,FLAC,AAC,WAV
Power	Power Supply	5V/2A
	Operation Power Consumption	N/A
	Built-in Battery	3.7V/5000mAh Lithium-ion polymer battery
Accessories	USER'S Manual	N/A
	Power Cable	N/A
	USB Cable	YES× 1
	OTG Cable	YES× 1
	Adapter	YES× 1
	Key Board	N/A
	Mouse	N/A
	Warranty	YES
Dimension	Weight of unit(kg)	0.564
	Unit Dimension (W x H x D mm)	262mm x 165mm x 11.5mm