





THIS PRODUCT IS THE CONNECT
USED FOR FPC/FFC AND COPES
WITH AUTOMATIC MOUNTING (SMT).



TYPE CONNECTOR.

58RF

AA J04-0180 H.T 04-07-02 ±0.2

1mm SPACING SMT CONNECTOR
(Cat. No. SFW__R-2ST__LF)

JSA 95856

RECOMMENDED CABLE (FPC)

n : NO. OF CONDUCTOR



PT. NO.	PARTS NAME	MATERIAL	THICKNESS (um)
1	BASE FILM	POLYIMIDE OR POLYESTER OR EQUAL	25
2	CONDUCTOR	COPPER FOIL(PLATING:SOLDER 1um MIN.)	35
3	OVERLAY	POLYIMIDE OR POLYESTER OR EQUAL	——
4	SUPPORTING TAPE	POLYESTER OR POLYIMIDE OR EQUAL	188

NOTES

1. NO BURR AT EACH PORTION.
2. NO PEELING IN COMMON USE.
3. TOTAL THICKNESS LIMIT OF EACH MATERIAL (INCLUDING ADHESIVE AGENT) IS SPECIFIED.
4. A AC SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

ltr	ecn no	dr	date
AA	J05-0055	H.T	05-02-04
AB	J06-0398	H.T	06-09-26
AC	S08-0276	DGOH	08-08-22

mat'l. code

surface ISO 1302 58

tolerance ISO 406 ISO 1101

tolerances unless otherwise specified

angles | linear

projection

mm

scale X

product family 58RF

CODE JP

title RECOMMENDED CABLE (Cat. No. SFW__R-1/2___)

dr	H. TAKAKURA	06-09-26
engr	H. TAKAKURA	06-09-26
chr	DENNIS GOH	08-08-22
appd	JOEY NG	08-08-22

dwg no JSA 91605

sheet 1 of 1

size A4

type Product Customer Drawing

sheet index	revision	AC
	sheet	1

Rev. AC

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

FCIconnect.com

form: A4

RECOMMENDED CABLE (FFC)

n : NO. OF CONDUCTOR



PT. NO.	PARTS NAME	MATERIAL	NOTE
1	INSULATOR	FLAME RESISTING POLYESTER OR EQUAL	———
2	CONDUCTOR	COPPER FOIL	PLATING:TIN OR SOLDER 1um MIN.
3	SUPPORTING TAPE	FLAME RESISTING POLYESTER OR EQUAL	———

NOTES

1. NO BURR AT EACH PORTION.
2. NO PEELING IN COMMON USE.
3. A AC SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

ltr	ecn no	dr	date
AA	J05-0055	H.T	05-02-04
AB	J06-0398	H.T	06-09-26
AC	S08-0276	DGOH	08-08-22

mat'l. code

surface 58 ISO 1302

tolerance ISO 406 ISO 1101

tolerances unless otherwise specified

angles | linear

projection

mm

scale X

dr	H. TAKAKURA	06-09-26
engr	H. TAKAKURA	06-09-26
chr	DENNIS GOH	08-08-22
appd	JOEY NG	08-08-22

product family 58RF

CODE JP

title RECOMMENDED CABLE (Cat. No. SFW__R-1/2___)

dwg no JSA 91604

sheet 1 of 1

size A4

type Product Customer Drawing

sheet index	revision	AC
	sheet	1

Rev. AC

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

FCIconnect.com

form: A4