

# HAND HELD CASES

## 62 Series Pock Boxes

UNIVERSAL ENCLOSURES

HAND HELD CASES

HEAVY DUTY ENCLOSURES

DIN RAIL BOXES

INTERFACE SUPPORTS

CONTROL STATIONS

DIECAST & METAL BOXES

DESKTOP & INSTRUMENT CASES

POTTING BOXES

19" ENCLOSURES

19" CABINETS

DEVELOPMENT BOARDS

CUSTOM SIZED ENCLOSURES

CUSTOM SERVICES


Contemporary range of small robust hand-held boxes with bevelled and rounded edges

- Moulded in high impact ABS
- Snap-fit assembly
- Recesses in lid and base for membrane keypads or overlays
- Excellent properties for machining
- Key-ring lug style available
- Optional EPDM gasket for IP65 seal

### SPECIFICATION

Material	Lid and base high impact ABS
Operating Temperature	Resistant to temperatures of up to 85°C
Protection class	IP62 as standard IP65 with gasket option
Standard colours	Light grey similar to RAL 7035 Black similar to RAL 9004
Standard unit includes	Lid & base
Options	IP65 gasket

BLACK	LIGHT GREY	LENGTH	WIDTH	HEIGHT	STYLE
CHH621BLK	CHH621GRY	55mm	40mm	18mm	-
CHH622BLK	CHH622GRY	60mm	40mm	18mm	key ring lug
CHH623BLK	CHH623GRY	70mm	50mm	20mm	-



### 62-IP Gasket

- EPDM rubber gasket
- IP65 protection
- Operating temperature -20°C to +85°C



TYPE NO.	DESCRIPTION
CHH62GASK	62 Series Gasket