



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
G	ECN 3639: REMOVED SPOOL FROM PACKAGING NOTE	10/14/08	D. FRISIELLO
H	ECN 4174: CN RELEASE	8/10/09	D. CASTRO
J	ECN 6596: UPD. NOTES, ADDED CHANNEL RATING NOTE, AND UPD. LOGO	12/27/12	D. DESJARDIN
K	ECN 6780: ADDED TRD695SZBLK (BLACK) AND TRD695SZR (RED) SERIES	4/9/13	D. DESJARDIN



NOTES:

- LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
- PLUG CONFORMS TO TIA-1096.
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12 [305] = +1 [25] / -0$ $> 12 [305] \leq 60 [1524] = +2 [51] / -0$ $> 60 [1524] \leq 120 [3048] = +4 [102] / -0$ $> 120 [3048] \leq 300 [7620] = +6 [152] / -0$ $> 300 [7620] = +3\% / -0\%$	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. PARHAM	03/15/2006	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	CHECKED BY J. KIEZULAS	03/16/2006	CATEGORY TELECOM/MODULAR
	APPROVED BY C. McCORMICK	03/16/2006	PRODUCT DESCRIPTION CBL RJ45 CAT 6 SHLD LSZH
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A FSCM NO. 43321 DWG. NO. TRD695SZ REV. K SCALE: NONE CAD FILE: TRD695SZ.SLDDRW SHEET 1 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD695SZ-1	LIGHT GRAY	1.0 [0.30]	TRD695SZBLK-1	BLACK	1.0 [0.30]	TRD695SZR-1	RED	1.0 [0.30]
TRD695SZ-2	LIGHT GRAY	2.0 [0.61]	TRD695SZBLK-2	BLACK	2.0 [0.61]	TRD695SZR-2	RED	2.0 [0.61]
TRD695SZ-3	LIGHT GRAY	3.0 [0.91]	TRD695SZBLK-3	BLACK	3.0 [0.91]	TRD695SZR-3	RED	3.0 [0.91]
TRD695SZ-5	LIGHT GRAY	5.0 [1.52]	TRD695SZBLK-5	BLACK	5.0 [1.52]	TRD695SZR-5	RED	5.0 [1.52]
TRD695SZ-7	LIGHT GRAY	7.0 [2.13]	TRD695SZBLK-7	BLACK	7.0 [2.13]	TRD695SZR-7	RED	7.0 [2.13]
TRD695SZ-10	LIGHT GRAY	10.0 [3.05]	TRD695SZBLK-10	BLACK	10.0 [3.05]	TRD695SZR-10	RED	10.0 [3.05]
TRD695SZ-15	LIGHT GRAY	15.0 [4.57]	TRD695SZBLK-15	BLACK	15.0 [4.57]	TRD695SZR-15	RED	15.0 [4.57]
TRD695SZ-20	LIGHT GRAY	20.0 [6.10]	TRD695SZBLK-20	BLACK	20.0 [6.10]	TRD695SZR-20	RED	20.0 [6.10]
TRD695SZ-25	LIGHT GRAY	25.0 [7.62]	TRD695SZBLK-25	BLACK	25.0 [7.62]	TRD695SZR-25	RED	25.0 [7.62]
TRD695SZ-30	LIGHT GRAY	30.0 [9.14]	TRD695SZBLK-30	BLACK	30.0 [9.14]	TRD695SZR-30	RED	30.0 [9.14]
TRD695SZ-40	LIGHT GRAY	40.0 [12.19]	TRD695SZBLK-40	BLACK	40.0 [12.19]	TRD695SZR-40	RED	40.0 [12.19]
TRD695SZ-50	LIGHT GRAY	50.0 [15.24]	TRD695SZBLK-50	BLACK	50.0 [15.24]	TRD695SZR-50	RED	50.0 [15.24]
TRD695SZ-60	LIGHT GRAY	60.0 [18.29]	TRD695SZBLK-60	BLACK	60.0 [18.29]	TRD695SZR-60	RED	60.0 [18.29]
TRD695SZ-75	LIGHT GRAY	75.0 [22.86]	TRD695SZBLK-75	BLACK	75.0 [22.86]	TRD695SZR-75	RED	75.0 [22.86]
TRD695SZ-80	LIGHT GRAY	80.0 [24.38]	TRD695SZBLK-100	BLACK	100.0 [30.48]	TRD695SZR-100	RED	100.0 [30.48]
TRD695SZ-90	LIGHT GRAY	90.0 [27.43]						
TRD695SZ-100	LIGHT GRAY	100.0 [30.48]						
TRD695SZ-150	LIGHT GRAY	150.0 [45.72]						
TRD695SZ-200	LIGHT GRAY	200.0 [60.96]						
TRD695SZ-250	LIGHT GRAY	250.0 [76.20]						
TRD695SZ-300	LIGHT GRAY	300.0 [91.44]						

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY TELECOM/MODULAR			
PRODUCT DESCRIPTION CBL RJ45 CAT 6 SHLD LSZH			
SIZE A	FSCM NO. 43321	DWG. NO. TRD695SZ	REV. K
SCALE: NONE		CAD FILE: TRD695SZ.SLDDRW	
			SHEET 2 OF 2