

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [46819-0011](#)
Status: **Active**
Overview: EXTreme Guardian™ System
Description: EXTreme Guardian™ High Power Terminal, 10 AWG Crimp, 0.76µm Gold (Au)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-46819-001 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	46819
Application	Power
Crimp Quality Equipment	Yes
Overview	EXTreme Guardian™ System
Product Name	EXTreme Guardian™
UPC	883906730932

Physical

Gender	Female
Material - Metal	Copper
Material - Plating Mating	Nickel
Material - Plating Termination	Gold
Net Weight	3.400/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	4.70mm max.
Wire Size AWG	10
Wire Size mm²	N/A

Material Info

Reference - Drawing Numbers

Product Specification	PS-46819-001
Sales Drawing	SD-46819-001




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

46819Series

Mates With

46817 Housing

Application Tooling | FAQ

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
Mini-Mac™ Applicator Air Feed for Power 60 Amp Crimp Terminals, 10 AWG	0638320800