

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [33472-0602](#)
Status: **Active**
Overview: MX150™ Sealed and Unsealed Connector System
Description: MX150™ Sealed Female Connector, Dual Row, 6 Circuits, Polarization B, without Connector Position Assurance, Light Gray

Documents:

[3D Model](#) [Application Specification AS-33611-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification AS-33472-100 \(PDF\)](#)

General

Product Family	Crimp Housings
Series	33472
Application	Power, Wire-to-Wire
Comments	No Connector Position Assurance (CPA)
More Detailed Tech Information	http://ewcap.uscarteams.org
Overview	<u>MX150™ Sealed and Unsealed Connector System</u>
Product Name	MX150™
UPC	800756537450

Physical

Circuits (maximum)	6
Circuits Detail	6
Color - Resin	Gray (Light), Natural
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	9.330/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	22.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Application Specification	AS-33472-100, AS-33611-001
Sales Drawing	150-S-006-2-Z02, SD-33472-061



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[33472Series](#)

Mates With

[33482](#) Male Dual Row Sealed Connector

Use With

[33012](#) MX150™ Female Terminal,
[34345-0001](#) MX150™ Cavity Plug Sealed