

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [48404-0003](#)  
**Status:** **Active**  
**Overview:** [Consumer USB Products](#)  
**Description:** Universal Serial Bus (USB 3.0) I/O Receptacle, Upright 90°, Type A, High-Temperature Blue Nylon, 15µ' Gold (Au) Plating, Height 7.30mm, Contact Height 1.25mm

**Documents:**

[3D Model](#) [Test Summary TS-48404-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-48404-001 \(PDF\)](#)

**General**

Product Family	I/O Connectors
Series	48404
Application	Wire-to-Board
Component Type	Receptacle
Overview	<a href="#">Consumer USB Products</a>
Product Name	USB 3.0
Type	A
UPC	887191519159

**Physical**

Circuits (Loaded)	9
Color - Resin	Blue
Durability (mating cycles max)	5,000
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Nickel, Tin
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	3.420/g
Number of Rows	2
Orientation	Upright
PC Tail Length	2.40mm
PCB Locator	Yes
PCB Retention	Yes
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	2.00mm, 2.50mm
Pitch - Termination Interface	2.00mm, 2.50mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-20°C to +85°C
Termination Interface: Style	Through Hole

**Electrical**

Current - Maximum per Contact	1.8A
Grounding to Panel	Yes
Voltage - Maximum	30V AC/DC

**Solder Process Data**

Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Reflow Capable (SMT only)



image - Reference only

Series

**EU RoHS**

**ELV and RoHS Compliant**

**REACH SVHC**

**Contains SVHC: No**  
**Low-Halogen Status**  
**Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

48404Series

**Mates With**

USB 3.0 Type A Plug

Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	255

### **Material Info**

### **Reference - Drawing Numbers**

Product Specification	PS-48404-001
Sales Drawing	SD-48404-001
Test Summary	TS-48404-001

This document was generated on 04/14/2015

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**