



Part Number: M85049/52
Straight Strain Relief Clamp



Dash Number	Cable Diameter Min - Imperial	Cable Diameter Min - Metric	Cable Diameter Max - Imperial	Cable Diameter Max - Metric
8	.125	3.2	.204	5.2
10	.187	4.7	.286	7.3
12	.291	7.4	.416	10.6
14	.351	8.9	.476	12.1
16	.501	12.7	.626	15.9
18	.518	13.2	.706	17.9
20	.581	14.8	.831	21.1
22	.644	16.4	.956	24.3
24	.706	17.9	1.081	27.5
28	.750	19.1	1.187	30.1
32	.875	22.2	1.250	31.8
36	.938	23.8	1.375	34.9
40	.938	23.8	1.500	38.1
44	1.188	30.2	1.750	44.5
48	1.312	33.3	1.875	47.6

Finish

A = Aluminum, Black Anodize

N = Electroless Nickel

S = 300 Series Steel, Passivated

W = Cadmium, Olive drab over Electroless Nickel

Joslyn Sunbank Company LLC.
1740 Commerce Way - Paso Robles, California 93446
805238-2840 fax805238-0241
www.sunbankcorp.com