

Audio Connector, Plug, 2.5 mm, 2-pole, solder terminal, insulated



Description

- Solder terminal: for cable mounting
- Audio entrances and exits
- Data and Signal transfer
- Audio Plug: 2-pole, insulated, straight

References

Alternative: Housing shielded [4831.1200](#)


Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#)

Technical Data

Diameter	2.5 mm	Allowable Operation Temp.	-20 °C to 70 °C
Number of Poles	2-pole	Terminal	solder terminal nickel-plated
Ratings DC	0.5 A / 30 VDC	Housing	insulated
Ratings AC	0.5 A / 30 VAC	Style	straight
Dielectric Strength	500 VDC	Lifetime	5000 Insertions
Insulation Resistance	> 100 MΩ @ 500 VDC		

Dimensions



Cable diameter max. 4.0 mm

All Variants

Product group	Diameter [mm]	Number of Poles	Terminal	Order Number
Audio Plug/Sockets	2.5	2-pole	solder terminal	4831.1210

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 100 Pcs

Mating Outlets/Connectors

Category / Description

[Audio Plug/Sockets Overview complete](#)

Audio Connector, Socket, 2.5 mm, 2-pole, solder terminal, shielded	4831.2200
Audio Connector, Socket, 2.5 mm, 2-pole, solder terminals for PCB, shielded	4831.2220
Audio Connector, Socket, 2.5 mm, 2-pole, solder terminals for PCB, insulated	4831.2230
Audio Connector, Plug, Inline Socket, 2.5 mm, 2-pole, solder terminal	4831.3200

[Audio Plug/Sockets further types to 4831 Audio-Stecker, D=2,5mm](#)