


Split Loom

Features

- Designed to Hold and Protect Cables, Harnesses, and Hoses
- Quick and Easy to Install. Slit Automatically Closes after Installation
- .013 Heavy Duty Wall Thickness Provides Greater Resistance to Abrasions and Vibrations
- Polyethylene Construction
- Flammability Rating: Meets UL94
- Temperature Rating:
 - +85°C (+185°F) Continuous Rating for 3000 Hours
 - +115°C (+239°F) Short Term Rating for 168 Hours

SL-01



Black Split Loom

NTE Type No.	Feet per Roll	Inner Diameter (in. / mm)	Outer Diameter (in. / mm)	Wall Thickness (in. / mm)	Diag No.
04-SLPE2500	100	.288 / 7.31	.390 / 9.90	.013 / .330	SL-01
04-SLPE2500A	25	.288 / 7.31	.390 / 9.90	.013 / .330	SL-01
04-SLPE3750	100	.415 / 10.54	.532 / 13.51	.013 / .330	SL-01
04-SLPE3750A	25	.415 / 10.54	.532 / 13.51	.013 / .330	SL-01
04-SLPE3750B	1800	.415 / 10.54	.532 / 13.51	.013 / .330	SL-01
04-SLPE5000	100	.511 / 12.97	.660 / 16.76	.013 / .330	SL-01
04-SLPE5000A	25	.511 / 12.97	.660 / 16.76	.013 / .330	SL-01
04-SLPE6250	100	.663 / 16.84	.806 / 20.47	.013 / .330	SL-01
04-SLPE6250A	25	.663 / 16.84	.806 / 20.47	.013 / .330	SL-01
04-SLPE6250B	900	.663 / 16.84	.806 / 20.47	.013 / .330	SL-01
04-SLPE7500	100	.790 / 20.06	.928 / 23.57	.013 / .330	SL-01
04-SLPE7500-5	5	.790 / 20.06	.928 / 23.57	.013 / .330	SL-01
04-SLPE7500-10	10	.790 / 20.06	.928 / 23.57	.013 / .330	SL-01
04-SLPE7500A	25	.790 / 20.06	.928 / 23.57	.013 / .330	SL-01
04-SLPE7500B	600	.790 / 20.06	.928 / 23.57	.013 / .330	SL-01
04-SLPE10000	100	.917 / 23.29	1.073 / 27.25	.013 / .330	SL-01
04-SLPE10000-5	5	.917 / 23.29	1.073 / 27.25	.013 / .330	SL-01
04-SLPE10000A	25	.917 / 23.29	1.073 / 27.25	.013 / .330	SL-01
04-SLPE12500-5	5	1.295 / 32.89	1.500 / 38.10	.013 / .330	SL-01
04-SLPE12500A	25	1.295 / 32.89	1.500 / 38.10	.013 / .330	SL-01
04-SLPE12500B	200	1.295 / 32.89	1.500 / 38.10	.013 / .330	SL-01
04-SLPE15000-5	5	1.468 / 37.21	1.734 / 44.04	.013 / .330	SL-01
04-SLPE15000A	25	1.468 / 37.21	1.734 / 44.04	.013 / .330	SL-01
04-SLPE15000	100	1.468 / 37.21	1.734 / 44.04	.013 / .330	SL-01