

## Power It! 6-Outlet Power Strip, 15-ft. Cord, 5-20P Plug, Metal Housing

MODEL NUMBER: TLM615NC20



### Description

Tripp Lite's Power It! TLM615NC20 power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment requiring heavy-duty 20-amp service. Includes 6 NEMA 5-15/20R outlets, 15-foot AC power cord and keyhole mounting slots. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features rugged metal case to stand up to the most demanding environments, illuminated power switch with transparent cover to prevent accidental shutoff and 20A integrated circuit breaker to prevent dangerous overloads.

INPUT/OUTPUT: Input: NEMA 5-20P/Output: 6 NEMA 5-15/20R

ELECTRICAL: 120V AC, 50/60Hz, 20A

FORMAT: 20A corded power distribution strip

### Features

- Multi-outlet power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment
- Includes 6 NEMA 5-15/20R outlets
- Illuminated on/off switch provides one-touch power control for connected equipment
- Transparent switch cover snaps tight to prevent accidental shutoff
- Convenient keyhole slots provide secure mounting options for a wide variety of surfaces and applications
- Heavy-duty 20A power handling capacity with integrated circuit breaker
- 120V AC, 50/60Hz electrical compatibility
- 15-foot AC power cord
- Rugged metal case provides extra safety and durability
- UL certification

### Highlights

- 6 NEMA 5-15/20R outlets
- Illuminated on/off switch with cover
- Rated for 20-amp electrical service
- 15 ft. power cord with NEMA 5-20P plug
- Rugged metal case
- Keyhole mounting slots

### Applications

- Offers a reliable, convenient and cost-effective method of power distribution for appliances, power tools, lighting and other electrical equipment in home, office or worksite.
- Unfiltered electrical pass-through makes the power strip ideal for distributing alternate waveform UPS or generator power to connected equipment.
- Heavy-duty 20-amp rating is compatible with applications requiring 20-amp electrical service and NEMA 5-15/20R outlets also allow standard 15-amp equipment to be connected.

### Package Includes

- TLM615NC20 power strip
- Warranty information
- Instruction manual



## Specifications

OVERVIEW	
Style	Strip
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15/20R
Output (Watts)	2400
Circuit Breaker (amps)	20
Overload Protection	20A circuit breaker
Outlet Orientation	Single row of 6
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V
Input Connection Type	NEMA 5-20P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.5
Input Cord Gauge Type	SJT 12AWG
Voltage Compatibility (VAC)	120
USER INTERFACE, ALERTS & CONTROLS	
Switches	Illuminated on/off switch controls power to all outlets
Locking Switch Cover	Transparent switch cover snaps tight to prevent accidental shutoff
PHYSICAL	
Shipping Dimensions (hwd / in.)	15.5 x 6.5 x 2.25
Shipping Dimensions (hwd / cm)	39.4 x 16.5 x 5.7
Shipping Weight (lbs.)	3.8
Shipping Weight (kg)	1.7
Unit Dimensions (hwd / in.)	13.75 x 2.5 x 2
Unit Dimensions (hwd / cm)	35 x 6.35 x 5.1
Unit Weight (lbs.)	3.6
Unit Weight (kg)	1.6
Material of Construction	Metal case



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Integrated Keyhole Mounting Tabs	Keyhole slots enable mounting to a variety of surfaces
Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray
Outlets Measurement (Center to Center)	41.3mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole slots = 261.92mm; Distance between end tabs = 330.17mm
<b>CERTIFICATIONS</b>	
Additional International Approvals	Complies with RoHS (Restriction of Hazardous Substances Directive)
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.