


RTD and Thermistor Extension Cables

- ✓ Retractable Cable Have 12" and 4' Initial Lengths with 5:1 Stretch
- ✓ Set-Length Extension Cables Provided in 10 and 25' Standard Lengths
- ✓ 3 Conductor Cables are Standard, 2 Conductor Cables are Provided When Ordered with 2-Pin Connectors Installed
- ✓ 3 Standard Cable Constructions Available
- ✓ Standard and Mini Quick Disconnect Connectors and Audio Connectors Available

Connector Codes

Ordering Code	Description
OTP-U-M	3-lead standard male
OTP-U-F	3-lead standard female
MTP-U-M	3-lead miniature male
MTP-U-F	3-lead miniature female
OST-U-M	2-lead standard male
OST-U-F	2-lead standard female
SMP-U-M	2-lead miniature male
SMP-U-F	2-lead miniature female
TA3M	T Series, male†
TA3F	T Series, female†

† An additional cost of cable for each end with T Series, visit us online for details.



To Order		
Model No.	Description	Length
RECU1-(*)-(*)	3 conductor TPE jacketed retractable extension cable	1', unstretched
RECU4-(*)-(*)	3 conductor TPE jacketed retractable extension cable	4', unstretched
GECU10-(*)-(*)	3 conductor fiberglass insulated and jacketed cable	10'
GECU25-(*)-(*)	3 conductor fiberglass insulated and jacketed cable	25'
TECU10-(*)-(*)	3 conductor PFA insulated and jacketed cable	10'
TECU25(*)-(*)	3 conductor PFA insulated and jacketed cable	25'

(*) If connectors are to be installed onto the cables, please insert the connection codes. Connection codes listed in chart above.

Notes: **RECU** cables contain three #28 AWG stranded copper wire with PFA insulation and TPE jacket. Temperature range is -30 to 150°C. Expansion ratio is 5:1. **GECU** cables contain three #26 AWG nickel plated copper conductors with fiberglass insulation and fiberglass jacket. Temperature range is -73 to 482°C. **TECU** cables contain three #26 AWG nickel plated copper conductors with PFA insulation and jacket. Temperature range is 267 to 260°C.

Ordering Examples: **RECU1-MTP-U-F-MTP-U-M**, RECU1 cable with a male MTP on one end and a female MTP connector on the other end. **TECU10-TA3F-TA3M**, 3-conductor PFA insulated cable, 10' long with TA3M connector one end and TA3F connector on the other.