

## ToLEDo Candle

ToLEDo Candle Clear 250LM B15 SL

0026916



### Range features

- Up to 88% energy saving compared to incandescent lamps
- Instant light
- 100% retrofit - Same dimensions as incandescent equivalent
- Suitable for replacement of up to 25W and 40W incandescent lamps
- Uniform light distribution
- Available in Homelight (2700K)
- Good colour rendering (CRI 80+)
- Average rated life 25,000 hrs



### PRODUCT OVERVIEW

Light colour	Homelight
Technology	LED
Ordering number	0026916
Average life (Rated) (h)	25000
Energy class	A+
Lamp shape	Candle
Lamp finish	Clear
Dimmable	No
Cap/Base	B15
Type	ToLEDo Candle
EAN code	5410288269160
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	250
Equivalent watt (W)	25
Watt (Nominal) (W)	3.7
Voltage (V)	220-240
Colour	Homelight

# ToLEDo Candle

ToLEDo Candle Clear 250LM B15 SL

0026916

## DATA TABLE

### General data

Dry applications use only	Yes
Technology	LED
Ordering number	0026916
Energy class	A+
Average life (Nominal) (h)	25000
Average life (Rated) (h)	25000
Energy saving lamp	Yes
Lamp finish	Clear
Lamp shape	Candle
Dimmable	No
Cap/Base	B15
Type	ToLEDo Candle
EAN code	5410288269160
Long description	Up to 88% energy saving compared to incandescent lamps. Instant light. 100% retrofit - Same dimensions as incandescent equivalent. Suitable for replacement of up to 25W and 40W incandescent lamps. Uniform light distribution. Available in Homelight (2700K). Good colour rendering (CRI 80+). Average rated life 25,000 hrs
Product name	ToLEDo Candle Clear 250LM B15 SL
Lamp mercury content (mg)	0
Starting time (max) (s)	0.05
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
Control gear required	No
Control gear availability	No
Intended purpose	No
No. of switching cycles before premature failure (min)	50000
Special purpose lamp	No
Sales pack quantity	6
Optimal operating condition (°C)	25

### Optical data

Light colour	Homelight
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	250
Lumen maintenance at end of nominal life (%)	70
Luminous flux (Nominal) (lm)	250

## ToLEDo Candle

ToLEDo Candle Clear 250LM B15 SL

**0026916**

### Electrical data

<b>kWh per 1000 hours burning time</b>	4
<b>Equivalent watt (W)</b>	25
<b>Watt (Rated) (W)</b>	3.7
<b>Watt (Nominal) (W)</b>	3.7
<b>Voltage (V)</b>	220-240
<b>Current (A)</b>	37
<b>Lamp power factor</b>	0.45

### Physical data

<b>Weight (kg)</b>	0.05
<b>Colour</b>	Homelight
<b>Lamp Length (mm) - C/L</b>	102
<b>Max. Lamp Diameter (mm) - D</b>	38
<b>Diameter (mm)</b>	38
<b>Single packaging type</b>	Box/Sleeve
<b>Single package dimensions (L x W x H) (cm)</b>	11.90 x 4.80 x 4.80
<b>Inner package dimensions (L x W x H) (cm)</b>	15.50 x 10.50 x 13.40
<b>Inner package net weight (kg)</b>	0.28
<b>Outer package dimensions (L x W x H) (cm)</b>	55.00 x 32.60 x 15.40


## ToLEDo Candle

ToLEDo Candle Clear 250LM B15 SL

0026916

### TECHNICAL DRAWINGS

---



### ENERGY LABEL

---

