

## ToLEDo Outdoor Ball

Ball IP44 Yellow E27

0026889



### Range features



### PRODUCT OVERVIEW

Light colour	
Technology	LED
Ordering number	0026889
Average life (Rated) (h)	25000
Lamp finish	Coloured
Lamp shape	Ball
Dimmable	No
Cap/Base	E27
Type	ToLEDo Outdoor Ball
EAN code	54 10288268897
CRI (Ra)	
Colour temperature (K)	
Luminous flux (Rated) (lm)	
Efficacy (Rated) (lm/w)	
Watt (Nominal) (W)	0.5
Voltage (V)	220-240
Colour	

# ToLEDo Outdoor Ball

Ball IP44 Yellow E27

**0026889**

## DATA TABLE

### General data

<b>Ordering number</b>	0026889
<b>Technology</b>	LED
<b>Dry applications use only</b>	No
<b>Average life (Nominal) (h)</b>	25000
<b>Average life (Rated) (h)</b>	25000
<b>Energy saving lamp</b>	Yes
<b>Lamp finish</b>	Coloured
<b>Lamp shape</b>	Ball
<b>Dimmable</b>	No
<b>Cap/Base</b>	E27
<b>Type</b>	ToLEDo Outdoor Ball
<b>EAN code</b>	5410288268897
<b>E-number SE</b>	8296510
<b>Product name</b>	Ball IP44 Yellow E27
<b>Lamp mercury content (mg)</b>	0
<b>Starting time (max) (s)</b>	0.05
<b>Warm-up time to 60% of full light (max) (s)</b>	< 1s => 60%
<b>Control gear required</b>	No
<b>Control gear availability</b>	No
<b>Intended purpose</b>	No
<b>No. of switching cycles before premature failure (min)</b>	100000
<b>Special purpose lamp</b>	Yes
<b>Sales pack quantity</b>	1
<b>Optimal operating condition (°C)</b>	25

### Optical data

<b>Light colour</b>	
<b>CRI (Ra)</b>	
<b>Colour temperature (K)</b>	
<b>Luminous flux (Rated) (lm)</b>	
<b>Lumen maintenance at end of nominal life (%)</b>	70
<b>Luminous flux (Nominal) (lm)</b>	

## ToLEDo Outdoor Ball

Ball IP44 Yellow E27

**0026889**

### Electrical data

<b>kWh per 1000 hours burning time</b>	1
<b>Efficacy (Rated) (lm/w)</b>	
<b>Watt (Rated) (W)</b>	0.5
<b>Watt (Nominal) (W)</b>	0.5
<b>Voltage (V)</b>	220-240
<b>Current (A)</b>	20
<b>Lamp power factor</b>	0.15

### Physical data

<b>Weight (kg)</b>	0.02
<b>Colour</b>	
<b>Length base to pin Min-Max - B</b>	70
<b>Lamp Length (mm) - C/L</b>	70
<b>Max. Lamp Diameter (mm) - D</b>	45
<b>Diameter (mm)</b>	45
<b>Single packaging type</b>	Box/Sleeve
<b>Single package dimensions (L x W x H) (cm)</b>	8.50 x 4.40 x 4.40
<b>Inner package dimensions (L x W x H) (cm)</b>	22.50 x 9.20 x 9.50
<b>Inner package net weight (kg)</b>	0.23
<b>Outer package dimensions (L x W x H) (cm)</b>	49.50 x 29.50 x 11.50

## ToLEDo Outdoor Ball

Ball IP44 Yellow E27

**0026889**

### TECHNICAL DRAWINGS

---

