

ToLEDo Outdoor Ball

Ball IP44 Green E14

0026891



Range features



PRODUCT OVERVIEW

Light colour	
Technology	LED
Ordering number	0026891
Average life (Rated) (h)	25000
Lamp finish	Coloured
Lamp shape	Ball
Dimmable	No
Cap/Base	E14
Type	ToLEDo Outdoor Ball
EAN code	54 10288268910
CRI (Ra)	
Colour temperature (K)	
Luminous flux (Rated) (lm)	
Efficacy (Rated) (lm/w)	
Watt (Nominal) (W)	0.5
Voltage (V)	220-240
Colour	

ToLEDo Outdoor Ball

Ball IP44 Green E14

0026891

DATA TABLE

General data

Ordering number	0026891
Technology	LED
Dry applications use only	No
Average life (Nominal) (h)	25000
Average life (Rated) (h)	25000
Energy saving lamp	Yes
Lamp finish	Coloured
Lamp shape	Ball
Dimmable	No
Cap/Base	E14
Type	ToLEDo Outdoor Ball
EAN code	5410288268910
E-number SE	8296513
Product name	Ball IP44 Green E14
Lamp mercury content (mg)	0
Starting time (max) (s)	0.05
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
Control gear required	No
Control gear availability	No
Intended purpose	No
No. of switching cycles before premature failure (min)	100000
Special purpose lamp	Yes
Sales pack quantity	1
Optimal operating condition (°C)	25

Optical data

Light colour	
CRI (Ra)	
Colour temperature (K)	
Luminous flux (Rated) (lm)	
Lumen maintenance at end of nominal life (%)	70
Luminous flux (Nominal) (lm)	

ToLEDo Outdoor Ball

Ball IP44 Green E14

0026891

Electrical data

kWh per 1000 hours burning time	1
Efficacy (Rated) (lm/w)	
Watt (Rated) (W)	0.5
Watt (Nominal) (W)	0.5
Voltage (V)	220-240
Current (A)	20
Lamp power factor	0.15

Physical data

Weight (kg)	0.02
Colour	
Length base to pin Min-Max - B	75
Lamp Length (mm) - C/L	75
Max. Lamp Diameter (mm) - D	45
Diameter (mm)	45
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	8.50 x 4.40 x 4.40
Inner package dimensions (L x W x H) (cm)	22.50 x 9.20 x 9.50
Inner package net weight (kg)	0.19
Outer package dimensions (L x W x H) (cm)	49.50 x 29.50 x 11.50

ToLEDo Outdoor Ball

Ball IP44 Green E14

0026891

TECHNICAL DRAWINGS

