




MultiPad Visconte 2

MORE POWERFUL PC IN FORM OF TABLET

Now even more faster on LATEST Intel® Dual-Core processor and Windows 8.1 that works longer with powerful battery



KEY FEATURES

- **AMAZING VIEW:** Capacitive multi touch(10 Dots) 10-inch display is remarkably crisp and bright thanks to IPS technology
- **BEYOND SMART:** Intelligent and beautiful Windows 8.1 with MS Office Home and Student 2013 edition pre-installed
- **FAST PERFORMANCE:** Great performance with Intel® Celeron® Dual-Core processor with up to 2.0 GHz and 2GB RAM
- **EXTRA LONG MOBILITY:** Powerful battery with 6400 mAh more than 5 hours of video playback time and 150 hours of standby time
- **GREAT CONNECTIVITY:** Top speed internet thanks to internal 3G 21 Mbps connection or WiFi
- **CAMERA:** Take pictures of your special moments with 5.0MP rear camera and make video calls with 1.0MP front camera
- **EXTRA LARGE:** 32GB / 64GB internal eMMC plus expandable up to 64GB storage with Micro SD cards

TECHNICAL SPECIFICATION

Display Size	10.1" 25.7cm
Resolution	1280*800 pixels (16:10)
Display Technology	LCD IPS Capacitive MultiTouch (10 dots)
CPU	Intel® Celeron Processor N2806 (1M Cache, 1.60 GHz) up to 2.0 GHz
GPU	Intel® HD Graphics, Open GL 4.0, 756Mhz
Power	Lithium battery 6400 mAh
Memory	2 GB DDR3 SDRAM / 32 or 64 GB eMMC
OS	MS Windows 8.1 / Windows 8.1 Pro
Internet	WiFi or/and 3G 21 Mbps
Communication	WiFi: 802.11 b/g/n WCDMA:850MHz/900MHz/1700MHz(AWS)/1900MHz/2100MHz
Interfaces	USB 2.0 Mini HDMI Micro SD (micro SDHC compatible)
Bluetooth	Support Bluetooth 4.0
Camera	Rear 5 MP, Front 1 MP
Slots	Micro SD slot supports up to 64GB
Speaker	Built-in stereo speaker 1W
Dimensions & Weight	258 x 172.6 x 10.5 mm/ 660 gram
Accessories Included	QSG, Warranty card, Unswitchable adaptor, EU plug, UK plug Stickers for after-service
Device Color	Dark Gray

*DETAILS

Article	PMP812EGR	PMP812E3GGR	PMP812FGR	PMP812F3GGR	PMP812F3GGRPRO
Storage	32GB			64GB	
OS	MS Windows 8.1 (64 bit)				MS Windows 8.1 Pro (64 bit)
Internet	WiFi	3G 21 Mbps and WiFi	WiFi	3G 21 Mbps and WiFi	3G 21 Mbps and WiFi
Connectivity	WiFi: 802.11 b/g/n	WiFi: 802.11 b/g/n WCDMA:850MHz/ 900MHz/1700MHz(AWS)/ 1900MHz/2100MHz	WiFi: 802.11 b/g/n	WiFi: 802.11 b/g/n WCDMA:850MHz/ 900MHz/1700MHz(AWS)/ 1900MHz/2100MHz	WiFi: 802.11 b/g/n WCDMA:850MHz/ 900MHz/ 1700MHz(AWS)/ 1900MHz/2100MHz