

# Section R

## Metal and Non-Metallic Raceway



### Index

| <b>Metal Raceway</b>                                     | <b>Page</b> |
|----------------------------------------------------------|-------------|
| Raceway Profiles - Quick Reference Guide .....           | R-2         |
| HBL500, HBL700 and HBL750 Series .....                   | R-3         |
| HBL2000 and HBL2000A Series .....                        | R-9         |
| Metal PlugTrak® .....                                    | R-12        |
| HBL2400 and HBL2400D Series .....                        | R-13        |
| HBL3000 Series .....                                     | R-17        |
| HBL4750 Series .....                                     | R-21        |
| HBL6750 Series .....                                     | R-27        |
| HBLALU2000 Series .....                                  | R-33        |
| Aluminum PlugTrak® .....                                 | R-36        |
| HBLALU3800 and HBLALU4800 Series .....                   | R-37        |
| HBLALU5000 and HBLALU7620 Series .....                   | R-41        |
| Plates and Outlets .....                                 | R-45        |
| Technical Information and Wire Fill Capacity Chart ..... | R-47        |
| Cross Reference .....                                    | R-48        |
| <b>Non-Metallic Raceway</b>                              | <b>Page</b> |
| PolyTrak® Non-Metallic Raceway .....                     | R-53        |
| PT1 PremiseTrak® (Non-Latching) Series .....             | R-54        |
| PP1 PremiseTrak® (Latching) Series .....                 | R-55        |
| PL1 LANTrak® Series .....                                | R-56        |
| PW1 WallTrak® Low Profile Series .....                   | R-57        |
| PW2 2 Channel WallTrak® Series .....                     | R-58        |
| PB2 2 Channel BaseTrak® Series .....                     | R-59        |
| PB3 3 Channel BaseTrak® Series .....                     | R-60        |
| PS3 3 Channel Super BaseTrak® .....                      | R-61        |
| Non-Metallic PlugTrak® and Portable PlugTrak® .....      | R-62        |
| Plates and Outlets .....                                 | R-63        |
| Technical Information and Wire Capacity Fill Chart ..... | R-64        |
| <b>Pre-Wired Raceway</b>                                 | <b>Page</b> |
| Introduction .....                                       | R-65        |
| Features and Benefits .....                              | R-66        |
| Aluminum, Steel and Non-Metallic Raceways .....          | R-67        |
| Hubbell Pre-Wired Raceway with LINKOSITY® .....          | R-68        |


### Metal Raceway



### Innovative Box Design



### Non-Metallic Raceway



### Pre-Wired Raceway



























# Metal Raceway

## Raceway Profiles - Quick Reference Guide

Dimensions

\* Available in **PRE-WIRED**



|                      |                                                                                                                                                                                                                                                                                                                  |                                                                                                                                                                                                                                                                                                                                                                               |                                                                                                                                                                                                                                                                       |                                                                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                          |
|----------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Metal Raceway        | Color - Ivory, Gray or White                                                                                                                                                                                                                                                                                     |                                                                                                                                                                                                                                                                                                                                                                               |                                                                                                                                                                                                                                                                       |                                                                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                          |
|                      | <div><b>HBL500</b><br/>Ivory</div> <div><div><div>.53" (13.46)</div><div>.76" (19.30)</div><div>.22 in.<sup>2</sup> (1.41cm<sup>2</sup>)</div></div></div> <div>Page R-4</div>                                                  | <div><b>HBL700</b><br/>Ivory/White</div> <div><div><div>.67" (16.90)</div><div>.76" (19.30)</div><div>.26 in.<sup>2</sup> (1.67cm<sup>2</sup>)</div></div></div> <div>Page R-4</div>                                                                                                         | <div><b>HBL750</b><br/>Ivory/White</div> <div><div><div>.85" (21.59)</div><div>.76" (19.30)</div><div>.40 in.<sup>2</sup> (2.58cm<sup>2</sup>)</div></div></div> <div>Page R-4</div> | <div><b>HBL2000/A</b><br/>Ivory/Gray</div> <div><div><div>.89 in.<sup>2</sup> (5.74cm<sup>2</sup>)</div><div>.83" (21.08)</div><div>1.31" (33.27)</div></div></div> <div>Page R-10</div>                                                                                              | <div><b>Metal PlugTrak®</b><br/>Ivory/Gray</div> <div><div><div>.83" (21.08)</div><div>1.31" (33.27)</div></div></div> <div>Page R-12</div>                            | <div><b>HBL2400</b><br/>Ivory</div> <div><div><div>1.39 in.<sup>2</sup> (8.97cm<sup>2</sup>)</div><div>.88" (22.40)</div><div>1.91" (48.51)</div></div></div> <div>Page R-14</div>                                         | <div><b>HBL2400D</b><br/>Ivory</div> <div><div><div>.86 in.<sup>2</sup> (5.55cm<sup>2</sup>)</div><div>.88" (22.40)</div><div>1.91" (48.51)</div><div>.37 in.<sup>2</sup> (2.39cm<sup>2</sup>)</div></div></div> <div>Page R-14</div> |
|                      | <div><b>HBL3000*</b><br/>Ivory/Gray</div> <div><div><div>3.70 in.<sup>2</sup> (23.87cm<sup>2</sup>)</div><div>1.53" (38.86)</div><div>2.75" (69.85)</div></div></div> <div>Page R-18</div>                                      | <div><b>HBL4750*</b><br/>Ivory/Gray</div> <div><div><div>7.20 in.<sup>2</sup> (46.45cm<sup>2</sup>)<br/>Undivided</div><div>1.75" (44.45)</div><div>4.75" (120.65)</div></div></div> <div>Page R-22</div>                                                                                    |                                                                                                                                                                                                                                                                       | <div><b>HBL6750*</b><br/>Ivory/Gray</div> <div><div><div>13.77 in.<sup>2</sup> (88.84cm<sup>2</sup>)<br/>Undivided</div><div>2.22" (56.39)</div><div>6.75" (171.45)</div></div></div> <div>Page R-28</div>                                                                           |                                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                          |
|                      |                                                                                                                                                                                                                                                                                                                  |                                                                                                                                                                                                                                                                                                                                                                               |                                                                                                                                                                                                                                                                       |                                                                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                          |
| Aluminum Raceway     | Color - Satin Anodized Finish                                                                                                                                                                                                                                                                                    |                                                                                                                                                                                                                                                                                                                                                                               |                                                                                                                                                                                                                                                                       |                                                                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                          |
|                      | <div><b>HBLALU2000</b></div> <div><div><div>1.20 in.<sup>2</sup> (7.74cm<sup>2</sup>)</div><div>.91" (23.11)</div><div>1.84" (46.74)</div></div></div> <div>Page R-34</div>                                                    | <div><b>Aluminum PlugTrak®</b></div> <div><div><div>.91" (23.11)</div><div>1.84" (46.74)</div></div></div> <div>Page R-36</div>                                                                                                                                                             | <div><b>HBLALU3800*</b></div> <div><div><div>5.80 in.<sup>2</sup> (37.42cm<sup>2</sup>)</div><div>2.25" (57.15)</div><div>3.00" (76.20)</div></div></div> <div>Page R-38</div>      | <div><b>HBLALU4800*</b></div> <div><div><div>5.80 in.<sup>2</sup> (37.42cm<sup>2</sup>)</div><div>5.80 in.<sup>2</sup> (37.42cm<sup>2</sup>)</div><div>2.25" (57.15)</div><div>6.00" (152.40)</div></div></div> <div>Page R-39</div>                                                |                                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                          |
|                      | <div><b>HBLALU5000*</b></div> <div><div><div>3.80 in.<sup>2</sup> (24.52)</div><div>3.80 in.<sup>2</sup> (24.52cm<sup>2</sup>)</div><div>1.75" (44.45)</div><div>5.08" (129.03)</div></div></div> <div>Page R-42</div>        | <div><b>HBLALU7620*</b></div> <div><div><div>5.00 in.<sup>2</sup> (32.26cm<sup>2</sup>)</div><div>5.00 in.<sup>2</sup> (32.26cm<sup>2</sup>)</div><div>5.00 in.<sup>2</sup> (32.26cm<sup>2</sup>)</div><div>2.25" (57.15)</div><div>7.62" (193.55)</div></div></div> <div>Page R-43</div> |                                                                                                                                                                                                                                                                       |                                                                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                          |
|                      |                                                                                                                                                                                                                                                                                                                  |                                                                                                                                                                                                                                                                                                                                                                               |                                                                                                                                                                                                                                                                       |                                                                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                          |
| Non-Metallic Raceway | Color - Office White                                                                                                                                                                                                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                               |                                                                                                                                                                                                                                                                       |                                                                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                          |
|                      | <div><b>PT1</b></div> <div><div><div>.68" (17.27)</div><div>.75" (19.05)</div><div>.29 in.<sup>2</sup> (1.87cm<sup>2</sup>)</div></div></div> <div>Page R-54</div>                                                            | <div><b>PP1</b></div> <div><div><div>.77" (19.56)</div><div>.84" (21.34)</div><div>.38 in.<sup>2</sup> (2.45cm<sup>2</sup>)</div></div></div> <div>Page R-55</div>                                                                                                                         | <div><b>PL1</b></div> <div><div><div>1.03 in.<sup>2</sup> (6.65cm<sup>2</sup>)</div><div>1.04" (26.42)</div><div>1.38" (35.05)</div></div></div> <div>Page R-56</div>              | <div><b>Non-Metallic PlugTrak®</b></div> <div><div><div>1.04" (26.42)</div><div>1.38" (35.05)</div></div></div> <div>Page R-62</div>                                                                                                                                                | <div><b>PW1</b></div> <div><div><div>.50" (12.70)</div><div>1.19" (30.23)</div><div>.30 in.<sup>2</sup> (1.94cm<sup>2</sup>)</div></div></div> <div>Page R-57</div> | <div><b>PW2</b></div> <div><div><div>.81 in.<sup>2</sup> (5.23cm<sup>2</sup>)</div><div>.79 in.<sup>2</sup> (5.10cm<sup>2</sup>)</div><div>1.04" (26.42)</div><div>2.12" (53.85)</div></div></div> <div>Page R-58</div> |                                                                                                                                                                                                                                                                                                                          |
|                      |                                                                                                                                                                                                                                                                                                                  |                                                                                                                                                                                                                                                                                                                                                                               |                                                                                                                                                                                                                                                                       |                                                                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                          |
|                      | <div><b>PB2*</b></div> <div><div><div>2.86 in.<sup>2</sup> (18.45cm<sup>2</sup>)</div><div>2.86 in.<sup>2</sup> (18.45cm<sup>2</sup>)</div><div>1.63" (41.40)</div><div>4.50" (114.30)</div></div></div> <div>Page R-59</div> | <div><b>PB3</b></div> <div><div><div>1.80 in.<sup>2</sup> (11.61cm<sup>2</sup>)</div><div>1.97 in.<sup>2</sup> (12.71cm<sup>2</sup>)</div><div>1.80 in.<sup>2</sup> (11.61cm<sup>2</sup>)</div><div>1.63" (41.40)</div><div>4.50" (114.30)</div></div></div> <div>Page R-60</div>          |                                                                                                                                                                                                                                                                       | <div><b>PS3*</b></div> <div><div><div>3.41 in.<sup>2</sup> (22.00cm<sup>2</sup>)</div><div>3.76 in.<sup>2</sup> (24.26cm<sup>2</sup>)</div><div>3.41 in.<sup>2</sup> (22.00cm<sup>2</sup>)</div><div>1.97" (50.04)</div><div>6.70" (170.18)</div></div></div> <div>Page R-61</div> |                                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                          |

Note: \*Available in PRE-WIRED.  
Channel Area in Square Inches (square centimeters).



### Innovative Box Design

- Hubbell Handi-Screw® eliminates difficult to install long screws for easier installation.
- Rounded corners eliminate sharp edges.
- One seam construction provides “clean” look.
- Box design allows standard wallplates to be mounted flush with virtually no perimeter profile exposed.
- Full line of metal wallplates available. See page R-45 for selection.



### Enhanced Datacom Capabilities

- Allows up to five Category 5e, three Category 6, or two Category 6A cables.
- Available with 1½ in. (38.10) Category 6 and 6A bend radius fittings.
- Largest single channel low profile raceway available in its class.
- Ideal for datacom and oversized neutral applications.
- HBL750 Series exclusive to Hubbell.



### White Metal Raceway

- HBL750 Series available in white.
- Full line of product.
- More color options available for architects and interior designers.



### Retrofit Box for Fire Alarm Detectors

- Fits most manufactures of audible alarm systems.
- Hubbell Handi-Screw® eliminates difficult to install long screws for easier installation.
- Compatible with both HBL500 and HBL750 Series Metal Raceway.
- Available in white and ivory.


# Metal Raceway

## HBL500, HBL700 and HBL750 Series

Metal Raceway and Switch/Receptacle Boxes




| HBL500, HBL700 and HBL750 Series | Description                                                                                                                                                                                           | Color                   | Length                    | HBL500 Series                                                                                   | HBL700 Series                                                                | HBL750 Series                                                                                   |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|---------------------------|-------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------|
|                                  | <b>Base and Cover</b><br>Available in 5 ft. (1.5m) lengths, packed 50 ft. (15m) per carton and 10 ft. (3m) lengths, packed 100 ft. (30m) per carton.<br>HBL5701C coupling furnished with each length. | Ivory<br>Ivory<br>White | 5 ft.<br>10 ft.<br>10 ft. | <b>HBL5005IV</b><br><b>HBL50010IV</b><br><b>HBL50010W</b><br>A: .53" (13.46)<br>B: .76" (19.30) | —<br><b>HBL700IV</b><br><b>HBL700W</b><br>A: .67" (16.90)<br>B: .76" (19.30) | <b>HBL7505IV</b><br><b>HBL75010IV</b><br><b>HBL75010W</b><br>A: .85" (21.59)<br>B: .76" (19.30) |



|            | Color          | 1-Gang                                                                                                | 2-Gang                                                                                                   | 3-Gang                                                                                                 | 4-Gang                                                                                | 5-Gang                                                                                 | 6-Gang                                                                                 |
|------------|----------------|-------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|
| Standard   | Ivory<br>White | <b>HBL57481VA</b><br><b>HBL57481WA</b><br>A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 1.75" (44.45)   | <b>HBL574821VA</b><br><b>HBL574821WA</b><br>A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 1.75" (44.45)   | <b>HBL574831VA</b><br><b>HBL574831WA</b><br>A: 4.54" (115.32)<br>B: 6.45" (163.88)<br>C: 1.75" (44.45) | <b>HBL574841VA</b><br>—<br>A: 4.54" (115.32)<br>B: 8.26" (209.91)<br>C: 1.75" (44.45) | <b>HBL574851VA</b><br>—<br>A: 4.54" (115.32)<br>B: 10.01" (255.93)<br>C: 1.75" (44.45) | <b>HBL574861VA</b><br>—<br>A: 4.54" (115.32)<br>B: 11.89" (301.96)<br>C: 1.75" (44.45) |
| Shallow    | Ivory<br>White | <b>HBL57471VA</b><br><b>HBL57471WA</b><br>A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 1.38" (35.05)   | <b>HBL574721VA</b><br><b>HBL574721WA</b><br>A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 1.38" (35.05)   | <b>HBL574731VA</b><br>—<br>A: 4.54" (115.32)<br>B: 6.45" (163.88)<br>C: 1.38" (35.05)                  | —                                                                                     | —                                                                                      | —                                                                                      |
| Deep       | Ivory<br>White | <b>HBL5744S1VA</b><br><b>HBL5744S1WA</b><br>A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 2.25" (57.00) | <b>HBL5744S21VA</b><br><b>HBL5744S21WA</b><br>A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 2.25" (57.00) | <b>HBL5744S31VA</b><br>—<br>A: 4.54" (115.32)<br>B: 6.45" (163.88)<br>C: 2.25" (57.00)                 | —                                                                                     | —                                                                                      | —                                                                                      |
| Extra Deep | Ivory<br>White | <b>HBL57441VA</b><br><b>HBL57441WA</b><br>A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 2.75" (69.85)   | <b>HBL574421VA</b><br><b>HBL574421WA</b><br>A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 2.75" (69.85)   | <b>HBL574431VA</b><br>—<br>A: 4.54" (115.32)<br>B: 6.45" (163.88)<br>C: 2.75" (69.85)                  | —                                                                                     | —                                                                                      | —                                                                                      |






|            |          |                           |          |          |          |          |
|------------|----------|---------------------------|----------|----------|----------|----------|
| Base Trade | 2 - 1/2" | 1 - 1/2", 3/4" Concentric | 3 - 1/2" | 4 - 1/2" | 5 - 1/2" | 6 - 1/2" |
| Size KO's  |          | 1 - Rectangular           |          |          |          |          |

Note: For datacom applications, box selection is dependent on depth of connectors (jacks). See pages R-45 and R-46 for datacom product selection, or visit our site at [www.hubbell-wiring.com](http://www.hubbell-wiring.com) for our Full Line Catalog and additional information.




| Extension Boxes | Description                                                                                                                                 | Color          | 1-Gang                                                                                              | 1-Gang Deep                                                                                           | 1-Gang Blank                                                                        | 2-Gang                                                                                | 3-Gang                                                                                |
|-----------------|---------------------------------------------------------------------------------------------------------------------------------------------|----------------|-----------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|                 | <b>Extension Boxes</b><br>To extend existing flush switch and receptacle boxes. Blank is used where it is desired to blank original outlet. | Ivory<br>White | <b>HBL57511VA</b><br><b>HBL57511WA</b><br>A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 1.38" (35.05) | <b>HBL5751A1VA</b><br><b>HBL5751A1WA</b><br>A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 1.75" (44.45) | <b>HBL57601VA</b><br>—<br>A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 1.13" (28.70) | <b>HBL575121VA</b><br>—<br>A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 1.38" (35.05) | <b>HBL575131VA</b><br>—<br>A: 4.54" (115.32)<br>B: 6.45" (163.88)<br>C: 1.38" (35.05) |

Dimensions in Inches (mm)

| 1-Gang Specialty Boxes | Description                                                                                                                                                        | Color          | 1-Gang                                                                                               | 2-Gang Specialty Boxes | Description                                                                                                                                                                                                                                                                                                          | Color                 | 2-Gang                                                                                                   |
|------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|------------------------------------------------------------------------------------------------------|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|----------------------------------------------------------------------------------------------------------|
|                        | <b>Low Profile Switch/Receptacle</b><br>Base has ½ in. trade size KOs.                                                                                             | Ivory<br>White | <b>HBL5748SIVA</b><br><b>HBL5748SWA</b><br>A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 1.13" (28.70) |                        | <b>Alarm Device Box</b><br>Surface mounting of alarm devices and safety signals.                                                                                                                                                                                                                                     | Ivory<br>White<br>Red | <b>HBL5752IVA</b><br>—<br><b>HBL5752RA</b><br>A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 1.38" (35.05) |
|                        |                                                                                   |                |                                                                                                      |                        |                                                                                                                                                                                                                                   |                       |                                                                                                          |
| 1-Gang Specialty Boxes | <b>Combination Switch/Recept.</b><br>Connects surface runs of ½ in. trade size conduit, one raceway twistout each side and three raceway twistouts top and bottom. | Ivory<br>White | <b>HBL5745IVA</b><br><b>HBL5745WA</b><br>A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 1.75" (44.45)   | 2-Gang Specialty Boxes | <b>Extra Deep Alarm Device Box</b><br>For surface mounting of alarm devices and safety signals. Cover is 2.75 in. (69.85) deep.                                                                                                                                                                                      | Ivory<br>White<br>Red | <b>HBL5753IVA</b><br>—<br><b>HBL5753RA</b><br>A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 2.75" (69.85) |
|                        |                                                                                   |                |                                                                                                      |                        |                                                                                                                                                                                                                                   |                       |                                                                                                          |
|                        | <b>Utility Box*</b><br>For use as a tee, cross, pull box, junction box or blank box. Base has ½ in. trade size KOs.                                                | Ivory<br>White | <b>HBL57242IVA</b><br><b>HBL57242WA</b><br>A: 4.12" (104.78)<br>B: 2.00" (50.80)<br>C: 1.39" (35.31) |                        | <b>Distribution Box</b><br>Twistouts permit three parallel raceway runs on each side. Cover takes devices with mounting screw centers of 2.75 in. (69.85), 3.5 in. (89.00), 4.06 in. (103.00) and canopy fixture not larger than 4.63 in. (117.00). Can be used with HBL5736IV (blank cover) to create junction box. | Ivory<br>White        | <b>HBL5735IVA</b><br>—<br>A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 1.38" (35.05)                     |
|                        |                                                                                   |                |                                                                                                      |                        |                                                                                                                                                                                                                                   |                       |                                                                                                          |

Note: \*Use catalog number HBL5791 for connecting ½ in. EMT to HBL5745 and HBL57242 boxes.



| Round Boxes | Description                                                                                                                                                                                                                                                    | Color          | 4.75 inches O.D.                                                               | 5.50 inches O.D.                                                                 | 6.38 inches O.D.                                                               |
|-------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|--------------------------------------------------------------------------------|----------------------------------------------------------------------------------|--------------------------------------------------------------------------------|
|             | <b>Extension Box (Open Base)</b><br>For mounting on 3.25 in. (83.00) or 4 in. (102.00) round or square conduit boxes or other recessed outlets. Cover takes any device with mounting screw centers of 2.75 in. (69.85), 3.5 in. (89.00) and 4.06 in. (103.00). | Ivory<br>White | <b>HBL5737IVA</b><br><b>HBL5737WA</b><br>A: 1.02" (26.00)<br>B: 4.75" (120.65) | <b>HBL5737AIVA</b><br><b>HBL5737AWA</b><br>A: 1.02" (26.00)<br>B: 5.50" (140.00) | <b>HBL5739AIVA</b><br>—<br>A: 1.02" (26.00)<br>B: 6.38" (162.01)               |
|             |                                                                                                                                                                              |                |                                                                                |                                                                                  |                                                                                |
| Round Boxes | <b>Fixture Box (Solid Base)</b><br>To hang fixtures. Cover takes any device with mounting screw centers of 2.75 in. (69.85), 3.5 in. (89.00) and 4.06 in. (103.00). Both boxes can be used as a pull or junction box when used with HBL5736IV/W (blank cover). | Ivory<br>White | <b>HBL5738IVA</b><br><b>HBL5738WA</b><br>A: 1.02" (26.00)<br>B: 4.75" (120.65) | <b>HBL5738AIVA</b><br><b>HBL5738AWA</b><br>A: 1.02" (26.00)<br>B: 5.50" (140.00) | <b>HBL5739IVA</b><br><b>HBL5739WA</b><br>A: 1.02" (26.00)<br>B: 6.38" (162.01) |
|             |                                                                                                                                                                             |                |                                                                                |                                                                                  |                                                                                |
|             |                                                                                                                                                                            |                |                                                                                |                                                                                  |                                                                                |

| Specialty Round Boxes | Description                                                                                                                                    | Color          | Catalog Number                                                                       | Round Covers | Description                                                                                                                                                    | Color          | Catalog Number                                                             |
|-----------------------|------------------------------------------------------------------------------------------------------------------------------------------------|----------------|--------------------------------------------------------------------------------------|--------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|----------------------------------------------------------------------------|
|                       | <b>Outlet Box</b><br>For devices with mounting screw centers of 1.47 in. (37.00), 1.63 in. (41.00), 1.69 in. (44.00) or 1.84 in. (46.00).      | Ivory<br>White | <b>HBL5733IVA</b><br>—<br>A: 1.02" (26.00)<br>B: 3.00" (76.00)                       |              | <b>Blank Cover</b><br>For use with HBL5733IVA. Has ½ in. trade size KO in center.                                                                              | Ivory<br>White | <b>HBL5731IV</b><br>—<br>A: .24" (6.10)<br>B: 2.40" (60.96)                |
|                       |                                                             |                |                                                                                      |              |                                                                           |                |                                                                            |
| Specialty Round Boxes | <b>Fanbox with Solid Base</b><br>Cover accepts fan bracket with mounting centers of 3.2 in. (81.00). Rated for fans and fixtures up to 50 lbs. | Ivory<br>White | <b>HBL5738AFIVA</b><br><b>HBL5738AFWA</b><br>A: .38" (9.75)<br>B: 4.19" (106.30)     | Round Covers | <b>Blank Cover</b><br>For use with HBL5735IVA, HBL5737IVA/WA, HBL5739AIVA, HBL5738IVA/WA, HBL5738AIVA/WA and HBL5739IVA/WA. Has ½ in. trade size KO in center. | Ivory<br>White | <b>HBL5736IV</b><br><b>HBL5736W</b><br>A: .38" (9.75)<br>B: 4.19" (106.30) |
|                       |                                                             |                |                                                                                      |              |                                                                           |                |                                                                            |
|                       | <b>Retrofit Box for Fire Alarm Detectors</b><br>For installing round alarm sensors.                                                            | Ivory<br>White | <b>HBL5739AABIVA</b><br><b>HBL5739AABWA</b><br>A: 1.62" (41.15)<br>B: 6.50" (165.10) |              |                                                                             |                |                                                                            |









Dimensions in Inches (mm)



# Metal Raceway



## HBL500, HBL700 and HBL750 Series

Elbow and Tee Fittings













| Elbows | Description                                                                                                                                                             | Color          | HBL500 Series                                                                                | HBL700 and HBL750 Series                                                                       | Description                                                                                                                                                                                                 | Color                                | HBL500, HBL700 & HBL750 Series                                                                                                                                                     |
|--------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|----------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|        | <b>Internal Elbow</b><br>For inside surfaces at right angles.                                                                                                           | Ivory<br>White | <b>HBL517IV</b><br><b>HBL517W</b><br>A: 3.33" (84.51)<br>B: .58" (14.73)<br>C: 3.33" (84.51) | <b>HBL717IVA</b><br><b>HBL717WA</b><br>A: 3.33" (84.51)<br>B: .90" (22.86)<br>C: 3.33" (84.51) | <b>Internal Elbow Bend Radius</b><br>For inside surface at right angles requiring a 1.5 in. (38.10) bend radius. Suitable for Category 5, 5e, 6 and 6A applications.                                        | Ivory<br>White                       | <b>HBL5717BRIVA</b><br>—<br>A: 3.33" (84.51)<br>B: .91" (23.11)<br>C: 3.33" (84.51)                                                                                                |
|        |       |                |                                                                                              |                                                                                                |                                        |                                      |                                                                                                                                                                                    |
|        | <b>External Elbow</b><br>For outside surfaces at right angles.                                                                                                          | Ivory<br>White | <b>HBL518IV</b><br><b>HBL518W</b><br>A: 2.59" (65.71)<br>B: .58" (14.73)<br>C: 2.59" (65.71) | <b>HBL718IVA</b><br><b>HBL718WA</b><br>A: 2.59" (65.71)<br>B: .90" (22.86)<br>C: 2.59" (65.71) | <b>External Elbow Bend Radius</b><br>For outside surfaces at right angles requiring a 1.5 in. (38.10) bend radius. Suitable for Category 5, 5e, 6 and 6A applications.                                      | Ivory<br>White                       | <b>HBL5718BRIVA</b><br>—<br>A: 4.86" (123.43)<br>B: .78" (19.80)<br>C: 1.35" (34.28)                                                                                               |
|        |       |                |                                                                                              |                                                                                                |                                        |                                      |                                                                                                                                                                                    |
|        | <b>90° Flat Elbow</b><br>For right angle turns on same surface.                                                                                                         | Ivory<br>White | <b>HBL511IV</b><br><b>HBL511W</b><br>A: 2.68" (68.13)<br>B: .61" (15.50)<br>C: 2.68" (68.13) | <b>HBL711IVA</b><br><b>HBL711WA</b><br>A: 2.68" (68.13)<br>B: .90" (22.86)<br>C: 2.68" (68.13) | <b>Flat Elbow Bend Radius</b><br>For right angle turns requiring a 1.5 in. (38.10) bend radius. Suitable for Category 5, 5e, 6 and 6A applications.                                                         | Ivory<br>White                       | <b>HBL5711BRIVA</b><br>—<br>A: 3.16" (80.34)<br>B: .91" (23.11)<br>C: 3.16" (80.34)                                                                                                |
|        |       |                |                                                                                              |                                                                                                |                                        |                                      |                                                                                                                                                                                    |
|        | <b>45° Flat Elbow</b><br>For diagonal 45° turns on same surface.                                                                                                        | Ivory<br>White | <b>HBL512IV</b><br>—<br>A: 2.46" (62.61)<br>B: .58" (14.73)<br>C: 2.46" (62.61)              | <b>HBL712IVA</b><br>—<br>A: 2.70" (68.49)<br>B: .91" (23.06)<br>C: 2.70" (68.49)               | <b>Internal Twisted Elbows</b><br>For 90° twist with 90° turn. For double turn at right angles from one to another. From a flat run on a side wall to a flat run on a ceiling, edge of door or window trim. | Ivory<br>White<br><br>Ivory<br>White | Right Elbow<br><b>HBL5711RHIVA</b><br><b>HBL5711RHWA</b><br><br>Left Elbow<br><b>HBL5711LHIVA</b><br><b>HBL5711LHWA</b><br>A: 2.98" (75.72)<br>B: .94" (23.75)<br>C: 3.00" (76.20) |
|        |   |                |                                                                                              |                                                                                                |                                    |                                      |                                                                                                                                                                                    |

| Tees | Description                                                                                                                                                             | Color          | HBL500, HBL700 & HBL750 Series                                                                    | Description                                                                                                                                                                | Color          | HBL500, HBL700 & HBL750 Series                                                       |
|------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|---------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|--------------------------------------------------------------------------------------|
|      | <b>Tee Fitting</b><br>For branches at right angles.                                                                                                                     | Ivory<br>White | <b>HBL5715IVA</b><br><b>HBL5715WA</b><br>A: 3.06" (77.67)<br>B: 1.14" (28.86)<br>C: 3.03" (76.96) | <b>Tee Fitting Bend Radius</b><br>For branches at right angles requiring a 1.5 in. (38.10) bend radius. Suitable for Category 5, 5e, 6 and 6A applications.                | Ivory<br>White | <b>HBL5715BRIVA</b><br>—<br>A: 5.55" (140.88)<br>B: .90" (22.86)<br>C: 3.16" (80.34) |
|      |   |                |                                                                                                   |   |                |                                                                                      |

| Fittings | Description                                                                                                                                                             | Color          | HBL500, HBL700 & HBL750 Series                          | Description                                                                                                                                                                | Color          | HBL500, HBL700 & HBL750 Series                                |
|----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|---------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|---------------------------------------------------------------|
|          | <b>Support Clip</b><br>For supporting lengths of HBL500, HBL700 or HBL750 Raceway.                                                                                      | Ivory<br>White | <b>HBL5703IV</b><br><b>HBL5703W</b><br>A: 2.51" (63.75) | <b>Flexible Section</b><br>For getting around offsets, side bends, twisted turns or curved surfaces.                                                                       | Ivory<br>White | <b>HBL5700FIVA</b><br><b>HBL5700FWA</b><br>A: 18.00" (457.20) |
|          |   |                |                                                         |   |                |                                                               |

Dimensions in Inches (mm)

| End Fittings | Description                                                                                                                                                                                                                                                        | Color          | HBL500, HBL700 & HBL750 Series                                                                      | Description                                                                                                                                                                                                   | Color          | HBL500, HBL700 & HBL750 Series                                                                    |
|--------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|-----------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|---------------------------------------------------------------------------------------------------|
|              | <b>Entrance Connector</b><br>One ¾ in. KO for panel or conduit connection. One ¾ in. chase nipple and locknut furnished.                                                                                                                                           | Ivory<br>White | <b>HBL5786AIVA</b><br><b>HBL5786AWA</b><br>A: 1.50" (38.10)<br>B: 1.84" (46.74)<br>C: 3.89" (98.87) | <b>Adjustable Offset Connector</b><br>Two ½ in. KOs for panel or conduit connection. Eliminates offsetting raceway when connecting to surface type panel boxes. One ½ in. chase nipple and locknut furnished. | Ivory<br>White | <b>HBL5786IVA</b><br><b>HBL5786WA</b><br>A: 1.50" (38.10)<br>B: 1.84" (46.74)<br>C: 3.89" (98.87) |
|              |                                                                                                  |                |                                                                                                     |                                         |                |                                                                                                   |
|              | <b>Elbow Box Connector</b><br>For connecting raceway at right angles to conduit boxes, panel boxes, etc. having ½ in. nipple for trade size conduit.                                                                                                               | Ivory<br>White | <b>HBL5783IVA</b><br>—<br>A: 2.13" (54.05)<br>B: 1.24" (31.50)                                      | <b>Elbow Conduit Connector</b><br>For connecting raceway at right angles to ½ in. trade size conduit or armored cable connectors.                                                                             | Ivory<br>White | <b>HBL5784IVA</b><br>—<br>A: 2.13" (54.05)<br>B: 1.24" (31.50)                                    |
|              |                                                                                                  |                |                                                                                                     |                                         |                |                                                                                                   |
|              | <b>Combination Connector</b><br>For connecting raceway without offsetting to any 3.25 in. (83.00) or 4 in. (102.00) outlet box mounted on the surface with a KO for ½ in. trade size conduit. Spring steel bushing eliminates need for conduit nipple and locknut. | Ivory<br>White | <b>HBL5785AIVA</b><br><b>HBL5785AWA</b><br>A: 1.50" (38.10)<br>B: 1.84" (46.74)<br>C: 3.89" (98.87) | <b>Corner Box</b><br>For connecting HBL500, HBL700 or HBL750 Raceway from ceiling or corner. Each leg of base has ½ in. trade size KO.                                                                        | Ivory<br>White | <b>HBL5719IVA</b><br><b>HBL5719WA</b><br>A: 2.50" (63.50)<br>B: 2.50" (63.50)<br>C: 2.40" (60.96) |
|              |                                                                                                  |                |                                                                                                     |                                         |                |                                                                                                   |

| Fittings | Description                                                                                                                                                                                  | Color          | HBL500 Series                                                                    | HBL700 Series                                                                    | HBL750 Series                                                                    |
|----------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|----------------------------------------------------------------------------------|----------------------------------------------------------------------------------|----------------------------------------------------------------------------------|
|          | <b>Transition Fitting</b><br>For transitioning from either Wiremold® V500 to Hubbell HBL500 Raceway or Wiremold® V700 to Hubbell HBL700 Raceway or Wiremold® V700 to Hubbell HBL750 Raceway. | Ivory<br>White | <b>HBL500TFIV</b><br>—<br>A: .65" (16.51)<br>B: .89" (22.61)<br>C: 2.15" (54.61) | <b>HBL700TFIV</b><br>—<br>A: .78" (19.80)<br>B: .89" (22.61)<br>C: 2.15" (54.61) | <b>HBL750TFIV</b><br>—<br>A: .98" (24.89)<br>B: .89" (22.61)<br>C: 2.15" (54.61) |
|          |                        |                |                                                                                  |                                                                                  |                                                                                  |
|          | <b>Mounting Strap (one- or two-hole)</b><br>For mounting HBL500, HBL700 or HBL750 Raceway to surface. Convert to one-hole by breaking off at score.                                          | Ivory<br>White | <b>HBL504IV</b><br><b>HBL504W</b><br>A: .58" (14.73)<br>B: .50" (12.70)          | <b>HBL7004IV</b><br><b>HBL7004W</b><br>A: .70" (17.68)<br>B: .50" (12.70)        | <b>HBL7504IV</b><br><b>HBL7504W</b><br>A: .90" (22.86)<br>B: .50" (12.70)        |
|          |                        |                |                                                                                  |                                                                                  |                                                                                  |
|          | <b>Connection Cover</b><br>To cover potential openings where two lengths of HBL500, HBL700 or HBL750 Raceway come together.                                                                  | Ivory<br>White | <b>HBL506IV</b><br><b>HBL506W</b><br>A: .60" (15.24)<br>B: .80" (20.31)          | <b>HBL7006IV</b><br><b>HBL7006W</b><br>A: .69" (17.40)<br>B: .80" (20.31)        | <b>HBL7506IV</b><br><b>HBL7506W</b><br>A: .91" (23.10)<br>B: .80" (20.31)        |
|          |                        |                |                                                                                  |                                                                                  |                                                                                  |
|          | <b>Bushing</b><br>Protect wires from potential abrasion. Fits into end of HBL500, HBL700 or HBL750 Raceway.                                                                                  | Steel*         | <b>HBL502B</b><br>A: .35" (8.83)<br>B: .70" (17.68)                              | <b>HBL7002B</b><br>A: .49" (12.50)<br>B: .78" (19.80)                            | <b>HBL7502B</b><br>A: .60" (15.24)<br>B: .70" (17.68)                            |
|          |                        |                |                                                                                  |                                                                                  |                                                                                  |

Note: \*Zinc Plated Steel.

Wiremold® is a registered trademark of the Wiremold Company.







Dimensions in Inches (mm)

# Metal Raceway

## HBL500, HBL700 and HBL750 Series

Fittings and Tools



|          |                                                                                                                                                   |                 |                                                                          |                                                                           |                                                                                                                                                                                                                                                                                               |                 |                                                        |
|----------|---------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|--------------------------------------------------------------------------|---------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|--------------------------------------------------------|
| Fittings | <b>Description</b>                                                                                                                                | <b>Material</b> | <b>HBL500, HBL700 &amp; HBL750 Series</b>                                |                                                                           | <b>Description</b>                                                                                                                                                                                                                                                                            | <b>Material</b> | <b>HBL500, HBL700 &amp; HBL750 Series</b>              |
|          | <b>Box Connector</b><br>For connecting raceway to conduit boxes or panel boxes having KO for conduit. May also be used for conduit type fittings. | Steel*          | <b>HBL5781</b><br>½" NPT (13) Male<br>A: .75" (19.1)<br>B: 1.24" (31.62) | <b>HBL5781A</b><br>¾" NPT (19) Male<br>A: .75" (19.1)<br>B: 1.24" (31.62) | <b>½ in. EMT Connector</b><br>For connecting raceway to conduit boxes or panel boxes having KO for conduit.                                                                                                                                                                                   | Steel*          | <b>HBL5791</b><br>A: 1.20" (30.48)<br>B: 1.09" (27.70) |
|          |                                                                  |                 |                                                                          |                                                                           |                                                                                                                                                                                                              |                 |                                                        |
|          | <b>Conduit Connector</b><br>For connecting raceway to conduit.                                                                                    | Steel*          | <b>HBL5782C</b><br>½" NPT (13) Female<br>A: .75" (19.1)<br>B: 1.75" (44) | <b>HBL5782A</b><br>¾" (19.1) Female<br>A: .75" (19.1)<br>B: 1.75" (44)    | <b>Coupling</b><br>For joining and supporting lengths of HBL500, HBL700 or HBL750 Raceway.                                                                                                                                                                                                    | Steel**         | <b>HBL5701C</b><br>A: 2.00" (50.80)                    |
|          |                                                                  |                 |                                                                          |                                                                           |                                                                                                                                                                                                              |                 |                                                        |
|          | <b>Grounding Clamp</b><br>Provides grounding means for ½ in. trade size conduit using locknut.                                                    | Steel**         | <b>HBL5709GC</b><br>A: 1.04" (26.03)<br>B: 1.18" (29.84)                 |                                                                           | <b>Ground Clamp</b><br>Used to provide additional grounding of raceway or to ground remotely located devices. Attach ground wire to screw as required by National Electrical Code.                                                                                                            | Steel**         | <b>HBL5709</b><br>A: 2.00" (50.80)                     |
|          |                                                                  |                 |                                                                          |                                                                           |                                                                                                                                                                                                              |                 |                                                        |
|          | <b>Special Nipple</b><br>For hanging or connecting either .375 in. (9.5) or .5 in. (12.7) fixtures to Hubbell fittings with ½ in. trade size KOs. | Steel*          | <b>HBL5780</b><br>A: .63" (16.00)                                        |                                                                           | <b>Armored Cable Connector</b><br>For connecting 14/2, 14/3, 12/2 and 12/3 "MC" and armored cable to Hubbell fittings. A short piece of HBL500, HBL700 or HBL750 Series Raceway must be used between this connector and the Hubbell fitting. Not for connection to ½ in. (12.7) flex conduit. | Steel**         | <b>HBL5790B</b><br>A: 2.00" (50.80)<br>B: .99" (25.25) |
|          |                                                                |                 |                                                                          |                                                                           |                                                                                                                                                                                                            |                 |                                                        |

Note: \*Zinc Plated Steel.  
\*\*Galvanized Steel.

|       |                                                                                     |                      |                      |                      |                                                                                        |              |                                           |
|-------|-------------------------------------------------------------------------------------|----------------------|----------------------|----------------------|----------------------------------------------------------------------------------------|--------------|-------------------------------------------|
| Tools | <b>Description</b>                                                                  | <b>HBL500 Series</b> | <b>HBL700 Series</b> | <b>HBL750 Series</b> | <b>Description</b>                                                                     | <b>Color</b> | <b>HBL500, HBL700 &amp; HBL750 Series</b> |
|       | <b>Cutter</b><br>Portable cutter for HBL500, HBL700 or HBL750 Series Raceways.      | <b>HBL605CUT</b>     | <b>HBL700CUT</b>     | <b>HBL607CUT</b>     | <b>Raceway Bender</b><br>Portable bender for HBL500, HBL700 or HBL750 Series Raceways. |              | <b>HBL600B</b>                            |
|       |  |                      |                      |                      |     |              |                                           |
|       | <b>Cutter Replacement Blade</b>                                                     | <b>HBL605K</b>       | <b>HBL700K</b>       | <b>HBL607K</b>       | <b>Touch-Up Paint Pen</b>                                                              | Ivory White  | <b>HBLIWEP</b><br><b>HBLWWEP</b>          |
|       |  |                      |                      |                      |     |              |                                           |

Dimensions in Inches (mm)



### HBL2000A Raceway

- Cover is 0.040 in. (1.016) thick which allows up to 600V AC.
- Higher capacity power applications (up to 26 #12AWG wires).
- Available in cover only or base and cover options.



### Innovative Box Design

- Hubbell Handi-Screw® eliminates difficult to install long screws for easier installation.
- Rounded corners eliminate sharp edges.
- One seam construction provides “clean” look.
- Box design allows standard wallplates to be mounted flush with virtually no perimeter profile exposed.
- Full line of metal wallplates available. See page R-45 for selection.



### Bend Radius Fittings

- 1½ in. (38.10) bend radius.
- Ideal for high speed data cables including Category 5, 5e, 6 and 6A applications.



### Metal PlugTrak® Featuring Exclusive Receptacle Design

- Gray or ivory scratch resistant finish.
- Multiple spacing configurations.
- Hubbell designed and manufactured single receptacle.
- Insulation displacement wiring provides superior wire retention.
- Mates with HBL2000 Series Metal Raceway.
- Available in 3 ft. (0.9m), 5 ft. (1.5m) and 6 ft. (1.8m) lengths.
- Tamper-Resistant versions available.

# Metal Raceway

## HBL2000 and HBL2000A Series

Metal Raceway, Device Boxes, Elbows and Tees



| HBL2000 Series | Description                                                                                                                                              | Color         | Catalog Number                                                                                          | HBL2000A Series | Description                                                                                                                                                                                                 | Color         | Catalog Number                                                                                            |
|----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|---------------------------------------------------------------------------------------------------------|-----------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|-----------------------------------------------------------------------------------------------------------|
|                | <b>Base and Cover (300V Rated)</b><br>Cover is 0.025 in. (0.635) thick up to 300V AC applications. Packed 50 ft. (15m) per carton, 5 ft. (1.5m) lengths. | Ivory<br>Gray | <b>HBL2000BCIV</b><br><b>HBL2000BCGY</b><br>A: 60.00" (1,524.00)<br>B: 1.31" (33.27)<br>C: .83" (21.08) |                 | <b>Base and Cover (600V Rated)</b><br>Cover is 0.040 in. (1.016) thick up to 600V AC or higher capacity power applications (up to 26 #12AWG wires). Packed 50 ft. (15m) per carton, 5 ft. (1.5m) lengths.   | Ivory<br>Gray | <b>HBL2000BCAIV</b><br><b>HBL2000BCAGY</b><br>A: 60.00" (1,524.00)<br>B: 1.31" (33.27)<br>C: .83" (21.08) |
| Base and Cover | <b>5 Ft. Base Only</b><br>For use with HBL2000 and HBL2000A raceway. Packed 50 ft. (15m) per carton, 5 ft. (1.5m) lengths.                               | Ivory<br>Gray | <b>HBL2000B5IV</b><br><b>HBL2000B5GY</b><br>A: 60.00" (1,524.00)<br>B: 1.31" (33.27)                    | Base and Cover  | <b>5 Ft. Cover Only (300V Rated)</b><br>Cover is 0.025 in. (0.635) thick. Packed 50 ft. (15m) per carton, 5 ft. (1.5m) lengths.                                                                             | Ivory<br>Gray | <b>HBL2000CIV</b><br><b>HBL2000CGY</b><br>A: 60.00" (1,524.00)<br>B: 1.31" (33.27)                        |
|                |                                                                                                                                                          |               |                                                                                                         |                 | <b>5 Ft. Cover Only (600V Rated)</b><br>Cover is 0.040 in. (1.016) thick up to 600V AC or higher capacity power applications (up to 26 #12AWG wires). Packed 50 ft. (15m) per carton, 5 ft. (1.5m) lengths. | Ivory<br>Gray | <b>HBL2000CAIV</b><br><b>HBL2000CAGY</b><br>A: 60.00" (1,524.00)<br>B: 1.31" (33.27)                      |
| Device Boxes   | <b>1-Gang Device Box</b><br>For deep switches and receptacles. Base has one ½ in. trade size KO and rectangular KO for extension to wall box.            | Ivory<br>Gray | <b>HBL2048IV</b><br><b>HBL2048GY</b><br>A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 1.75" (44.45)       | Device Boxes    | <b>2-Gang Device Box</b><br>For deep switches and receptacles. Base has one ½ in. trade size KO and rectangular KO for extension to wall box.                                                               | Ivory<br>Gray | <b>HBL20482IV</b><br><b>HBL20482GY</b><br>A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 1.75" (44.45)      |
|                |                                                                                                                                                          |               |                                                                                                         |                 |                                                                                                                                                                                                             |               |                                                                                                           |
| Elbows         | <b>Internal Corner Coupling</b><br>For surfaces at right angles, or for use as a straight-through fitting. Furnished with one fiber bushing.             | Steel**       | <b>HBL2017TC</b><br>A: 1.30" (32.98)<br>B: 1.40" (35.56)                                                | Elbows          | <b>Internal Elbow Bend Radius</b><br>For inside surface at right angles requiring a 1.5" (38.10) bend radius. Suitable for Category 5, 5e, 6 and 6A applications.                                           | Ivory<br>Gray | <b>HBL2017BRIV*</b><br><b>HBL2017BRGY*</b><br>A: .85" (21.56)<br>B: 3.47" (88.11)                         |
|                | <b>External Elbow Coupling</b><br>For right angle turns around external corners.                                                                         | Ivory<br>Gray | <b>HBL2018CIV</b><br><b>HBL2018CGY</b><br>A: 1.88" (47.75)                                              |                 | <b>External Elbow Bend Radius</b><br>For outside surfaces at right angles requiring a 1.5 in. (38.10) bend radius. Suitable for Category 5, 5e, 6 and 6A applications.                                      | Ivory<br>Gray | <b>HBL2018BRIV*</b><br><b>HBL2018BRGY*</b><br>A: 5.11" (129.72)                                           |
|                | <b>90° Flat Elbow</b><br>For right angle turns on same surface.                                                                                          | Ivory<br>Gray | <b>HBL2011IV*</b><br><b>HBL2011GY*</b><br>A: 2.56" (65.02)                                              |                 | <b>Flat Elbow Bend Radius</b><br>For branches at right angles requiring a 1.5 in. (38.10) bend radius. Suitable for Category 5, 5e, 6 and 6A applications.                                                  | Ivory<br>Gray | <b>HBL2011BRIV*</b><br><b>HBL2011BRGY*</b><br>A: 4.29" (109.03)                                           |
| Tees           | <b>Tee Fitting</b><br>For branches at right angles. Couplings furnished.                                                                                 | Ivory<br>Gray | <b>HBL2015IV*</b><br><b>HBL2015GY*</b><br>A: 6.00" (152.40)<br>B: 2.81" (71.44)<br>C: 4.00" (101.60)    | Tees            | <b>Tee Fitting Bend Radius</b><br>For branches at right angles. Couplings furnished. Suitable for Category 5, 5e, 6 and 6A applications.                                                                    | Ivory<br>Gray | <b>HBL2015BRIV*</b><br><b>HBL2015BRGY*</b><br>A: 7.35" (186.78)<br>B: 4.33" (110.00)                      |
|                |                                                                                                                                                          |               |                                                                                                         |                 |                                                                                                                                                                                                             |               |                                                                                                           |

Note: \*HBL2001C couplings included.

\*\*Galvanized Steel.

Dimensions in Inches (mm)

| End Fittings | Description                                                                                                                                                                                                                                                                                                  | Color         | Catalog Number                                                                                      | Description                                                                                                                                                                                                                                                                                                                                                                                                 | Color         | Catalog Number                                                                                       |
|--------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|-----------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|------------------------------------------------------------------------------------------------------|
|              | <b>Transition Fitting</b><br>For transitioning from Wiremold® 2000 Raceway to Hubbell HBL2000 Raceway.                                     | Ivory<br>Gray | <b>HBL2000TFIV</b><br><b>HBL2000TFGY</b><br>A: .82" (20.71)<br>B: 1.38" (35.12)<br>C: 2.04" (51.82) | <b>Entrance End Fitting</b><br>For connecting HBL2000 Raceway with one ½ in. conduit and armored cable connectors.                                                                                                                    | Ivory<br>Gray | <b>HBL2010A2IV</b><br><b>HBL2010A2GY</b><br>A: 3.01" (76.45)<br>B: 1.30" (33.02)<br>C: 1.49" (37.85) |
|              | <b>Blank End Fitting</b><br>For closing open end of HBL2000 Raceway.                                                                       | Ivory<br>Gray | <b>HBL2010BIV</b><br><b>HBL2010BGY</b><br>A: .78" (19.94)                                           | <b>Large Capacity Entrance End Fitting</b><br>Offers larger capacity than HBL2010A2IV/GY. One ½ in. trade size KO on each side, ½ in. and ¾ in. concentric KOs on end and bottom.                                                     | Ivory<br>Gray | <b>HBL2010A3IV</b><br><b>HBL2010A3GY</b><br>A: 3.69" (93.80)<br>B: 2.02" (51.18)<br>C: 1.79" (45.36) |
| Fittings     | <b>End Reducing Connector</b><br>For connecting HBL2000 Raceway to HBL500 Raceway through end of HBL2000 Raceway.                          | Ivory         | <b>HBL2089EIV</b><br>A: .78" (19.81)                                                                | <b>Side Reducing Connector</b><br>For connecting HBL2000 Raceway to HBL500 Raceway through side of HBL2000 Raceway.                                                                                                                   | Ivory         | <b>HBL2089IV*</b><br>A: 6.00" (152.40)<br>B: 3.25" (82.55)                                           |
|              | <b>Cover Clip</b><br>Use to cover potential openings where two pieces of HBL2000 Raceway cover come together.                              | Ivory<br>Gray | <b>HBL2006IV</b><br><b>HBL2006GY</b><br>A: .75" (19.05)                                             | <b>Flush Plate Adaptor</b><br>For feeding HBL2000 Raceway from an existing wall outlet. ½ in. threaded stud with steel locknut for grounding.                                                                                         | Ivory<br>Gray | <b>HBL2051HIV</b><br><b>HBL2051HGY</b><br>A: 4.50" (114.30)                                          |
|              | <b>Wire Clip</b><br>For holding conductors in place in the raceway base. For use when using the HBL2000CIV/GY cover only.              | Steel**       | <b>HBL2000WC</b><br>A: .44" (11.18)<br>B: .24" (6.03)<br>C: 1.24" (31.50)                           | <b>Wire Clip</b><br>For holding conductors in place in the raceway base. For use when using the HBL2000CAIV/GY cover only.                                                                                                        | Steel**       | <b>HBL2000WCA</b><br>A: .44" (11.18)<br>B: .60" (15.17)<br>C: 1.24" (31.50)                          |
|              | <b>Coupling</b><br>For joining lengths of HBL2000 Raceway.                                                                             | Steel**       | <b>HBL2001C</b><br>A: 2.00" (50.80)                                                                 | <b>Supporting Clip</b><br>For temporarily supporting lengths of HBL2000 Raceway at any point. Mount with #6 flat head fastener. Has set screw for locking to raceway. Raceway must be screwed to the wall for secure fastening.   | Steel**       | <b>HBL2003SC</b><br>A: 2.00" (50.80)                                                                 |
|              | <b>Ground Clamp</b><br>For connection of equipment grounding conductor to provide an additional ground to raceway. Galvanized steel.   | Steel**       | <b>HBL2009GC</b><br>A: 1.00" (25.64)                                                                |                                                                                                                                                                                                                                                                                                                                                                                                             |               |                                                                                                      |

Note: \*HBL2001C couplings included.  
 \*\*Galvanized Steel.

| Tools | Description                                                                                                                                                                          | Catalog Number   | Description                                                                                                     | Color         | Catalog Number                   |
|-------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|-----------------------------------------------------------------------------------------------------------------|---------------|----------------------------------|
|       | <b>Cutter</b><br>Portable cutter for HBL2000 Series Raceway. (Not for use with HBL2000A series).  | <b>HBL620C</b>   | <b>Touch-Up Paint Pen</b>  | Ivory<br>Gray | <b>HBLIWEP</b><br><b>HBLGWEP</b> |
|       | <b>Cutter Replacement Blade Set</b>                                                               | <b>HBL620BCK</b> |                                                                                                                 |               |                                  |

# Metal Raceway Metal PlugTrak®

Metal PlugTrak®, Portable Metal PlugTrak®, Boxes and Fittings



Available in Standard, Isolated Ground (IG) and Tamper-Resistant (TR) versions.

Tamper-Resistant



|        | Amp | Circuits  | # Single Recept. | Receptacle Spacing (in.) | Color                 |                       |
|--------|-----|-----------|------------------|--------------------------|-----------------------|-----------------------|
|        |     |           |                  |                          | Ivory                 | Gray                  |
| 3 Foot | 15  | Single    | 6                | 6                        | <b>HBL20GB306IV</b>   | <b>HBL20GB306GY</b>   |
|        | 15  | IG/Single | 6                | 6                        | <b>HBL20IG306IV</b>   | <b>HBL20IG306GY</b>   |
|        | 15  | TR/Single | 6                | 6                        | <b>HBL20GB306IVTR</b> | <b>HBL20GB306GYTR</b> |
|        | 20  | Single    | 6                | 6                        | <b>HBL24GB306IV</b>   | <b>HBL24GB306GY</b>   |
|        | 20  | TR/Single | 6                | 6                        | <b>HBL24GB306IVTR</b> | <b>HBL24GB306GYTR</b> |
| 5 Foot | 15  | Single    | 10               | 6                        | <b>HBL20GB506IV</b>   | <b>HBL20GB506GY</b>   |
|        | 15  | Single    | 5                | 12                       | <b>HBL20GB512IV</b>   | <b>HBL20GB512GY</b>   |
|        | 15  | Two       | 5                | 12                       | <b>HBL20GBA512IV</b>  | <b>HBL20GBA512GY</b>  |
|        | 15  | IG/Single | 5                | 12                       | <b>HBL20IG512IV</b>   | <b>HBL20IG512GY</b>   |
|        | 15  | TR/Single | 5                | 12                       | <b>HBL20GB512IVTR</b> | <b>HBL20GB512GYTR</b> |
|        | 20  | Single    | 10               | 6                        | <b>HBL24GB506IV</b>   | <b>HBL24GB506GY</b>   |
|        | 20  | Single    | 5                | 12                       | <b>HBL24GB512IV</b>   | <b>HBL24GB512GY</b>   |
|        | 20  | Two       | 5                | 12                       | <b>HBL24GBA512IV</b>  | <b>HBL24GBA512GY</b>  |
| 6 Foot | 20  | TR/Two    | 5                | 12                       | <b>HBL24GB512IVTR</b> | <b>HBL24GB512GYTR</b> |
|        | 15  | Single    | 12               | 6                        | <b>HBL20GB606IV</b>   | <b>HBL20GB606GY</b>   |
|        | 15  | Single    | 8                | 9                        | <b>HBL20GB609IV</b>   | <b>HBL20GB609GY</b>   |
|        | 15  | Single    | 6                | 12                       | <b>HBL20GB612IV</b>   | <b>HBL20GB612GY</b>   |
|        | 15  | Single    | 4                | 18                       | <b>HBL20GB618IV</b>   | <b>HBL20GB618GY</b>   |
|        | 15  | Two       | 8                | 9                        | <b>HBL20GBA609IV</b>  | <b>HBL20GBA609GY</b>  |
|        | 15  | Two       | 6                | 12                       | <b>HBL20GBA612IV</b>  | <b>HBL20GBA612GY</b>  |
|        | 15  | Two       | 4                | 18                       | <b>HBL20GBA618IV</b>  | <b>HBL20GBA618GY</b>  |
|        | 15  | IG/Single | 12               | 6                        | <b>HBL20IG606IV</b>   | <b>HBL20IG606GY</b>   |
|        | 20  | Single    | 12               | 6                        | <b>HBL24GB606IV</b>   | <b>HBL24GB606GY</b>   |
|        | 20  | Single    | 6                | 12                       | <b>HBL24GB612IV</b>   | <b>HBL24GB612GY</b>   |
|        | 20  | Single    | 4                | 18                       | <b>HBL24GB618IV</b>   | <b>HBL24GB618GY</b>   |
|        | 20  | Two       | 6                | 12                       | <b>HBL24GBA612IV</b>  | <b>HBL24GBA612GY</b>  |
|        | 20  | Two       | 4                | 18                       | <b>HBL24GBA618IV</b>  | <b>HBL24GBA618GY</b>  |



| Portable | Amp | Circuits | Length (in.) | Cord Length (ft.) | # Single Recept. | Color              |                    |
|----------|-----|----------|--------------|-------------------|------------------|--------------------|--------------------|
|          |     |          |              |                   |                  | Ivory              | Gray               |
|          | 15  | Single   | 40           | 6                 | 6                | <b>HBL20C215IV</b> | <b>HBL20C215GY</b> |
|          | 15  | Single   | 64           | 6                 | 10               | <b>HBL20C315IV</b> | <b>HBL20C315GY</b> |

Note: IG = Isolated Ground and TR = Tamper-Resistant.

Hubbell Metal PlugTrak is supplied with two HBL2010BIV/GY blank end fittings and one HBL2001C coupling. Catalog number suffix "IV" for ivory finish and "GY" for gray finish. Outlets match raceway color. "IG" Isolated ground receptacles are orange color. Portable PlugTrak includes 15A circuit breaker.

|                 | Description                | Color         | Catalog Number                           |
|-----------------|----------------------------|---------------|------------------------------------------|
|                 |                            |               |                                          |
| Boxes           | 1-Gang Device Box          | Ivory<br>Gray | <b>HBL2048IV</b><br><b>HBL2048GY</b>     |
|                 | 2-Gang Device Box          | Ivory<br>Gray | <b>HBL20482IV</b><br><b>HBL20482GY</b>   |
| Elbows and Tees | External Elbow             | Ivory<br>Gray | <b>HBL2018CIV</b><br><b>HBL2018CGY</b>   |
|                 | Flat Elbow                 | Ivory<br>Gray | <b>HBL2011IV</b><br><b>HBL2011GY</b>     |
|                 | Tee                        | Ivory<br>Gray | <b>HBL2015IV</b><br><b>HBL2015GY</b>     |
|                 |                            |               |                                          |
| End Fittings    | Entrance End Fitting       | Ivory<br>Gray | <b>HBL2010A2IV</b><br><b>HBL2010A2GY</b> |
|                 | Large Entrance End Fitting | Ivory<br>Gray | <b>HBL2010A3IV</b><br><b>HBL2010A3GY</b> |
|                 | Blank End Fitting          | Ivory<br>Gray | <b>HBL2010BIV</b><br><b>HBL2010BGY</b>   |
|                 |                            |               |                                          |
| Fittings        | Cover Clip                 | Ivory<br>Gray | <b>HBL2006IV</b><br><b>HBL2006GY</b>     |
|                 | Supporting Clip            | Steel**       | <b>HBL2003SC*</b>                        |
|                 | Coupling                   | Steel**       | <b>HBL2001C</b>                          |
|                 | Internal Corner Coupling   | Steel**       | <b>HBL2017TC</b>                         |

Note: \*Support clip HBL2003SC for supporting Portable Metal PlugTrak only.

\*\*Galvanized Steel.

See pages R-10 and R-11 for additional information.



### HBL2400 and HBL2400D Raceway

- Increased capacity, more than the HBL2000 Series Raceway.
- Divided base allows for dual services within one raceway profile.



### Bend Radius Fittings


- 1½ in. (38.10) bend radius.
- Ideal for high speed data cables including Category 5, 5e, 6 and 6A applications.










### Innovative Box Design

- Hubbell Handi-Screw® eliminates difficult to install long screws for easier installation.
- Rounded corners eliminate sharp edges.
- One seam construction provides “clean” look.
- Box design allows standard wallplates to be mounted flush with virtually no perimeter profile exposed.
- Full line of metal wallplates available. See page R-45 for selection.

| HBL2400 Series | Description                                                                                 | Color | Catalog Number                                                                    |
|----------------|---------------------------------------------------------------------------------------------|-------|-----------------------------------------------------------------------------------|
|                | <b>Undivided Base and Cover</b><br>Packed 50 ft. (15m) per carton,<br>5 ft. (1.5m) lengths. | Ivory | <b>HBL2400BCIV</b><br>A: 60.00" (1,524.00)<br>B: 1.91" (48.51)<br>C: .88" (22.40) |







| HBL2400 Series<br>Base and Cover | Description                                                                                 | Color | Catalog Number                                                   | HBL2400 Series<br>Base and Cover | Description                                                                    | Color | Catalog Number                                                |
|----------------------------------|---------------------------------------------------------------------------------------------|-------|------------------------------------------------------------------|----------------------------------|--------------------------------------------------------------------------------|-------|---------------------------------------------------------------|
|                                  | <b>10 Ft. Base, Undivided</b><br>Packed 100 ft. (30.5m) per carton,<br>10 ft. (3m) lengths. | Ivory | <b>HBL2400B10IV</b><br>A: 120.00" (3,048.00)<br>B: 1.91" (48.51) |                                  | <b>5 Ft. Cover</b><br>Packed 50 ft. (15m) per carton,<br>5 ft. (1.5m) lengths. | Ivory | <b>HBL2400CIV</b><br>A: 60.00" (1,524.00)<br>B: 1.89" (48.00) |
|                                  | <b>5 Ft. Base, Undivided</b><br>Packed 50 ft. (15m) per carton,<br>5 ft. (1.5m) lengths.    | Ivory | <b>HBL2400BIV</b><br>A: 60.00" (1,524.00)<br>B: 1.91" (48.51)    |                                  |                                                                                |       |                                                               |
|                                  | <b>10 Ft. Base, Divided</b><br>Packed 100 ft. (30.5m) per carton,<br>10 ft. (3m) lengths.   | Ivory | <b>HBL2400BDIV</b><br>A: 120.00" (3,048.00)<br>B: 1.91" (48.51)  |                                  |                                                                                |       |                                                               |







| Device Boxes | Description                                                                                                                                        | Color | Type      | 1-Gang                                                    |                                                           | 2-Gang                                                     |                                                            |
|--------------|----------------------------------------------------------------------------------------------------------------------------------------------------|-------|-----------|-----------------------------------------------------------|-----------------------------------------------------------|------------------------------------------------------------|------------------------------------------------------------|
|              |                                                                                                                                                    |       |           | Standard                                                  | Extra Deep                                                | Standard                                                   | Extra Deep                                                 |
|              | <b>Device Box</b><br>For deep switches and<br>receptacles. Base has one<br>½ in. trade size KO and<br>rectangular KO for extension<br>to wall box. | Ivory | Divided   | —                                                         | <b>HBL2444DIV</b>                                         | —                                                          | <b>HBL2444D2AIV</b>                                        |
|              |                                                                                                                                                    | Ivory | Undivided | <b>HBL2448IV</b>                                          | <b>HBL2444IV</b>                                          | <b>HBL24482IV</b>                                          | <b>HBL24442IV</b>                                          |
|              |                                                                                                                                                    |       |           | A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 1.75" (44.45) | A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 2.75" (69.85) | A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 1.75" (44.45) | A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 2.75" (69.85) |







| Elbows and Tees | Description                                                                                                                                                                        | Color | Type      | Catalog Number                                            | Elbows and Tees | Description                                                                                                                                      | Color | Type      | Catalog Number                                             |
|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|-----------|-----------------------------------------------------------|-----------------|--------------------------------------------------------------------------------------------------------------------------------------------------|-------|-----------|------------------------------------------------------------|
|                 | <b>Internal Elbow Bend Radius</b><br>For inside surfaces at right<br>angles, requiring a 1.5 in.<br>(38.10) bend radius. Suitable<br>for Category 5, 5e, 6<br>and 6A applications. | Ivory | Divided   | <b>HBL2417DFOIV*</b>                                      |                 | <b>External Elbow Bend Radius</b><br>For right angle turns around<br>external corners. Suitable for<br>Category 5, 5e, 6 and<br>6A applications. | Ivory | Divided   | <b>HBL2418DFOIV*</b>                                       |
|                 |                                                                                                                                                                                    | Ivory | Undivided | <b>HBL2417IV**</b>                                        |                 |                                                                                                                                                  | Ivory | Undivided | <b>HBL2418IV**</b>                                         |
|                 |                                                                                                                                                                                    |       |           | A: 1.91" (48.51)<br>B: 3.60" (91.30)                      |                 |                                                                                                                                                  |       |           | A: 1.91" (48.51)<br>B: 3.83" (97.28)                       |
|                 | <b>90° Flat Elbow Bend Radius</b><br>For right angle turns on<br>same surface. Suitable for<br>Category 5, 5e, 6 and<br>6A applications.                                           | Ivory | Divided   | <b>HBL2411DFOIV*</b>                                      |                 | <b>Tee Fitting Bend Radius</b><br>For branches at right angles.<br>Suitable for Category 5, 5e,<br>6 and 6A applications.                        | Ivory | Divided   | <b>HBL2415DFOIV*</b>                                       |
|                 |                                                                                                                                                                                    | Ivory | Undivided | <b>HBL2411IV**</b>                                        |                 |                                                                                                                                                  | Ivory | Undivided | <b>HBL2415IV**</b>                                         |
|                 |                                                                                                                                                                                    |       |           | A: 6.00" (152.40)<br>B: 5.00" (127.00)<br>C: .90" (22.86) |                 |                                                                                                                                                  |       |           | A: 7.30" (185.42)<br>B: 4.99" (126.75)<br>C: 1.44" (36.58) |



Note: \*HBL2401DC couplings included.  
 \*\*HBL2401C couplings included.

Dimensions in Inches (mm)

| End Fittings | Description                                                                                                                                                         | Color | Type      | Catalog Number                                                                | Description                                                                                                                                                                                                                           | Color | Type      | Catalog Number                                                                 |
|--------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|-----------|-------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|-----------|--------------------------------------------------------------------------------|
|              | <b>Entrance End Fitting</b><br>End fitting with ½ in. and ¾ in. concentric trade size KOs on end and bottom. Additional ½ in. trade size KOs on sides.              | Ivory | Divided   | —                                                                             | <b>Entrance End Fitting Bend Radius</b><br>Divided, bend radius end fitting to feed HBL2400 and HBL2400D Series Raceway. Includes 1 in. and ¾ in. trade size KOs on back and end. Removable divider and bend radius inserts included. | Ivory | Divided   | <b>HBL2410DFOIV</b>                                                            |
|              |                                                                                                                                                                     | Ivory | Undivided | <b>HBL2410CIV</b><br>A: 3.69" (93.8)<br>B: 2.02" (51.2)<br>C: 1.79" (45.4)    |                                                                                                                                                                                                                                       | Ivory | Undivided | —<br>A: 7.08" (179.83)<br>B: 4.72" (119.89)<br>C: 2.76" (70.10)                |
|              |   |       |           |                                                                               |                                                                 |       |           |                                                                                |
| End Fittings | <b>Entrance End Fitting</b><br>For connecting HBL2400 Raceway with one ½ in. conduit and armored cable connectors.                                                  | Ivory | Divided   | —                                                                             | <b>Entrance End Fitting Full Capacity</b><br>Full capacity entrance end to feed HBL2400 Series Raceway. Includes three 1 in. and ¾ in. concentric trade size KOs.                                                                     | Ivory | Divided   | —                                                                              |
|              |                                                                                                                                                                     | Ivory | Undivided | <b>HBL2410AIV</b><br>A: 1.16" (29.50)<br>B: 1.89" (49.00)<br>C: 1.66" (42.20) |                                                                                                                                                                                                                                       | Ivory | Undivided | <b>HBL2410FCIV</b><br>A: 3.04" (77.23)<br>B: 2.61" (66.29)<br>C: 2.23" (56.64) |
|              |   |       |           |                                                                               |                                                                 |       |           |                                                                                |
| End Fittings | <b>Transition Fitting</b><br>For transitioning from Wiremold® 2400D/2400 Raceway to Hubbell HBL2400/HBL2400D Raceway.                                               | Ivory | Divided   | <b>HBL2400DTFIV</b>                                                           | <b>Blank End Fitting</b><br>For closing open end of HBL2400 Raceway.                                                                                                                                                                  | Ivory | Divided   | <b>HBL2410BDIV</b>                                                             |
|              |                                                                                                                                                                     | Ivory | Undivided | <b>HBL2400TFIV</b><br>A: 2.02" (51.31)<br>B: 1.06" (26.92)                    |                                                                                                                                                                                                                                       | Ivory | Undivided | <b>HBL2410BIV</b><br>A: 1.17" (29.72)<br>B: 1.96" (49.78)<br>C: .84" (21.34)   |
|              |   |       |           |                                                                               |                                                                 |       |           |                                                                                |

| Fittings | Description                                                                                                                                                             | Color   | Catalog Number                                                                  | Description                                                                                                                                                                 | Color   | Catalog Number                                                                   |
|----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|---------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|----------------------------------------------------------------------------------|
|          | <b>End Reducing Connector</b><br>For connecting HBL2400 Raceway to HBL2000 Raceway through end of HBL2400 Raceway.                                                      | Ivory   | <b>HBL2420REDIV*</b><br>A: 3.81" (96.77)<br>B: 2.07" (52.58)<br>C: .90" (22.86) | <b>End Reducing Connector</b><br>For connecting HBL4750 Raceway to HBL2400 Raceway through end of HBL4750 Raceway. Includes HBL2401DC coupling (HBL4751AC not included).    | Ivory   | <b>HBL4724REDIV</b><br>A: 4.75" (120.65)<br>B: 3.00" (76.20)<br>C: 1.55" (39.37) |
|          |   |         |                                                                                 |   |         |                                                                                  |
|          | <b>Side Reducing Connector</b><br>For connecting HBL2400 Raceway to HBL500 Raceway through side of HBL2400 Raceway.                                                     | Ivory   | <b>HBL2489IV*</b><br>A: 3.75" (95.25)<br>B: 1.91" (48.51)<br>C: .82" (20.83)    | <b>Bridge Fitting</b><br>For allowing HBL2400 Series Raceway to bridge over existing installations of HBL2400, HBL750 and HBL500 Series Raceways.                           | Ivory   | <b>HBL2475DBRIV</b><br>A: 5.60" (142.24)<br>B: 2.92" (74.17)<br>C: 1.63" (41.40) |
|          |   |         |                                                                                 |   |         |                                                                                  |
|          | <b>Cover Clip</b><br>Use to cover potential openings where two pieces of HBL2400 Raceway cover come together.                                                           | Ivory   | <b>HBL2406IV</b><br>A: 1.50" (38.10)                                            | <b>Flush Plate Adaptor</b><br>For feeding HBL2400 Raceway from an existing wall outlet box ½ in. trade size male nipple. Provided with locknut for grounding.               | Ivory   | <b>HBL2451HIV*</b><br>A: 4.50" (114.30)                                          |
| Fittings |   |         |                                                                                 |   |         |                                                                                  |
|          | <b>Wire Clip (Plated)</b><br>For holding conductors in place.                                                                                                           | Steel** | <b>HBL2400WC</b><br>A: 1.69" (42.93)<br>B: 1.00" (25.40)<br>C: .79" (20.00)     | <b>Ground Clamp (Plated)</b><br>For connection of equipment grounding conductor to provide an additional ground to raceway.                                                 | Steel** | <b>HBL2409GC</b><br>A: .41" (10.41)                                              |
|          |   |         |                                                                                 |   |         |                                                                                  |
| Fittings | <b>Coupling (Plated), Divided</b><br>For joining lengths of HBL2400 Raceway.                                                                                            | Steel** | <b>HBL2401DC</b><br>A: 2.00" (50.80)<br>B: 1.86" (47.24)                        | <b>Coupling (Plated), Undivided</b><br>For joining lengths of HBL2400 Raceway.                                                                                              | Steel** | <b>HBL2401C</b><br>A: 2.00" (50.80)<br>B: 1.86" (47.24)                          |
|          |   |         |                                                                                 |   |         |                                                                                  |

Note: \*Only used on HBL2400 Series Undivided Raceway.

\*\*Galvanized Steel.




# Metal Raceway

## HBL2400 and HBL2400D Series

Frames and Tools



Devices and Frames

| Description                                                                                                                                                                     | Color | Catalog Number                                                                  | Description                                                                                                                                                                            | Color | Catalog Number                                               |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|---------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|--------------------------------------------------------------|
| <b>Receptacle Bracket and Frame</b><br>For use with power devices with maximum width of 1.35 in. (84.3) and in low voltage applications with ISFxxAL frames found on page R-45. | Ivory | <b>HBL24106RRK*</b><br>A: 6.00" (152.40)<br>B: 2.02" (51.31)                    | <b>Duplex Bracket and Frame</b><br>For use with power devices with maximum width of 1.35 in. (84.3) and in low voltage applications with BR106AL and Q106AL frames found on page R-45. | Ivory | <b>HBL24106DRK*</b><br>A: 6.00" (152.40)<br>B: 2.02" (51.31) |
|                                                                                                |       |                                                                                 |                                                                                                      |       |                                                              |
| <b>Lamp Holder</b><br>Medium base lamp holder<br>660W 250V ceramic. Ivory (Cover)<br>White Ceramic (Lamp Holder).                                                               | Ivory | <b>HBL24261IV*</b><br>A: 5.00" (127.00)<br>B: 1.89" (48.01)<br>C: 1.03" (26.16) |                                                                                                                                                                                        |       |                                                              |
|                                                                                                |       |                                                                                 |                                                                                                                                                                                        |       |                                                              |

Note: \*Only used on HBL2400 Series Undivided Raceway.

| Tools | Description                                                                         |  | Catalog Number   |  | Color                                                                              |  | Catalog Number       |  |
|-------|-------------------------------------------------------------------------------------|--|------------------|--|------------------------------------------------------------------------------------|--|----------------------|--|
|       | <b>Cutter</b><br>Portable cutter for HBL2400/<br>HBL2400D Series Raceway.           |  | <b>HBL624CUT</b> |  | <b>Touch-Up Paint Pen</b>                                                          |  | <b>Ivory HBLIWEP</b> |  |
|       |   |  |                  |  |  |  |                      |  |
|       | <b>Cutter Replacement Blade Set</b>                                                 |  | <b>HBL624BCK</b> |  |                                                                                    |  |                      |  |
|       |  |  |                  |  |                                                                                    |  |                      |  |

Dimensions in Inches (mm)



### Extensive Line

- Full line of large, single channel, two piece metal raceway.
- Easily mounts on walls or bench tops.
- Large single channel base for power or datacom cables.
- UL Listed and CSA Certified.
- Available in ivory or gray powder coat finish.



### Plates and Covers

- Wide range of covers and cover plates accommodate the most demanding applications.
- Removable cover and cover plates provide easy access to wiring compartment.
- Precut covers and plates provide quick installation and are available in common configurations.



Wiremold® 3000 Series to Hubbell HBL3000 Series utilizing Hubbell transition fitting.

### Transition Fittings

- UL Classified to transition from Wiremold® 3000 Series Metal Raceway to Hubbell HBL3000 Series Metal Raceway.
- Reducer fitting provides transition from Hubbell HBL3000 Series to Hubbell HBL2000 Series Raceway.



Wiremold® is a registered trademark of the Wiremold Company.

### Boxes

- Hubbell Handi-Screw® eliminates “difficult-to-install” long screws for faster mounting.
- Rounded corners eliminate sharp edges.
- One seam construction provides “clean” look.
- Large capacity allows for the installation of 30, 50 or 60A receptacles.
- Utility box can be used as a tee, cross, junction box or as a branch circuit extension.

# Metal Raceway

## HBL3000 Series

Metal Raceway, Device Boxes, Elbows and Tees

Available in  
**PRE-WIRED**








| HBL3000 Series                                                                                                                                                                  | Description | Color | Catalog Number                       | Description                                                                          | Color | Catalog Number                           |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|-------|--------------------------------------|--------------------------------------------------------------------------------------|-------|------------------------------------------|
|                                                                                                                                                                                 |             |       |                                      |                                                                                      |       |                                          |
| <b>Single Channel Base</b><br>Packed 100 ft. (30.5m) per carton,<br>10 ft. (3m) lengths.<br><br>Assembled cover and<br>base dimensions.<br>W: 2.75" (69.85)<br>H: 1.53" (38.86) |             | Ivory | <b>HBL3000BIV</b>                    | <b>5 Ft. Cover</b><br>Packed 100 ft. (30.5m) per carton,<br>5 ft. (1.5m) lengths.    | Ivory | <b>HBL3000CEIV</b>                       |
|                                                                                                                                                                                 |             | Gray  | <b>HBL3000BGY</b>                    |                                                                                      | Gray  | <b>HBL3000CEGY</b>                       |
|                                                                                                                                                                                 |             |       | A: 2.73" (69.34)<br>B: 1.47" (37.34) |                                                                                      |       | A: 60.00" (1,524.00)<br>B: 2.75" (69.85) |
|                                                                                                                                                                                 |             |       |                                      | <b>19.5 In. Precut Cover*</b><br>For mounting devices on<br>24 in. (610.00) centers. | Ivory | <b>HBL3000C195IV</b>                     |
|                                                                                                                                                                                 |             |       |                                      |                                                                                      | Gray  | <b>HBL3000C195GY</b>                     |
|                                                                                                                                                                                 |             |       |                                      |                                                                                      |       | A: 19.50" (495.30)<br>B: 2.75" (69.85)   |
|                                                                                                                                                                                 |             |       |                                      | <b>7.5 In. Precut Cover*</b><br>For mounting devices on<br>12 in. (305.00) centers.  | Ivory | <b>HBL3000C075IV</b>                     |
|                                                                                                                                                                                 |             |       |                                      |                                                                                      | Gray  | <b>HBL3000C075GY</b>                     |
|                                                                                                                                                                                 |             |       |                                      |                                                                                      |       | A: 7.50" (190.50)<br>B: 2.75" (69.85)    |






Note: \*Packed 10 pieces per carton. Device centers vary based on cover selection. Consult factory for details.

| Boxes                                                                                                                                                    | Description | Color | Catalog Number                                             | Description                                                                                                          | Color | Catalog Number                                             |
|----------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|-------|------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------|-------|------------------------------------------------------------|
|                                                                                                                                                          |             |       |                                                            |                                                                                                                      |       |                                                            |
| <b>Utility Box</b><br>Cover has twistouts on all sides, allows for<br>box to be used as tee, cross, junction box<br>or for branch<br>circuit extensions. |             | Ivory | <b>HBL3028IV</b>                                           | <b>2-Gang Extra Deep Switch<br/>and Receptacle Box</b><br>For standard 30, 50 and 60A straight<br>blade receptacles. | Ivory | <b>HBL30442IV</b>                                          |
|                                                                                                                                                          |             | Gray  | <b>HBL3028GY</b>                                           |                                                                                                                      | Gray  | <b>HBL30442GY</b>                                          |
|                                                                                                                                                          |             |       | A: 6.41" (162.89)<br>B: 6.41" (162.89)<br>C: 1.90" (48.26) |                                                                                                                      |       | A: 6.38" (162.05)<br>B: 6.38" (162.05)<br>C: 2.75" (69.85) |









| Elbows and Tees                                                                                              | Description | Color | Catalog Number                         | Description                                                                          | Color | Catalog Number                          |
|--------------------------------------------------------------------------------------------------------------|-------------|-------|----------------------------------------|--------------------------------------------------------------------------------------|-------|-----------------------------------------|
|                                                                                                              |             |       |                                        |                                                                                      |       |                                         |
| <b>Internal Corner Coupling</b><br>For surfaces at right angles or for<br>use as a straight-through fitting. |             | Ivory | <b>HBL3017TCEIV</b>                    | <b>External Corner Coupling</b><br>For right angle turns around<br>external corners. | Ivory | <b>HBL3018AEIV</b>                      |
|                                                                                                              |             | Gray  | <b>HBL3017TCEGY</b>                    |                                                                                      | Gray  | <b>HBL3018AEGY</b>                      |
|                                                                                                              |             |       | A: 2.61" (66.29)                       |                                                                                      |       | A: 4.00" (101.60)                       |
| <b>90° Flat Elbow</b><br>For right angle turns on same surface.                                              |             | Ivory | <b>HBL3011EIV</b>                      | <b>Tee Fitting</b><br>For branches at right angles.<br>Couplings furnished.          | Ivory | <b>HBL3015EIV</b>                       |
|                                                                                                              |             | Gray  | <b>HBL3011EGY</b>                      |                                                                                      | Gray  | <b>HBL3015EGY</b>                       |
|                                                                                                              |             |       | A: 6.40" (162.40)<br>B: 6.00" (152.40) |                                                                                      |       | A: 10.31" (261.94)<br>B: 8.00" (203.20) |

Dimensions in Inches (mm)

| End Fittings | Description                                                                                                                                                         | Color         | Catalog Number                                                                                     | Description                                                                                                                                                             | Color         | Catalog Number                                                                                                                            |
|--------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|----------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|-------------------------------------------------------------------------------------------------------------------------------------------|
|              | <b>Entrance End Fitting</b><br>For connecting HBL3000 Raceway with ½ in. conduit and armored cable connectors.                                                      | Ivory<br>Gray | <b>HBL3010AEIV</b><br><b>HBL3010AEGY</b><br>A: 2.75" (69.85)<br>B: 3.42" (86.87)                   | <b>Entrance End Fitting</b><br>For connecting HBL3000 Raceway with rigid or flexible conduit. Concentric ½ in., ¾ in. and 1 in. trade size KOs on end and each side.    | Ivory<br>Gray | <b>HBL3010CIV</b><br><b>HBL3010CGY</b><br>A: 2.75" (69.85)<br>B: 3.25" (82.55)<br>C: 2.00" (50.80)                                        |
|              |   |               |                                                                                                    |   |               |                                                                                                                                           |
|              | <b>Blank End Fitting</b><br>For closing open end of HBL3000 Raceway. Has concentric ½ in. and ¾ in. trade size KOs.                                                 | Ivory<br>Gray | <b>HBL3010BIV</b><br><b>HBL3010BGY</b><br>A: 2.71" (68.92)<br>B: 1.79" (45.36)<br>C: 1.41" (35.84) | <b>Panel Connector</b><br>To connect HBL3000 Raceway with surface type boxes.                                                                                           | Ivory<br>Gray | <b>HBL3086IV</b><br><b>HBL3086GY</b><br>A: 4.60" (116.71)<br>B: 1.19" (30.16)<br>C: 3.00" (76.20)<br>D: 1.94" (49.40)<br>E: 3.76" (95.50) |
|              |   |               |                                                                                                    |   |               |                                                                                                                                           |
|              | <b>Conduit Connector</b><br>To connect end of HBL3000 Raceway to 1½ in. trade size conduit or connector.                                                            | Gray          | <b>HBL3082GY</b><br>A: 2.91" (74.00)<br>B: 2.75" (69.85)                                           |                                                                                                                                                                         |               |                                                                                                                                           |
|              |   |               |                                                                                                    |                                                                                                                                                                         |               |                                                                                                                                           |

| Fittings | Description                                                                                                                                                             | Color         | Catalog Number                                                                                       | Description                                                                                                                                                                 | Color         | Catalog Number                                                                     |
|----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|------------------------------------------------------------------------------------|
|          | <b>Transition Fitting</b><br>For transitioning from Wiremold® 3000 Raceway to Hubbell HBL3000 Raceway.                                                                  | Ivory<br>Gray | <b>HBL3000TFIV</b><br><b>HBL3000TFGY</b><br>A: 2.85" (72.39)<br>B: 2.15" (54.61)<br>C: 1.50" (38.04) | <b>Take-Off Connector (Reducer)</b><br>Transition Hubbell HBL3000 Raceway to Hubbell HBL2000 Raceway.                                                                       | Ivory<br>Gray | <b>HBL3200REDIV</b><br><b>HBL3200REDGY</b><br>A: 2.75" (69.85)<br>B: 2.25" (57.15) |
|          |   |               |                                                                                                      |   |               |                                                                                    |
|          | <b>Wall Box Connector</b><br>For connecting to HBL3000 Raceway from a flush mounted wall box.                                                                           | Ivory<br>Gray | <b>HBL3014CIV</b><br><b>HBL3014CGY</b><br>A: 8.00" (203.20)<br>B: 3.28" (83.31)                      | <b>Tap-Off Fitting</b><br>Has concentric ½ in. and ¾ in. trade size KOs and twistout for communication cables.                                                              | Ivory<br>Gray | <b>HBL3046H2IV</b><br><b>HBL3046H2GY</b><br>A: 4.75" (120.65)                      |
|          |   |               |                                                                                                      |   |               |                                                                                    |
|          | <b>Cover Clip</b><br>Use to cover potential openings where two pieces of HBL3000 Raceway come together.                                                                 | Ivory<br>Gray | <b>HBL3006EIV</b><br><b>HBL3006EGY</b><br>A: 2.78" (70.60)<br>B: .75" (19.05)                        | <b>Supporting Clip</b><br>For supporting lengths of HBL3000 Raceway at any point. Mount with #8 flat head fastener. Has set screw for locking to raceway.                   | Ivory<br>Gray | <b>HBL3003IV</b><br><b>HBL3003GY</b><br>A: 2.81" (71.33)<br>B: .75" (19.05)        |
|          |   |               |                                                                                                      |   |               |                                                                                    |
|          | <b>Wire Clip (Plated)</b><br>For holding conductors in place.                                                                                                           | Steel*        | <b>HBL3000WCGY</b><br>A: 1.00" (25.40)                                                               | <b>Rigid Inside Coupling (Plated)</b><br>For joining lengths of HBL3000 Raceway when added rigidity is required, i.e. raceway suspended overhead.                           | Steel*        | <b>HBL3001AGY</b><br>A: 6.00" (152.40)                                             |
|          |   |               |                                                                                                      |   |               |                                                                                    |
|          | <b>Coupling (Plated)</b><br>For joining lengths of HBL3000 Raceway.                                                                                                     | Steel*        | <b>HBL3001GY</b><br>A: 2.20" (55.75)                                                                 |                                                                                                                                                                             |               |                                                                                    |
|          |   |               |                                                                                                      |                                                                                                                                                                             |               |                                                                                    |

Note: \*Galvanized Steel.

| Device Bracket and Cover Plates | Description                                                                                                                                                                                      | Color         | Catalog Number                                                | Description                                                                                                                                                                                                                  | Color         | Catalog Number                                                |
|---------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|---------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|---------------------------------------------------------------|
|                                 | <b>Switch Cover</b><br>For installing single pole, two pole, three way or four way switches. Includes HBL3007CGY device bracket.                                                                 | Ivory<br>Gray | <b>HBL3040CEIV</b><br><b>HBL3040CEGY</b><br>A: 4.50" (114.30) | <b>Rectangular Style Line® Recept. Cover</b><br>For installing 15A and 20A rectangular duplex receptacles, GFCI, surge devices, and rectangular communication frames shown on page R-45. Includes HBL3007CGY device bracket. | Ivory<br>Gray | <b>HBL3048RIV</b><br><b>HBL3048RGY</b><br>A: 4.50" (114.30)   |
|                                 |                                |               |                                                               |                                                         |               |                                                               |
|                                 | <b>Duplex Receptacle Cover</b><br>For installing 15A and 20A duplex receptacles and duplex communication frames shown on page R-45. Includes HBL3007CGY device bracket.                          | Ivory<br>Gray | <b>HBL3043BEIV</b><br><b>HBL3043BEGY</b><br>A: 4.50" (114.30) | <b>Duplex Receptacle Cover</b><br>For high strain/vibration. For installing 15A and 20A duplex receptacles and duplex communication frames shown on page R-45. Includes device brackets.                                     | Ivory<br>Gray | <b>HBL3046BEIV</b><br><b>HBL3046BEGY</b><br>A: 5.38" (136.65) |
|                                 |                                |               |                                                               |                                                         |               |                                                               |
|                                 | <b>Single Receptacle Cover</b><br>For installing straight blade and locking single receptacles with face diameters of 1.38 in. to 1.39 in. (35.05 to 35.31). Includes HBL3007CGY device bracket. | Ivory<br>Gray | <b>HBL3027AEIV</b><br><b>HBL3027AEGY</b><br>A: 4.50" (114.30) | <b>Single Receptacle Cover</b><br>For installing straight blade and locking single receptacles with face diameters of 1.56 in. to 1.57 in. (39.62 to 39.88). Includes HBL3007CGY device bracket.                             | Ivory<br>Gray | <b>HBL3033JEIV</b><br><b>HBL3033JEGY</b><br>A: 4.50" (114.30) |
|                                 |                                |               |                                                               |                                                         |               |                                                               |
|                                 | <b>Blank Cover</b><br>Has one ½ in. trade size KO in center. Includes HBL3007CGY bracket.                                                                                                        | Ivory<br>Gray | <b>HBL3036HEIV</b><br><b>HBL3036HEGY</b><br>A: 4.50" (114.30) | <b>Extension Cover</b><br>Cover accepts 3-wire 30A and 50A devices and standard commercially available flush plates. Includes HBL3007CGY device bracket. See page R-45 for plate options.                                    | Ivory<br>Gray | <b>HBL3051LEIV</b><br><b>HBL3051LEGY</b><br>A: 4.50" (114.30) |
|                                 |                            |               |                                                               |                                                     |               |                                                               |
|                                 | <b>Device Bracket</b><br>For mounting standard devices in HBL3000 Raceway. Use with commercially available flush plate (not furnished).                                                          | Steel*        | <b>HBL3007CGY</b><br>A: 4.50" (114.30)<br>B: 3.28" (83.31)    |                                                                                                                                                                                                                              |               |                                                               |
|                                 |                            |               |                                                               |                                                                                                                                                                                                                              |               |                                                               |

Note: \*Galvanized Steel.

| Tools | Description                                                                         | Color         | Catalog Number                   | Description                                                                           | Catalog Number   |
|-------|-------------------------------------------------------------------------------------|---------------|----------------------------------|---------------------------------------------------------------------------------------|------------------|
|       | <b>Base Cutter</b><br>Portable cutter for HBL3000 Raceway Base.                     |               | <b>HBL630B</b>                   | <b>Cover Cutter</b><br>Portable cutter for HBL3000 Raceway Cover.                     | <b>HBL630C</b>   |
|       |  |               |                                  |  |                  |
|       | <b>Replacement Blade Cutter and Die Set</b><br>Base blade set.                      |               | <b>HBL630BDK</b>                 | <b>Replacement Blade Cutter and Die Set</b><br>Cover blade set.                       | <b>HBL630CDK</b> |
|       |  |               |                                  |  |                  |
|       | <b>Touch-Up Paint Pen</b>                                                           | Ivory<br>Gray | <b>HBLIWEP</b><br><b>HBLGWEP</b> |                                                                                       |                  |
|       |  |               |                                  |                                                                                       |                  |

Dimensions in Inches (mm)



### HBL4750 Device Bracket

- HBL4750 Device Bracket Plate provides excellent solution for power, data, voice, audio and video applications.
- For use with Hubbell KP plates and Hubbell iSTATION modules and bezels.
- Provides flush finish with overlap feature to hide potential miscuts.



### Application Capacity and Flexibility

- Flexible channel divider provides industry leading data capacity in the same profile with a 2/3 datacom split.
- By-Pass Divider opening accepts GFCI or surge devices to be mounted in 70/30 divided channel.
- Greater capacity offers more room for moves, adds and changes.
- 50/50 split available by utilizing standard divider and divider clips.
- Raceway channel can also be used with no divider for maximum cable fill in single service applications.





### End Reducing Connector

- Connects HBL4750 Raceway to HBL2400 Raceway through the end of HBL4750 Raceway.
- Used to connect two different sized raceway profiles.






### Extensive Line




- 1¼ in. (31.75mm) bend radius fittings meet TIA/EIA requirements.
- Integral bend radius offers a fixed solution that does not have to be installed as an option.
- Large cross sectional area provides for maximum cable capacity throughout entire system.
- Available external, internal, flat, tee and entrance end fittings.
- UL Listed, CSA Certified.
- Available in ivory or gray powder coat finish.

| HBL4750 Series | Description                                                                                                                                                                | Color         | Catalog Number                                                                                              | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                               | Color                                                                        | Catalog Number                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
|----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|-------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                | <b>Single Channel Base</b><br>Packed 50 ft. (15.24m) per carton, 10 ft. (3m) lengths.<br><br>Assembled cover and base dimensions.<br>W: 4.75" (120.65)<br>H: 1.75" (44.45) | Ivory<br>Gray | <b>HBL4750B10IV</b><br><b>HBL4750B10GY</b><br>A: 120.00" (3048.00)<br>B: 4.75" (120.65)<br>C: 1.62" (41.20) | <b>5 Ft. Cover</b><br>Packed 50 ft. (15.24m) per carton, 5 ft. (1.5m) lengths.<br><br><b>31 In. Precut Cover*</b><br>For 36 in. (915.00) centers with HBL4747 and HBL4750 Plates.<br><br><b>19 In. Precut Cover*</b><br>For 24 in. (610.00) centers with HBL4747 and HBL4750 Plates.<br><br><b>13 In. Precut Cover*</b><br>For 18 in. (457.00) centers with HBL4747 and HBL4750 Plates.<br><br><b>7 In. Precut Cover*</b><br>For 12 in. (305.00) centers with HBL4747 and HBL4750 Plates. | Ivory<br>Gray<br><br>Ivory<br>Gray<br><br>Ivory<br>Gray<br><br>Ivory<br>Gray | <b>HBL4750CIV</b><br><b>HBL4750CGY</b><br>A: 60.00" (1,524.0)<br>B: 4.75" (120.65)<br><br><b>HBL4750C315IV</b><br><b>HBL4750C315GY</b><br>A: 31.50" (800.10)<br>B: 4.75" (120.65)<br><br><b>HBL4750C195IV</b><br><b>HBL4750C195GY</b><br>A: 19.50" (495.30)<br>B: 4.75" (120.65)<br><br><b>HBL4750C135IV</b><br><b>HBL4750C135GY</b><br>A: 13.50" (342.90)<br>B: 4.75" (120.65)<br><br><b>HBL4750C075IV</b><br><b>HBL4750C075GY</b><br>A: 7.50" (190.50)<br>B: 4.75" (120.65) |
|                |                                                                                           |               |                            |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |                                                                              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
|                |                                                                                                                                                                            |               |                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                         |                                                                              |                                                                                                                                                                                                                                                                                                                                                                                            |
|                |                                                                                                                                                                            |               |                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |                                                                              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |

Note: \*Packed 10 pieces per carton. Device centers vary based on cover selection. Consult factory for details.


| Fittings | Description                                                                                                                                                                          | Color            | Catalog Number                                                                      | Description                                                                                                                                                                                            | Color            | Catalog Number                                                                        |
|----------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|---------------------------------------------------------------------------------------|
|          | <b>Divider</b><br>Divides HBL4750 Raceway into two channels. Packed 50 ft. (15.24m) per carton, 5 ft. (1.5m) lengths. HBL4751DA Divider Clips are required to hold divider in place. | Painted<br>Steel | <b>HBL4750DGY</b><br>A: 60.00" (1,524.0)<br>B: 1.51" (38.46)                        | <b>By-Pass Divider</b><br>Divides HBL4750 Raceway into two channels with a 70/30 split. Allows for a larger power or datacom wire fill. HBL4751DA Divider Clips are required to hold divider in place. | Painted<br>Steel | <b>HBL4750BP</b><br>A: 7.12" (180.74)<br>B: .89" (22.54)                              |
|          |                                                                                                   |                  |  |                                                                                                                    |                  |  |
|          | <b>Divider Clip</b><br>Required for holding HBL4750DGY in place. Use one every 2.5 ft. (.762m).                                                                                      | Steel**          | <b>HBL4751DA</b><br>A: 4.64" (117.77)<br>B: 1.46" (37.07)                           | <b>Wire Clip (Plated)</b><br>For holding conductors in place.                                                                                                                                          | Steel**          | <b>HBL4750WCGY</b><br>A: 4.60" (116.74)<br>B: 1.58" (40.13)<br>C: 1.00" (25.40)       |
|          |                                                                                                   |                  |  |                                                                                                                    |                  |  |
|          | <b>Internal Corner Coupling (Plated)</b><br>Concealed fitting for making an internal corner while continuing original run in a straight line.                                        | Steel**          | <b>HBL4717TCAGY</b><br>A: 4.59" (116.59)<br>B: 2.71" (68.73)<br>C: 1.47" (37.34)    | <b>Coupling (Plated)</b><br>For joining lengths of HBL4750 Raceway. Sold in pairs.                                                                                                                     | Steel**          | <b>HBL4751AC</b><br>A: 1.47" (37.30)<br>B: .42" (10.59)                               |
|          |                                                                                                   |                  |  |                                                                                                                    |                  |  |





Note: \*\*Galvanized Steel.

| Elbows | Description                                                                                                                       | Color         | Catalog Number                                                                                              | Description                                                                                               | Color         | Catalog Number                                                                                        |
|--------|-----------------------------------------------------------------------------------------------------------------------------------|---------------|-------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------|---------------|-------------------------------------------------------------------------------------------------------|
|        | <b>Internal Elbow, Divided</b><br>For inside surfaces at right angles.<br>Full capacity 1¼ in. bend radius internal elbow.        | Ivory<br>Gray | <b>HBL4717DFOIV*</b><br><b>HBL4717DFOGY*</b><br>A: 4.74" (120.47)<br>B: 4.75" (120.65)                      | <b>Internal Elbow, Undivided</b><br>For inside surfaces at right angles.                                  | Ivory<br>Gray | <b>HBL4717IV*</b><br><b>HBL4717GY*</b><br>A: 4.74" (120.47)<br>B: 4.75" (120.65)                      |
|        |                                                  |               |                                                                                                             |                         |               |                                                                                                       |
|        | <b>External Elbow, Divided</b><br>For right angle turns around external corners. Full capacity 1¼ in. bend radius external elbow. | Ivory<br>Gray | <b>HBL4718DFOIV*</b><br><b>HBL4718DFOGY*</b><br>A: 4.88" (123.90)<br>B: 4.75" (120.65)                      | <b>External Elbow, Undivided</b><br>For right angle turns around external corners.                        | Ivory<br>Gray | <b>HBL4718IV*</b><br><b>HBL4718GY*</b><br>A: 4.88" (123.90)<br>B: 4.75" (120.65)                      |
|        |                                                  |               |                                                                                                             |                         |               |                                                                                                       |
|        | <b>Flat Elbow, Divided</b><br>For right angle turns on same surface.<br>Full capacity 1¼ in. bend radius flat elbow.              | Ivory<br>Gray | <b>HBL4711DFOIV*</b><br><b>HBL4711DFOGY*</b><br>A: 7.23" (183.76)<br>B: 1.62" (41.15)                       | <b>Flat Elbow, Undivided</b><br>For right angle turns on same surface.                                    | Ivory<br>Gray | <b>HBL4711IV*</b><br><b>HBL4711GY*</b><br>A: 7.23" (183.76)<br>B: 1.62" (41.15)                       |
|        |                                                  |               |                                                                                                             |                         |               |                                                                                                       |
|        | <b>Internal or External 45° Elbow</b><br>For making internal or external turns in a run of HBL4750 Raceway.                       | Ivory<br>Gray | <b>HBL4712TXIV</b><br><b>HBL4712TXGY</b><br>A: 6.04" (153.45)<br>B: 4.59" (116.59)                          | <b>Inverted Internal Elbow</b><br>For connecting a vertical run of HBL4750 Raceway with a horizontal run. | Ivory<br>Gray | <b>HBL4717NIV</b><br><b>HBL4717NGY</b><br>A: 4.60" (116.84)<br>B: 1.66" (42.29)                       |
|        |                                                |               |                                                                                                             |                       |               |                                                                                                       |
| Tees   | Description                                                                                                                       | Color         | Catalog Number                                                                                              | Description                                                                                               | Color         | Catalog Number                                                                                        |
|        | <b>Tee Fitting, Divided</b><br>For branches at right angles.<br>Full capacity 1¼ in. bend radius tee fitting.                     | Ivory<br>Gray | <b>HBL4715DFOIV*</b><br><b>HBL4715DFOGY*</b><br>A: 10.93" (277.63)<br>B: 7.27" (184.54)<br>C: 1.62" (41.15) | <b>Tee Fitting, Undivided</b><br>For branches at right angles.                                            | Ivory<br>Gray | <b>HBL4715IV*</b><br><b>HBL4715GY*</b><br>A: 10.93" (277.63)<br>B: 7.27" (184.54)<br>C: 1.62" (41.15) |
|        |                                                |               |                                                                                                             |                       |               |                                                                                                       |













Note: \*HBL4751AC couplings included.

Dimensions in Inches (mm)

| End Fittings | Description                                                                                                                                                                                                                                                                              | Color         | Catalog Number                                                                                             | Description                                                                                                                                                                 | Color         | Catalog Number                                                                                         |
|--------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|--------------------------------------------------------------------------------------------------------|
|              | <b>Entrance End Fitting, Divided</b><br>For connecting HBL4750 Raceway with rigid or flexible conduit. Concentric ¼ in., 1 in. and 1½ in. trade size KOs on back and end. Full capacity 1½ in. bend radius entrance end fitting. Includes ¼ in., 1 in., 1½ in. KO and removable divider. | Ivory<br>Gray | <b>HBL4710DFOIV*</b><br><b>HBL4710DFOGY*</b><br>A: 6.76" (171.70)<br>B: 4.75" (120.65)<br>C: 2.66" (67.50) | <b>Entrance End Fitting, Undivided</b><br>For connecting HBL4750 Raceway with rigid or flexible conduit. Concentric ¼ in., 1 in. and 1½ in. trade size KOs on back and end. | Ivory<br>Gray | <b>HBL4710IIV*</b><br><b>HBL4710IGY*</b><br>A: 6.76" (171.70)<br>B: 4.75" (120.65)<br>C: 2.66" (67.50) |
|              |                                                                                                                                                                                                         |               |                                                                                                            |                                                                                           |               |                                                                                                        |
|              | <b>Blank End Fitting</b><br>For closing open end of HBL4750 Raceway. Has two ½ in. trade size KOs.                                                                                                                                                                                       | Ivory<br>Gray | <b>HBL4710BIV</b><br><b>HBL4710BGY</b><br>A: 4.59" (116.50)<br>B: 1.64" (41.60)<br>C: 1.31" (33.37)        | <b>Panel Connector</b><br>To connect HBL4750 Raceway with surface type panel boxes.                                                                                         | Ivory<br>Gray | <b>HBL4786AIV</b><br><b>HBL4786AGY</b><br>A: 7.50" (190.50)                                            |
|              |                                                                                                                                                                                                         |               |                                                                                                            |                                                                                           |               |                                                                                                        |







| Fittings | Description                                                                                                                                                                  | Color         | Catalog Number                                                                                        | Description                                                                                                                                                                                                            | Color         | Catalog Number                                                                                             |
|----------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|-------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|------------------------------------------------------------------------------------------------------------|
|          | <b>Transition Fitting</b><br>For transitioning Wiremold® 4000 Raceway to Hubbell HBL4750 Raceway.                                                                            | Ivory<br>Gray | <b>HBL4750TFIV</b><br><b>HBL4750TFGY</b><br>A: 5.02" (127.53)<br>B: 2.79" (70.78)                     | <b>Wall Box Connector</b><br>For back feeding HBL4750 Raceway.                                                                                                                                                         | Ivory<br>Gray | <b>HBL4714AIV</b><br><b>HBL4714AGY</b><br>A: 12.00" (304.80)<br>B: 4.75" (120.65)<br>C: 1.62" (41.15)      |
|          |                                                                                             |               |                                                                                                       |                                                                                                                                      |               |                                                                                                            |
|          | <b>End Reducing Connector</b><br>For connecting HBL4750 Raceway to HBL2400 Raceway through the end of HBL4750 Raceway. Includes HBL2401DC coupling (HBL4751AC not included). | Ivory<br>Gray | <b>HBL4724REDIV</b><br>A: 4.75" (120.65)<br>B: 3.00" (76.20)<br>C: 1.55" (39.37)                      | <b>Bridge Fitting</b><br>To bridge HBL4750 series raceway over perpendicular run of raceway or other obstruction. Use standard raceway base and cover, cut in field to required length. Consists of two bridge pieces. | Ivory<br>Gray | <b>HBL4775DKITIV</b><br><b>HBL4775DKITGY</b><br>A: 4.76" (120.90)<br>B: 5.00" (127.00)<br>C: 3.38" (85.85) |
|          |                                                                                           |               |                                                                                                       |                                                                                                                                    |               |                                                                                                            |
|          | <b>Take-Off Connector (HBL4750 To HBL3000)</b><br>For 90° tee connection of HBL3000 Raceway from HBL4750 Raceway.                                                            | Ivory<br>Gray | <b>HBL4774AIV</b><br><b>HBL4774AGY</b><br>A: 11.31" (287.38)<br>B: 4.88" (124.00)<br>C: 3.14" (79.78) | <b>2-Gang Tap-Off Fitting</b><br>Has four concentric ½ in. and ¾ in. trade size KOs.                                                                                                                                   | Ivory<br>Gray | <b>HBL4746H2IV</b><br><b>HBL4746H2GY</b><br>A: 4.75" (120.65)<br>B: 4.75" (120.65)                         |
|          |                                                                                           |               |                                                                                                       |                                                                                                                                    |               |                                                                                                            |
|          | <b>Connection Cover</b><br>For covering potential openings where two covers come together.                                                                                   | Ivory<br>Gray | <b>HBL4756AIV</b><br><b>HBL4756AGY</b><br>A: 4.77" (121.16)<br>B: .75" (19.05)<br>C: .13" (3.36)      |                                                                                                                                                                                                                        |               |                                                                                                            |
|          |                                                                                           |               |                                                                                                       |                                                                                                                                                                                                                        |               |                                                                                                            |

Note: \*HBL4751AC couplings included.

| Device Plates and Mounting Bracket             | Description                                                                                                                                                                                                | Color         | Catalog Number                                                                      | Description                                                                                                                                                                                                                                   | Color         | Catalog Number                                                                         |
|------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|----------------------------------------------------------------------------------------|
|                                                | <b>1-Gang Commercial Device Plate Vertical Mount</b><br>Use with commercially available 1-gang flush plates. See page R-45 for plate options. For single service applications only.                        | Ivory<br>Gray | <b>HBL4747CVMIV</b><br><b>HBL4747CVMGY</b><br>A: 2.50" (63.50)<br>B: 4.75" (120.65) | <b>2-Gang Commercial Device Plate Vertical Mount</b><br>Use with commercially available 2-gang flush plates. See page R-45 for plate options. For single service applications only.                                                           | Ivory<br>Gray | <b>HBL4747CVM2IV</b><br><b>HBL4747CVM2GY</b><br>A: 4.32" (109.86)<br>B: 4.75" (120.65) |
|                                                |                                                                                                                           |               |                                                                                     |                                                                                                                                                            |               |                                                                                        |
| 2-Gang Cover Plates (Include Mounting Bracket) | <b>2-Gang, One Opening for 1-Gang Comm. Device Plate, One Blank</b><br>Use with commercially available 1-gang flush plates. See page R-45 for plate options.                                               | Ivory<br>Gray | <b>HBL4747C1IV</b><br><b>HBL4747C1GY</b><br>A: 5.12" (130.18)<br>B: 4.75" (120.65)  | <b>2-Gang, One Opening for 2-Gang Commercial Device Plate</b><br>Use with commercially available 2-gang flush plates. See page R-45 for plate options.                                                                                        | Ivory<br>Gray | <b>HBL4747C2IV</b><br><b>HBL4747C2GY</b><br>A: 5.12" (130.18)<br>B: 4.75" (120.65)     |
|                                                |                                                                                                                           |               |                                                                                     |                                                                                                                                                            |               |                                                                                        |
|                                                | <b>Device Mounting Bracket</b><br>Mounting bracket for mounting Hubbell KP Plates, iSTATION Modules and Bezels. See pages R-45 and R-46 for datacom product selection.                                     | Ivory<br>Gray | <b>HBL4750IV</b><br><b>HBL4750GY</b><br>A: 5.25" (133.35)<br>B: 4.76" (120.90)      |                                                                                                                                                                                                                                               |               |                                                                                        |
| 2-Gang Cover Plates (Include Mounting Bracket) | <b>2-Gang Cover, Single Round Opening, One Blank</b><br>For single receptacle with face diameter of 1.38 in. to 1.39 in. (35.00 to 36.00).                                                                 | Ivory<br>Gray | <b>HBL4747AXIV</b><br><b>HBL4747AXGY</b><br>A: 5.43" (137.97)<br>B: 4.75" (120.65)  | <b>2-Gang, Single Round Opening, One Blank</b><br>For single receptacle with face diameter of 1.56 in. to 1.58 in. (39.62 to 40.13).                                                                                                          | Ivory<br>Gray | <b>HBL4747JXIV</b><br><b>HBL4747JXGY</b><br>A: 5.43" (137.97)<br>B: 4.75" (120.65)     |
|                                                |                                                                                                                         |               |                                                                                     |                                                                                                                                                          |               |                                                                                        |
|                                                | <b>2-Gang, One Duplex Opening, One Blank</b><br>For 15A and 20A duplex receptacles and duplex communication frames shown on page R-45.                                                                     | Ivory<br>Gray | <b>HBL4747BXIV</b><br><b>HBL4747BXGY</b><br>A: 5.43" (137.97)<br>B: 4.75" (120.65)  | <b>2-Gang, One Style Line® Opening, One Blank</b><br>For Style Line rectangular receptacles, GFCI and surge devices and rectangular communication frames shown on page R-45.                                                                  | Ivory<br>Gray | <b>HBL4747RXIV</b><br><b>HBL4747RXGY</b><br>A: 5.43" (137.97)<br>B: 4.75" (120.65)     |
|                                                |                                                                                                                         |               |                                                                                     |                                                                                                                                                          |               |                                                                                        |
|                                                | <b>2-Gang, Two Duplex Openings</b><br>For 15A and 20A duplex receptacles and duplex communication frames shown on page R-45.                                                                               | Ivory<br>Gray | <b>HBL4747BBIV</b><br><b>HBL4747BBGY</b><br>A: 5.43" (137.97)<br>B: 4.75" (120.65)  | <b>2-Gang, One Style Line® Opening, One Modular Furniture</b><br>For Style Line rectangular receptacles, GFCI, surge devices and rectangular communication frames shown on page R-45. Includes modular furniture with two keystone twistouts. | Ivory<br>Gray | <b>HBL4747RFIV</b><br><b>HBL4747RFGY</b><br>A: 5.43" (137.97)<br>B: 4.75" (120.65)     |
|                                                |                                                                                                                         |               |                                                                                     |                                                                                                                                                          |               |                                                                                        |
|                                                | <b>2-Gang, One Duplex Opening, One Modular Furniture</b><br>For 15A and 20A duplex receptacles and duplex communication frames shown on page R-45. Includes modular furniture with two keystone twistouts. | Ivory<br>Gray | <b>HBL4747BFIV</b><br><b>HBL4747BFGY</b><br>A: 5.43" (137.97)<br>B: 4.75" (120.65)  | <b>2-Gang, One Duplex Opening, One Style Line® Opening</b><br>For 15A and 20A duplex receptacles and Style Line rectangular receptacles, GFCI, surge devices and rectangular communication frames shown on page R-45.                         | Ivory<br>Gray | <b>HBL4747BRIV</b><br><b>HBL4747BRGY</b><br>A: 5.43" (137.97)<br>B: 4.75" (120.65)     |
|                                                |                                                                                                                         |               |                                                                                     |                                                                                                                                                          |               |                                                                                        |
|                                                | <b>2-Gang, One Duplex Opening, One Ortronics® Series II® Mini Adapter Bezel</b> For 15A and 20A duplex recept. and duplex communication plates. Includes Ortronics® Series II® Mini Adapter Bezel.         | Ivory<br>Gray | <b>HBL4747BSIV</b><br><b>HBL4747BSGY</b><br>A: 5.43" (137.97)<br>B: 4.75" (120.65)  | <b>2-Gang, One Duplex Opening, One Ortronics® TracJack® Mini Adapter Bezel</b> For 15A and 20A duplex recept. and duplex communication plates. Includes Ortronics® TracJack® Mini Adapter Bezel.                                              | Ivory<br>Gray | <b>HBL4747BTIV</b><br><b>HBL4747BTGY</b><br>A: 5.43" (137.97)<br>B: 4.75" (120.65)     |
|                                                |                                                                                                                         |               |                                                                                     |                                                                                                                                                          |               |                                                                                        |

Ortronics®, Series II® and TracJack® are registered trademarks of The Ortronics Company.

Dimensions in Inches (mm)

| 4-Gang Cover Plates (Include Mounting Bracket) | Description                                                                                                                                                                                                                                | Color         | Catalog Number                                                                            | Description                                                                                                                                                                                                                                                  | Color         | Catalog Number                                                                            |
|------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|-------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|-------------------------------------------------------------------------------------------|
|                                                | <b>4-Gang, Four Duplex Openings</b><br>For 15A and 20A duplex receptacles and duplex communication frames shown on page R-45.                                                                                                              | Ivory<br>Gray | <b>HBL47472BBBBIV</b><br><b>HBL47472BBBBGY</b><br>A: 10.22" (259.56)<br>B: 4.75" (120.65) | <b>4-Gang, Two Style Line® Openings, Two Blanks</b><br>For Style Line rectangular receptacles, GFCI, surge devices and rectangular communication frames shown on page R-45. Includes two blanks.                                                             | Ivory<br>Gray | <b>HBL47472RRXXIV</b><br><b>HBL47472RRXXGY</b><br>A: 10.22" (259.56)<br>B: 4.75" (120.65) |
|                                                |                                                                          |               |                                                                                           |                                                                                         |               |                                                                                           |
|                                                | <b>4-Gang, Two Duplex Openings, Two Style Line® Openings</b><br>For 15A and 20A duplex receptacles. Includes Style Line openings for rectangular receptacles, GFCI, surge devices and rectangular communication frames shown on page R-45. | Ivory<br>Gray | <b>HBL47472BBRRIV</b><br><b>HBL47472BBRRGY</b><br>A: 10.22" (259.56)<br>B: 4.75" (120.65) | <b>4-Gang, Two Duplex Openings, Two Ortronics® Series II® Mini Adapter Bezels</b><br>For 15A and 20A duplex receptacles and duplex communication plates. Includes two Ortronics® Series II® Mini Adapter Bezels.                                             | Ivory<br>Gray | <b>HBL47472BBSSIV</b><br><b>HBL47472BBSSGY</b><br>A: 10.22" (259.56)<br>B: 4.75" (120.65) |
|                                                |                                                                          |               |                                                                                           |      |               |                                                                                           |
|                                                | <b>4-Gang, Two Duplex Openings, Two Modular Furniture</b><br>For 15A and 20A duplex receptacles and duplex communication frames shown on page R-45. Includes two modular furniture with two keystone twistouts.                            | Ivory<br>Gray | <b>HBL47472BBFFIV</b><br><b>HBL47472BBFFGY</b><br>A: 10.22" (259.56)<br>B: 4.75" (120.65) | <b>4-Gang, Two Duplex Openings, Two Ortronics® TracJack® Mini Adapter Bezels</b><br>For 15A and 20A duplex receptacles and duplex communication plates. Includes two Ortronics® TracJack® Mini Adapter Bezels.                                               | Ivory<br>Gray | <b>HBL47472BBTTIV</b><br><b>HBL47472BBTTGY</b><br>A: 10.22" (259.56)<br>B: 4.75" (120.65) |
|                                                |                                                                        |               |                                                                                           |    |               |                                                                                           |
|                                                | <b>4-Gang, Two Duplex Openings, Two Blanks</b><br>For 15A and 20A duplex receptacles and duplex communication frames shown on page R-45. Includes two blanks.                                                                              | Ivory<br>Gray | <b>HBL47472BBXXIV</b><br><b>HBL47472BBXXGY</b><br>A: 10.22" (259.56)<br>B: 4.75" (120.65) |                                                                                                                                                                                                                                                              |               |                                                                                           |
|                                                |                                                                      |               |                                                                                           |                                                                                                                                                                                                                                                              |               |                                                                                           |

| Tools | Description                                                                         | Color         | Catalog Number                   | Description                                                                           | Catalog Number   |
|-------|-------------------------------------------------------------------------------------|---------------|----------------------------------|---------------------------------------------------------------------------------------|------------------|
|       | <b>Base Cutter</b><br>Cutter for cutting base of HBL4750 Raceway.                   |               | <b>HBL640B</b>                   | <b>Cover Cutter</b><br>Cutter for cutting cover of HBL4750 Raceway.                   | <b>HBL640C</b>   |
|       |  |               |                                  |  |                  |
|       | <b>Replacement Blade Cutter and Die Set</b><br>Base blade set.                      |               | <b>HBL640BDK</b>                 | <b>Replacement Blade Cutter and Die Set</b><br>Cover blade set.                       | <b>HBL640CDK</b> |
|       |  |               |                                  |  |                  |
|       | <b>Touch-Up Paint Pen</b>                                                           | Ivory<br>Gray | <b>HBLIWEP</b><br><b>HBLGWEP</b> |                                                                                       |                  |
|       |  |               |                                  |                                                                                       |                  |


Ortronics®, Series II® and TracJack® are registered trademarks of The Ortronics Company.

Dimensions in Inches (mm)




### Bracket and Devices

- HBL6750 Device Bracket Plate provides excellent solution for three channel power, data, voice, audio and video applications.
- For use with Hubbell KP plates and Hubbell iSTATION Modules and Bezels.
- Provides flush finish with overlap feature to hide potential miscuts.



### Maximum Capacity

- HBL6750 Series options include single channel (no divider), two channel (1/3, 2/3 divider) or three channel (1/3, 1/3, 1/3 divider).
- HBL6750 Series offers maximum capacity in a low profile raceway.
- HBL6750, two channel version, features industry leading capacity equivalent to a HBL4750 single channel profile with an additional channel.
- Low profile raceway provides a less conspicuous profile than competitive versions.
- Available in 10 ft. (3m) lengths.





### Unique Line of Fittings

- 1¼ in. (31.75mm) bend radius fittings meet TIA/EIA requirements.
- Integral bend radius offers a fixed solution that does not have to be field installed.
- Large cross sectional area provides for maximum cable capacity throughout entire system.
- Available external, internal, flat, tee and entrance end fittings.
- UL Listed, CSA Certified.
- Available in ivory or gray powder coat finish.





### Plates and Covers

- Wide variety of overlapping cover plates provide flexibility for power, data, voice, audio and video applications.
- Available in both three and six-gang options.
- Cover plates accept wide selection of Hubbell iSTATION Modules and Bezels.
- Cover plates help to conceal unsightly gaps caused by miscuts.
- Precut cover options allow for 12 in. (304.80mm), 18 in. (457.20mm), 24 in. (609.60mm) and 36 in. (914.40mm) "on-center" mounting.
- Open System architecture available.

| HBL6750 Series | Description                                                                                                                                                              | Color         | Catalog Number                                                                                              | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | Color                                                                        | Catalog Number                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
|----------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|-------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                |                                                                                                                                                                          |               |                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |                                                                              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
|                | <b>Single Channel Base</b><br>Packed 20 ft. (6.1m) per carton, 10 ft. (3m) lengths.<br><br>Assembled cover and base dimensions.<br>W: 6.75" (171.45)<br>H: 2.22" (56.39) | Ivory<br>Gray | <b>HBL6750B10IV</b><br><b>HBL6750B10GY</b><br>A: 120.00" (3048.00)<br>B: 6.75" (171.45)<br>C: 2.12" (53.85) | <b>5 Ft. Cover</b><br>Packed 20 ft. (6.1m) per carton, 5 ft. (1.5m) lengths.<br><br><b>31 In. Precut Cover*</b><br>For 36 in. (915.00) centers with HBL6747 and HBL6750 Plates.<br><br><b>19 In. Precut Cover*</b><br>For 24 in. (610.00) centers with HBL6747 and HBL6750 Plates.<br><br><b>13 In. Precut Cover*</b><br>For 18 in. (457.00) centers with HBL6747 and HBL6750 Plates.<br><br><b>7 In. Precut Cover*</b><br>For 12 in. (305.00) centers with HBL6747 and HBL6750 Plates. | Ivory<br>Gray<br><br>Ivory<br>Gray<br><br>Ivory<br>Gray<br><br>Ivory<br>Gray | <b>HBL6750CIV</b><br><b>HBL6750CGY</b><br>A: 60.00" (1,524.0)<br>B: 6.75" (171.45)<br><br><b>HBL6750C315IV</b><br><b>HBL6750C315GY</b><br>A: 31.50" (800.10)<br>B: 6.75" (171.45)<br><br><b>HBL6750C195IV</b><br><b>HBL6750C195GY</b><br>A: 19.50" (495.30)<br>B: 6.75" (171.45)<br><br><b>HBL6750C135IV</b><br><b>HBL6750C135GY</b><br>A: 13.50" (342.90)<br>B: 6.75" (171.45)<br><br><b>HBL6750C075IV</b><br><b>HBL6750C075GY</b><br>A: 7.50" (190.50)<br>B: 6.75" (171.45) |
|                |                                                                                         |               |                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                       |                                                                              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
|                |                                                                                                                                                                          |               |                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |                                                                              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
|                |                                                                                                                                                                          |               |                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |                                                                              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
|                |                                                                                                                                                                          |               |                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |                                                                              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |

Note: \*Packed 10 pieces per carton. Device centers vary based on cover selection. Consult factory for details.



| Fittings | Description                                                                                                                                                                                     | Color            | Catalog Number                                                | Description                                                                          | Color   | Catalog Number                                              |
|----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|---------------------------------------------------------------|--------------------------------------------------------------------------------------|---------|-------------------------------------------------------------|
|          |                                                                                                                                                                                                 |                  |                                                               |                                                                                      |         |                                                             |
|          | <b>Divider</b><br>Divides HBL6750 Raceway into two or three channels. Packed 50 ft. (15.24m) per carton, 5 ft. (1.5m) lengths. HBL6751DAGY Divider Clips are required to hold divider in place. | Painted<br>Steel | <b>HBL6750DAGY</b><br>A: 60.00" (1524.00)<br>B: 2.03" (51.56) | <b>Wire Clip (Plated)</b><br>For holding conductors in place.                        | Steel** | <b>HBL6750WCGY</b><br>A: 6.61" (167.80)<br>B: 2.09" (53.05) |
|          |                                                                                                              |                  |                                                               |  |         |                                                             |
|          | <b>Divider Clip (Plated)</b><br>Required for holding HBL6750DAGY in place. Use one every 2.5 ft. (.762m).                                                                                       | Steel**          | <b>HBL6751DAGY</b><br>A: 6.60" (167.67)<br>B: 1.97" (50.10)   | <b>Coupling (Plated)</b><br>For joining lengths of HBL6750 Raceway. Sold in pairs.   | Steel** | <b>HBL6751A</b><br>A: 2.00" (50.71)<br>B: .42" (10.59)      |
|          |                                                                                                              |                  |                                                               |  |         |                                                             |
|          | <b>Internal Corner Coupling (Plated)</b><br>Concealed fitting for making an internal corner while continuing original run in a straight line.                                                   | Steel**          | <b>HBL6717TCAGY</b><br>A: 6.56" (166.62)<br>B: 1.94" (49.28)  |                                                                                      |         |                                                             |
|          |                                                                                                              |                  |                                                               |                                                                                      |         |                                                             |




Note: \*\*Galvanized Steel.

| Elbows | Description                                                                                                                          | Color         | Catalog Number                                                                                                                                       | Description                                                                                               | Color         | Catalog Number                                                                                                                                 |
|--------|--------------------------------------------------------------------------------------------------------------------------------------|---------------|------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------|---------------|------------------------------------------------------------------------------------------------------------------------------------------------|
|        | <b>Internal Elbow, Divided</b><br>For inside surface at right angles.<br>Full capacity 1 1/4 in. bend radius internal elbow.         | Ivory<br>Gray | <b>HBL6717DFOIV*</b><br><b>HBL6717DFOGY*</b><br>A: 4.74" (120.47)<br>B: 6.75" (171.45)                                                               | <b>Internal Elbow, Undivided</b><br>For inside surface at right angles.                                   | Ivory<br>Gray | <b>HBL6717IV*</b><br><b>HBL6717GY*</b><br>A: 4.74" (120.47)<br>B: 6.75" (171.45)                                                               |
|        | <b>External Elbow, Divided</b><br>For right angle turns around external corners. Full capacity 1 1/4 in. bend radius external elbow. | Ivory<br>Gray | <b>HBL6718DFOIV*</b><br><b>HBL6718DFOGY*</b><br>A: 5.83" (148.21)<br>B: 6.75" (171.45)                                                               | <b>External Elbow, Undivided</b><br>For right angle turns around external corners.                        | Ivory<br>Gray | <b>HBL6718IV*</b><br><b>HBL6718GY*</b><br>A: 5.83" (148.21)<br>B: 6.75" (171.45)                                                               |
|        | <b>Flat Elbow, Divided</b><br>For right angle turns on same surface.<br>Full capacity 1 1/4 in. bend radius flat elbow.              | Ivory<br>Gray | <b>HBL6711DFOIV*</b><br><b>HBL6711DFOGY*</b><br>A: 9.23" (234.45)<br>B: 6.75" (171.45)<br>C: 2.14" (54.23)<br>D: 9.83" (249.69)<br>E: 6.75" (171.45) | <b>Flat Elbow, Undivided</b><br>For right angle turns on same surface.                                    | Ivory<br>Gray | <b>HBL6711IV*</b><br><b>HBL6711GY*</b><br>A: 9.23" (234.45)<br>B: 6.75" (171.45)<br>C: 2.14" (54.23)<br>D: 9.83" (249.69)<br>E: 6.75" (171.45) |
|        | <b>Internal or External 45° Elbow</b><br>For making internal or external turns in a run of HBL6750 Raceway.                          | Ivory<br>Gray | <b>HBL6712TXIV</b><br><b>HBL6712TXGY</b><br>A: 6.53" (165.93)<br>B: 6.56" (166.62)                                                                   | <b>Inverted Internal Elbow</b><br>For connecting a vertical run of HBL6750 Raceway with a horizontal run. | Ivory<br>Gray | <b>HBL6717NIV</b><br><b>HBL6717NGY</b><br>A: 6.56" (166.62)<br>B: 5.13" (130.30)                                                               |
|        |                                                                                                                                      |               |                                                                                                                                                      |                                                                                                           |               |                                                                                                                                                |
|        |                                                                                                                                      |               |                                                                                                                                                      |                                                                                                           |               |                                                                                                                                                |
|        |                                                                                                                                      |               |                                                                                                                                                      |                                                                                                           |               |                                                                                                                                                |
| Tees   | Description                                                                                                                          | Color         | Catalog Number                                                                                                                                       | Description                                                                                               | Color         | Catalog Number                                                                                                                                 |
|        | <b>Tee Fitting, Divided</b><br>For branches at right angles.<br>Full capacity 1 1/4 in. bend radius tee fitting.                     | Ivory<br>Gray | <b>HBL6715DFOIV*</b><br><b>HBL6715DFOGY*</b><br>A: 8.75" (222.25)<br>B: 6.63" (168.40)<br>C: 3.56" (90.48)<br>D: 7.92" (201.07)<br>E: 6.75" (171.45) | <b>Tee Fitting, Undivided</b><br>For branches at right angles.                                            | Ivory<br>Gray | <b>HBL6715IV*</b><br><b>HBL6715GY*</b><br>A: 8.75" (222.25)<br>B: 6.63" (168.40)<br>C: 3.56" (90.48)<br>D: 7.92" (201.07)<br>E: 6.75" (171.45) |

Note: \*HBL6751A couplings included.








Dimensions in Inches (mm)

| End Fittings | Description                                                                                                                                                                                                                                                                                  | Color         | Catalog Number                                                                                              | Description                                                                                                                                                                 | Color         | Catalog Number                                                                                                         |
|--------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|-------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|------------------------------------------------------------------------------------------------------------------------|
|              | <b>Entrance End Fitting, Divided</b><br>For connecting HBL6750 Raceway with rigid or flexible conduit. Concentric ¼ in., 1 in. and 1½ in. trade size KOs on back and end. Full capacity 1½ in. bend radius entrance end fitting. Includes ¼ in., 1 in. and 1½ in. KO and removable dividers. | Ivory<br>Gray | <b>HBL6710DFOIV*</b><br><b>HBL6710DFOGY*</b><br>A: 6.75" (171.45)<br>B: 6.75" (171.45)<br>C: 3.18" (180.71) | <b>Entrance End Fitting, Undivided</b><br>For connecting HBL6750 Raceway with rigid or flexible conduit. Concentric ¼ in., 1 in. and 1½ in. trade size KOs on back and end. | Ivory<br>Gray | <b>HBL6710IV*</b><br><b>HBL6710GY*</b><br>A: 6.75" (171.45)<br>B: 6.75" (171.45)<br>C: 3.18" (180.71)                  |
|              |                                                                                                                                                                                                             |               |                                                                                                             |                                                                                           |               |                                                                                                                        |
|              | <b>Blank End Fitting</b><br>For closing open end of HBL6750 Raceway. Has three ½ in. trade size KOs.                                                                                                                                                                                         | Ivory<br>Gray | <b>HBL6710BIV</b><br><b>HBL6710BGY</b><br>A: 6.56" (166.62)<br>B: 1.98" (50.41)<br>C: 1.33" (33.90)         | <b>Panel Connector</b><br>To connect HBL6750 Raceway with surface type panel boxes.                                                                                         | Ivory<br>Gray | <b>HBL6786IV</b><br><b>HBL6786GY</b><br>A: 7.51" (190.86)<br>B: 2.00" (50.83)<br>C: 7.89" (200.37)<br>D: 2.38" (60.34) |
|              |                                                                                                                                                                                                             |               |                                                                                                             |                                                                                           |               |                                                                                                                        |

| Fittings | Description                                                                                                    | Color         | Catalog Number                                                                                                               | Description                                                                          | Color         | Catalog Number                                                                                       |
|----------|----------------------------------------------------------------------------------------------------------------|---------------|------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------|------------------------------------------------------------------------------------------------------|
|          | <b>Transition Fitting</b><br>For transitioning from Wiremold® 6000 Raceway to Hubbell HBL6750 Raceway.         | Ivory<br>Gray | <b>HBL6750TFIV</b><br><b>HBL6750TFGY</b><br>A: 4.35" (110.42)<br>B: 6.96" (176.87)                                           | <b>Wall Box Connector</b><br>For back feeding HBL6750 Raceway.                       | Ivory<br>Gray | <b>HBL6714AIV</b><br><b>HBL6714AGY</b><br>A: 6.75" (171.45)<br>B: 2.14" (54.28)<br>C: 9.90" (251.46) |
|          |                              |               |                                                                                                                              |   |               |                                                                                                      |
|          | <b>Take-Off Connector (HBL6750-HBL4750)</b><br>For 90° tee connection of HBL4750 Raceway from HBL6750 Raceway. | Ivory<br>Gray | <b>HBL6774AIV</b><br><b>HBL6774AGY</b><br>A: 14.36" (364.76)<br>B: 6.75" (171.45)<br>C: 11.47" (291.29)<br>D: 6.72" (170.69) | <b>3-Gang Tap-Off Fitting</b><br>Has six concentric ½ in. and ¾ in. trade size KOs.  | Ivory<br>Gray | <b>HBL6746HHHIV</b><br><b>HBL6746HHHGY</b><br>A: 4.35" (110.42)<br>B: 6.96" (176.87)                 |
|          |                             |               |                                                                                                                              |  |               |                                                                                                      |
|          | <b>Connection Cover</b><br>For covering potential openings where two covers come together.                     | Ivory<br>Gray | <b>HBL6756AIV</b><br><b>HBL6756AGY</b><br>A: 6.75" (171.45)<br>B: .59" (14.89)                                               |                                                                                      |               |                                                                                                      |
|          |                             |               |                                                                                                                              |                                                                                      |               |                                                                                                      |

Note: \*HBL4751AC couplings included.

| Device Plates & Mounting Bracket               | Description                                                                                                                                                                                                                                                               | Color         | Catalog Number                                                                       | Description                                                                                                                                                                                                                                        | Color         | Catalog Number                                                                       |
|------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|--------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|--------------------------------------------------------------------------------------|
|                                                |                                                                                                                                                                                                                                                                           |               |                                                                                      |                                                                                                                                                                                                                                                    |               |                                                                                      |
|                                                | <b>3-Gang, One Opening for 1-Gang Commercial Device Plate, Two Blanks</b><br>Use with commercially available 1-gang flush plates. See page R-45 for plate options.                                                                                                        | Ivory<br>Gray | <b>HBL6747C1IV</b><br><b>HBL6747C1GY</b><br>A: 5.43" (137.97)<br>B: 6.75" (171.45)   | <b>3-Gang, One Opening for 2-Gang Commercial Device Plate, One Blank</b><br>Use with commercially available 2-gang flush plates. See page R-45 for plate options.                                                                                  | Ivory<br>Gray | <b>HBL6747C2IV</b><br><b>HBL6747C2GY</b><br>A: 5.43" (137.97)<br>B: 6.75" (171.45)   |
|                                                | <b>Device Mounting Bracket</b><br>Mounting bracket for mounting Hubbell KP Plates, iSTATION Modules and Bezels. See pages R-45 and R-46 for datacom product selection.                                                                                                    | Ivory<br>Gray | <b>HBL6750IV</b><br><b>HBL6750GY</b><br>A: 5.25" (133.35)<br>B: 6.75" (171.45)       |                                                                                                                                                                                                                                                    |               |                                                                                      |
| 3-Gang Cover Plates (Include Mounting Bracket) | <b>3-Gang, One Duplex Opening, Two Blanks</b><br>For 15A and 20A duplex receptacles and duplex communication plates.                                                                                                                                                      | Ivory<br>Gray | <b>HBL6747BXXIV</b><br><b>HBL6747BXXGY</b><br>A: 5.43" (137.97)<br>B: 6.75" (171.45) | <b>3-Gang, One Single Round Opening, Two Blanks</b><br>For single receptacle with face diameter of 1.38 in. to 1.39 in. (35.05 to 35.31).                                                                                                          | Ivory<br>Gray | <b>HBL6747AXXIV</b><br><b>HBL6747AXXGY</b><br>A: 5.43" (137.97)<br>B: 6.75" (171.45) |
|                                                | <b>3-Gang, Three Duplex Openings</b><br>For 15A and 20A duplex receptacles and duplex communication plates.                                                                                                                                                               | Ivory<br>Gray | <b>HBL6747BBBIV</b><br><b>HBL6747BBBGY</b><br>A: 5.43" (137.97)<br>B: 6.75" (171.45) | <b>3-Gang, One Single Round Opening, Two Blanks</b><br>For single receptacle with face diameter of 1.56 in. to 1.58 in. (39.62 to 40.13).                                                                                                          | Ivory<br>Gray | <b>HBL6747JXXIV</b><br><b>HBL6747JXXGY</b><br>A: 5.43" (137.97)<br>B: 6.75" (171.45) |
|                                                | <b>3-Gang, One Duplex Opening, Two Style Line® Openings</b><br>For 15A and 20A duplex receptacles and duplex communication plates. Includes Style Line openings for rectangular receptacles, GFCI, surge devices and rectangular communication frames shown on page R-45. | Ivory<br>Gray | <b>HBL6747BRRIV</b><br><b>HBL6747BRRGY</b><br>A: 5.43" (137.97)<br>B: 6.75" (171.45) | <b>3-Gang, One Style Line® Opening, Two Blanks</b><br>For one Style Line rectangular receptacle, GFCI, surge device or rectangular communication device.                                                                                           | Ivory<br>Gray | <b>HBL6747RXXIV</b><br><b>HBL6747RXXGY</b><br>A: 5.43" (137.97)<br>B: 6.75" (171.45) |
|                                                | <b>3-Gang, Two Duplex Openings, One Modular Furniture</b><br>For 15A and 20A duplex receptacles and duplex communication frames shown on page R-45. Includes modular furniture with two keystone twistouts.                                                               | Ivory<br>Gray | <b>HBL6747BBFIV</b><br><b>HBL6747BBFGY</b><br>A: 5.43" (137.97)<br>B: 6.75" (171.45) | <b>3-Gang, Two Style Line® Openings, One Modular Furniture</b><br>For two Style Line rectangular receptacles, GFCI, surge devices and rectangular communication frames shown on page R-45. Includes modular furniture with two keystone twistouts. | Ivory<br>Gray | <b>HBL6747RRFIV</b><br><b>HBL6747RRFGY</b><br>A: 5.43" (137.97)<br>B: 6.75" (171.45) |
|                                                | <b>3-Gang, Two Duplex Openings, One Ortronics® Series II® Mini Adapter Bezel</b><br>For two 15A and 20A duplex receptacles and duplex communication frames shown on page R-45. Includes Ortronics® Series II® Mini Adapter Bezel.                                         | Ivory<br>Gray | <b>HBL6747BBSIV</b><br><b>HBL6747BBSGY</b><br>A: 5.43" (137.97)<br>B: 6.75" (171.45) | <b>3-Gang, Two Duplex Openings, One Ortronics® TracJack® Mini Adapter Bezel</b><br>For 15A and 20A duplex receptacles and duplex communication frames shown on page R-45. Includes Ortronics® TracJack® Mini Adapter Bezel.                        | Ivory<br>Gray | <b>HBL6747BBTIV</b><br><b>HBL6747BBTGY</b><br>A: 5.43" (137.97)<br>B: 6.75" (171.45) |
|                                                |                                                                                                                                                                                                                                                                           |               |                                                                                      |                                                                                                                                                                                                                                                    |               |                                                                                      |

| 6-Gang Cover Plates (Include Mounting Bracket) | Description                                                                                                                                                                                                                                                                  | Color         | Catalog Number                                                                                | Description                                                                                                                                                                                                                                                   | Color         | Catalog Number                                                                                |
|------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|-----------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|-----------------------------------------------------------------------------------------------|
|                                                | <b>6-Gang, Six Duplex Openings</b><br>For 15A and 20A duplex receptacles and duplex communication frames shown on page R-45.                                                                                                                                                 | Ivory<br>Gray | <b>HBL67473BBBBBBIV</b><br><b>HBL67473BBBBBBGY</b><br>A: 10.22" (259.56)<br>B: 6.75" (171.45) | <b>6-Gang, Four Style Line® Openings, Two Blanks</b><br>For four Style Line rectangular receptacles, GFCI, surge devices and rectangular communication frames shown on page R-45.                                                                             | Ivory<br>Gray | <b>HBL67473RRRRXXIV</b><br><b>HBL67473RRRRXXGY</b><br>A: 10.22" (259.56)<br>B: 6.75" (171.45) |
|                                                |                                                                                                            |               |                                                                                               |                                                                                          |               |                                                                                               |
|                                                | <b>6-Gang, Two Duplex Openings, Four Style Line® Openings</b><br>For 15A and 20A duplex receptacles and duplex communication frames shown on page R-45. Includes Style Line openings for rectangular receptacles, GFCI, surge devices and rectangular communication devices. | Ivory<br>Gray | <b>HBL67473BBRRRRIV</b><br><b>HBL67473BBRRRRGY</b><br>A: 10.22" (259.56)<br>B: 6.75" (171.45) | <b>6-Gang, Four Duplex Openings, Two Ortronics® Series II® Mini Adapter Bezels</b><br>For 15A and 20A duplex receptacles and duplex communication frames shown on page R-45. Includes two Ortronics® Series II® Mini Adapter Bezels.                          | Ivory<br>Gray | <b>HBL67473BBBBSSIV</b><br><b>HBL67473BBBBSSGY</b><br>A: 10.22" (259.56)<br>B: 6.75" (171.45) |
|                                                |                                                                                                            |               |                                                                                               |       |               |                                                                                               |
|                                                | <b>6-Gang, Four Duplex Openings, Two Modular Furniture</b><br>For 15A and 20A duplex receptacles and duplex communication frames shown on page R-45. Includes two modular furniture with two keystone twistouts.                                                             | Ivory<br>Gray | <b>HBL67473BBBBFFIV</b><br><b>HBL67473BBBBFFGY</b><br>A: 10.22" (259.56)<br>B: 6.75" (171.45) | <b>6-Gang, Four Duplex Openings, Two Ortronics® TracJack® Mini Adapter Bezels</b><br>For 15A and 20A duplex receptacles and duplex communication frames shown on page R-45. Includes two Ortronics® TracJack® Mini Adapter Bezels.                            | Ivory<br>Gray | <b>HBL67473BBBBTTIV</b><br><b>HBL67473BBBBTTGY</b><br>A: 10.22" (259.56)<br>B: 6.75" (171.45) |
|                                                |                                                                                                          |               |                                                                                               |    |               |                                                                                               |
|                                                | <b>6-Gang, Four Duplex Openings, Two Blanks</b><br>For four 15A and 20A duplex receptacles and duplex communication frames shown on page R-45.                                                                                                                               | Ivory<br>Gray | <b>HBL67473BBBBXXIV</b><br><b>HBL67473BBBBXXGY</b><br>A: 10.22" (259.56)<br>B: 6.75" (171.45) |                                                                                                                                                                                                                                                               |               |                                                                                               |
|                                                |                                                                                                        |               |                                                                                               |                                                                                                                                                                                                                                                               |               |                                                                                               |

| Tools | Description                                                                         | Color         | Catalog Number                   | Description                                                                           | Catalog Number   |
|-------|-------------------------------------------------------------------------------------|---------------|----------------------------------|---------------------------------------------------------------------------------------|------------------|
|       | <b>Base Cutter</b><br>Cutter for cutting base of HBL6750 Raceway.                   |               | <b>HBL660B</b>                   | <b>Cover Cutter</b><br>Cutter for cutting cover of HBL6750 Raceway.                   | <b>HBL660C</b>   |
|       |  |               |                                  |  |                  |
|       | <b>Replacement Blade Cutter and Die Set</b><br>Base blade set.                      |               | <b>HBL660BDK</b>                 | <b>Replacement Blade Cutter and Die Set</b><br>Cover blade set.                       | <b>HBL660CDK</b> |
|       |  |               |                                  |  |                  |
|       | <b>Touch-Up Paint Pen</b>                                                           | Ivory<br>Gray | <b>HBLIWEP</b><br><b>HBLGWEP</b> |                                                                                       |                  |
|       |  |               |                                  |                                                                                       |                  |

Ortronics®, Series II® and TracJack® are registered trademarks of The Ortronics Company.

Dimensions in Inches (mm)



### Single Channel

- Single channel aluminum raceway.
- Satin anodized finish.
- Resists oxidation, corrosion and fading.
- Can be installed as recessed or surface mounted.
- UL Listed and CSA Certified.



### Wide Selection of Fittings

- Elbows (external, internal, flat) and tee fitting available to accommodate all types of applications.
- HBLALU2001 Coupling included with elbows and tee fitting.



### Aluminum Boxes

- Both in-line and standard boxes available.
- Hubbell Handi-Screw® eliminates difficult to install long screws for easier installation.
- Rounded corners eliminate sharp edges.
- One seam construction provides “clean” look.
- Box design allows standard wallplates to be mounted flush with virtually no perimeter profile exposed.
- Full line of metal wallplates available. See section N for selection.



### Aluminum PlugTrak® Featuring Exclusive Receptacle Design

- Satin anodized scratch resistant finish.
- Multiple spacing configurations.
- Hubbell designed and manufactured single receptacle.
- Insulation displacement wiring provides superior wire retention.
- Mates with HBLALU2000 Aluminum Raceway.
- Available in 3 ft. (0.9m), 5 ft. (1.5m) and 6 ft. (1.8m) lengths.
- Tamper-Resistant versions available.




# Aluminum Raceway

## HBLALU2000 Series

Aluminum Raceway, Device Boxes, Elbows and Tees





| HBLALU2000 Series | Description                                                                                         | Material                                                                          | Catalog Number                                              | Description                                                                                    | Material          | Catalog Number                          |
|-------------------|-----------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------|------------------------------------------------------------------------------------------------|-------------------|-----------------------------------------|
|                   | <b>5 Ft. Base</b><br>Satin anodized finish. Packed 60 ft. (18.3m) per carton, 5 ft. (1.5m) lengths. | Anodized Aluminum                                                                 | <b>HBLALU2000B5</b><br>A: .82" (21.00)<br>B: 1.84" (46.74)  | <b>Cover</b><br>Satin anodized finish. Packed 60 ft. (18.3m) per carton, 5 ft. (1.5m) lengths. | Anodized Aluminum | <b>HBLALU2000C5</b><br>A: 1.84" (46.74) |
|                   | <b>10 Ft. Base</b><br>Satin anodized finish. Packed 60 ft. (18.3m) per carton, 10 ft. (3m) lengths. | Anodized Aluminum                                                                 | <b>HBLALU2000B10</b><br>A: .82" (21.00)<br>B: 1.84" (46.74) |              |                   |                                         |
|                   | Assembled cover and base dimensions.<br>W: 1.84" (46.74)<br>H: .91" (23.11)                         |  |                                                             |                                                                                                |                   |                                         |



| Standard | Description                                                 | Material          | 1-Gang                                                                         | 2-Gang                                                                           | Description                                                                                                                                                            | Material          | Round Box                                                  |
|----------|-------------------------------------------------------------|-------------------|--------------------------------------------------------------------------------|----------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|------------------------------------------------------------|
|          | <b>Device Box</b><br>For standard switches and receptacles. | Anodized Aluminum | <b>HBLALU2047</b><br>A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 1.38" (35.05) | <b>HBLALU20472</b><br>A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 1.38" (35.05) | <b>Fixture Box with Solid Base</b><br>To hang fixtures. Cover takes any device with mounting screw centers of 2.75 in. (69.85), 3.5 in. (89.00) and 4.06 in. (103.00). | Anodized Aluminum | <b>HBLALU2038</b><br>A: 1.38" (35.05)<br>B: 4.93" (125.22) |
| Deep     | <b>Device Box</b><br>For deep switches and receptacles.     | Anodized Aluminum | <b>HBLALU2044</b><br>A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 2.25" (57.15) | <b>HBLALU20442</b><br>A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 2.75" (69.85) |                                                                                                                                                                        |                   |                                                            |



Base Trade Size KOs


1 - 1/2", 3/4" Concentric 1 - 1/2"  
1 - Rectangular 1 - Rectangular




| Elbows and Tees | Description                                                                         | Material          | Catalog Number                                             | Description                                                                          | Material          | Catalog Number                                              |
|-----------------|-------------------------------------------------------------------------------------|-------------------|------------------------------------------------------------|--------------------------------------------------------------------------------------|-------------------|-------------------------------------------------------------|
|                 | <b>Internal Elbow</b><br>For making a 90° internal turn in a raceway run.           | Anodized Aluminum | <b>HBLALU2017*</b><br>A: 3.00" (76.20)<br>B: 3.00" (76.20) | <b>External Elbow</b><br>For making a 90° external turn in a raceway run.            | Anodized Aluminum | <b>HBLALU2018*</b><br>A: 2.91" (74.04)<br>B: 2.91" (74.04)  |
|                 |  |                   |                                                            |  |                   |                                                             |
|                 | <b>Flat Elbow</b><br>For making a 90° flat turn in a raceway run.                   | Anodized Aluminum | <b>HBLALU2011*</b><br>A: 3.00" (76.20)<br>B: 3.00" (76.20) | <b>Tee Fitting</b><br>For branch connections of right angles.                        | Anodized Aluminum | <b>HBLALU2015*</b><br>A: 4.00" (101.60)<br>B: 3.40" (86.36) |
|                 |  |                   |                                                            |  |                   |                                                             |

Note: \*HBLALU2001 couplings included.

Dimensions in Inches (mm)

| End Fittings | Description                                                                       | Material                | Catalog Number                                                                | Description                                                                         | Material          | Catalog Number                                            |
|--------------|-----------------------------------------------------------------------------------|-------------------------|-------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------|-----------------------------------------------------------|
|              | <b>Entrance End Fitting</b><br>½ in. NPT steel fitting.                           | Anodized Aluminum Plate | <b>HBLALU2010A</b><br>A: 1.84" (47.74)<br>B: .91" (23.11)<br>C: 1.51" (38.35) | <b>Blank End Fitting</b><br>For closing end of raceway.                             | Anodized Aluminum | <b>HBLALU2010B</b><br>A: 1.84" (46.74)<br>B: .91" (23.11) |
|              |  |                         |                                                                               |  |                   |                                                           |

| Fittings | Description                                                                                                      | Material          | Catalog Number                                             | Description                                                                         | Material          | Catalog Number                                            |
|----------|------------------------------------------------------------------------------------------------------------------|-------------------|------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------|-----------------------------------------------------------|
|          | <b>Cover Clip</b><br>Use to cover potential openings where two pieces of HBLALU2000 Raceway cover come together. | Stainless Steel   | <b>HBLALU2006</b><br>A: 1.00" (25.40)                      | <b>Wire Clip</b><br>For holding conductors in place.                                | Anodized Aluminum | <b>HBLALU2000WC</b><br>A: .44" (11.20)                    |
|          |                                 |                   |                                                            |  |                   |                                                           |
|          |                                 |                   |                                                            |  |                   |                                                           |
|          | <b>Flush Plate Adaptor</b><br>For feeding HBL2000 Raceway from an existing wall outlet. Locknut included.        | Anodized Aluminum | <b>HBLALU2051H</b><br>A: 4.50" (114.3)<br>B: 4.50" (114.3) | <b>Coupling (Pair)</b><br>For joining lengths of HBLALU2000 Raceway.                | Aluminum          | <b>HBLALU2001</b><br>A: 1.67" (42.42)<br>B: 1.67" (42.42) |
|          |                                 |                   |                                                            |   |                   |                                                           |
|          |                                 |                   |                                                            |  |                   |                                                           |

| Devices and In-Line Fittings | Description                                                                                                                                                                         | Material                         | Catalog Number                                                                                                             | Description                                                                                                                                                                                                          | Material          | Catalog Number                                              |
|------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------|----------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|-------------------------------------------------------------|
|                              | <b>In-Line Receptacle Fitting</b><br>Use this fitting with single receptacle below.                                                                                                 | Anodized Aluminum                | <b>HBLALU2043*</b><br>A: 1.84" (46.74)<br>B: 6.00" (152.40)                                                                | <b>In-Line Switch Fitting</b><br>(Switch sold separately).                                                                                                                                                           | Anodized Aluminum | <b>HBLALU2040A</b><br>A: 4.12" (104.65)<br>B: 1.84" (46.74) |
|                              |                                                                                                  |                                  |                                                                                                                            |                                                                                                                                 |                   |                                                             |
|                              | <b>Single Receptacle</b><br>15A 125V<br>15A 125V, Isolated Ground<br>20A 125V<br>20A 125V, Isolated Ground<br><br>#12 AWG THHN stranded copper wires with 21 in. leads on each end. | Gray<br>Orange<br>Gray<br>Orange | <b>PT1RCGY</b><br><b>PT1RCIG</b><br><b>PT1RGY</b><br><b>PT1RIG</b><br>A: 2.00" (50.7)<br>B: 1.20" (30.4)<br>C: .87" (22.2) | <b>Ground Adapter (Plated)</b><br>For connection of equipment grounding conductor to provide an additional ground to raceway. Screws included.                                                                       | Steel**           | <b>HBLALU2009</b><br>A: 2.35" (59.8)<br>B: 1.18" (30.0)     |
|                              |                                                                                                  |                                  |                                                                                                                            |                                                                                                                                 |                   |                                                             |
|                              |                                                                                                                                                                                     |                                  |                                                                                                                            | <b>Supporting Clip</b><br>For mounting lengths of HBLALU2000 Raceway at any point. Mount with #6 flat head fastener. Has set screw for locking to raceway. Raceway must be screwed to the wall for secure fastening. | Stainless Steel   | <b>HBLALU2003</b><br>A: 2.00" (50.80)                       |
|                              |                                                                                                                                                                                     |                                  |                                                                                                                            |                                                                                                                                 |                   |                                                             |

Note: \*HBLALU2001 couplings included.  
 \*\*Galvanized Steel.

Dimensions in Inches (mm)

Available in Standard, Isolated Ground (IG) and Tamper-Resistant (TR) versions.

 Tamper-Resistant



|        | Amp | Circuits  | # Single Recept. | Receptacle Spacing (in.) | Catalog Number                                                                                           |
|--------|-----|-----------|------------------|--------------------------|----------------------------------------------------------------------------------------------------------|
| 3 Foot | 15  | Single    | 6                | 6                        | <b>HBLALU20GB306</b>                                                                                     |
|        | 15  | IG/Single | 6                | 6                        | <b>HBLALU20IG306</b>                                                                                     |
|        | 15  | TR/Single | 6                | 6                        | <b>HBLALU20GB306TR</b>  |
|        | 20  | Single    | 6                | 6                        | <b>HBLALU24GB306</b>                                                                                     |
|        | 20  | IG/Single | 6                | 6                        | <b>HBLALU24IG306</b>                                                                                     |
|        | 20  | TR/Single | 6                | 6                        | <b>HBLALU24GB306TR</b>  |
| 5 Foot | 15  | Single    | 10               | 6                        | <b>HBLALU20GB506</b>                                                                                     |
|        | 15  | Single    | 5                | 12                       | <b>HBLALU20GB512</b>                                                                                     |
|        | 15  | IG/Single | 10               | 6                        | <b>HBLALU20IG506</b>                                                                                     |
|        | 15  | TR/Single | 5                | 12                       | <b>HBLALU20GB512TR</b>  |
|        | 20  | Single    | 10               | 6                        | <b>HBLALU24GB506</b>                                                                                     |
|        | 20  | Single    | 5                | 12                       | <b>HBLALU24GB512</b>                                                                                     |
|        | 20  | IG/Single | 10               | 6                        | <b>HBLALU24IG506</b>                                                                                     |
|        | 20  | TR/Single | 5                | 12                       | <b>HBLALU24GB512TR</b>  |
| 6 Foot | 15  | Single    | 12               | 6                        | <b>HBLALU20GB606</b>                                                                                     |
|        | 15  | Single    | 6                | 12                       | <b>HBLALU20GB612</b>                                                                                     |
|        | 15  | Single    | 4                | 18                       | <b>HBLALU20GB618</b>                                                                                     |
|        | 15  | Two       | 12               | 6                        | <b>HBLALU20GBA606</b>                                                                                    |
|        | 15  | Two       | 6                | 12                       | <b>HBLALU20GBA612</b>                                                                                    |
|        | 15  | Two       | 4                | 18                       | <b>HBLALU20GBA618</b>                                                                                    |
|        | 15  | IG/Single | 12               | 6                        | <b>HBLALU20IG606</b>                                                                                     |
|        | 20  | Single    | 12               | 6                        | <b>HBLALU24GB606</b>                                                                                     |
|        | 20  | Single    | 6                | 12                       | <b>HBLALU24GB612</b>                                                                                     |
|        | 20  | Single    | 4                | 18                       | <b>HBLALU24GB618</b>                                                                                     |
|        | 20  | Two       | 12               | 6                        | <b>HBLALU24GBA606</b>                                                                                    |
|        | 20  | Two       | 6                | 12                       | <b>HBLALU24GBA612</b>                                                                                    |
|        | 20  | Two       | 4                | 18                       | <b>HBLALU24GBA618</b>                                                                                    |
|        | 20  | IG/Single | 12               | 6                        | <b>HBLALU24IG606</b>                                                                                     |

Note: IG = Isolated Ground and TR = Tamper-Resistant.  
 Hubbell Aluminum PlugTrak is supplied with two HBLALU2010B blank end fittings and one HBLALU2001 coupling.

|                 | Description                                                                                                    | Catalog Number     |
|-----------------|----------------------------------------------------------------------------------------------------------------|--------------------|
| Device Boxes    | Standard 1-Gang Device Box  | <b>HBLALU2047</b>  |
|                 | Deep 1-Gang Device Box      | <b>HBLALU2044</b>  |
|                 | Standard 2-Gang Device Box  | <b>HBLALU20472</b> |
|                 | Deep 2-Gang Device Box      | <b>HBLALU20442</b> |
|                 | Round Box                   | <b>HBLALU2038</b>  |
|                 |                                                                                                                |                    |
| Elbows and Tees | External Elbow              | <b>HBLALU2018</b>  |
|                 | Internal Elbow              | <b>HBLALU2017</b>  |
|                 | Flat Elbow                 | <b>HBLALU2011</b>  |
|                 | Tee                       | <b>HBLALU2015</b>  |
| Fittings        | Cover Clip                | <b>HBLALU2006</b>  |
|                 | Supporting Clip           | <b>HBLALU2003</b>  |
|                 | Coupling                  | <b>HBLALU2001</b>  |
|                 | Entrance End Fitting      | <b>HBLALU2010A</b> |
|                 | In-Line Switch Fitting    | <b>HBLALU2040A</b> |
|                 | Blank End Fitting         | <b>HBLALU2010B</b> |

Note: See pages R-34 and R-35 for additional information.



### Single and Two Channel

- Single and two channel aluminum raceways.
- Satin anodized finish.
- Resists oxidation, corrosion and fading.
- Can be installed as recessed or surface mounted.
- UL Listed and CSA Certified.



### Wide Selection of Fittings

- External, internal, flat and tee fittings available to accommodate all types of applications.
- Available in both single and two channel versions.



### Split Covers


- Single and two channel raceways utilize common cover.
- Split covers allow access to one service at a time.
- Common aesthetics throughout line.



### Device Cover Plates

- Cover plates can be used for both HBLALU3800 and HBLALU4800 Raceways.
- Cover plates offer option for most common power device applications.
- Low profile bezel cover accommodates Hubbell iSTATION Modules.
- Open System data option available.
- Base mounted cover plates available for added strength.

| HBLALU3800 Series | Description                                                                                                                                                                                      | Color             | Catalog Number                                               | Description                                                                                     | Color             | Catalog Number                      |
|-------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|--------------------------------------------------------------|-------------------------------------------------------------------------------------------------|-------------------|-------------------------------------|
|                   | <b>Single Channel Base</b><br>Satin anodized finish. Packed 40 ft. (12.19m) per carton, 10 ft. (3m) lengths.<br><br>Assembled cover and base dimensions.<br>W: 3.00" (76.20)<br>H: 2.25" (57.15) | Anodized Aluminum | <b>HBLALU3800B10</b><br>A: 2.10" (53.34)<br>B: 3.00" (76.20) | <b>Cover</b><br>Satin anodized finish. Packed 40 ft. (12.19m) per carton, 5 ft. (1.5m) lengths. | Anodized Aluminum | <b>HBLALUC5</b><br>A: 3.00" (76.20) |



| Elbows and Tees | Description                                                                                                        | Color             | Catalog Number                                               | Description                                                                                                                   | Color             | Catalog Number                                                |
|-----------------|--------------------------------------------------------------------------------------------------------------------|-------------------|--------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|-------------------|---------------------------------------------------------------|
|                 | <b>Internal Elbow</b><br>For making a 90° internal turn in a raceway run.                                          | Anodized Aluminum | <b>HBLALU3817*</b><br>A: 6.00" (152.40)<br>B: 6.00" (152.40) | <b>Inverted Internal Elbow</b><br>For connecting a vertical run of HBLALU3800 with a horizontal run with its cover facing up. | Anodized Aluminum | <b>HBLALU3817N*</b><br>A: 6.00" (152.40)<br>B: 5.98" (151.89) |
|                 | <b>External Elbow</b><br>For making a 90° external turn in a raceway run.                                          | Anodized Aluminum | <b>HBLALU3818*</b><br>A: 6.00" (152.40)<br>B: 6.00" (152.40) | <b>Tee</b><br>For branch connections of two runs of HBLALU3800 Raceway.                                                       | Anodized Aluminum | <b>HBLALU3815*</b><br>A: 6.00" (152.40)<br>B: 6.00" (152.40)  |
| End Fittings    | <b>Flat Elbow</b><br>For making a 90° flat turn in a raceway run.                                                  | Anodized Aluminum | <b>HBLALU3811*</b><br>A: 6.00" (152.40)<br>B: 6.00" (152.40) | <b>Blank End Fitting</b><br>For closing end of raceway.                                                                       | Anodized Aluminum | <b>HBLALU3810B</b><br>A: 3.00" (76.20)<br>B: 2.31" (58.74)    |
|                 | <b>Entrance End Fitting</b><br>For feeding raceway, has concentric ½ in. and ¼ in. trade size KOs.                 | Anodized Aluminum | <b>HBLALU3810B1</b><br>A: 3.00" (76.20)<br>B: 2.31" (58.74)  | <b>Wire Clip</b><br>For holding conductors in place. Can be used for either HBLALU3800 or HBLALU4800 Raceway.                 | Anodized Aluminum | <b>HBLALUWC</b><br>A: 1.00" (25.40)                           |
| Fittings        | <b>Cover Clip</b><br>To cover seam where lengths of HBLALU3800 Raceway come together.                              | Stainless Steel   | <b>HBLALU3806</b><br>A: 1.38" (34.92)                        | <b>Grounding Adapter</b><br>For connection of equipment grounding. #10-32 Locking screws included.                            | Galvanized Steel  | <b>HBLALU09</b><br>A: 4.00" (101.80)<br>B: 2.00" (50.83)      |
|                 | <b>Internal Corner Coupling</b><br>For butting two raceway sections to form an internal 90° turn in a raceway run. | Anodized Aluminum | <b>HBLALU17A</b><br>A: 4.00" (101.80)<br>B: 2.00" (50.83)    | <b>Couplings (Pair)</b><br>To join lengths of HBLALU3800 or HBLALU4800 base.                                                  | Aluminum          | <b>HBLALU01</b><br>A: 2.85" (72.39)<br>B: 4.00" (101.80)      |
|                 |                                                                                                                    |                   |                                                              |                                                                                                                               |                   |                                                               |

Note: \*HBLALU01 couplings included.  
 See page R-40 for cover plates.










Dimensions in Inches (mm)

| HBLALU4800 Series | Description                                                                                                                                                                                    | Color             | Catalog Number                                                | Description                                                                                     | Color             | Catalog Number                      |
|-------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|---------------------------------------------------------------|-------------------------------------------------------------------------------------------------|-------------------|-------------------------------------|
|                   | <b>Two Channel Base</b><br>Satin anodized finish. Packed 40 ft. (12.19m) per carton, 10 ft. (3m) lengths.<br><br>Assembled cover and base dimensions.<br>W: 6.00" (152.40)<br>H: 2.25" (57.15) | Anodized Aluminum | <b>HBLALU4800B10</b><br>A: 2.10" (53.34)<br>B: 6.00" (152.40) | <b>Cover</b><br>Satin anodized finish. Packed 40 ft. (12.19m) per carton, 5 ft. (1.5m) lengths. | Anodized Aluminum | <b>HBLALUC5</b><br>A: 3.00" (76.20) |

| Elbows and Tees | Description                                                                                                          | Color             | Catalog Number                                               | Description                                                                                                                                 | Color             | Catalog Number                                                |
|-----------------|----------------------------------------------------------------------------------------------------------------------|-------------------|--------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------|-------------------|---------------------------------------------------------------|
|                 | <b>Internal Elbow (Two Channel)</b><br>For making a 90° internal turn in a raceway run.                              | Anodized Aluminum | <b>HBLALU4817*</b><br>A: 6.00" (152.40)<br>B: 6.00" (152.40) | <b>Inverted Internal Elbow (Two Channel)</b><br>For connecting a vertical run of HBLALU4800 with a horizontal run with its cover facing up. | Anodized Aluminum | <b>HBLALU4817N*</b><br>A: 6.00" (152.40)<br>B: 5.98" (151.89) |
|                 | <b>External Elbow (Two Channel)</b><br>For making a 90° external turn in a raceway run.                              | Anodized Aluminum | <b>HBLALU4818*</b><br>A: 6.00" (152.40)<br>B: 6.00" (152.40) | <b>Tee (Two Channel)</b><br>For branch connections of two runs of HBLALU4800 Raceway.                                                       | Anodized Aluminum | <b>HBLALU4815*</b><br>A: 9.00" (228.60)<br>B: 9.00" (228.60)  |
| End Fittings    | <b>Flat Elbow (Two Channel)</b><br>For making a 90° flat turn in a raceway run.                                      | Anodized Aluminum | <b>HBLALU4811*</b><br>A: 9.00" (228.60)<br>B: 9.00" (228.60) | <b>Blank End Fitting (Two Channel)</b><br>For closing end of raceway.                                                                       | Anodized Aluminum | <b>HBLALU4810B</b><br>A: 6.00" (152.40)<br>B: 2.31" (58.74)   |
|                 | <b>Entrance End Fitting (Two Channel)</b><br>For feeding raceway, has two concentric ½ in. and ¾ in. trade size KOs. | Anodized Aluminum | <b>HBLALU4810B2</b><br>A: 6.00" (152.40)<br>B: 2.31" (58.74) | <b>Wire Clip</b><br>Used for holding conductors in place on raceway. Can be used for either HBLALU3800 or HBLALU4800 Raceway.               | Anodized Aluminum | <b>HBLALUWC</b><br>A: 1.00" (25.40)                           |
| Fittings        | <b>Cover Clip</b><br>To cover seam where lengths of HBLALU4800 Raceway come together.                                | Stainless Steel   | <b>HBLALU4806</b><br>A: 1.38" (34.92)                        | <b>Grounding Adapter</b><br>For connection of equipment grounding. #10-32 Locking screws included.                                          | Galvanized Steel  | <b>HBLALU09</b><br>A: 4.00" (101.80)<br>B: 2.00" (50.83)      |
|                 | <b>Internal Corner Coupling</b><br>For butting two raceway sections to form an internal 90° turn in a raceway run.   | Anodized Aluminum | <b>HBLALU17A</b><br>A: 4.00" (101.80)<br>B: 2.00" (50.83)    |                                                                                                                                             |                   |                                                               |
|                 | <b>Couplings (Pair)</b><br>To join lengths of HBLALU3800 or HBLALU4800 base.                                         | Aluminum          | <b>HBLALU01</b><br>A: 2.85" (72.39)<br>B: 4.00" (101.80)     |                                                                                                                                             |                   |                                                               |

Note: \*HBLALU01 couplings included.  
 See page R-40 for cover plates.

Dimensions in Inches (mm)

|              |                                                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                             |                                                                                                                                                                                                          |                                                                                                                                                                        |
|--------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Cover Plates | <b>Duplex Receptacle Cover</b><br>For duplex receptacles and duplex communication frames shown on page R-45.                                                                                                                              | Anodized Aluminum<br><b>HBLALUDR</b><br>A: 3.00" (76.20)<br>B: 12.00" (304.80)<br><b>HBLALU34DRBM</b><br>(Base Mounted Device)<br>A: 3.00" (76.20)<br>B: 12.00" (304.80)                                                    | <b>Toggle Switch Cover</b><br>For single pole, two pole, three way or four way switches.                               | Anodized Aluminum<br><b>HBLALUN</b><br>A: 3.00" (76.20)<br>B: 12.00" (304.80)<br><b>HBLALU34NBM</b><br>(Base Mounted Device)<br>A: 3.00" (76.20)<br>B: 12.00" (304.80) |
|              | <b>Rectangular Style Line® Cover</b><br>For Style Line rectangular duplex receptacle, GFCI, surge device or rectangular communication frames shown on page R-45.                                                                          | Anodized Aluminum<br><b>HBLALUG</b><br>A: 3.00" (76.20)<br>B: 12.00" (304.80)<br><b>HBLALU34GBM</b><br>(Base Mounted Device)<br>A: 3.00" (76.20)<br>B: 12.00" (304.80)                                                      | <b>Single Receptacle Cover</b><br>For single receptacle with face diameters of 1.38 in. to 1.39 in. (35.05 to 35.31).  | Anodized Aluminum<br><b>HBLALUE</b><br>A: 3.00" (76.20)<br>B: 12.00" (304.80)<br><b>HBLALU34EBM</b><br>(Base Mounted Device)<br>A: 3.00" (76.20)<br>B: 12.00" (304.80) |
|              | <b>Single Receptacle Cover</b><br>For single receptacle with face diameters of 1.56 in. to 1.59 in. (39.62 to 40.39).                                                                                                                     | Anodized Aluminum<br><b>HBLALUF</b><br>A: 3.00" (76.20)<br>B: 12.00" (304.80)<br><b>HBLALU34FBM</b><br>(Base Mounted Device)<br>A: 3.00" (76.20)<br>B: 12.00" (304.80)                                                      | <b>Single Receptacle Cover</b><br>For single receptacle with face diameter of 2.13 in. (54.10).                        | Anodized Aluminum<br><b>HBLALUJ</b><br>A: 3.00" (76.20)<br>B: 12.00" (304.80)<br><b>HBLALU34JBM</b><br>(Base Mounted Device)<br>A: 3.00" (76.20)<br>B: 12.00" (304.80) |
|              | <b>Blank Cover</b><br>To cover 12 in. (305.00) section of raceway.                                                                                                                                                                       | Anodized Aluminum<br><b>HBLALUBL</b><br>A: 3.00" (76.20)<br>B: 12.00" (304.80)                                                                                                                                              | <b>Ortronics® Cover Plate</b><br>For two Ortronics TracJack® or one Series II® datacom insert. Both bezels included.  | Anodized Aluminum<br><b>HBLALUABRT</b><br>A: 3.00" (76.20)<br>B: 12.00" (304.80)                                                                                       |
|              | <b>Hubbell iSTATION Cover</b><br>For mounting Hubbell iSTATION Modules. For the HBLALUPB use the KPIMBZGY on page R-45 with modules from page R-46. For the HBLALULPBA use the IMF1GY on page R-46 or any IFPxxGY plates on page R-45.  | Anodized Aluminum<br><b>HBLALUPB</b><br>A: 3.00" (76.20)<br>B: 12.00" (304.80)<br>C: 1.90 (48.26)<br>D: 4.21 (106.93)<br><b>HBLALULPBA</b><br>A: 3.00" (76.20)<br>B: 12.00" (304.80)<br>C: 1.90 (48.26)<br>D: 3.00" (76.20) |                                                                                                                      |                                                                                                                                                                        |

### Base Mounted Device Cover Design

No exposed screw holes. Receptacle is securely mounted to the raceway base rather than the cover.


Ortronics®, Series II® and TracJack® are registered trademarks of The Ortronics Company.

Dimensions in Inches (mm)



### Two and Three Channel

- Two and three channel aluminum raceways.
- Satin anodized finish.
- Resists oxidation, corrosion and fading.
- Can be installed as recessed or surface mounted.
- UL Listed and CSA Certified.



### Wide Selection of Fittings

- External, internal, flat and tee fittings available to accommodate all types of applications.
- Available in both two and three channel versions.





### Covers

- Two and three channel raceway utilize common covers.
- Available in single and dual channel cover designs.
- Single covers allow access to one service at a time.
- Dual channel cover fits over two channels for a seamless look.
- Common aesthetics throughout line.



### Compatible Cover Plates













- Cover plates can be used for both HBLALU5000 and HBLALU7620 Raceways.
- Cover plates offer option for most common power device applications.
- Low profile bezel cover accommodates Hubbell iSTATION Modules.
- Open System data option available.
- Base mounted cover plates available for added strength.

| HBLALU5000 Series | Description                                                                                                                                                                                    | Color             | Catalog Number                                                | Description                                                                                                                                                            | Color             | Catalog Number                         |
|-------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|---------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|----------------------------------------|
|                   | <b>Two Channel Base</b><br>Satin anodized finish. Packed 40 ft. (12.19m) per carton, 10 ft. (3m) lengths.<br><br>Assembled cover and base dimensions.<br>W: 5.08" (129.03)<br>H: 1.75" (44.45) | Anodized Aluminum | <b>HBLALU5000B10</b><br>A: 1.66" (42.16)<br>B: 5.08" (129.03) | <b>Cover - Single Channel</b><br>Satin anodized finish. Packed 40 ft. (12.19m) per carton, 5 ft. (1.5m) lengths.                                                       | Anodized Aluminum | <b>HBLALUC57</b><br>A: 2.54" (64.52)   |
|                   |                              |                   |                                                               |   |                   |                                        |
|                   |                                                                                                                                                                                                |                   |                                                               | <b>Cover - Two Channel</b><br>Satin anodized finish. Packed 40 ft. (12.19m) per carton, 5 ft. (1.5m) lengths.                                                          | Anodized Aluminum | <b>HBLALU2C57</b><br>A: 5.08" (129.03) |
|                   |                                                                                                                                                                                                |                   |                                                               |   |                   |                                        |

| Elbows and Tees | Description                                                                                                                                                             | Color             | Catalog Number                                               | Description                                                                                                                                                                 | Color             | Catalog Number                                                |
|-----------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|--------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|---------------------------------------------------------------|
|                 | <b>Internal Elbow</b><br>For making a 90° internal turn in a raceway run.                                                                                               | Anodized Aluminum | <b>HBLALU5017*</b><br>A: 6.00" (152.40)<br>B: 6.00" (152.40) | <b>Inverted Internal Elbow</b><br>For connecting a vertical run of HBLALU5000 with a horizontal run with its cover facing up.                                               | Anodized Aluminum | <b>HBLALU5017N*</b><br>A: 5.91" (150.20)<br>B: 5.98" (151.89) |
|                 |       |                   |                                                              |       |                   |                                                               |
|                 | <b>External Elbow</b><br>For making a 90° external turn in a raceway run.                                                                                               | Anodized Aluminum | <b>HBLALU5018*</b><br>A: 6.00" (152.40)<br>B: 6.00" (152.40) | <b>Tee</b><br>For branch connections of two runs of HBLALU5000 Raceway.                                                                                                     | Anodized Aluminum | <b>HBLALU5015*</b><br>A: 9.00" (228.60)<br>B: 8.08" (205.30)  |
|                 |     |                   |                                                              |     |                   |                                                               |
|                 | <b>Flat Elbow</b><br>For making a 90° flat turn in a raceway run.                                                                                                       | Anodized Aluminum | <b>HBLALU5011*</b><br>A: 9.00" (228.60)<br>B: 9.00" (228.60) |                                                                                                                                                                             |                   |                                                               |
|                 |   |                   |                                                              |                                                                                                                                                                             |                   |                                                               |
| End Fittings    | <b>Entrance End Fitting</b><br>For feeding raceway, has concentric ½ in. and ¾ in. trade size KOs.                                                                      | Anodized Aluminum | <b>HBLALU5010B2</b><br>A: 5.08" (129.10)<br>B: 1.75" (44.40) | <b>Blank End Fitting</b><br>For closing end of raceway.                                                                                                                     | Anodized Aluminum | <b>HBLALU5010B</b><br>A: 5.08" (129.10)<br>B: 1.75" (44.40)   |
|                 |   |                   |                                                              |   |                   |                                                               |
| Fittings        | <b>Cover Clip</b><br>To cover seam where lengths of HBLALU5000 Raceway come together.                                                                                   | Stainless Steel   | <b>HBLALU5006</b><br>A: 1.38" (34.92)                        | <b>Wire Clip</b><br>For holding conductors in place. Can be used for either HBLALU5000 or HBLALU7620 Raceway.                                                               | Anodized Aluminum | <b>HBLALU57WC</b><br>A: 1.00" (25.40)                         |
|                 |   |                   |                                                              |   |                   |                                                               |
|                 | <b>Internal Corner Coupling</b><br>For butting two raceway sections to form an internal 90° turn in a raceway run.                                                      | Anodized Aluminum | <b>HBLALU5717A</b><br>A: 3.50" (88.90)<br>B: 2.38" (60.30)   | <b>Grounding Adapter</b><br>For connection of equipment grounding. #10-32 Locking screws included.                                                                          | Galvanized Steel  | <b>HBLALU5709</b><br>A: 3.37" (85.50)<br>B: 2.00" (50.83)     |
|                 |   |                   |                                                              |   |                   |                                                               |
|                 | <b>Couplings (Pair)</b><br>To join lengths of HBLALU5000 or HBLALU7620 base.                                                                                            | Aluminum          | <b>HBLALU5701</b><br>A: 2.38" (60.30)<br>B: 4.00" (101.80)   |                                                                                                                                                                             |                   |                                                               |
|                 |   |                   |                                                              |                                                                                                                                                                             |                   |                                                               |

Note: \*HBLALU5701 couplings included.  
 See page R-44 for cover plates.

Dimensions in Inches (mm)

|                          |                                                                                                                                                                                                                        |                                   |                                                                                         |                                                                                                                                                                             |                                   |                                                                                        |
|--------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|-----------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|----------------------------------------------------------------------------------------|
| <b>HBLALU7620 Series</b> | <b>Description</b><br><b>Three Channel Base</b><br>Satin anodized finish. Packed 40 ft. (12.19m) per carton, 10 ft. (3m) lengths.<br><br>Assembled cover and base dimensions.<br>W: 7.62" (193.55)<br>H: 2.25" (57.15) | <b>Color</b><br>Anodized Aluminum | <b>Catalog Number</b><br><b>HBLALU7620B10</b><br>A: 2.16" (54.86)<br>B: 7.62" (193.55)  | <b>Description</b><br><b>Cover - Single Channel</b><br>Satin anodized finish. Packed 40 ft. (12.19m) per carton, 5 ft. (1.5m) lengths.                                      | <b>Color</b><br>Anodized Aluminum | <b>Catalog Number</b><br><b>HBLALUC57</b><br>A: 2.54" (64.52)                          |
|                          |                                                      |                                   |                                                                                         |       |                                   |                                                                                        |
|                          |                                                                                                                                                                                                                        |                                   |                                                                                         | <b>Description</b><br><b>Cover - Two Channel</b><br>Satin anodized finish. Packed 40 ft. (12.19m) per carton, 5 ft. (1.5m) lengths.                                         | <b>Color</b><br>Anodized Aluminum | <b>Catalog Number</b><br><b>HBLALU2C57</b><br>A: 5.08" (129.03)                        |
|                          |                                                                                                                                                                                                                        |                                   |                                                                                         |       |                                   |                                                                                        |
| <b>Elbow Fittings</b>    | <b>Description</b><br><b>Internal Elbow</b><br>For making a 90° internal turn in a raceway run.                                                                                                                        | <b>Color</b><br>Anodized Aluminum | <b>Catalog Number</b><br><b>HBLALU7617*</b><br>A: 6.50" (165.10)<br>B: 6.50" (165.10)   | <b>Description</b><br><b>Inverted Internal Elbow</b><br>For connecting a vertical run of HBLALU7620 with a horizontal run with its cover facing up.                         | <b>Color</b><br>Anodized Aluminum | <b>Catalog Number</b><br><b>HBLALU7617N*</b><br>A: 6.50" (165.10)<br>B: 5.98" (151.89) |
|                          |                                                      |                                   |                                                                                         |       |                                   |                                                                                        |
|                          | <b>Description</b><br><b>External Elbow</b><br>For making a 90° external turn in a raceway run.                                                                                                                        | <b>Color</b><br>Anodized Aluminum | <b>Catalog Number</b><br><b>HBLALU7618*</b><br>A: 5.50" (139.70)<br>B: 5.50" (139.70)   | <b>Description</b><br><b>Tee</b><br>For branch connections of two runs of HBLALU7620 Raceway.                                                                               | <b>Color</b><br>Anodized Aluminum | <b>Catalog Number</b><br><b>HBLALU7615*</b><br>A: 9.00" (228.60)<br>B: 10.62" (269.80) |
|                          |                                                    |                                   |                                                                                         |      |                                   |                                                                                        |
| <b>End Fittings</b>      | <b>Description</b><br><b>Flat Elbow</b><br>For making a 90° flat turn in a raceway run.                                                                                                                                | <b>Color</b><br>Anodized Aluminum | <b>Catalog Number</b><br><b>HBLALU7611*</b><br>A: 11.54" (293.10)<br>B: 11.54" (293.10) |                                                                                                                                                                             |                                   |                                                                                        |
|                          |                                                  |                                   |                                                                                         |                                                                                                                                                                             |                                   |                                                                                        |
|                          | <b>Description</b><br><b>Entrance End Fitting</b><br>For feeding raceway, has concentric ½ in. and ¾ in. trade size KO's.                                                                                              | <b>Color</b><br>Anodized Aluminum | <b>Catalog Number</b><br><b>HBLALU7610B2</b><br>A: 7.62" (193.50)<br>B: 2.31" (58.70)   | <b>Description</b><br><b>Blank End Fitting</b><br>For closing end of raceway.                                                                                               | <b>Color</b><br>Anodized Aluminum | <b>Catalog Number</b><br><b>HBLALU7610B</b><br>A: 7.62" (193.50)<br>B: 2.31" (58.70)   |
|                          |                                                  |                                   |                                                                                         |   |                                   |                                                                                        |
| <b>Fittings</b>          | <b>Description</b><br><b>Cover Clip</b><br>To cover seam where lengths of HBLALU7620 Raceway come together.                                                                                                            | <b>Color</b><br>Stainless Steel   | <b>Catalog Number</b><br><b>HBLALU7606</b><br>A: 1.38" (34.92)                          | <b>Description</b><br><b>Wire Clip</b><br>For holding conductors in place. Can be used for either HBLALU5000 or HBLALU7620 Raceway.                                         | <b>Color</b><br>Anodized Aluminum | <b>Catalog Number</b><br><b>HBLALU57WC</b><br>A: 1.00" (25.40)                         |
|                          |                                                  |                                   |                                                                                         |   |                                   |                                                                                        |
|                          | <b>Description</b><br><b>Internal Corner Coupling</b><br>For butting two raceway sections to form an internal 90° turn in a raceway run.                                                                               | <b>Color</b><br>Anodized Aluminum | <b>Catalog Number</b><br><b>HBLALU5717A</b><br>A: 3.50" (88.90)<br>B: 2.38" (60.30)     | <b>Description</b><br><b>Grounding Adapter</b><br>For connection of equipment grounding. #10-32 Locking screws included.                                                    | <b>Color</b><br>Galvanized Steel  | <b>Catalog Number</b><br><b>HBLALU5709</b><br>A: 3.37" (85.50)<br>B: 2.00" (50.83)     |
|                          |                                                  |                                   |                                                                                         |   |                                   |                                                                                        |
|                          | <b>Description</b><br><b>Couplings (Pair)</b><br>To join lengths of HBLALU5000 or HBLALU7620 base.                                                                                                                     | <b>Color</b><br>Aluminum          | <b>Catalog Number</b><br><b>HBLALU5701</b><br>A: 2.38" (60.30)<br>B: 4.00" (101.80)     |                                                                                                                                                                             |                                   |                                                                                        |
|                          |                                                  |                                   |                                                                                         |                                                                                                                                                                             |                                   |                                                                                        |

Note: \*HBLALU5701 couplings included.  
 See page R-44 for cover plates.

Dimensions in Inches (mm)

| Cover Plates | Description                                                                                                                                                      | Color             | Catalog Number                                                                                                                                        | Description                                                                                                           | Color             | Catalog Number                                                                                                                                      |
|--------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|-------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|
|              | <b>Duplex Receptacle Cover</b><br>For duplex receptacles and duplex communication frames shown on page R-45.                                                     | Anodized Aluminum | <b>HBLALU57DR</b><br>A: 2.54" (64.50)<br>B: 12.00" (304.80)<br><b>HBLALU57DRBM</b><br>(Base Mounted Device)<br>A: 2.54" (64.50)<br>B: 12.00" (304.80) | <b>Toggle Switch Cover</b><br>For single pole, two pole, three way or four way switches.                              | Anodized Aluminum | <b>HBLALU57N</b><br>A: 2.54" (64.50)<br>B: 12.00" (304.80)<br><b>HBLALU57NBM</b><br>(Base Mounted Device)<br>A: 2.54" (64.50)<br>B: 12.00" (304.80) |
|              | <b>Rectangular Style Line® Cover</b><br>For Style Line rectangular duplex receptacle, GFCI, surge device or rectangular communication frames shown on page R-45. | Anodized Aluminum | <b>HBLALU57G</b><br>A: 2.54" (64.50)<br>B: 12.00" (304.80)<br><b>HBLALU57GBM</b><br>(Base Mounted Device)<br>A: 2.54" (64.50)<br>B: 12.00" (304.80)   | <b>Blank Cover</b><br>To cover 12 in. (305.00) section of raceway.                                                    | Anodized Aluminum | <b>HBLALU57BL</b><br>A: 2.54" (64.50)<br>B: 12.00" (304.80)                                                                                         |
|              | <b>Single Receptacle Cover</b><br>For single receptacle with face diameters of 1.38 in. to 1.39 in. (35.05 to 35.31).                                            | Anodized Aluminum | <b>HBLALU57E</b><br>A: 2.54" (64.50)<br>B: 12.00" (304.80)<br><b>HBLALU57EBM</b><br>(Base Mounted Device)<br>A: 2.54" (64.50)<br>B: 12.00" (304.80)   | <b>Single Receptacle Cover</b><br>For single receptacle with face diameters of 1.56 in. to 1.59 in. (39.62 to 40.39). | Anodized Aluminum | <b>HBLALU57F</b><br>A: 2.54" (64.50)<br>B: 12.00" (304.80)<br><b>HBLALU57FBM</b><br>(Base Mounted Device)<br>A: 2.54" (64.50)<br>B: 12.00" (304.80) |
|              | <b>Hubbell iSTATION Cover</b><br>For mounting Hubbell iSTATION modules. IMF1GY or IFPxxGY frames and plates on pages R-45 and R-46.                              | Anodized Aluminum | <b>HBLALU57LPB</b><br>A: 2.54" (64.50)<br>B: 12.00" (304.80)<br>C: 1.90 (48.26)<br>D: 3.00" (76.20)                                                   | <b>Ortronics® Cover Plate</b><br>For two Ortronics TracJack® or one Series II® datacom insert. Both bezels included.  | Anodized Aluminum | <b>HBLALU57ABRT</b><br>A: 2.54" (64.50)<br>B: 12.00" (304.80)                                                                                       |
|              | <b>2-Gang Raised Device Box</b><br>KP device plates only, found on page R-45.                                                                                    | Gray PVC          | <b>HBLALU57KP2G</b><br>A: 5.08" (129.10)<br>B: 7.64" (193.90)                                                                                         |                                   |                   |                                                                                                                                                     |

### Base Mounted Device Cover Design

No exposed screw holes. Receptacle is securely mounted to the raceway base rather than the cover.

Ortronics®, Series II® and TracJack® are registered trademarks of The Ortronics Company.





Dimensions in Inches (mm)

| 1. Choose Device Mounting Bracket | Description                                                                                                                  | Color         | HBL4750 Series                                                                    |                                      | HBL6750 Series                                                                                                              |
|-----------------------------------|------------------------------------------------------------------------------------------------------------------------------|---------------|-----------------------------------------------------------------------------------|--------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|
|                                   | Device Mounting Bracket for HBL4750 and HBL6750 Series Metal Raceway. Ivory metal raceway matches almond devices and plates. | Ivory<br>Gray |  | <b>HBL4750IV</b><br><b>HBL4750GY</b> | <br><b>HBL6750IV</b><br><b>HBL6750GY</b> |

| 2. Choose 1-Gang "KP" Plates | Color          | Catalog Number                                                                                                                                                  | Catalog Number                                                                                                                                               | Catalog Number                                                                                                                                                                                                             | Catalog Number                                                                                                                                    | Catalog Number                                                                                                                                     |
|------------------------------|----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|
|                              | Almond<br>Gray | <br><b>KP8AL</b><br><b>KP8GY</b><br>Duplex                                     | <br><b>KP26AL</b><br><b>KP26GY</b><br>Style Line®                           | <br><b>KP1AL</b><br><b>KP1GY</b><br>Toggle                                                                                                | <br><b>KP7AL</b><br><b>KP7GY</b><br>Receptacle<br>(1.41 ID)    | <br><b>KP720AL</b><br><b>KP720GY</b><br>Receptacle<br>(1.60 ID) |
|                              | Almond<br>Gray | <br><b>KP14AL</b><br><b>KP14GY</b><br>Blank                                    | <br><b>KP212AL</b><br><b>KP212GY</b><br>Coax (2)                            | <br><b>KP2140AL</b><br><b>KP2140GY</b><br>Jack/Coax                                                                                       | <br><b>KP2162AL</b><br><b>KP2162GY</b><br>Modular<br>Jacks (2) | <br><b>KP2163AL</b><br><b>KP2163GY</b><br>Modular<br>Jacks (3)  |
|                              | Almond<br>Gray | <br><b>KPORTAL</b><br><b>KPORTGY</b><br>Ortronics<br>Series II®<br>Data Module | <br><b>KPPANAL</b><br><b>KPPANGY</b><br>Panduit<br>Mini-Com®<br>Data Module | <br><b>KPIMBZAL</b><br><b>KPIMBZGY</b><br>3-Unit iSTATION<br>(Accepts all Hubbell iSTATION Modules<br>located in Network Wiring section). |                                                                                                                                                   |                                                                                                                                                    |

| Comm. "IFP" Plates & Frames | Color          | Catalog Number                                                                                                                             | Catalog Number                                                                                                                               | Catalog Number                                                                                                                               | Catalog Number                                                                                                                                 | Catalog Number                                                                                                                                 |
|-----------------------------|----------------|--------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------|
|                             | Almond<br>Gray | <br><b>IFP126AL</b><br>—<br>Style Line®                   | <br><b>ISF2AL</b><br><b>ISF2GY</b><br>Style Line®<br>2-Port | <br><b>ISF3AL</b><br><b>ISF3GY</b><br>Style Line®<br>3-Port | <br><b>ISF4AL</b><br><b>ISF4GY</b><br>Style Line®<br>4-Port | <br><b>ISF6AL</b><br><b>ISF6GY</b><br>Style Line®<br>6-Port |
|                             | Almond<br>Gray | <br><b>IFP18AL</b><br>—<br>Duplex                       | <br><b>BR106AL</b><br><b>BR106G</b><br>Duplex<br>2-Port   | <br><b>Q106AL</b><br><b>Q106G</b><br>Duplex<br>4-Port     |                                                                                                                                                |                                                                                                                                                |
|                             | Almond<br>Gray | <br><b>IFP12AL</b><br><b>IFP12GY</b><br>Flush<br>2-Port | <br><b>IFP13AL</b><br><b>IFP13GY</b><br>Flush<br>3-Port   | <br><b>IFP14AL</b><br><b>IFP14GY</b><br>Flush<br>4-Port   | <br><b>IFP16AL</b><br><b>IFP16GY</b><br>Flush<br>6-Port   |                                                                                                                                                |

Note: Ivory metal raceway matches almond devices and plates. For HBL3000 series raceway applications, catalog number HBL3051LEIV/GY must be used with plates and devices. See page R-46 or section W for additional information on datacom products.

| Painted Steel Plates | Color          | 1-Gang                                                                                                                                             | 2-Gang                                                                                                                                        | 3-Gang                                                                                                                              | 4-Gang                                                                                                                                          | 5-Gang                                                                                                                                          | 6-Gang                                                                                                                               |
|----------------------|----------------|----------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|
|                      | Almond<br>Gray | <br><b>SP1AL</b><br><b>SP1G</b><br>Toggle                       | <br><b>SP2AL</b><br><b>SP2G</b><br>Toggle                  | <br><b>SP3AL</b><br>—<br>Toggle                  | <br><b>SP4AL</b><br>—<br>Toggle                            | <br><b>SP5AL</b><br>—<br>Toggle                            | <br><b>SP6AL</b><br>—<br>Toggle                 |
|                      | Almond<br>Gray | <br><b>SP8AL</b><br><b>SP8G</b><br>Duplex                       | <br><b>SP82AL</b><br><b>SP82G</b><br>Duplex                | <br><b>SP83AL</b><br>—<br>Duplex                 | <br>—<br>Duplex                                            | <br>—<br>Duplex                                            | <br>—<br>Duplex                                 |
|                      | Almond<br>Gray | <br><b>PHPS1AL</b><br><b>PHPS1G</b><br>Style Line®              | <br><b>PHPS2AL</b><br><b>PHPS2G</b><br>Style Line®         | <br><b>PHPS3AL</b><br>—<br>Style Line®           | <br><b>PHPS4AL</b><br>—<br>Style Line®                     | <br><b>PHPS5AL</b><br>—<br>Style Line®                     | <br><b>PHPS6AL</b><br>—<br>Style Line®          |
|                      | Almond<br>Gray | <br><b>SP7AL</b><br><b>SP7G</b><br>Single recept.<br>(1.41" ID) | <br><b>SP18AL</b><br><b>SP18G</b><br>Combination           | <br><b>SP28AL</b><br><b>SP28G</b><br>Combination | <br><b>PJS126AL</b><br><b>PJS126G</b>                      | <br>—<br><b>PJS226G</b>                                    |                                                                                                                                      |
|                      | Color          | 1-Gang                                                                                                                                             | 2-Gang                                                                                                                                        | 3-Gang                                                                                                                              | 1-Gang                                                                                                                                          | 2-Gang                                                                                                                                          | 3-Gang                                                                                                                               |
|                      | Almond<br>Gray | <br><b>SP14BAL</b><br><b>SP14BG</b><br>Blank,<br>Box Mount      | <br><b>SP24BAL</b><br><b>SP24BG</b><br>Blank,<br>Box Mount | <br><b>SP34BAL</b><br>—<br>Blank,<br>Box Mount   | <br><b>SP14AL</b><br><b>SP14G</b><br>Blank,<br>Strap Mount | <br><b>SP24AL</b><br><b>SP24G</b><br>Blank,<br>Strap Mount | <br><b>SP34AL</b><br>—<br>Blank,<br>Strap Mount |

Panduit® and Mini-Com® are registered trademarks of Panduit Corp.  
 Ortronics® and Series II® are registered trademarks of Ortronics/Legrand.

| 1. Choose Plate Frame                   | Description                                                                                                                                                                                                                                                                                                                                                                   | Color        | HBL4750 Series                                                                                                   | HBL6750 Series                                                                                                     |
|-----------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------|
|                                         | Front loading plate will accept any modules in three unit combinations. Angled fixtures to be used in bottom opening only. Use KPIMBZAL/GY plate with modules for HBL4750 and HBL6750 Series device mounting bracket located on page R-45. See section W for additional Hubbell iSTATION modules and datacom products. Ivory metal raceway matches almond devices and plates. | Office White |  <b>IMF1AL</b><br><b>IMF1GY</b> |  <b>IMF2AL</b><br><b>IMF2GY</b> |
| Note: Each gang accepts 3 module units. |                                                                                                                                                                                                                                                                                                                                                                               |              |                                                                                                                  |                                                                                                                    |

| 2. Choose Modules | Color       | Catalog Number                                                                                                                                            | Catalog Number                                                                                                                                                                                                                                                                           | Catalog Number                                                                                                                                              | Catalog Number                                                                                                                                          | Catalog Number                                                                                                                                              |
|-------------------|-------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                   | Almond Gray |  <b>IMB05AL</b><br><b>IMB05GY</b><br>Blank Module<br>.5 Unit             |  <b>IMB1AL</b><br><b>IMB1GY</b><br>Blank Module<br>1 Unit                                                                                                                                               |  <b>IMB15AL</b><br><b>IMB15GY</b><br>Blank Module<br>1.5 Unit              |  <b>IM1K1AL</b><br><b>IM1K1GY</b><br>Modular Flat<br>1 Unit            |  <b>IM2K1AL</b><br><b>IM2K1GY</b><br>Modular Flat<br>1 Unit              |
|                   | Almond Gray |  <b>IM1KA15AL</b><br><b>IM1KA15GY</b><br>Modular Angled<br>1.5 Unit      |  <b>IM2KA15AL</b><br><b>IM2KA15GY</b><br>Modular Angled<br>1.5 Unit                                                                                                                                     |  <b>IM1SCA15AL</b><br><b>IM1SCA15GY</b><br>SC 1 Duplex<br>Angled, 1.5 Unit |  <b>IM2SCA2AL</b><br><b>IM2SCA2GY</b><br>SC 2 Duplex<br>Angled, 2 Unit |  <b>IM1IA15AL</b><br><b>IM1IA15GY</b><br>Modular<br>Recessed<br>1.5 Unit |
|                   | Almond Gray |  <b>IM2IA15AL</b><br><b>IM2IA15GY</b><br>Modular<br>Recessed<br>1.5 Unit | <b>Keystone Opening</b><br>Hole size for mounting<br>all Hubbell Jacks. <div style="display: flex; align-items: center;"> <div style="border: 1px solid black; width: 20px; height: 20px; margin-right: 5px;"></div> <div> <p>A: .580" (14.73)</p> <p>B: .760" (19.30)</p> </div> </div> |                                                                                                                                                             |                                                                                                                                                         |                                                                                                                                                             |

Modular connectors to be used with any plate with a standard modular opening. Not recommended for use with KP plates. For KP applications use KPIMBZAL/GY bezel and appropriate Hubbell iSTATION modules located in the section W. Use appropriate Hubbell iSTATION modules for SC fiber adapters. See section W for additional modular connectors. Ivory metal raceway matches almond devices and plates.

| Modular Connector Fittings | Color              | Catalog Number                                                                                                                                                                       | Catalog Number                                                                                                                                                                         | Catalog Number                                                                                                                                                                          | Catalog Number                                                                                                                                       | Catalog Number                                                                                                                                 |
|----------------------------|--------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------|
|                            | Almond Gray        |  <b>SFFGAL</b><br><b>SFFGGY</b><br>F-Type Coupler<br>Gold                                         |  <b>SFFALX</b><br><b>SFFGX</b><br>F-Type Coupler<br>Nickel                                          |  <b>SFBAL</b><br><b>SFBGY</b><br>BNC<br>Connector                                                    |  <b>SF35SJAL</b><br><b>SF35SJGY</b><br>3.5mm<br>Stereo Jacks     |  <b>SFBAL10</b><br><b>SFBG10</b><br>Blank<br>(10 Pack)    |
|                            | Almond Gray        |  <b>SFRCRFFAL</b><br><b>SFRCRFFGY</b><br>RCA Gold<br>Pass-through<br>F/F Coupler<br>Red Insulator |  <b>SFRCWFFAL</b><br><b>SFRCWFFGY</b><br>RCA Gold<br>Pass-through<br>F/F Coupler<br>White Insulator |  <b>SFRCYFFAL</b><br><b>SFRCYFFGY</b><br>RCA Gold<br>Pass-through<br>F/F Coupler<br>Yellow Insulator |  <b>SFSV110AL</b><br><b>SFSV110GY</b><br>S-Video 110             |  <b>SFSVAL</b><br><b>SFSVGY</b><br>S-Video<br>F/F Coupler |
|                            | Black housing only |  <b>SFRC110R</b><br>RCA 110<br>Punchdown<br>Red Insulator                                         |  <b>SFRC110W</b><br>RCA 110<br>Punchdown<br>White Insulator                                         |  <b>SFRC110Y</b><br>RCA 110<br>Punchdown<br>Yellow Insulator                                         |  <b>SFSPGBK*</b><br><b>SFSPGR**</b><br>Speaker Post<br>Connector |                                                                                                                                                |

Note: \*Office white housing with black ring color.

\*\*Office white housing with red ring color.

| Xcelerator Modular Jacks | Color       | Catalog Number                                                                                                                                      | Catalog Number                                                                                                                                   | Catalog Number                                                                                                                                |
|--------------------------|-------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
|                          | Almond Gray |  <b>HXJ5EAL</b><br><b>HXJ5EGY</b><br>Cat. 5e, T568A, T568B, RJ45 |  <b>HXJ6AL</b><br><b>HXJ6GY</b><br>Cat. 6, T568A, T568B, RJ45 |  <b>HXJUAL</b><br><b>HXJUGY</b><br>6 Position USOC, RJ25 |

Note: Ivory metal raceway matches almond devices and plates.

Jack Color Options (Replace AL or GY suffix with additional colors below)

AL=Almond BK=Black B=Blue EI=Elec. Ivory GY=Gray GN=Green LA=Lt. Almond OR=Orange OW=Off. White R=Red W=White Y=Yellow

| Metal Raceway Wire Fill Capacities     |                                                      |                           |                           |           |           |        |         |                         |            |           |            |               |                                        |                        |                         |
|----------------------------------------|------------------------------------------------------|---------------------------|---------------------------|-----------|-----------|--------|---------|-------------------------|------------|-----------|------------|---------------|----------------------------------------|------------------------|-------------------------|
|                                        |                                                      |                           | Power<br>(THHN/T90 Nylon) |           |           | Voice  |         | Data<br>(Copper Cables) |            |           |            |               | Data (Multimode<br>Fiber Optic Cables) |                        |                         |
|                                        |                                                      |                           | 14<br>AWG                 | 12<br>AWG | 10<br>AWG | 4-Pair | 25-Pair | Type<br>RG59U           | Cat.<br>5e | Cat.<br>6 | Cat.<br>6A | Cat. 6<br>STP | (2) or<br>(4) Fiber<br>Round<br>Cable  | Fiber Optic<br>Jumpers | Fiber Optic<br>Zip Cord |
| Wire O.D. (in):                        |                                                      |                           | 0.111                     | 0.13      | 0.164     | 0.19   | 0.41    | 0.242                   | 0.21       | 0.25      | 0.35       | 0.29          | 0.19                                   | 0.118                  | .12 X .24               |
| Wire Area<br>(sq. in.):                |                                                      |                           | 0.0097                    | 0.0133    | 0.0211    | 0.0283 | 0.1320  | 0.0460                  | 0.0346     | 0.0491    | 0.0962     | 0.0660        | 0.0283                                 | 0.0109                 | 0.0288                  |
| Series                                 |                                                      | Channel Area<br>(sq. in.) | Wire Fill Capacity        |           |           | 40%    | 40%     | 40%                     | 40%        | 40%       | 40%        | 40%           | 40%                                    | 40%                    | 40%                     |
| HBL500                                 |                                                      | 0.22                      | 7                         | 5         | 3         | 2      | 0       | 1                       | 2          | 1         | 1          | 1             | 2                                      | 8                      | 2                       |
| HBL700                                 |                                                      | 0.26                      | 10                        | 7         | 4         | 3      | 0       | 2                       | 3          | 2         | 1          | 1             | 3                                      | 8                      | 3                       |
| HBL750                                 |                                                      | 0.40                      | 12                        | 9         | 5         | 6      | 1       | 3                       | 5          | 3         | 2          | 2             | 6                                      | 15                     | 6                       |
| HBL2000                                |                                                      | 0.89                      | 7                         | 7         | 0         | 13     | 3       | 8                       | 10         | 7         | 4          | 5             | 13                                     | 33                     | 12                      |
| HBL2000A                               |                                                      | 0.86                      | 35                        | 26        | 16        | 11     | 2       | 7                       | 9          | 7         | 4          | 5             | 13                                     | 33                     | 12                      |
| HBL2400                                |                                                      | 1.39                      | 57                        | 41        | 26        | 19     | 4       | 12                      | 16         | 11        | 5          | 8             | 19                                     | 51                     | 19                      |
| HBL2400D                               | Channel- A                                           | 0.86                      | 26                        | 19        | 11        | 12     | 2       | 7                       | 9          | 7         | 3          | 5             | 12                                     | 31                     | 11                      |
| <div>A</div> <div>B</div>              | Channel- B                                           | 0.37                      | 11                        | 9         | 6         | 5      | 1       | 3                       | 4          | 3         | 1          | 2             | 5                                      | 13                     | 5                       |
| HBL3000                                |                                                      | 3.70                      | 152                       | 111       | 70        | 52     | 11      | 32                      | 43         | 30        | 15         | 22            | 52                                     | 136                    | 51                      |
| HBL4750                                | No Barriers                                          | 7.20                      | 296                       | 216       | 136       | 102    | 22      | 63                      | 83         | 59        | 30         | 44            | 102                                    | 264                    | 100                     |
| <div>A</div> <div>B</div>              | Barrier Centered Ch. A                               | 3.10                      | 127                       | 93        | 58        | 44     | 9       | 27                      | 36         | 25        | 13         | 19            | 44                                     | 114                    | 43                      |
|                                        | Barrier Centered Ch. B                               | 3.30                      | 127                       | 93        | 58        | 47     | 10      | 29                      | 38         | 27        | 14         | 20            | 47                                     | 121                    | 46                      |
| <div>A</div> <div>B</div>              | Barrier Offset Ch. A                                 | 2.10                      | 86                        | 63        | 39        | 30     | 6       | 18                      | 24         | 17        | 9          | 13            | 30                                     | 77                     | 29                      |
|                                        | Barrier Offset Ch. B                                 | 4.30                      | 176                       | 129       | 81        | 61     | 13      | 37                      | 50         | 35        | 18         | 26            | 61                                     | 158                    | 60                      |
| HBL6750                                | No Barriers                                          | 13.77                     | 566                       | 412       | 259       | 195    | 42      | 120                     | 159        | 112       | 57         | 83            | 195                                    | 505                    | 191                     |
| <div>A</div> <div>A</div> <div>A</div> | Barrier Offset 1/3 Ch. A                             | 4.59                      | 189                       | 138       | 86        | 65     | 14      | 40                      | 53         | 37        | 19         | 28            | 65                                     | 168                    | 64                      |
| <div>A</div> <div>B</div>              | Barrier Offset 2/3 Ch. B                             | 9.18                      | 379                       | 278       | 173       | 130    | 28      | 80                      | 106        | 75        | 38         | 56            | 130                                    | 337                    | 128                     |
| HBLALU2000                             |                                                      | 1.20                      | 49                        | 36        | 22        | 16     | 3       | 10                      | 13         | 9         | 4          | 7             | 16                                     | 44                     | 16                      |
| HBLALU3800                             |                                                      | 5.80                      | 214                       | 156       | 98        | 82     | 18      | 50                      | 67         | 47        | 24         | 35            | 82                                     | 213                    | 81                      |
| HBLALU4800                             | Center<br>Barrier/<br>Both Channels                  | 11.60                     | 428                       | 312       | 196       | 164    | 35      | 101                     | 134        | 95        | 48         | 70            | 164                                    | 426                    | 161                     |
| <div></div> <div></div>                | Center<br>Barrier/<br>1 Channel                      | 5.80                      | 214                       | 156       | 98        | 82     | 18      | 50                      | 67         | 47        | 24         | 35            | 82                                     | 213                    | 81                      |
| HBLALU5000                             | Center<br>Barrier/<br>Both Channels                  | 7.60                      | 312                       | 228       | 142       | 106    | 22      | 64                      | 86         | 60        | 30         | 46            | 106                                    | 278                    | 104                     |
| <div></div> <div></div>                | Center<br>Barrier/<br>1 Channel                      | 3.80                      | 156                       | 114       | 71        | 53     | 11      | 32                      | 43         | 30        | 15         | 23            | 53                                     | 139                    | 52                      |
| HBLALU7620                             | 2 Barriers<br>with 3 Equal<br>Channels/Total         | 15.00                     | 618                       | 450       | 282       | 210    | 45      | 129                     | 171        | 120       | 60         | 90            | 210                                    | 549                    | 207                     |
| <div></div> <div></div> <div></div>    | 2 Barriers<br>with 3 Equal<br>Channels/<br>1 Channel | 5.00                      | 206                       | 150       | 94        | 70     | 15      | 43                      | 57         | 40        | 20         | 30            | 70                                     | 183                    | 69                      |

Note: Pathway (Raceway) fill shall be 40% maximum. Raceway fittings and outlets/receptacles reduce the cross section of the raceway system, thus reducing overall cable fill capacity.

### Physical Properties

Material Galvanized Steel or Anodized Aluminum

### Metal PlugTrak Specifications

Receptacle Rating NEMA 5-15R and NEMA 5-20R  
Wire #12 AWG Stranded Copper  
Receptacle Face Thermoplastic

### Codes/Standards

TIA/EIA 569B  
UL Standard UL 5  
Listings E253976 /E253830 /E253833  
CSA Standard C22.2 no. 62  
Certification LR87514



| Hubbell<br>Catalog Number   | Wiremold®             | Mono-<br>Systems, Inc.™ |
|-----------------------------|-----------------------|-------------------------|
| <b>HBL500 Series</b>        | <b>500 Series</b>     |                         |
| HBL502B                     | 502                   | SMS502                  |
| HBL605CUT                   | 605                   | SMS605                  |
| HBL600B                     | 600B                  | N/A                     |
| HBL605K                     | 605K                  | N/A                     |
| HBL500TFIV                  | N/A                   | N/A                     |
| HBL50010IV                  | V500                  | SMS500                  |
| HBL5005IV                   | V500-5                | N/A                     |
| HBL504IV                    | V504                  | SMS504                  |
| HBL506IV                    | V506                  | SMS506                  |
| HBL511IV                    | V511                  | SMS511                  |
| HBL512IV                    | V512                  | SMS512                  |
| HBL517IV                    | V517                  | SMS517                  |
| HBL518IV                    | V518                  | SMS518                  |
| <b>HBL750 Series</b>        | <b>700 Series</b>     |                         |
| HBL607CUT                   | 607                   | SMS607                  |
| HBL702B                     | 702                   | SMS702                  |
| HBL607K                     | 607K                  | N/A                     |
| HBL750TFIV                  | N/A                   | N/A                     |
| HBL75010IV                  | V700                  | SMS700                  |
| HBL7505IV                   | V700-5                | N/A                     |
| HBL704IV                    | V704                  | SMS704                  |
| HBL706IV                    | V706                  | SMS706                  |
| HBL711IV                    | V711                  | SMS711                  |
| HBL712IV                    | V712                  | SMS712                  |
| HBL717IV                    | V717                  | SMS717                  |
| HBL718IV                    | V718                  | SMS718                  |
| <b>HBL500/HBL750 Series</b> | <b>500/700 Series</b> |                         |
| HBL5701C                    | 5701                  | SMS5701                 |
| HBL5709                     | 5709                  | SMS5709                 |
| HBL5780                     | 5780                  | SMS5780                 |
| HBL5781                     | 5781                  | SMS5781                 |
| HBL5782C                    | 5782                  | SMS5782                 |
| HBL5791                     | 5791                  | N/A                     |
| HBL5709GC                   | 5709GC                | N/A                     |
| HBL5781A                    | 5781A                 | SMS5781A                |
| HBL5782A                    | 5782A                 | SMS5782A                |
| HBL5790B                    | 5790B                 | SMS5790B                |
| HBL5752R                    | R5752                 | SMS5752R                |
| HBL5753R                    | R5753                 | SMS5753R                |
| HBL5700FIV                  | V5700F                | SMS5700F                |
| HBL5703IV                   | V5703                 | SMS5703                 |
| HBL5711LHIV                 | V5711LH               | SMS5711LH               |
| HBL5711RHIV                 | V5711RH               | SMS5711RH               |
| HBL5715IV                   | V5715                 | SMS5715                 |
| HBL5719IV                   | V5719                 | SMS5719                 |
| HBL57242IV                  | V57242                | SMS57242                |
| HBL5731IV                   | V5731                 | SMS5731                 |
| HBL5733IV                   | V5733                 | SMS5733                 |
| HBL5735IV                   | V5735                 | SMS5735                 |
| HBL5736IV                   | V5736                 | SMS5736                 |
| HBL5737IV                   | V5737                 | SMS5737                 |
| HBL5737AIV                  | V5737A                | SMS5737A                |
| HBL5738IV                   | V5738                 | SMS5738                 |
| HBL5738AIV                  | V5738A                | SMS5738A                |
| HBL5738AFIV                 | V5738AF               | SMS5738AF               |
| HBL5739IV                   | V5739                 | SMS5739                 |
| HBL5739AIV                  | V5739A                | SMS5739A                |
| HBL5744IV                   | V5744                 | SMS5744                 |
| HBL57442IV                  | V5744-2               | SMS57442                |
| HBL57443IV                  | V5744-3               | SMS57443                |
| HBL5744SIV                  | V5744S                | SMS5744S                |
| HBL5744S2IV                 | V5744S-2              | SMS5744S2               |
| HBL5744S3IV                 | V5744S-3              | SMS5744S3               |
| HBL5745IV                   | V5745                 | SMS5745                 |
| HBL5747IV                   | V5747                 | SMS5747                 |

| Hubbell<br>Catalog Number | Wiremold®          | Mono-<br>Systems, Inc.™ |
|---------------------------|--------------------|-------------------------|
| <b>HBL57472IV</b>         | <b>V5747-2</b>     | <b>SMS57472</b>         |
| <b>HBL57473IV</b>         | <b>V5747-3</b>     | <b>SMS57473</b>         |
| <b>HBL5748IV</b>          | <b>V5748</b>       | <b>SMS5748</b>          |
| <b>HBL57482IV</b>         | <b>V5748-2</b>     | <b>SMS57482</b>         |
| <b>HBL57483IV</b>         | <b>V5748-3</b>     | <b>SMS57483</b>         |
| <b>HBL57484IV</b>         | <b>V5748-4</b>     | <b>SMS57484</b>         |
| <b>HBL57485IV</b>         | <b>V5748-5</b>     | <b>SMS57485</b>         |
| <b>HBL57486IV</b>         | <b>V5748-6</b>     | <b>SMS57486</b>         |
| <b>HBL5751IV</b>          | <b>V5751</b>       | <b>SMS5751</b>          |
| <b>HBL57512IV</b>         | <b>V5751-2</b>     | <b>SMS5751-2</b>        |
| <b>HBL57513IV</b>         | <b>V5751-3</b>     | <b>SMS5751-3</b>        |
| <b>HBL5751AIV</b>         | <b>V5751A</b>      | <b>N/A</b>              |
| <b>HBL5752IV</b>          | <b>V5752</b>       | <b>SMS5752</b>          |
| <b>HBL5753IV</b>          | <b>V5753</b>       | <b>SMS5753</b>          |
| <b>HBL5760IV</b>          | <b>V5760</b>       | <b>SMS5760</b>          |
| <b>HBL5783IV</b>          | <b>V5783</b>       | <b>SMS5783</b>          |
| <b>HBL5784IV</b>          | <b>V5784</b>       | <b>SMS5784</b>          |
| <b>HBL5785IV</b>          | <b>V5785</b>       | <b>SMS5785</b>          |
| <b>HBL5786IV</b>          | <b>V5786</b>       | <b>SMS5786</b>          |
| <b>HBL5786AIV</b>         | <b>N/A</b>         | <b>N/A</b>              |
| <b>HBL5711BRIV</b>        | <b>N/A</b>         | <b>SMS5711-1</b>        |
| <b>HBL5715BRIV</b>        | <b>N/A</b>         | <b>N/A</b>              |
| <b>HBL5717BRIV</b>        | <b>N/A</b>         | <b>SMS5717-1</b>        |
| <b>HBL5718BRIV</b>        | <b>N/A</b>         | <b>SMS5718-1</b>        |
| <b>HBL2000 Series</b>     | <b>2000 Series</b> |                         |
| HBL620C                   | 620                | SMS621BC                |
| HBL2001C                  | 2001               | SMS2101                 |
| HBL2003SC                 | 2003               | SMS2103                 |
| HBL2009GC                 | 2009               | SMS2109                 |
| HBL2000WC                 | 2000WC             | SMS2100WC               |
| HBL2000WCA                | N/A                | N/A                     |
| HBL2017TC                 | 2017TC             | SMS2117TC               |
| HBL620BCK                 | 620BCK             | N/A                     |
| HBL2000B5GY               | G2000B-5           | N/A                     |
| HBL2000BCGY               | G2000BC            | N/A                     |
| HBL2000BCAGY              | N/A                | N/A                     |
| HBL2000CGY                | G2000C             | N/A                     |
| HBL2000CAGY               | G2100C             | N/A                     |
| HBL2006GY                 | G2006              | N/A                     |
| HBL2010A2GY               | G2010A2            | N/A                     |
| HBL2010A3GY               | G2010A3            | N/A                     |
| HBL2010BGY                | G2010B             | N/A                     |
| HBL2011GY                 | G2011              | N/A                     |
| HBL2011BRGY               | N/A                | N/A                     |
| HBL2015GY                 | G2015              | N/A                     |
| HBL2015BRGY               | N/A                | N/A                     |
| HBL2017BRGY               | N/A                | N/A                     |
| HBL2018BRGY               | N/A                | N/A                     |
| HBL2018CGY                | G2018C             | N/A                     |
| HBL2048GY                 | G2048              | N/A                     |
| HBL20482GY                | G2048-2            | N/A                     |
| HBL2051HGY                | G2051H             | N/A                     |
| HBL2000TFIV               | N/A                | N/A                     |
| HBL2000TFGY               | N/A                | N/A                     |
| HBL2000B5IV               | V2000B-5           | N/A                     |
| HBL2000BCIV               | V2000BC            | SMS2100B                |
| HBL2000BCAIV              | N/A                | N/A                     |
| HBL2000CIV                | V2000C             | SMS2100C                |
| HBL2000CAIV               | V2100C             | SMS2100C                |
| HBL2006IV                 | V2006              | SMS2106                 |
| HBL2010A2IV               | V2010A2            | SMS2110A                |
| HBL2010A3IV               | V2010A3            | SMS2110C                |
| HBL2010BIV                | V2010B             | SMS2110B                |
| HBL2011IV                 | V2011              | SMS2111                 |
| HBL2011BRIV               | N/A                | SMS2111-FO              |
| HBL2015IV                 | V2015              | SMS2115                 |
| HBL2015BRIV               | N/A                | SMS2115-FO              |
| HBL2017BRIV               | N/A                | SMS2117TC-FO            |

Wiremold® is a registered trademark of The Wiremold Company. Mono-Systems, Inc.™ is a trademark of Mono-Systems, Inc. Hubbell Inc. is not affiliated with Mono-Systems, Inc.™ or The Wiremold Company.

# Metal Raceway Cross Reference

HBL2400/HBL2400D, HBL3000 and HBL4750 Series



| Hubbell<br>Catalog Number  | Wiremold®            | Mono-<br>Systems, Inc.™ | Hubbell<br>Catalog Number | Wiremold®   | Mono-<br>Systems, Inc.™ |
|----------------------------|----------------------|-------------------------|---------------------------|-------------|-------------------------|
| HBL2018BRIV                | N/A                  | SMS2118A-FO             | HBL3007CGY                | G3007C      | SMS3022                 |
| HBL2018CIV                 | V2018C               | SMS2118A                | HBL3010AEGY               | G3010AE     | SMS3005                 |
| HBL2048IV                  | V2048                | SMS2141                 | HBL3010BGY                | G3010B      | SMS3004                 |
| HBL20482IV                 | V2048-2              | SMS21412                | HBL3010CGY                | G3010C      | SMS3005                 |
| HBL2051HIV                 | V2051H               | SMS2051H                | HBL3011EGY                | G3011E      | SMS3009                 |
| HBL2089IV                  | V2089                | N/A                     | HBL3014CGY                | G3014C      | SMS3030                 |
| HBL2089EIV                 | V2089E               | N/A                     | HBL3015EGY                | G3015E      | SMS3010                 |
|                            |                      |                         | HBL3017TCEGY              | G3017TCE    | SMS3014                 |
| HBL2400/HBL2400D<br>Series | 2400/2400D<br>Series |                         | HBL3018AEGY               | G3018AE     | SMS3018                 |
| HBL624CUT                  | 624                  | N/A                     | HBL3027AEGY               | G3027AE     | N/A                     |
| HBL2401C                   | 2401                 | SMS2401                 | HBL3028GY                 | G3028       | SMS3028                 |
| HBL2409GC                  | 2409                 | SMS2409                 | HBL3033JEGY               | G3033JE     | SMS3045                 |
| HBL2400WC                  | 2400WC               | SMS2400WC               | HBL3036HEGY               | G3036HE     | SMS3053                 |
| HBL2401DC                  | 2401D                | N/A                     | HBL3040CEGY               | G3040CE     | SMS3048                 |
| HBL624BCK                  | 624BCK               | N/A                     | HBL3043BEGY               | G3043BE     | SMS3046                 |
| HBL24DRK                   | N/A                  | N/A                     | HBL30442GY                | G3044-2     | SMS3062                 |
| HBL24SRK                   | N/A                  | N/A                     | HBL3046BEGY               | G3046BE     | N/A                     |
| HBL24106DRK                | N/A                  | N/A                     | HBL3046H2GY               | G3046H-2    | N/A                     |
| HBL24106RRK                | N/A                  | N/A                     | HBL3048RGY                | G3048R      | SMS3023                 |
| HBL4724REDIV               | N/A                  | N/A                     | HBL3051LEGY               | G3051LE     | SMS3051                 |
| HBL2420REDIV               | N/A                  | N/A                     | HBL3082GY                 | G3082       | N/A                     |
| HBL2400TFIV                | N/A                  | N/A                     | HBL3086GY                 | G3086       | SMS3086                 |
| HBL2400DTFIV               | N/A                  | N/A                     | HBL3200REDIV              | N/A         | N/A                     |
| HBL2400BIV                 | V2400B               | N/A                     | HBL3200REDGY              | N/A         | N/A                     |
| HBL2400B10IV               | V2400B-10            | SMS2400B                | HBL3000TFIV               | N/A         | N/A                     |
| HBL2400BCIV                | V2400BC              | N/A                     | HBL3000TFGY               | N/A         | N/A                     |
| HBL2400BDIV                | V2400BD              | SMS2400BD               | HBL3000BIV                | V3000B      | SMS3000-I               |
| HBL2400CIV                 | V2400C               | SMS2400C                | HBL3000C075IV             | V3000C075   | N/A                     |
| HBL2406IV                  | V2406                | SMS2406                 | HBL3000C195IV             | V3000C195   | N/A                     |
| HBL2410AIV                 | V2410A               | N/A                     | HBL3000CEIV               | V3000CE     | SMS3003-I               |
| HBL2410BIV                 | V2410B               | SMS2410B                | HBL3003IV                 | V3003       | SMS3008-I               |
| HBL2410BDIV                | V2410BD              | N/A                     | HBL3006EIV                | V3006E      | SMS3007-I               |
| HBL2410CIV                 | V2410C               | N/A                     | HBL3010AEIV               | V3010AE     | SMS3005-I               |
| HBL2410DFOIV               | V2410DFO             | N/A                     | HBL3010BIV                | V3010B      | SMS3004-I               |
| HBL2410FCIV                | V2410FC              | SMS2410C                | HBL3010CIV                | V3010C      | SMS3005-I               |
| HBL2411DFOIV               | V2411DFO             | SMS2411DFO              | HBL3011EIV                | V3011E      | SMS3009-I               |
| HBL2415DFOIV               | V2411DFO             | SMS2415DFO              | HBL3014CIV                | V3014C      | SMS3030-I               |
| HBL2411IV                  | V2411FO              | SMS2411FO               | HBL3015EIV                | V3015E      | SMS3010-I               |
| HBL2415IV                  | V2415FO              | SMS2415FO               | HBL3017TCEIV              | V3017TCE    | SMS3014-I               |
| HBL2417DFOIV               | V2417DFO             | SMS2417DFO              | HBL3018AEIV               | V3018AE     | SMS3018-I               |
| HBL2417IV                  | V2417FO              | SMS2417FO               | HBL3027AEIV               | V3027AE     | N/A                     |
| HBL2418DFOIV               | V2418DFO             | SMS2418DFO              | HBL3028IV                 | V3028       | SMS3028-I               |
| HBL2418IV                  | V2418FO              | SMS2418FO               | HBL3033JEIV               | V3033JE     | SMS3045-I               |
| HBL2426IV                  | V2426                | N/A                     | HBL3036HEIV               | V3036HE     | SMS3053-I               |
| HBL2444IV                  | V2444                | SMS2444                 | HBL3040CEIV               | V3040CE     | SMS3048-I               |
| HBL24442IV                 | V2444-2              | SMS2444-2               | HBL3043BEIV               | V3043BE     | SMS3046-I               |
| HBL2444DIV                 | V2444D               | SMS2444D                | HBL30442IV                | V3044-2     | SMS3062-I               |
| HBL2444D2AIV               | V2444D-2A            | SMS2444D-2              | HBL3046BEIV               | V3046BE     | N/A                     |
| HBL2448IV                  | V2448                | SMS2448                 | HBL3046H2IV               | V3046H-2    | N/A                     |
| HBL24482IV                 | V2448-2              | N/A                     | HBL3048RIV                | V3048R      | SMS3023-I               |
| HBL2451HIV                 | V2451H               | N/A                     | HBL3051LEIV               | V3051LE     | SMS3051-I               |
| HBL2475DBRIV               | V2475D               | SMS2475B                | HBL3086IV                 | V3086       | SMS3086-I               |
| HBL2489IV                  | V2489                | N/A                     |                           |             |                         |
| HBL3000 Series             | 3000 Series          |                         | HBL4750 Series            | 4000 Series |                         |
| HBL630B                    | 630B                 | SMS632B                 | HBL4751AC                 | 4001A       | SMS4202                 |
| HBL630BDK                  | 630BDK               | N/A                     | HBL4750IV                 | V4050       | N/A                     |
| HBL630C                    | 630C                 | SMS632C                 | HBL640C                   | 640C        | SMS642C                 |
| HBL630CDK                  | 630CDK               | N/A                     | HBL4750B10GY              | G4000B-10   | SMS4200                 |
| HBL3000BGY                 | G3000B               | SMS3200                 | HBL4750C075GY             | G4000C075   | SMS4261                 |
| HBL3000C075GY              | G3000C075            | N/A                     | HBL4750C195GY             | G4000C195   | SMS4265                 |
| HBL3000C195GY              | G3000C195            | N/A                     | HBL640B                   | 640B        | SMS642B                 |
| HBL3000CEGY                | G3000CE              | SMS3003                 | HBL4747RXIV               | V4047RX     | N/A                     |
| HBL3000WCGY                | G3000WC              | SMS3006                 | HBL4747RFIV               | V4047RF     | N/A                     |
| HBL3001GY                  | G3001                | SMS3002                 | HBL4747C1GY               | G4047C-1    | N/A                     |
| HBL3001AGY                 | G3001A               | SMS3001                 | HBL4747BXGY               | G4047BX     | N/A                     |
| HBL3003GY                  | G3003                | SMS3008                 | HBL4747RXGY               | G4047RX     | N/A                     |
| HBL3006EGY                 | G3006E               | SMS3007                 | HBL4747RFGY               | G4047RF     | N/A                     |
|                            |                      |                         | HBL4747JXGY               | G4047JX     | N/A                     |
|                            |                      |                         | HBL4747C2GY               | G4047C-2    | N/A                     |

Wiremold® is a registered trademark of The Wiremold Company. Mono-Systems, Inc.™ is a trademark of Mono-Systems, Inc.  
Hubbell Inc. is not affiliated with Mono-Systems, Inc.™ or The Wiremold Company.

# Metal Raceway HBL4750 and HBL6750 Series

HBL4750 and HBL6750 Series



| Hubbell<br>Catalog Number | Wiremold®   | Mono-<br>Systems, Inc.™ |
|---------------------------|-------------|-------------------------|
| HBL4715DFOGY              | G4015DFO    | SMS4211FO               |
| HBL4717NGY                | G4017N      | N/A                     |
| HBL4746H2GY               | G4046H-2    | N/A                     |
| HBL4718DFOGY              | G4018FO     | SMS4218FO               |
| HBL47472BBFFGY            | G4047-2BBFF | N/A                     |
| HBL47472BBBBBGY           | G4047-2BBBB | N/A                     |
| HBL47472BBSSGY            | G4047-2BBSS | N/A                     |
| HBL47472BBXXGY            | G4047-2BBXX | N/A                     |
| HBL47472BBTTGY            | G4047-2BBTT | N/A                     |
| HBL4747AXGY               | G4047AX     | N/A                     |
| HBL47472RRXXGY            | G4047-2RRXX | N/A                     |
| HBL4747BFGY               | G4047BF     | N/A                     |
| HBL4747BBGY               | G4047BB     | N/A                     |
| HBL4747BRGY               | N/A         | N/A                     |
| HBL4747BRIV               | N/A         | N/A                     |
| HBL4747BTGY               | G4047BT     | N/A                     |
| HBL4747BSGY               | G4047BS     | N/A                     |
| HBL4774AGY                | G4074A      | N/A                     |
| HBL4750GY                 | G4050       | N/A                     |
| HBL47472RRXXIV            | V4047-2RRXX | N/A                     |
| HBL47472BBXXIV            | V4047-2BBXX | N/A                     |
| HBL4747BBIV               | V4047BB     | N/A                     |
| HBL4747AXIV               | V4047AX     | N/A                     |
| HBL4747BFIV               | V4047BF     | N/A                     |
| HBL4747BTIV               | V4047BT     | N/A                     |
| HBL4747BSIV               | V4047BS     | N/A                     |
| HBL4747C1IV               | V4047C-1    | N/A                     |
| HBL4747BXIV               | V4047BX     | N/A                     |
| HBL4747JXIV               | V4047JX     | N/A                     |
| HBL4747C2IV               | V4047C-2    | N/A                     |
| HBL4750CIV                | V4000C      | SMS4203-I               |
| HBL4750B10IV              | V4000B-10   | SMS4200-I               |
| HBL4750C315IV             | V4000C315   | SMS4267-I               |
| HBL4750C195IV             | V4000C195   | SMS4265-I               |
| HBL4711DFOIV              | V4011FO     | SMS4209FI               |
| HBL4711IV                 | V4011       | SMS4209-I               |
| HBL4710DFOIV              | V4010DFO    | SMS4205-I               |
| HBL4710IV                 | V4010       | SMS4205-I               |
| HBL4710BIV                | V4010B      | SMS4204-I               |
| HBL4756AIV                | V4006       | N/A                     |
| HBL4714AIV                | V4014A      | SMS4230-I               |
| HBL4712TXIV               | V4012TX     | SMS4215-I               |
| HBL4750C135IV             | V4000C135   | SMS4263-I               |
| HBL4750C075IV             | V4000C075   | SMS4261-I               |
| HBL4717DFOIV              | V4017FO     | SMS4214FI               |
| HBL4717IV                 | V4017       | SMS4214-I               |
| HBL4715DFOIV              | V4015DFO    | SMS4211FI               |
| HBL4715IV                 | V4015       | SMS4211-I               |
| HBL4718DFOIV              | V4018FO     | SMS4218FI               |
| HBL4718IV                 | V4018       | SMS4218-I               |
| HBL4717NIV                | V4017N      | N/A                     |
| HBL47472BBBBIV            | V4047-2BBBB | N/A                     |
| HBL4746H2IV               | V4046H-2    | N/A                     |
| HBL47472BBTTIV            | V4047-2BBTT | N/A                     |
| HBL47472BBSSIV            | V4047-2BBSS | N/A                     |
| HBL4747CVMGY              | G6007C-1    | N/A                     |
| HBL4786AGY                | G4086A      | SMS4286                 |
| HBL4750TFIV               | N/A         | N/A                     |
| HBL4747CVM2GY             | G6007C-2    | N/A                     |
| HBL4750BP                 | N/A         | N/A                     |
| HBL4750TFGY               | N/A         | N/A                     |
| HBL4756AGY                | G4006       | N/A                     |
| HBL4751DA                 | 4001DA      | SMS4201                 |
| HBL640BDK                 | 640BDK      | N/A                     |
| HBL640CDK                 | 640CDK      | N/A                     |
| HBL4750CGY                | G4000C      | SMS4203                 |
| HBL4750C135GY             | G4000C135   | SMS4263                 |
| HBL4750C315GY             | G4000C315   | SMS4267                 |
| HBL4750DGY                | G4000D      | SMS4207                 |

| Hubbell<br>Catalog Number | Wiremold® | Mono-<br>Systems, Inc.™                                              |
|---------------------------|-----------|----------------------------------------------------------------------|
| HBL4750WCGY               | G4000WC   | SMS4206                                                              |
| HBL4710BGY                | G4010B    | SMS4204                                                              |
| HBL4710DFOGY              | G4010DFO  | SMS4205                                                              |
| HBL4710GY                 | G4010     | SMS4205                                                              |
| HBL4711DFOGY              | G4011FO   | SMS4209FO                                                            |
| HBL4711GY                 | G4011     | SMS4209                                                              |
| HBL4712TXGY               | G4012TX   | SMS4215                                                              |
| HBL4714AGY                | G4014A    | SMS4230                                                              |
| HBL4717DFOGY              | G4017FO   | SMS4214FO                                                            |
| HBL4717GY                 | G4017     | SMS4214                                                              |
| HBL4717TCAGY              | G4017TCA  | N/A                                                                  |
| HBL4774AIV                | V4074A    | N/A                                                                  |
| HBL4786AIV                | V4086A    | SMS4286-I                                                            |
| HBL4747CVMIV              | V6007C-1  | N/A                                                                  |
| HBL4747CVM2IV             | V6007C-2  | N/A                                                                  |
| <b>HBL6750 Series</b>     |           | <b>6000 Series</b>                                                   |
| HBL6751A                  | 6001A     | SMS4402                                                              |
| HBL660C                   | 640C      | SMS644C                                                              |
| HBL660CDK                 | 640CDK    | N/A                                                                  |
| HBL660B                   | 660B      | SMS644B                                                              |
| HBL660BDK                 | 660BDK    | N/A                                                                  |
| HBL6718DFOGY              | G4018FO   | N/A                                                                  |
| HBL6718GY                 | G6017TX   | SMS4418                                                              |
| HBL6746HHHGY              | G4046H-2  | N/A                                                                  |
| HBL67473BBBBBBBGY         |           | (4000 Series 2-Gang)<br>G4047-2BBBB                                  |
| HBL67473BBBBFFGY          |           | (4000 Series 2-Gang)<br>G4047-2BBFF                                  |
| HBL67473BBBBSSGY          |           | (4000 Series 2-Gang)<br>G4047-2BBSS                                  |
| HBL67473BBBBTTGY          |           | (4000 Series 2-Gang)<br>G4047-2BBTT                                  |
| HBL67473BBBBXXGY          |           | (4000 Series 2-Gang)<br>G4047-2BBXX                                  |
| HBL6747AXXGY              |           | (4000 Series 2-Gang)<br>G4047AX                                      |
| HBL6747BBBGY              |           | (4000 Series 2-Gang)<br>G4047BB                                      |
| HBL6747BFBGY              |           | (4000 Series 2-Gang)<br>G4047BF                                      |
| HBL6747BBSGY              |           | (4000 Series 2-Gang)<br>G4047BS                                      |
| HBL6747BBTGY              |           | (4000 Series 2-Gang)<br>G4047BT                                      |
| HBL6747BXXGY              |           | (4000 Series 2-Gang)<br>G4047BX                                      |
| HBL6747C1GY               |           | (4000 Series 2-Gang)<br>V4047C-1 (4000 Series<br>1-Gang Overlapping) |
| HBL6747C2GY               |           | (4000 Series 2-Gang)<br>V4047C-2 (4000 Series<br>2-Gang Overlapping) |
| HBL6747JXXGY              |           | (4000 Series 2-Gang)<br>G4047JX                                      |
| HBL6747RRFGY              |           | (4000 Series 2-Gang)<br>G4047RF                                      |
| HBL6747RXXGY              |           | (4000 Series 2-Gang)<br>G4047RX                                      |
| HBL67473RRRRXXGY          |           | (4000 Series 2-Gang)<br>G4047-2RRXX                                  |
| HBL6750GY                 | G4050     | N/A                                                                  |
| HBL6750B10GY              | G6000B-10 | SMS4400                                                              |
| HBL6750CGY                | G6000C    | SMS4203                                                              |
| HBL6750DAGY               | G6000DA   | SMS4407                                                              |
| HBL6750WCGY               | G6000WC   | SMS4406                                                              |
| HBL6751DAGY               | G6001DA   | SMS4401                                                              |
| HBL6756AGY                | G6006     | SMS4408                                                              |
| HBL6710BGY                | G6010B    | SMS4404                                                              |
| HBL6711DFOGY              | G6011TX   | SMS4419                                                              |
| HBL6711GY                 | G6011TX   | SMS4419                                                              |

Wiremold® is a registered trademark of The Wiremold Company. Mono-Systems, Inc.™ is a trademark of Mono-Systems, Inc.  
Hubbell Inc. is not affiliated with Mono-Systems, Inc.™ or The Wiremold Company.



| Hubbell<br>Catalog Number | Wiremold®             | Mono-<br>Systems, Inc.™ |
|---------------------------|-----------------------|-------------------------|
| HBL6712TXGY               | G6012TX               | SMS4415                 |
| HBL6714AGY                | G6014A                | SMS4430                 |
| HBL6717DFOGY              | G6017TX               | SMS4418                 |
| HBL6717GY                 | G6017TX               | SMS4418                 |
| HBL6774AGY                | G6074A                | SMS4473                 |
| HBL6786GY                 | G6086                 | SMS4486                 |
| HBL6750C075IV             | N/A                   | N/A                     |
| HBL6750C075GY             | N/A                   | N/A                     |
| HBL6750C135IV             | N/A                   | N/A                     |
| HBL6750C135GY             | N/A                   | N/A                     |
| HBL6750C195IV             | N/A                   | N/A                     |
| HBL6750C195GY             | N/A                   | N/A                     |
| HBL6750C315IV             | N/A                   | N/A                     |
| HBL6750C315GY             | N/A                   | N/A                     |
| HBL6715DFOIV              | N/A                   | SMS4410-I               |
| HBL6715IV                 | N/A                   | SMS4410-I               |
| HBL6715DFOGY              | N/A                   | N/A                     |
| HBL6715GY                 | N/A                   | SMS4410                 |
| HBL6717NIV                | N/A                   | N/A                     |
| HBL6717NGY                | N/A                   | N/A                     |
| HBL6717TCAGY              | N/A                   | N/A                     |
| HBL6710DFOIV              | N/A                   | N/A                     |
| HBL6710DFOGY              | N/A                   | N/A                     |
| HBL6750TFIV               | N/A                   | N/A                     |
| HBL6750TFGY               | N/A                   | N/A                     |
| HBL6718DFOIV              | V4018FO               | N/A                     |
| HBL6746HHHIV              | V4046H-2              | N/A                     |
|                           | (4000 Series 2-Gang)  |                         |
| HBL67473BBBBXXGY          | V4047-2BBBB           | N/A                     |
|                           | (4000 Series 2-Gang)  |                         |
| HBL67473BBBBFFIV          | V4047-2BBFF           | N/A                     |
|                           | (4000 Series 2-Gang)  |                         |
| HBL67473BBBBSSIV          | V4047-2BBSS           | N/A                     |
|                           | (4000 Series 2-Gang)  |                         |
| HBL67473BBBBTTIV          | V4047-2BBTT           | N/A                     |
|                           | (4000 Series 2-Gang)  |                         |
| HBL67473BBBBXXIV          | V4047-2BBXX           | N/A                     |
|                           | (4000 Series 2-Gang)  |                         |
| HBL6747AXXIV              | V4047AX               | N/A                     |
|                           | (4000 Series 2-Gang)  |                         |
| HBL6747BBBIV              | V4047BB               | N/A                     |
|                           | (4000 Series 2-Gang)  |                         |
| HBL6747BBFIV              | V4047BF               | N/A                     |
|                           | (4000 Series 2-Gang)  |                         |
| HBL6747BBSIV              | V4047BS               | N/A                     |
|                           | (4000 Series 2-Gang)  |                         |
| HBL6747BBTIV              | V4047BT               | N/A                     |
|                           | (4000 Series 2-Gang)  |                         |
| HBL6747BXXIV              | V4047BX               | N/A                     |
|                           | (4000 Series 2-Gang)  |                         |
| HBL6747C1IV               | V4047C-1 (4000 Series | N/A                     |
|                           | 1-Gang Overlapping)   |                         |
| HBL6747C2IV               | V4047C-2 (4000 Series | N/A                     |
|                           | 2-Gang Overlapping)   |                         |
| HBL6747JXXIV              | V4047JX               | N/A                     |
|                           | (4000 Series 2-Gang)  |                         |
| HBL6747RRFIV              | V4047RF               | N/A                     |
|                           | (4000 Series 2-Gang)  |                         |
| HBL6747RXXIV              | V4047RX               | N/A                     |
|                           | (4000 Series 2-Gang)  |                         |
| HBL67473RRRRXXIV          | V4047-2RRXX           | N/A                     |
| HBL6750IV                 | V4050                 | N/A                     |
| HBL6750B10IV              | V6000B-10             | SMS4400-I               |
| HBL6750CIV                | V6000C                | SMS4203-I               |
| HBL6756AIV                | V6006                 | SMS4408-I               |
| HBL6710BIV                | V6010B                | SMS4404-I               |
| HBL6711DFOIV              | V6011TX               | SMS4419-I               |

| Hubbell<br>Catalog Number | Wiremold®  | Mono-<br>Systems, Inc.™ |
|---------------------------|------------|-------------------------|
| HBL6711IV                 | V6011TX    | SMS4419-I               |
| HBL6712TXIV               | V6012TX    | SMS4415-I               |
| HBL6714AIV                | V6014A     | SMS4430-I               |
| HBL6774AIV                | V6074A     | SMS4473-I               |
| HBL6786IV                 | V6086      | SMS4486-I               |
| <b>Metal PlugTrak®</b>    |            |                         |
| HBL20C215IV               | V20-C2     | SSC40                   |
| HBL20C215GY               | G20-C2     | N/A                     |
| HBL20C315IV               | N/A        | SSC52                   |
| HBL20C315GY               | N/A        | N/A                     |
| HBL20GB306GY              | G20GB306   | N/A                     |
| HBL20IG306GY              | G20IG306   | N/A                     |
| HBL20GB506GY              | G20GB506   | N/A                     |
| HBL20GB512GY              | G20GB512   | N/A                     |
| HBL20GB606GY              | G20GB606   | N/A                     |
| HBL20GB609GY              | G20GB609   | N/A                     |
| HBL20GB612GY              | G20GB612   | N/A                     |
| HBL20GB618GY              | G20GB618   | N/A                     |
| HBL20GBA512GY             | G20GBA512  | N/A                     |
| HBL20GBA609GY             | G20GBA609  | N/A                     |
| HBL20GBA612GY             | G20GBA612  | N/A                     |
| HBL20GBA618GY             | G20GBA618  | N/A                     |
| HBL20IG512GY              | G20IG512   | N/A                     |
| HBL20IG606GY              | G20IG606   | N/A                     |
| HBL24GB306GY              | G24GB306   | N/A                     |
| HBL24GB506GY              | G24GB506   | N/A                     |
| HBL24GB512GY              | G24GB512   | N/A                     |
| HBL24GBA512GY             | G24GBA512  | N/A                     |
| HBL24GB606GY              | G24GB606   | N/A                     |
| HBL24GB612GY              | G24GB612   | N/A                     |
| HBL24GB618GY              | G24GB618   | N/A                     |
| HBL24GBA612GY             | G24GBA612  | N/A                     |
| HBL24GBA618GY             | G24GBA618  | N/A                     |
| HBL20GB306IV              | V20GB306   | 19GB306                 |
| HBL20IG306IV              | V20IG306   | 19IG306                 |
| HBL20GB506IV              | V20GB506   | 19GB506                 |
| HBL20GB512IV              | V20GB512   | 19GB512                 |
| HBL20GB606IV              | V20GB606   | 19GB606                 |
| HBL20GB609IV              | V20GB609   | 19GB609                 |
| HBL20GB612IV              | V20GB612   | 19GB612                 |
| HBL20GB618IV              | V20GB618   | 19GB618                 |
| HBL20GBA512IV             | V20GBA512  | 19GBA512                |
| HBL20GBA609IV             | V20GBA609  | 19GBA609                |
| HBL20GBA612IV             | V20GBA612  | 19GBA612                |
| HBL20GBA618IV             | V20GBA618  | 19GBA618                |
| HBL20IG512IV              | V20IG512   | 19IG512                 |
| HBL20IG606IV              | V20IG606   | 19IG606                 |
| HBL24GB306IV              | V24GB306   | 192GB306                |
| HBL24GB506IV              | V24GB506   | 192GB506                |
| HBL24GB512IV              | V24GB512   | 192GB512                |
| HBL24GBA512IV             | V24GBA512  | 192GBA512               |
| HBL24GB606IV              | V24GB606   | 192GB606                |
| HBL24GB612IV              | V24GB612   | 192GB612                |
| HBL24GB618IV              | V24GB618   | 192GB618                |
| HBL24GBA612IV             | V24GBA612  | 192GBA612               |
| HBL24GBA618IV             | V24GBA618  | 192GBA618               |
| <b>HBLALU2000 Series</b>  |            |                         |
| HBLALU2000B10             | AL2000B-10 | N/A                     |
| HBLALU2000B5              | AL2000B-5  | N/A                     |
| HBLALU2000C5              | AL2000C-5  | N/A                     |
| HBLALU2000WC              | AL2000WC   | N/A                     |
| HBLALU2001                | AL2001     | N/A                     |
| HBLALU2003                | AL2003     | N/A                     |
| HBLALU2006                | AL2006     | N/A                     |
| HBLALU2009                | AL2009     | N/A                     |
| HBLALU2010A               | AL2010A    | N/A                     |
| <b>ALA2000 Series</b>     |            |                         |
|                           |            |                         |

Wiremold® is a registered trademark of The Wiremold Company. Mono-Systems, Inc.™ is a trademark of Mono-Systems, Inc. Hubbell Inc. is not affiliated with Mono-Systems, Inc.™ or The Wiremold Company.



| Hubbell<br>Catalog Number | Wiremold® | Mono-<br>Systems, Inc.™ |
|---------------------------|-----------|-------------------------|
| HBLALU2010B               | AL2010B   | N/A                     |
| HBLALU2011                | AL2011    | N/A                     |
| HBLALU2015                | AL2015    | N/A                     |
| HBLALU2017                | AL2017    | N/A                     |
| HBLALU2018                | AL2018    | N/A                     |
| HBLALU2038                | AL2038    | N/A                     |
| HBLALU2040A               | AL2040A   | N/A                     |
| HBLALU2043                | AL2043    | N/A                     |
| HBLALU2044                | AL2044    | N/A                     |
| HBLALU20442               | AL2044-2  | N/A                     |
| HBLALU2047                | AL2047    | N/A                     |
| HBLALU20472               | AL2047-2  | N/A                     |
| HBLALU2051H               | AL2051H   | N/A                     |

| Aluminum<br>PlugTrak® | Aluminum Plugmold® |     |
|-----------------------|--------------------|-----|
| HBLALU20GB306         | AL20GB306          | N/A |
| HBLALU20GB506         | AL20GB506          | N/A |
| HBLALU20GB512         | AL20GB512          | N/A |
| HBLALU20GB606         | AL20GB606          | N/A |
| HBLALU20GB612         | AL20GB612          | N/A |
| HBLALU20GB618         | AL20GB618          | N/A |
| HBLALU20GBA606        | AL20GBA606         | N/A |
| HBLALU20GBA612        | AL20GBA612         | N/A |
| HBLALU20GBA618        | AL20GBA618         | N/A |
| HBLALU20IG306         | AL20IG306          | N/A |
| HBLALU20IG506         | AL20IG506          | N/A |
| HBLALU20IG606         | AL20IG606          | N/A |
| HBLALU24GB306         | N/A                | N/A |
| HBLALU24IG306         | N/A                | N/A |
| HBLALU24GB506         | N/A                | N/A |
| HBLALU24GB512         | N/A                | N/A |
| HBLALU24IG506         | N/A                | N/A |
| HBLALU24GB606         | N/A                | N/A |
| HBLALU24GB612         | N/A                | N/A |
| HBLALU24GB618         | N/A                | N/A |
| HBLALU24GBA606        | N/A                | N/A |
| HBLALU24GBA612        | N/A                | N/A |
| HBLALU24GBA618        | N/A                | N/A |
| HBLALU24IG606         | N/A                | N/A |

| HBLALU3800 Series | ALA3800 Series |         |
|-------------------|----------------|---------|
| HBLALU3800B10     | ALA3800B-10    | SWA3300 |
| HBLALU3806        | ALA3806        | SWA3306 |
| HBLALU3810B       | ALA3810B       | SWA3304 |
| HBLALU3810B1      | ALA3810B1      | SWA3304 |
| HBLALU3811        | ALA3811        | SWA3309 |
| HBLALU3815        | ALA3815        | SWA3310 |
| HBLALU3817        | ALA3817        | SWA3314 |
| HBLALU3817N       | ALA3817N       | N/A     |
| HBLALU3818        | ALA3818        | SWA3318 |
| HBLALUC5          | ALAC-5         | SWA3303 |
| HBLALUWC          | ALAWC          | N/A     |

| Hubbell<br>Catalog Number | Wiremold®      | Mono-<br>Systems, Inc.™ |
|---------------------------|----------------|-------------------------|
| HBLALU4800 Series         | ALA4800 Series |                         |
| HBLALU01                  | ALA01          | SWA4802                 |
| HBLALU09                  | ALA09          | SWA33GC                 |
| HBLALU17A                 | ALA17A         | N/A                     |
| HBLALU4800B10             | ALA4800B-10    | SWA4804                 |
| HBLALU4806                | ALA4806        | SWA4806                 |
| HBLALU4810B               | ALA4810B       | SWA4804                 |
| HBLALU4810B2              | ALA4810B2      | SWA4804                 |
| HBLALU4811                | ALA4811        | SWA4809                 |
| HBLALU4815                | ALA4815        | SWA4810                 |
| HBLALU4817                | ALA4817        | SWA4814                 |
| HBLALU4817N               | ALA4817N       | SWA4817                 |
| HBLALU4818                | ALA4818        | SWA4818                 |
| HBLALUABRT                | ALA-ABRT       | N/A                     |
| HBLALUBL                  | ALA-BL         | N/A                     |
| HBLALUDR                  | ALA-DR         | SWA3346/SWA4846         |
| HBLALUE                   | ALA-E          | SWA3325/SWA4825         |
| HBLALUF                   | ALA-F          | SWA3345/SWA4826         |
| HBLALUG                   | ALA-G          | SWA3323/SWA4823         |
| HBLALUJ                   | ALA-J          | SWA4845                 |
| HBLALUN                   | ALA-N          | SWA3348/SWA4848         |
| HBLALULPB                 | N/A            | N/A                     |

| Touch-Up Paint | Touch-Up Paint |         |
|----------------|----------------|---------|
| HBLGWEP        | GWE-S          | SMSPT-G |
| HBLIWEP        | IWE-S          | SMSPT-I |



### Complete Line of Raceway

- PolyTrak® Non-Metallic Surface Raceway is a complete system with raceway, fittings, boxes and devices.
- Sizes range from single channel PremiseTrak® to three channel Super BaseTrak® for all types of surface raceway requirements.
- Single and two channel latching raceways are dual-rated for both power and data applications, reducing inventory requirements.
- UL Listed and CSA Certified to 600 volts.
- Office white color.



### Non-Metallic PlugTrak®

- Available as hard wired multi-outlet assembly or relocatable power tap.
- Hubbell designed and manufactured 15 or 20 Amp receptacles.
- UL Listed and CSA Certified.
- Office white color.

#### Hard Wired Multi-Outlet PlugTrak®:

- Available in 5 ft. (1.5m) or 6 ft. (1.8m) lengths.
- Available in single, two circuit and is inherently an isolated ground product.
- Multiple spacing configurations.
- Hard wired PlugTrak® mates with LANTrak® fittings and boxes.
- Tamper-Resistant versions available.

#### Portable PlugTrak®:

- Available in 3 ft. (0.9m) or 5 ft. (1.5m) lengths.
- 6 ft. (1.8m) length 15 or 20 Amp molded cord set allows reliable access.
- Pre-punched holes make mounting easy.



### One Box, Three Systems








- Boxes have three cut-aways that can be utilized with WallTrak®, LANTrak and PremiseTrak (Latching) systems.
- Reduces inventory requirements.
- Eliminates need to order three separate boxes.
- Boxes available in low, standard and deep profiles.
- Two-gang divided box available for power, data, voice, audio and video applications.
- Boxes utilize Hubbell KP plates or Hubbell iSTATION Modules and Bezels.









### Flush or Full Capacity Boxes





- Super BaseTrak® and BaseTrak® Raceway offer multiple solutions for box installation.
- Super BaseTrak® in-line three-gang box allows maximum capacity in a flush design.
- Super BaseTrak® and BaseTrak® available in single, two and three-gang full capacity boxes.
- Two and three channel BaseTrak® (PB2 and PB3) available with one and two-gang in-line boxes.
- Full capacity in-line boxes eliminate the need to de-rate the wire fill capacity due to the intrusion of devices into the raceway channel.

|                  |                                                                                                         |  |                                                                                   |                |                                                                      |                                                                        |
|------------------|---------------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------|----------------|----------------------------------------------------------------------|------------------------------------------------------------------------|
| PT1 PremiseTrak® | Description                                                                                             |  | Color                                                                             | Length         | Without Adhesive                                                     | With Adhesive                                                          |
|                  | <b>Base and Cover</b><br>Single channel raceway.<br>Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths. |  | Office White                                                                      | 5 ft.<br>7 ft. | <b>PT1BC5</b><br><b>PT1BC7</b><br>A: .68" (17.27)<br>B: .75" (19.05) | <b>PT1ABC5</b><br><b>PT1ABC7</b><br>A: .68" (17.27)<br>B: .75" (19.05) |
|                  |                        |  |  |                |                                                                      |                                                                        |

|                                                                                                                                                                         |                                                                                                                                                                         |  |              |                                                                           |                                                                             |                                                                                                                                                                                                                             |  |  |              |                                                                              |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------|---------------------------------------------------------------------------|-----------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|--------------|------------------------------------------------------------------------------|
| Device Boxes                                                                                                                                                            | Description                                                                                                                                                             |  |              | Color                                                                     | Catalog Number                                                              | Description                                                                                                                                                                                                                 |  |  | Color        | Catalog Number                                                               |
|                                                                                                                                                                         | <b>1-Gang Low Profile Box</b><br>For shallow switches and receptacles.<br>See page R-63 for recommended plate options.                                                  |  |              | Office White                                                              | <b>PT12LPB</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 1.12" (28.45) | <b>1-Gang Deep Box</b><br>For deep devices or applications where additional room is beneficial.<br>See page R-63 for recommended plate options.                                                                             |  |  | Office White | <b>PT12DBA</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 1.91" (48.51)  |
|                                                                                                                                                                         |       |  |              |                                                                           |                                                                             |                                                        |  |  |              |                                                                              |
|                                                                                                                                                                         | <b>1-Gang Standard Box</b><br>For standard switches and receptacles.<br>See page R-63 for recommended plate options.                                                    |  |              | Office White                                                              | <b>PT12SBA</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 1.63" (41.40) | <b>2-Gang Deep Box</b><br>For deep devices or applications where additional room is beneficial.<br>Uses 2-gang "KP", "IMF", or "IFP" plates for power or data applications.<br>See page R-63 for recommended plate options. |  |  | Office White | <b>PT12TGB</b><br>A: 4.90" (124.46)<br>B: 5.06" (128.52)<br>C: 1.91" (48.51) |
|                                                                                                                                                                         |       |  |              |                                                                           |                                                                             |                                                      |  |  |              |                                                                              |
|                                                                                                                                                                         | <b>Round Lighting Fixture Box</b><br>To hang fixtures.                                                                                                                  |  |              | Office White                                                              | <b>PT12LFB</b><br>A: 5.31" (134.87)<br>B: 1.04" (26.52)                     |                                                                                                                                                                                                                             |  |  |              |                                                                              |
|                                                                                                                                                                         |     |  |              |                                                                           |                                                                             |                                                                                                                                                                                                                             |  |  |              |                                                                              |
| Fittings                                                                                                                                                                | <b>Internal Elbow, Cover Only</b><br>For inside surfaces at right angles.                                                                                               |  |              | Office White                                                              | <b>PT1IE</b><br>A: 1.34" (34.04)<br>B: 1.34" (34.04)<br>C: 0.89" (22.61)    | <b>External Elbow, Cover Only</b><br>For outside surfaces at right angles.                                                                                                                                                  |  |  | Office White | <b>PT1EE</b><br>A: 1.24" (31.50)<br>B: 1.24" (31.50)<br>C: 0.88" (22.35)     |
|                                                                                                                                                                         |   |  |              |                                                                           |                                                                             |                                                    |  |  |              |                                                                              |
|                                                                                                                                                                         | <b>Flat Elbow, Cover Only</b><br>For right angle turns on same surface.                                                                                                 |  |              | Office White                                                              | <b>PT1FE</b><br>A: 1.33" (33.78)<br>B: 1.33" (33.78)<br>C: 0.74" (18.80)    | <b>Tee, Cover Only</b><br>For T-connection off PremiseTrak® Raceway.                                                                                                                                                        |  |  | Office White | <b>PT1TC</b><br>A: 1.77" (44.90)<br>B: 1.33" (33.78)<br>C: 0.74" (18.80)     |
|                                                                                                                                                                         |   |  |              |                                                                           |                                                                             |                                                    |  |  |              |                                                                              |
|                                                                                                                                                                         | <b>Splice Cover</b><br>For covering potential openings where two lengths of raceway come together.                                                                      |  |              | Office White                                                              | <b>PT1SC</b><br>A: 1.00" (25.40)<br>B: 0.74" (18.80)<br>C: 0.89" (22.61)    | <b>End Cap</b><br>For closing end of raceway.                                                                                                                                                                               |  |  | Office White | <b>PT1EC</b><br>A: 0.88" (22.35)<br>B: 0.74" (18.80)<br>C: 0.89" (22.61)     |
|                                                                                                                                                                         |   |  |              |                                                                           |                                                                             |                                                    |  |  |              |                                                                              |
| <b>Conduit Adapter/Ceiling Fitting</b><br>For connecting conduit to raceway.<br>Also use for ceiling feeds. Has combination ½ in., ¾ in. and 1 in. trade size KOs.      |                                                                                                                                                                         |  | Office White | <b>PT12CA</b><br>A: 1.64" (41.66)<br>B: 1.62" (41.15)<br>C: 2.50" (63.50) |                                                                             |                                                                                                                                                                                                                             |  |  |              |                                                                              |
|   |                                                                                                                                                                         |  |              |                                                                           |                                                                             |                                                                                                                                                                                                                             |  |  |              |                                                                              |

|                  |                                                                                                         |                                                                                   |              |                                                                                    |                                                                        |                                                                          |
|------------------|---------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|--------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------|--------------------------------------------------------------------------|
| PP1 PremiseTrak® | Description                                                                                             |                                                                                   | Color        | Length                                                                             | Without Adhesive                                                       | With Adhesive                                                            |
|                  | <b>Base and Cover</b><br>Single channel raceway.<br>Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths. |                                                                                   | Office White | 5 ft.<br>7 ft.                                                                     | <b>PP1BC5</b><br><b>PP1BC7</b><br>A: 0.77" (19.56)<br>B: 0.84" (21.34) | <b>PP1ABC5</b><br><b>PP1ABC7</b><br>A: 0.77" (19.56)<br>B: 0.84" (21.34) |
|                  |                                                                                                         |  |              |  |                                                                        |                                                                          |

|                                                                                     |                                                                                                                                                                                |                                                                                     |                                                                                   |                                                                                       |                                                                                                                                                  |                                                                                       |                                                                                     |                                                                                |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------|
| Device Boxes                                                                        | Description                                                                                                                                                                    |                                                                                     | Color                                                                             | Catalog Number                                                                        | Description                                                                                                                                      |                                                                                       | Color                                                                               | Catalog Number                                                                 |
|                                                                                     | <b>1-Gang Low Profile Box</b><br>For shallow switches and receptacles.<br>See page R-63 for recommended plate options.                                                         |                                                                                     | Office White                                                                      | <b>PDB12LP</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 1.25" (31.75)           | <b>1-Gang Deep Box</b><br>For deep devices or applications where additional room is beneficial.<br>See page R-63 for recommended plate options.  |                                                                                       | Office White                                                                        | <b>PDB12D</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 2.44" (61.98)     |
|                                                                                     |                                                                                               |                                                                                     |  |                                                                                       |                                                               |                                                                                       |  |                                                                                |
|                                                                                     | <b>1-Gang Standard Box</b><br>For standard switches and receptacles.<br>See page R-63 for recommended plate options.                                                           |                                                                                     | Office White                                                                      | <b>PDB12S</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 1.78" (45.21)            | <b>Round Lighting Fixture Box</b><br>To hang fixtures.                                                                                           |                                                                                       | Office White                                                                        | <b>PDB12LF</b><br>A: 5.31" (134.87)<br>B: 1.29" (32.77)                        |
|                                                                                     |                                                                                               |                                                                                     |  |                                                                                       |                                                               |                                                                                       |  |                                                                                |
|                                                                                     | <b>2-Gang Deep Divided Box</b><br>For deep switches, receptacles and communication devices. See page R-63 for single gang "KP" plate options.<br>Comes with removable divider. |                                                                                     | Office White                                                                      | <b>PDB12TGD</b><br>A: 4.90" (124.46)<br>B: 5.06" (128.52)<br>C: 2.44" (61.98)         | <b>2-Gang Deep Undivided Box</b><br>For low voltage applications only. Use with 2-gang "IFP" or "IMF" plates only.<br>See page R-63 for details. |                                                                                       | Office White                                                                        | <b>PDB12TGLV</b><br>A: 4.90" (124.46)<br>B: 5.06" (128.52)<br>C: 2.44" (61.98) |
|  |                                                                                                                                                                                |  |                                                                                   |  |                                                                                                                                                  |  |                                                                                     |                                                                                |

|                                                                                                                                                                 |                                                                                                    |                                                                                     |                                                                                     |                                                                                                                              |                                                                                       |                                                                                       |                                                                                       |                                                                                                 |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------|
| Fittings                                                                                                                                                        | <b>Internal Elbow</b><br>Full capacity 1¼ in. bend radius internal elbow.                          |                                                                                     | Office White                                                                        | <b>PP1IE*</b><br><b>PP1IEBC**</b><br>A: 2.40" (60.96)<br>B: 1.03" (26.16)<br>C: 2.40" (60.96)                                | <b>External Elbow</b><br>Full capacity 1¼ in. bend radius external elbow.             |                                                                                       | Office White                                                                          | <b>PP1EE*</b><br><b>PP1EEBC**</b><br>A: 4.47" (113.54)<br>B: 1.03" (26.16)<br>C: 4.47" (113.54) |
|                                                                                                                                                                 |                 |                                                                                     |  |                                                                                                                              |  |                                                                                       |  |                                                                                                 |
|                                                                                                                                                                 | <b>Flat Elbow</b><br>Full capacity 1¼ in. bend radius flat elbow.                                  |                                                                                     | Office White                                                                        | <b>PP1FE*</b><br><b>PP1FEBC**</b><br>A: 2.62" (66.55)<br>B: 2.62" (66.55)<br>C: 0.85" (21.59)                                | <b>Tee</b><br>Full capacity 1¼ in. bend radius tee.                                   |                                                                                       | Office White                                                                          | <b>PP1TC*</b><br><b>PP1TCBC**</b><br>A: 4.22" (107.19)<br>B: 2.62" (66.55)<br>C: 0.85" (21.59)  |
|                                                                                                                                                                 |                 |                                                                                     |  |                                                                                                                              |  |                                                                                       |  |                                                                                                 |
|                                                                                                                                                                 | <b>Splice Cover</b><br>For covering potential openings where two lengths of raceway come together. |                                                                                     | Office White                                                                        | <b>PP1SC</b><br>A: 1.09" (27.69)<br>B: 1.02" (25.91)<br>C: 0.85" (21.59)                                                     | <b>End Cap</b><br>For closing end of raceway.                                         |                                                                                       | Office White                                                                          | <b>PP1EC</b><br>A: 1.00" (25.40)<br>B: 0.84" (21.34)<br>C: 0.77" (19.56)                        |
|                                                                              |                                                                                                    |  |                                                                                     |                                         |                                                                                       |  |                                                                                       |                                                                                                 |
| <b>Conduit Adapter/Ceiling Fitting</b><br>For connecting conduit to raceway. Also use for ceiling feeds. Has combination ½ in., ¾ in. and 1 in. trade size KOs. |                                                                                                    | Office White                                                                        | <b>PLP1CACF</b><br>A: 2.29" (58.17)<br>B: 3.31" (84.07)<br>C: 3.90" (99.06)         | <b>Safety Strap</b><br>For preventing potential tampering with PP1 PremiseTrak cover.<br>Can also be used as a splice cover. |                                                                                       | Office White                                                                          | <b>PP1SS</b><br>A: 0.62" (15.75)<br>B: 1.94" (49.28)<br>C: 0.86" (21.84)              |                                                                                                 |
|                                                                              |                                                                                                    |  |                                                                                     |                                         |                                                                                       |  |                                                                                       |                                                                                                 |

Note: \*Cover only. \*\*Base and Cover.

Dimensions in Inches (mm)

| PL1 LANTrak® | Description                                                                                             | Color        | Length         | Without Adhesive                                                       | With Adhesive                                                            |
|--------------|---------------------------------------------------------------------------------------------------------|--------------|----------------|------------------------------------------------------------------------|--------------------------------------------------------------------------|
|              | <b>Base and Cover</b><br>Single channel raceway.<br>Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths. | Office White | 5 ft.<br>7 ft. | <b>PL1BC5</b><br><b>PL1BC7</b><br>A: 1.04" (26.42)<br>B: 1.38" (35.05) | <b>PL1ABC5</b><br><b>PL1ABC7</b><br>A: 1.04" (26.42)<br>B: 1.38" (35.05) |





| Device Boxes | Description                                                                                                                                                                 | Color        | Catalog Number                                                                                | Description                                                                                                                                   | Color        | Catalog Number                                                                                  |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|-----------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|--------------|-------------------------------------------------------------------------------------------------|
|              | <b>1-Gang Low Profile Box</b><br>For shallow switches and receptacles. See page R-63 for recommended plate options.                                                         | Office White | <b>PDB12LP</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 1.25" (31.75)                   | <b>1-Gang Deep Box</b><br>For deep devices or applications where additional room is beneficial. See page R-63 for recommended plate options.  | Office White | <b>PDB12D</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 2.44" (61.98)                      |
|              | <b>1-Gang Standard Box</b><br>For standard switches and receptacles. See page R-63 for recommended plate options.                                                           | Office White | <b>PDB12S</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 1.78" (45.21)                    | <b>Round Lighting Fixture Box</b><br>To hang fixtures.                                                                                        | Office White | <b>PDB12LF</b><br>A: 5.31" (134.87)<br>B: 1.29" (32.77)                                         |
|              | <b>2-Gang Deep Divided Box</b><br>For deep switches, receptacles and communication devices. See page R-63 for single gang "KP" plate options. Comes with removable divider. | Office White | <b>PDB12TGD</b><br>A: 4.90" (124.46)<br>B: 5.06" (128.52)<br>C: 2.44" (61.98)                 | <b>2-Gang Deep Undivided Box</b><br>For low voltage applications only. Use with 2-gang "IFP" or "IMF" plates only. See page R-63 for details. | Office White | <b>PDB12TGLV</b><br>A: 4.90" (124.46)<br>B: 5.06" (128.52)<br>C: 2.44" (61.98)                  |
| Fittings     | <b>Internal Elbow</b><br>Full capacity 1¼ in. bend radius internal elbow.                                                                                                   | Office White | <b>PL1IE*</b><br><b>PL1IEBC**</b><br>A: 2.51" (63.75)<br>B: 1.57" (39.88)<br>C: 2.51" (63.75) | <b>External Elbow</b><br>Full capacity 1¼ in. bend radius external elbow.                                                                     | Office White | <b>PL1EE*</b><br><b>PL1EEBC**</b><br>A: 5.06" (128.52)<br>B: 1.57" (39.88)<br>C: 5.06" (128.52) |
|              | <b>Flat Elbow</b><br>Full capacity 1¼ in. bend radius flat elbow.                                                                                                           | Office White | <b>PL1FE*</b><br><b>PL1FEBC**</b><br>A: 3.19" (81.03)<br>B: 3.19" (81.03)<br>C: 1.11" (28.19) | <b>Tee</b><br>Full capacity 1¼ in. bend radius tee.                                                                                           | Office White | <b>PL1TC*</b><br><b>PL1TCBC**</b><br>A: 4.75" (120.65)<br>B: 3.15" (80.01)<br>C: 1.11" (28.19)  |
|              | <b>Splice Cover</b><br>For covering potential openings where two lengths of raceway come together.                                                                          | Office White | <b>PL1SC</b><br>A: 1.12" (28.45)<br>B: 1.55" (39.37)<br>C: 1.11" (28.19)                      | <b>End Cap</b><br>For closing end of raceway.                                                                                                 | Office White | <b>PL1EC</b><br>A: 1.00" (25.40)<br>B: 1.39" (35.31)<br>C: 1.04" (26.42)                        |
|              | <b>Conduit Adapter/Ceiling Fitting</b><br>For connecting conduit to raceway. Also use for ceiling feeds. Has combination ½ in., ¾ in. and 1 in. trade size KOs.             | Office White | <b>PLP1CACF</b><br>A: 2.29" (58.17)<br>B: 3.31" (84.07)<br>C: 3.90" (99.06)                   | <b>Safety Strap</b><br>For preventing potential tampering with PL1 LANTrak cover. Can also be used as a splice cover.                         | Office White | <b>PL1SS</b><br>A: 0.62" (15.75)<br>B: 2.68" (68.07)<br>C: 1.12" (28.45)                        |

Note: \*Cover only. \*\*Base and Cover.









Dimensions in Inches (mm)

|                                                                                    |                                                                                                         |  |              |                |                                                                       |                                                                         |
|------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------|--|--------------|----------------|-----------------------------------------------------------------------|-------------------------------------------------------------------------|
| PW1 WallTrak®                                                                      | Description                                                                                             |  | Color        | Length         | Without Adhesive                                                      | With Adhesive                                                           |
|                                                                                    | <b>Base and Cover</b><br>Single channel raceway.<br>Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths. |  | Office White | 5 ft.<br>7 ft. | <b>PW1BC5</b><br><b>PW1BC7</b><br>A: .50" (12.70)<br>B: 1.19" (30.23) | <b>PW1ABC5</b><br><b>PW1ABC7</b><br>A: .50" (12.70)<br>B: 1.19" (30.23) |
|  |                                                                                                         |  |              |                |                                                                       |                                                                         |

|                                                                                     |                                                                                                                        |              |                                                        |                                                                            |                                                                                                                                                                                                                     |  |              |                                                                             |
|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------|--------------|--------------------------------------------------------|----------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------|-----------------------------------------------------------------------------|
| Device Boxes                                                                        | Description                                                                                                            |              | Color                                                  | Catalog Number                                                             | Description                                                                                                                                                                                                         |  | Color        | Catalog Number                                                              |
|                                                                                     | <b>1-Gang Low Profile Box</b><br>For shallow switches and receptacles.<br>See page R-63 for recommended plate options. |              | Office White                                           | <b>PW1LPB</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 1.13" (28.70) | <b>1-Gang Deep Box</b><br>For deep devices or applications where additional room is beneficial.<br>See page R-63 for recommended plate options.                                                                     |  | Office White | <b>PW1DBA</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 1.91" (48.51)  |
|                                                                                     |                                       |              |                                                        |                                                                            |                                                                                                                                  |  |              |                                                                             |
|                                                                                     | <b>1-Gang Standard Box</b><br>For standard switches and receptacles.<br>See page R-63 for recommended plate options.   |              | Office White                                           | <b>PW1SBA</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 1.63" (41.40) | <b>2-Gang Deep Box</b><br>For deep devices or applications where additional room is beneficial.<br>Uses 2-gang "KP" or "IFP" plates for power or data applications.<br>See page R-63 for recommended plate options. |  | Office White | <b>PW1TGB</b><br>A: 4.90" (124.46)<br>B: 5.06" (128.52)<br>C: 1.91" (48.51) |
|                                                                                     |                                       |              |                                                        |                                                                            |                                                                                                                                 |  |              |                                                                             |
| <b>Round Lighting Fixture Box</b><br>To hang fixtures.                              |                                                                                                                        | Office White | <b>PW1LFB</b><br>A: 5.31" (134.87)<br>B: 1.04" (26.52) |                                                                            |                                                                                                                                                                                                                     |  |              |                                                                             |
|  |                                                                                                                        |              |                                                        |                                                                            |                                                                                                                                                                                                                     |  |              |                                                                             |



|                                                                                                                                                                    |                                                                                                    |              |                                                                          |                                                                                       |                                                                                       |  |              |                                                                          |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------|--------------|--------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|--|--------------|--------------------------------------------------------------------------|
| Fittings                                                                                                                                                           | <b>Internal Elbow, Cover Only</b><br>For inside surfaces at right angles.                          |              | Office White                                                             | <b>PW1IE</b><br>A: 1.75" (44.45)<br>B: 1.43" (36.32)<br>C: 1.75" (44.45)              | <b>External Elbow, Cover Only</b><br>For outside surfaces at right angles.            |  | Office White | <b>PW1EE</b><br>A: 1.50" (38.10)<br>B: 1.43" (36.32)<br>C: 1.50" (38.10) |
|                                                                                                                                                                    |                 |              |                                                                          |                                                                                       |  |  |              |                                                                          |
|                                                                                                                                                                    | <b>Flat Elbow, Cover Only</b><br>For right angle turns on same surface.                            |              | Office White                                                             | <b>PW1FE</b><br>A: 2.18" (55.37)<br>B: 2.18" (55.37)<br>C: .60" (15.24)               | <b>Tee, Cover Only</b><br>For T-connection off PremiseTrak® Raceway.                  |  | Office White | <b>PW1TC</b><br>A: 2.93" (74.42)<br>B: 2.18" (55.37)<br>C: .60" (15.24)  |
|                                                                                                                                                                    |                 |              |                                                                          |                                                                                       |  |  |              |                                                                          |
|                                                                                                                                                                    | <b>Splice Cover</b><br>For covering potential openings where two lengths of raceway come together. |              | Office White                                                             | <b>PW1SC</b><br>A: 1.00" (25.40)<br>B: 1.43" (36.32)<br>C: .60" (15.24)               | <b>End Cap</b><br>For closing end of raceway.                                         |  | Office White | <b>PW1EC</b><br>A: 1.00" (25.40)<br>B: 1.24" (31.50)<br>C: .50" (12.70)  |
|                                                                                 |                                                                                                    |              |                                                                          |  |                                                                                       |  |              |                                                                          |
| <b>Conduit Adapter/Ceiling Fitting</b><br>For connecting conduit to raceway.<br>Also use for ceiling feeds. Has combination ½ in., ¾ in. and 1 in. trade size KOs. |                                                                                                    | Office White | <b>PW1CA</b><br>A: 1.40" (35.56)<br>B: 2.34" (59.44)<br>C: 3.22" (81.79) |                                                                                       |                                                                                       |  |              |                                                                          |
|                                                                                 |                                                                                                    |              |                                                                          |                                                                                       |                                                                                       |  |              |                                                                          |


Dimensions in Inches (mm)





| PW2 WallTrak® | Description                                                                                                                                                                                                                                                         |              | Color                                                                                           | Length                                                                                | Without Adhesive                                                       | With Adhesive                                                            |
|---------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|-------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|------------------------------------------------------------------------|--------------------------------------------------------------------------|
|               | <b>Base and Cover</b><br>Two channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.                                                                                                                                                                   |              | Office White                                                                                    | 5 ft.<br>7 ft.                                                                        | <b>PW2BC5</b><br><b>PW2BC7</b><br>A: 1.04" (26.42)<br>B: 2.12" (53.85) | <b>PW2ABC5</b><br><b>PW2ABC7</b><br>A: 1.04" (26.42)<br>B: 2.12" (53.85) |
| Device Boxes  | <b>1-Gang Low Profile Box</b><br>For shallow switches and receptacles. See page R-63 for recommended plate options.                                                                                                                                                 | Office White | <b>PDB12LP</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 1.25" (31.75)                     |      |                                                                        |                                                                          |
|               | <b>1-Gang Standard Box</b><br>For standard switches and receptacles. See page R-63 for recommended plate options. If using dual services, the PDB1DIV must be ordered.                                                                                              | Office White | <b>PDB12S</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 1.78" (45.21)                      |      |                                                                        |                                                                          |
|               | <b>1-Gang Deep Box</b><br>For deep devices or applications where additional room is beneficial. See page R-63 for recommended plate options. If using dual services, the PDB1DIV must be ordered.                                                                   | Office White | <b>PDB12D</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 2.44" (61.98)                      |     |                                                                        |                                                                          |
|               | <b>1-Gang Divider</b><br>For use with PDB12S and PDB12D 1-gang boxes. Required when two services are passing through box.                                                                                                                                           | Office White | <b>PDB1DIV</b><br>A: 2.79" (70.86)<br>B: 1.40" (35.56)<br>C: 0.94" (23.88)                      |    |                                                                        |                                                                          |
|               | <b>Round Lighting Fixture Box</b><br>To hang fixtures.                                                                                                                                                                                                              | Office White | <b>PDB12LF</b><br>A: 5.31" (134.87)<br>B: 1.29" (32.77)                                         |    |                                                                        |                                                                          |
|               | <b>2-Gang Deep Undivided Box</b><br>For low voltage applications only. Use with 2-gang "IFP" or "IMF" plates only. See page R-63 for details.                                                                                                                       | Office White | <b>PDB12TGLV</b><br>A: 4.90" (124.46)<br>B: 5.06" (128.52)<br>C: 2.44" (61.98)                  |    |                                                                        |                                                                          |
| Fittings      | <b>2-Gang Deep Divided Box</b><br>For deep devices or applications where additional room is beneficial. See page R-63 for single gang "KP" plate options. Comes with removable divider. If using dual services, in a perpendicular run the PDB2DIV must be ordered. | Office White | <b>PDB12TGD</b><br>A: 4.90" (124.46)<br>B: 5.06" (128.52)<br>C: 2.44" (61.98)                   |     |                                                                        |                                                                          |
|               | <b>2-Gang Divider</b><br>For use with PDB12TGD 2-gang box only. Required when two services are passing through box and mounting devices perpendicular to raceway.                                                                                                   | Office White | <b>PDB2DIV</b><br>A: 4.62" (117.35)<br>B: 2.76" (70.10)<br>C: 0.94" (23.88)                     |    |                                                                        |                                                                          |
|               | <b>Internal Elbow</b><br>Full capacity 1 1/4 in. bend radius internal elbow.                                                                                                                                                                                        | Office White | <b>PW2IE*</b><br><b>PW2IEBC**</b><br>A: 2.83" (71.88)<br>B: 3.25" (82.55)<br>C: 2.83" (71.88)   |    |                                                                        |                                                                          |
|               | <b>Flat Elbow</b><br>Full capacity 1 1/4 in. bend radius flat elbow.                                                                                                                                                                                                | Office White | <b>PW2FE*</b><br><b>PW2FEBC**</b><br>A: 3.94" (100.08)<br>B: 3.94" (100.08)<br>C: 1.11" (28.19) |    |                                                                        |                                                                          |
|               | <b>Splice Cover</b><br>For covering potential openings where two lengths of raceway come together.                                                                                                                                                                  | Office White | <b>PW2SC</b><br>A: 1.11" (28.19)<br>B: 2.30" (58.42)<br>C: 1.11" (28.19)                        |     |                                                                        |                                                                          |
|               | <b>Conduit Adapter/Ceiling Fitting</b><br>For connecting conduit to raceway. Also use for ceiling feeds. Has combination 1/2 in., 3/4 in. and 1 in. trade size KOs.                                                                                                 | Office White | <b>PW2CACF</b><br>A: 4.18" (106.17)<br>B: 3.32" (84.33)<br>C: 4.20" (106.68)                    |    |                                                                        |                                                                          |
| Fittings      | <b>End Cap</b><br>For closing end of PW2 WallTrak Raceway.                                                                                                                                                                                                          | Office White | <b>PW2EC</b><br>A: 1.00" (25.40)<br>B: 2.14" (54.36)<br>C: 1.04" (26.42)                        |    |                                                                        |                                                                          |
|               | <b>Reducer</b><br>Reduces from PW2 WallTrak Raceway to one or two PP1 PremiseTrak Raceway(s).                                                                                                                                                                       | Office White | <b>PW2RED</b><br>A: 1.62" (41.15)<br>B: 2.40" (60.96)<br>C: 1.15" (29.21)                       |    |                                                                        |                                                                          |
| Fittings      | <b>External Elbow</b><br>Full capacity 1 1/4 in. bend radius external elbow.                                                                                                                                                                                        | Office White | <b>PW2EE*</b><br><b>PW2EEBC**</b><br>A: 5.00" (127.00)<br>B: 2.32" (58.93)<br>C: 5.00" (127.00) |   |                                                                        |                                                                          |
|               | <b>Tee</b><br>Full capacity 1 1/4 in. bend radius tee.                                                                                                                                                                                                              | Office White | <b>PW2TC*</b><br><b>PW2TCBC**</b><br>A: 5.42" (137.67)<br>B: 3.91" (99.31)<br>C: 1.90" (48.26)  |  |                                                                        |                                                                          |
| Fittings      | <b>Safety Strap</b><br>For preventing potential tampering with PW2 WallTrak Cover. Can also be used as a splice cover.                                                                                                                                              | Office White | <b>PW2SS</b><br>A: 0.62" (15.75)<br>B: 3.43" (87.12)<br>C: 1.12" (28.45)                        |  |                                                                        |                                                                          |
|               | <b>Reducer</b><br>Reduces from PW2 WallTrak Raceway to one or two PP1 PremiseTrak Raceway(s).                                                                                                                                                                       | Office White | <b>PW2RED</b><br>A: 1.62" (41.15)<br>B: 2.40" (60.96)<br>C: 1.15" (29.21)                       |  |                                                                        |                                                                          |

Note: \*Cover only. \*\*Base and Cover.










Dimensions in Inches (mm)

| PB2 BaseTrak® | Description                                                                                                                                                                    | Color           | Length          | Catalog Number                                                         | Description                                                                                                                                                                                          | Color           | Length          | Catalog Number                                        |
|---------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|-----------------|------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|-----------------|-------------------------------------------------------|
|               | <b>Base</b><br>Two channel raceway.<br>Available in 5 ft. (1.5m) and 10 ft. (3m) lengths.<br><br>Assembled cover and base dimensions.<br>W: 4.50" (114.30)<br>H: 1.63" (41.40) | Office<br>White | 5 ft.<br>10 ft. | <b>PB2B5</b><br><b>PB2B10</b><br>A: 1.42" (36.07)<br>B: 4.50" (114.30) | <b>Cover</b><br>Cover allows access to multiple channels. Available in 5 ft. (1.5m) and 10 ft. (3m) lengths.                                                                                         | Office<br>White | 5 ft.<br>10 ft. | <b>PB2C5</b><br><b>PB2C10</b><br>B: 4.50" (114.30)    |
|               |                                                                                               |                 |                 |                                                                        | <b>Split Cover</b><br>Cover allows separation of channels and access to a single channel. Available in 5 ft. (1.5m) and 10 ft. (3m) lengths. Two split covers are required for each raceway section. | Office<br>White | 5 ft.<br>10 ft. | <b>PB2SPL5</b><br><b>PB2SPL10</b><br>B: 2.22" (56.39) |
|               |                                                                                                                                                                                |                 |                 |                                                                        |                                                                                                                   |                 |                 |                                                       |

| Device Boxes | Description                                                                                                                                                             | Color           | Catalog Number                                                                |
|--------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|-------------------------------------------------------------------------------|
|              | <b>2-Gang In-Line Box</b><br>For switches, receptacles and communication devices.<br>Provides flush look. See page R-63 for recommended single gang "KP" plate options. | Office<br>White | <b>PB2IND2G</b><br>A: 7.66" (194.56)<br>B: 4.74" (120.40)<br>C: 1.84" (46.74) |
|              |                                                                                       |                 |                                                                               |

| Fittings | Description                                                                                                                                                                     | Color           | Catalog Number                                                                 | Description                                                                                                            | Color           | Catalog Number                                                                 |
|----------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|--------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------|-----------------|--------------------------------------------------------------------------------|
|          | <b>Internal Elbow, Base and Cover</b><br>Full capacity 1¼ in. bend radius internal elbow.                                                                                       | Office<br>White | <b>PB3IEBCA</b><br>A: 4.36" (110.74)<br>B: 4.72" (119.89)<br>C: 4.36" (110.74) | <b>External Elbow, Base and Cover</b><br>Full capacity 1¼ in. bend radius external elbow.                              | Office<br>White | <b>PB3EEBCA</b><br>A: 6.48" (164.59)<br>B: 4.72" (119.89)<br>C: 6.48" (164.59) |
|          |                                                                                               |                 |                                                                                |                                    |                 |                                                                                |
|          | <b>Flat Elbow, Base and Cover</b><br>Full capacity 1¼ in. bend radius flat elbow.                                                                                               | Office<br>White | <b>PB3FEBCA</b><br>A: 7.64" (194.66)<br>B: 7.64" (194.66)<br>C: 1.71" (43.43)  | <b>Tee, Base and Cover</b><br>Full capacity 1¼ in. bend radius tee.                                                    | Office<br>White | <b>PB3TCBCA</b><br>A: 7.37" (187.20)<br>B: 7.08" (179.83)<br>C: 2.72" (69.09)  |
|          |                                                                                              |                 |                                                                                |                                   |                 |                                                                                |
|          | <b>Splice Cover</b><br>For covering potential openings where two lengths of raceway come together.                                                                              | Office<br>White | <b>PB3SC</b><br>A: 1.56" (39.62)<br>B: 4.74" (120.40)<br>C: 1.69" (42.93)      | <b>Safety Strap</b><br>For preventing potential tampering with PB2 BaseTrak cover. Can also be used as a splice cover. | Office<br>White | <b>PB3SS</b><br>A: 1.50" (38.10)<br>B: 6.01" (152.65)<br>C: 1.74" (44.20)      |
|          |                                                                                              |                 |                                                                                |                                   |                 |                                                                                |
|          | <b>Conduit Adapter/Ceiling Fitting</b><br>For connecting conduit to raceway. Also use for ceiling feeds. Has combination ½ in., ¾ in., 1 in., 1¼ in. and 1½ in. trade size KOs. | Office<br>White | <b>PB2CACF</b><br>A: 4.72" (119.89)<br>B: 5.22" (132.70)<br>C: 6.30" (160.02)  | <b>Reducer</b><br>Reduces from PB2 BaseTrak Raceway to PW2 WallTrak Raceway.                                           | Office<br>White | <b>PB3REDA</b><br>A: 3.50" (88.90)<br>B: 4.72" (119.89)<br>C: 1.73" (43.94)    |
|          |                                                                                              |                 |                                                                                |                                   |                 |                                                                                |
|          | <b>Transition Fitting</b><br>Transitions horizontal PB2 BaseTrak to vertical PW2 WallTrak, PL1 LANTrak or PP1 PremiseTrak.                                                      | Office<br>White | <b>PB3TRBC</b><br>A: 3.22" (81.79)<br>B: 7.28" (184.91)<br>C: 2.42" (61.47)    | <b>Surface Panel Connector</b><br>For connecting PB2 Raceway with surface type panel boxes.                            | Office<br>White | <b>PB3SPCA</b><br>A: 2.22" (56.39)<br>B: 5.66" (143.76)<br>C: 1.60" (40.64)    |
|          |                                                                                              |                 |                                                                                |                                   |                 |                                                                                |
|          | <b>Wire Clip</b><br>For holding conductors in place.                                                                                                                            | Office<br>White | <b>PB2WC</b><br>A: 1.29" (50.20)<br>B: 1.00" (25.40)                           | <b>End Cap</b><br>For closing end of PB2 BaseTrak Raceway.                                                             | Office<br>White | <b>PB3ECA</b><br>A: 2.02" (51.31)<br>B: 4.68" (118.97)<br>C: 1.72" (43.69)     |
|          |                                                                                              |                 |                                                                                |                                   |                 |                                                                                |

Dimensions in Inches (mm)

|                                                                                                                            |                                                                                                                                                                                                                 |                                                                                      |                                                                                                                     |                                                                                                                                                                                                                                                   |                                                                                            |                                                                                                   |
|----------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|
| PB3 BaseTrak®                                                                                                              | Description                                                                                                                                                                                                     |                                                                                      | Color                                                                                                               | Length                                                                                                                                                                                                                                            | Catalog Number                                                                             |                                                                                                   |
|                                                                                                                            | <b>Base and Cover</b><br>Three channel raceway. Available in 5 ft. (1.5m) and 10 ft. (3m) lengths.                                                                                                              |                                                                                      | Office White                                                                                                        | 5 ft.<br>10 ft.                                                                                                                                                                                                                                   | <b>PB3BC5</b><br><b>PB3BC10</b><br>A: 1.63" (41.40)<br>B: 4.50" (114.30)                   |                                                                                                   |
|                                           |                                                                                                                                                                                                                 |    |                                                                                                                     |                                                                                                                                                                                                                                                   |                                                                                            |                                                                                                   |
| Device Boxes                                                                                                               | <b>Description</b>                                                                                                                                                                                              | Color                                                                                | Catalog Number                                                                                                      | Catalog Number                                                                                                                                                                                                                                    | Catalog Number                                                                             |                                                                                                   |
|                                                                                                                            | <b>Full Capacity Boxes</b><br>1-, 2- and 3-Gang boxes that allows full capacity from PB3 Raceway to box for either power or datacom applications. See page R-63 for recommended single gang "KP" plate options. | Office White                                                                         | <b>PB3FCIB</b><br>(1-Gang)<br>A: 4.38" (111.25)<br>B: 4.80" (121.92)<br>C: 3.17" (80.52)                            | <b>PB3FCIB2G</b><br>(2-Gang)<br>A: 7.20" (182.88)<br>B: 4.80" (121.92)<br>C: 3.17" (80.52)                                                                                                                                                        | <b>PB3FCIB3G</b><br>(3-Gang)<br>A: 9.96" (252.98)<br>B: 4.80" (121.92)<br>C: 3.17" (80.52) |                                                                                                   |
|                                                                                                                            |                                                                                                                                |     |                                  |                                                                                                                                                                                                                                                   |                                                                                            |                                                                                                   |
|                                                                                                                            | <b>1-Gang In-Line Box</b><br>For switches, receptacles and communication devices. Provides flush look. See page R-63 for recommended plate options.                                                             | Office White                                                                         | <b>PB3IND</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 1.25" (31.75)                                          | <b>2-Gang In-Line Box</b><br>For switches, receptacles and communication devices. Barriers allow separation of power and datacom. Removal of barriers allows for expanded capacity. See page R-63 for recommended single gang "KP" plate options. | Office White                                                                               | <b>PB3IND2G</b><br>A: 4.90" (124.46)<br>B: 3.25" (82.55)<br>C: 2.44" (61.98)                      |
|                                           |                                                                                                                              |                                                                                      |                                                                                                                     |                                                                                                                                                                                                                                                   |                                                                                            |                                                                                                   |
| Fittings                                                                                                                   | <b>Internal Elbow</b><br>Full capacity 1¼ in. bend radius internal elbow.                                                                                                                                       | Office White                                                                         | <b>PB3IE*</b><br><b>PB3IEBCA**</b><br>A: 4.36" (110.74)<br>B: 4.72" (119.89)<br>C: 4.36" (110.74)                   | <b>External Elbow</b><br>Full capacity 1¼ in. bend radius external elbow.                                                                                                                                                                         | Office White                                                                               | <b>PB3EE*</b><br><b>PB3EEBCA**</b><br>A: 6.48" (164.59)<br>B: 4.72" (119.89)<br>C: 6.48" (164.59) |
|                                                                                                                            |                                                                                                                                |    |                                                                                                                     |                                                                                                                                                                                                                                                   |                                                                                            |                                                                                                   |
|                                                                                                                            | <b>Flat Elbow</b><br>Full capacity 1¼ in. bend radius flat elbow.                                                                                                                                               | Office White                                                                         | <b>PB3FE*</b><br><b>PB3FEBCA**</b><br>A: 7.64" (194.66)<br>B: 7.64" (194.66)<br>C: 1.71" (43.43)                    | <b>Tee</b><br>Full capacity 1¼ in. bend radius tee.                                                                                                                                                                                               | Office White                                                                               | <b>PB3TCBCA**</b><br>A: 7.37" (187.20)<br>B: 7.08" (179.83)<br>C: 2.72" (69.09)                   |
|                                                                                                                            |                                                                                                                              |  |                                                                                                                     |                                                                                                                                                                                                                                                   |                                                                                            |                                                                                                   |
|                                                                                                                            | <b>Splice Cover</b><br>For covering potential openings where two lengths of raceway come together.                                                                                                              | Office White                                                                         | <b>PB3SC*</b><br>A: 1.56" (39.62)<br>B: 4.74" (120.40)<br>C: 1.69" (42.93)                                          | <b>Safety Strap</b><br>Prevents potential tampering with PB3 BaseTrak cover. Can also be used as a splice cover.                                                                                                                                  | Office White                                                                               | <b>PB3SS*</b><br>A: 1.50" (38.10)<br>B: 6.01" (152.65)<br>C: 1.74" (44.20)                        |
|                                                                                                                            |                                                                                                                              |  |                                                                                                                     |                                                                                                                                                                                                                                                   |                                                                                            |                                                                                                   |
|                                                                                                                            | <b>Conduit Adapter/Ceiling Fitting</b><br>For connecting conduit to raceway. Also use for ceiling feeds. Has combination ½ in., ¾ in., 1 in., 1¼ in. and 1½ in. trade size KOs.                                 | Office White                                                                         | <b>PB3CACF**</b><br>A: 4.72" (119.89)<br>B: 5.22" (132.70)<br>C: 6.30" (160.02)                                     | <b>Reducer</b><br>Reduces from PB3 BaseTrak Raceway to PW2 WallTrak Raceway.                                                                                                                                                                      | Office White                                                                               | <b>PB3REDA**</b><br>A: 3.50" (88.90)<br>B: 4.72" (119.89)<br>C: 1.73" (43.94)                     |
|                                                                                                                            |                                                                                                                              |  |                                                                                                                     |                                                                                                                                                                                                                                                   |                                                                                            |                                                                                                   |
| <b>Transition Fitting</b><br>Transitions horizontal PB3 BaseTrak to vertical PW2 WallTrak, PL1 LANTrak or PP1 PremiseTrak. | Office White                                                                                                                                                                                                    | <b>PB3TRBC**</b><br>A: 3.22" (81.79)<br>B: 7.28" (184.91)<br>C: 2.42" (61.47)        | <b>Transition Fitting</b><br>Transitions from BT3 (old style) BaseTrak Raceway to PB3 (new style) BaseTrak Raceway. | Office White                                                                                                                                                                                                                                      | <b>BTPB3TF*</b><br>A: 2.22" (56.39)<br>B: 5.66" (143.76)<br>C: 1.35" (34.29)               |                                                                                                   |
|                                         |                                                                                                                             |                                                                                      |                                                                                                                     |                                                                                                                                                                                                                                                   |                                                                                            |                                                                                                   |
| <b>Surface Panel Connector</b><br>For connecting PB3 Raceway with surface type panel boxes.                                | Office White                                                                                                                                                                                                    | <b>PB3SPCA*</b><br>A: 2.22" (56.39)<br>B: 5.66" (143.76)<br>C: 1.60" (40.64)         | <b>End Cap</b><br>For closing end of PB3 BaseTrak Raceway.                                                          | Office White                                                                                                                                                                                                                                      | <b>PB3ECA*</b><br>A: 2.02" (51.31)<br>B: 4.68" (118.97)<br>C: 1.72" (43.69)                |                                                                                                   |
|                                         |                                                                                                                             |                                                                                      |                                                                                                                     |                                                                                                                                                                                                                                                   |                                                                                            |                                                                                                   |
| <b>Wire Clip</b><br>For holding conductors in place.                                                                       | Office White                                                                                                                                                                                                    | <b>PB3WC</b><br>A: 1.34" (34.10)<br>B: 1.00" (25.40)                                 |                                                                                                                     |                                                                                                                                                                                                                                                   |                                                                                            |                                                                                                   |
|                                         |                                                                                                                                                                                                                 |                                                                                      |                                                                                                                     |                                                                                                                                                                                                                                                   |                                                                                            |                                                                                                   |

Note: \*Cover only. \*\*Base and Cover.  
 Dimensions in Inches (mm)

| PS3 BaseTrak® | Description                                                                                                                                                                                                     |  | Color        | Length          | Catalog Number                                                           |
|---------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------|-----------------|--------------------------------------------------------------------------|
|               | <b>Base and Cover</b><br>Three channel raceway. Available in 5 ft. (1.5m) and 10 ft. (3m) lengths.                                                                                                              |  | Office White | 5 ft.<br>10 ft. | <b>PS3BC5</b><br><b>PS3BC10</b><br>A: 1.97" (50.04)<br>B: 6.70" (170.18) |
| Device Boxes  | <b>Full Capacity Boxes</b><br>1-, 2- and 3-Gang boxes that allows full capacity from PS3 Raceway to box for either power or datacom applications. See page R-63 for recommended single gang "KP" plate options. |  | Office White |                 |                                                                          |
|               | <b>PS3FCIB</b><br>(1-Gang)<br>A: 4.38" (111.25)<br>B: 6.95" (176.53)<br>C: 3.46" (87.88)                                                                                                                        |  |              |                 |                                                                          |
|               | <b>PS3FCIB2G</b><br>(2-Gang)<br>A: 7.20" (182.88)<br>B: 6.95" (176.53)<br>C: 3.46" (87.88)                                                                                                                      |  |              |                 |                                                                          |
| Device Boxes  | <b>3-Gang In-Line Box</b><br>For any combination of power and datacom applications. Provides flush look. See page R-63 for recommended single gang "KP" plate options.                                          |  | Office White |                 |                                                                          |
|               | <b>PS3FCIB3G</b><br>(3-Gang)<br>A: 9.96" (252.98)<br>B: 6.95" (176.53)<br>C: 3.46" (87.88)                                                                                                                      |  |              |                 |                                                                          |
| Fittings      | <b>Internal Elbow</b><br>Full capacity 1¼ in. bend radius internal elbow.                                                                                                                                       |  | Office White |                 |                                                                          |
|               | <b>PS3IE*</b><br><b>PS3IEBC**</b><br>A: 4.36" (110.74)<br>B: 6.93" (176.02)<br>C: 4.36" (110.74)                                                                                                                |  |              |                 |                                                                          |
|               | <b>External Elbow</b><br>Full capacity 1¼ in. bend radius external elbow.                                                                                                                                       |  | Office White |                 |                                                                          |
|               | <b>PS3EE*</b><br><b>PS3EEBC**</b><br>A: 6.81" (172.97)<br>B: 6.93" (176.02)<br>C: 6.81" (172.97)                                                                                                                |  |              |                 |                                                                          |
|               | <b>Flat Elbow</b><br>Full capacity 1¼ in. bend radius flat elbow.                                                                                                                                               |  | Office White |                 |                                                                          |
|               | <b>PS3FE*</b><br><b>PS3FEBC**</b><br>A: 9.85" (250.19)<br>B: 9.85" (250.19)<br>C: 2.08" (52.83)                                                                                                                 |  |              |                 |                                                                          |
|               | <b>Tee</b><br>Full capacity 1¼ in. bend radius tee.                                                                                                                                                             |  | Office White |                 |                                                                          |
|               | <b>PS3TCBC**</b><br>A: 10.00" (254.00)<br>B: 9.68" (245.87)<br>C: 3.30" (83.82)                                                                                                                                 |  |              |                 |                                                                          |
|               | <b>Splice Cover</b><br>For covering potential openings where two lengths of raceway come together.                                                                                                              |  | Office White |                 |                                                                          |
|               | <b>PS3SC*</b><br>A: 1.56" (39.62)<br>B: 6.95" (176.53)<br>C: 2.03" (51.62)                                                                                                                                      |  |              |                 |                                                                          |
| Fittings      | <b>Safety Strap</b><br>Prevents potential tampering with PS3 Super BaseTrak Raceway. Can also be used as a splice cover.                                                                                        |  | Office White |                 |                                                                          |
|               | <b>PS3SS*</b><br>A: 1.50" (38.10)<br>B: 8.24" (209.30)<br>C: 2.08" (52.85)                                                                                                                                      |  |              |                 |                                                                          |
|               | <b>Conduit Adapter/Ceiling Fitting</b><br>For connecting conduit to raceway. Also use for ceiling feeds. Has combination ½ in., ¾ in., 1 in., 1¼ in. and 1½ in. trade size KOs.                                 |  | Office White |                 |                                                                          |
|               | <b>PS3CACF**</b><br>A: 6.93" (176.02)<br>B: 4.32" (109.73)<br>C: 6.29" (159.77)                                                                                                                                 |  |              |                 |                                                                          |
|               | <b>Reducer</b><br>Reduces from PS3 Super BaseTrak Raceway to PB3 BaseTrak Raceway.                                                                                                                              |  | Office White |                 |                                                                          |
|               | <b>PS3RED**</b><br>A: 4.81" (122.17)<br>B: 6.93" (176.02)<br>C: 2.05" (52.07)                                                                                                                                   |  |              |                 |                                                                          |
| Fittings      | <b>Surface Panel Connector</b><br>To connect PS3 Raceway with surface type panel boxes.                                                                                                                         |  | Office White |                 |                                                                          |
|               | <b>PS3SPC*</b><br>A: 1.00" (25.40)<br>B: 7.87" (199.90)<br>C: 2.54" (64.52)                                                                                                                                     |  |              |                 |                                                                          |
| Fittings      | <b>End Cap</b><br>For closing end of PS3 Super BaseTrak Raceway.                                                                                                                                                |  | Office White |                 |                                                                          |
|               | <b>PS3EC*</b><br>A: 1.50" (38.10)<br>B: 6.88" (174.75)<br>C: 2.06" (52.32)                                                                                                                                      |  |              |                 |                                                                          |
| Fittings      | <b>Wire Clip</b><br>For holding conductors in place.                                                                                                                                                            |  | Office White |                 |                                                                          |
|               | <b>PS3WC</b><br>A: 1.62" (41.15)<br>B: 1.00" (25.40)                                                                                                                                                            |  |              |                 |                                                                          |

Note: \*Cover only. \*\*Base and Cover.

Dimensions in Inches (mm)

 Tamper-Resistant



| 5 Foot Base and Cover | Amp | Circuits  | # Duplex Receptacles | Receptacle Spacing (in.) | Catalog Number                                                                                      |
|-----------------------|-----|-----------|----------------------|--------------------------|-----------------------------------------------------------------------------------------------------|
|                       | 15  | Single    | 5                    | 12                       | <b>PT155112</b>                                                                                     |
|                       | 15  | Two       | 5                    | 12                       | <b>PT155212</b>                                                                                     |
|                       | 15  | Single    | 4                    | 15                       | <b>PT155115</b>                                                                                     |
|                       | 15  | Single    | 2                    | 30                       | <b>PT155130</b>                                                                                     |
|                       | 15  | TR/Single | 5                    | 12                       | <b>PT155112TR</b>  |
|                       | 20  | Single    | 5                    | 12                       | <b>PT205112</b>                                                                                     |
|                       | 20  | Two       | 5                    | 12                       | <b>PT205212</b>                                                                                     |
|                       | 20  | Single    | 4                    | 15                       | <b>PT205115</b>                                                                                     |
|                       | 20  | Two       | 4                    | 15                       | <b>PT205215</b>                                                                                     |
|                       | 20  | Single    | 2                    | 30                       | <b>PT205130</b>                                                                                     |
| 6 Foot Base and Cover | 20  | TR/Single | 5                    | 12                       | <b>PT205112TR</b>  |
|                       | 15  | Single    | 6                    | 12                       | <b>PT156112</b>                                                                                     |
|                       | 15  | Two       | 6                    | 12                       | <b>PT156212</b>                                                                                     |
|                       | 15  | Single    | 4                    | 18                       | <b>PT156118</b>                                                                                     |
|                       | 15  | Single    | 3                    | 24                       | <b>PT156124</b>                                                                                     |
|                       | 20  | Single    | 18                   | 8                        | <b>PT206108</b>                                                                                     |
|                       | 20  | Two       | 18                   | 8                        | <b>PT206208</b>                                                                                     |
|                       | 20  | Single    | 6                    | 12                       | <b>PT206112</b>                                                                                     |
|                       | 20  | Two       | 6                    | 12                       | <b>PT206212</b>                                                                                     |
|                       | 20  | Single    | 4                    | 18                       | <b>PT206118</b>                                                                                     |
|                       | 20  | Two       | 4                    | 18                       | <b>PT206218</b>                                                                                     |
|                       | 20  | Single    | 3                    | 24                       | <b>PT206124</b>                                                                                     |
|                       | 20  | Two       | 3                    | 24                       | <b>PT206224</b>                                                                                     |
|                       | 20  | Single    | 2                    | 36                       | <b>PT206136</b>                                                                                     |

Note: Each Non-Metallic PlugTrak is supplied with one PL1EC end cap and "IG" stickers for isolated ground applications.



| Portable | Amp                                             | Length (ft.) | Cord Length (ft.) | # Duplex Receptacles | Catalog Number   |
|----------|-------------------------------------------------|--------------|-------------------|----------------------|------------------|
|          | 15                                              | 3            | 6                 | 3                    | <b>PT153112P</b> |
|          | 15                                              | 5            | 6                 | 5                    | <b>PT155112P</b> |
|          | 20                                              | 3            | 6                 | 2                    | <b>PT203112P</b> |
|          | 20                                              | 5            | 6                 | 5                    | <b>PT205112P</b> |
|          | Supporting Mounting Clip for Portable PlugTrak. |              |                   |                      | <b>PL1MC</b>     |

Note: Includes on/off switch and circuit breaker.



| Device Boxes | Description                     | Catalog Number                                                                                           | Description               | Catalog Number                                                                                         |
|--------------|---------------------------------|----------------------------------------------------------------------------------------------------------|---------------------------|--------------------------------------------------------------------------------------------------------|
|              | 1-Gang Low Profile              | <b>PDB12LP</b><br>    | 1-Gang Deep               | <b>PDB12D</b><br>   |
|              | 1-Gang Standard                 | <b>PDB12S</b><br>     | 2-Gang Deep Divided       | <b>PDB12TGD</b><br> |
| Fittings     | Round Lighting Fixture          | <b>PDB12LF</b><br>    |                           |                                                                                                        |
|              | Internal Elbow Base and Cover   | <b>PL1IEBC</b><br>    | Internal Elbow Cover Only | <b>PL1IE</b><br>    |
|              | External Elbow Base and Cover   | <b>PL1EEBC</b><br>   | External Elbow Cover Only | <b>PL1EE</b><br>   |
|              | Flat Elbow Base and Cover       | <b>PL1FEBC</b><br>  | Flat Elbow Cover Only     | <b>PL1FE</b><br>  |
|              | Tee Base and Cover              | <b>PL1TCBC</b><br>  | Tee Cover Only            | <b>PL1TC</b><br>  |
|              | Splice Cover                    | <b>PL1SC</b><br>    | Safety Strap              | <b>PL1SS</b><br>  |
|              | Conduit Adapter/Ceiling Fitting | <b>PLP1CACF</b><br> | End Cap                   | <b>PL1EC</b><br>  |

Note: See page R-56 for additional information.



**PL1MC**  
Supporting Mounting Clip

| 1-Gang and 2-Gang "KP" Plates | Color        | Catalog Number                                                                                                                          | Catalog Number                                                                                                                       | Catalog Number                                                                                                                                                                                    | Catalog Number                                                                                                            | Catalog Number                                                                                                              |
|-------------------------------|--------------|-----------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|
|                               | Office White |  <b>KP8</b><br>Duplex                                  |  <b>KP26</b><br>Style Line®                         |  <b>KP1</b><br>Toggle                                                                                            |  <b>KP7</b><br>Receptacle<br>(1.41 ID) |  <b>KP720</b><br>Receptacle<br>(1.60 ID) |
|                               | Office White |  <b>KP14</b><br>Blank                                  |  <b>KP212</b><br>Coax (2)                           |  <b>KP2140</b><br>Jack/Coax                                                                                      |  <b>KP2162</b><br>Modular Jacks (2)    |  <b>KP2163</b><br>Modular Jacks (3)      |
|                               | Office White |  <b>KPORTOW</b><br>Ortronics Series II®<br>Data Module |  <b>KPPANOW</b><br>Panduit Mini-Com®<br>Data Module |  <b>KPIMBZOW</b><br>3-Unit iSTATION<br>(Accepts all Hubbell iSTATION Modules located in Network Wiring section). |                                                                                                                           |                                                                                                                             |
|                               | Office White |  <b>KP82</b><br>2-Gang Duplex                          |  <b>KP262</b><br>2-Gang Style Line®                 |  <b>KP2</b><br>2-Gang Toggle                                                                                     |  <b>KP24</b><br>2-Gang Blank           |                                                                                                                             |

Note: 2-Gang "KP" plates, for use with PT12TGB and PW1TGB only.

| Comm. "IFP" Plates & Frames | Color        | Catalog Number                                                                                                        | Catalog Number                                                                                                           | Catalog Number                                                                                                           | Catalog Number                                                                                                             | Catalog Number                                                                                                             |
|-----------------------------|--------------|-----------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------|
|                             | Office White |  <b>IFP126OW</b><br>Style Line®      |  <b>ISF2OW</b><br>Style Line®<br>2-Port |  <b>ISF3OW</b><br>Style Line®<br>3-Port |  <b>ISF4OW</b><br>Style Line®<br>4-Port |  <b>ISF6OW</b><br>Style Line®<br>6-Port |
|                             | Office White |  <b>IFP18OW</b><br>Duplex            |  <b>BR106C</b><br>Duplex<br>2-Port      |  <b>Q106O</b><br>Duplex<br>4-Port       |  <b>IFP12OW</b><br>Flush<br>2-Port      |  <b>IFP13OW</b><br>Flush<br>3-Port      |
|                             | Office White |  <b>IFP14OW</b><br>Flush<br>4-Port |  <b>IFP16OW</b><br>Flush<br>6-Port    |  <b>IFP26OW</b><br>2-Gang<br>6-Port   |  <b>IFP29OW</b><br>2-Gang<br>9-Port   |  <b>IFP212OW</b><br>2-Gang<br>12-Port |

Note: Ivory metal raceway matches almond devices and plates. For HBL3000 series raceway applications, catalog number HBL3051LEV/GY must be used with plates and devices.

| Frames & Modules | Description                                                                                                                                                                                                                        | Color        | 1-Gang                                                                                              | 2-Gang                                                                                              |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|-----------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------|
|                  | Front loading plate will accept any modules in three unit combinations. Angled fixtures to be used in bottom opening only. See section W for additional information on Hubbell iSTATION modules. Each gang accepts 3 module units. | Office White |  <b>IMF1OW</b> |  <b>IMF2OW</b> |

Modular connectors to be used with any plate with a standard modular opening. Not recommended for use with KP plates. For KP applications use KPIMBZOW bezel and appropriate Hubbell iSTATION modules located in section W. Use appropriate Hubbell iSTATION modules for SC fiber adapters. See section W for additional information on modular connectors.

| Modular Connector Fittings | Color              | Catalog Number                                                                                                              | Catalog Number                                                                                                        | Catalog Number                                                                                                            | Catalog Number                                                                                                                     |
|----------------------------|--------------------|-----------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------|
|                            | Office White       |  <b>SFFX</b><br>F-Connector              |  <b>SFST</b><br>ST Fiber Connector |  <b>SFBOW</b><br>BNC Connector        |  <b>SFB10</b><br>Blank<br>(10 Pack)           |
|                            | Black housing only |  <b>SFRC110R</b><br>RCA 110<br>Punchdown |  <b>SFSV110BK</b><br>Super S-Video |  <b>FASCMPB6</b><br>SC Duplex Adapter |  <b>FASTSCMPB6</b><br>SC to ST Duplex Adapter |

| Xcelerator Modular Jacks | Color        | Catalog Number                                                                                                                    | Catalog Number                                                                                                                  | Catalog Number                                                                                                               |
|--------------------------|--------------|-----------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|
|                          | Office White |  <b>HXJ5EOW</b><br>Cat. 5e, T568A, T568B, RJ45 |  <b>HXJ6OW</b><br>Cat. 6, T568A, T568B, RJ45 |  <b>HXJUOW</b><br>6 Position USOC, RJ25 |

Jack Color Options (Replace OW suffix with additional colors below)

AL=Almond BK=Black B=Blue EI=Elec. Ivory GY=Gray GN=Green LA=Lt. Almond OR=Orange OW=Off. White R=Red W=White Y=Yellow

Panduit® and Mini-Com® are registered trademarks of Panduit Corp.  
Ortronics® and Series II® are registered trademarks of Ortronics/Legrand.

# Non-Metallic Raceway

## Technical Information and Wire Fill Capacity Chart

Technical Information



| Non-Metallic Raceway Wire Fill Capacities |         |                           |                           |           |           |        |         |                         |            |           |            |               |                                        |                        |                         |           |
|-------------------------------------------|---------|---------------------------|---------------------------|-----------|-----------|--------|---------|-------------------------|------------|-----------|------------|---------------|----------------------------------------|------------------------|-------------------------|-----------|
|                                           |         |                           | Power<br>(THHN/T90 Nylon) |           |           | Voice  |         | Data<br>(Copper Cables) |            |           |            |               | Data<br>(Multimode Fiber Optic Cables) |                        |                         |           |
|                                           |         |                           | 14<br>AWG                 | 12<br>AWG | 10<br>AWG | 4-Pair | 25-Pair | Type<br>RG59U           | Cat.<br>5e | Cat.<br>6 | Cat.<br>6A | Cat. 6<br>STP | (2) or (4)<br>Fiber Round<br>Cable     | Fiber Optic<br>Jumpers | Fiber Optic<br>Zip Cord |           |
|                                           |         |                           | Wire O.D. (in.):          | 0.111     | 0.13      | 0.164  | 0.19    | 0.41                    | 0.242      | 0.21      | 0.25       | 0.35          | 0.29                                   | 0.19                   | 0.118                   | .12 X .24 |
|                                           |         |                           | Wire Area (sq. in.):      | 0.0097    | 0.0133    | 0.0211 | 0.0283  | 0.1320                  | 0.0460     | 0.0346    | 0.0491     | 0.0962        | 0.0660                                 | 0.0283                 | 0.0109                  | 0.0288    |
| Series                                    | Channel | Channel Area<br>(sq. in.) | Wire Fill Capacity        |           |           | 40%    | 40%     | 40%                     | 40%        | 40%       | 40%        | 40%           | 40%                                    | 40%                    | 40%                     |           |
| PT1                                       | A       | 0.29                      | 5                         | 8         | 5         | 4      | 1       | 3                       | 3          | 2         | 1          | 2             | 4                                      | 11                     | 4                       |           |
| PP1                                       | A       | 0.38                      | 12                        | 11        | 8         | 5      | 1       | 3                       | 4          | 3         | 2          | 2             | 5                                      | 14                     | 5                       |           |
| PL1                                       | A       | 1.03                      | 42                        | 34        | 22        | 15     | 3       | 9                       | 12         | 8         | 4          | 6             | 15                                     | 38                     | 14                      |           |
| PW1                                       | A       | 0.30                      | 6                         | 10        | 4         | 4      | 0       | 2                       | 3          | 2         | 1          | 2             | 4                                      | 11                     | 4                       |           |
| PW2                                       | A+B     | 1.60                      | 41                        | 36        | 22        | 23     | 5       | 14                      | 18         | 13        | 7          | 10            | 23                                     | 59                     | 22                      |           |
| A B                                       | A       | 0.81                      | 12                        | 22        | 12        | 11     | 2       | 7                       | 9          | 7         | 3          | 5             | 11                                     | 30                     | 11                      |           |
|                                           | B       | 0.79                      | 12                        | 22        | 10        | 11     | 2       | 7                       | 9          | 6         | 3          | 5             | 11                                     | 29                     | 11                      |           |
| PB2                                       | A+B     | 5.72                      | 60                        | 36        | 45        | 81     | 17      | 50                      | 66         | 47        | 24         | 35            | 81                                     | 210                    | 79                      |           |
| A B                                       | A or B  | 2.86                      | 42                        | 30        | 28        | 40     | 9       | 25                      | 33         | 23        | 12         | 17            | 40                                     | 105                    | 40                      |           |
| PB3                                       | A+B+C   | 5.57                      | 60                        | 36        | 45        | 79     | 17      | 48                      | 64         | 45        | 23         | 34            | 79                                     | 204                    | 77                      |           |
| A B C                                     | A or C  | 1.80                      | 42                        | 30        | 28        | 25     | 5       | 16                      | 21         | 15        | 7          | 11            | 25                                     | 66                     | 25                      |           |
|                                           | B       | 1.97                      | 42                        | 30        | 28        | 28     | 6       | 17                      | 23         | 16        | 8          | 12            | 28                                     | 72                     | 27                      |           |
| PS3                                       | A+B+C   | 10.58                     | 72                        | 66        | 78        | 150    | 32      | 92                      | 122        | 86        | 44         | 64            | 150                                    | 388                    | 147                     |           |
| A B C                                     | A or C  | 3.41                      | 42                        | 36        | 42        | 48     | 10      | 30                      | 39         | 28        | 14         | 21            | 48                                     | 125                    | 47                      |           |
|                                           | B       | 3.76                      | 42                        | 36        | 42        | 53     | 11      | 33                      | 43         | 31        | 16         | 23            | 53                                     | 138                    | 52                      |           |

Note: Pathway (Raceway) fill shall be 40% maximum. Raceway fittings and outlets/receptacles reduce the cross section of the raceway system, thus reducing overall cable fill capacity.

| Recommended Plate to Box Compatibility Selection Chart |                          |            |      |        |        |            |       |      |        |        |               |              |     |      |                        |     |
|--------------------------------------------------------|--------------------------|------------|------|--------|--------|------------|-------|------|--------|--------|---------------|--------------|-----|------|------------------------|-----|
| Non-Metallic Raceway<br>Box Series                     |                          | PS3 Series |      |        |        | PB3 Series |       |      |        |        | PB2<br>Series | PDB12 Series |     |      | PT12 & PW1<br>Series   |     |
| Plate Style                                            | Sample Catalog<br>Number | IND        | FCIB | FCIB2G | FCIB3G | IND        | IND2G | FCIB | FCIB2G | FCIB3G | IND2G         | LP,<br>S, D  | TGD | TGLV | LP(B), S(BA),<br>D(BA) | TGB |
| 1-Gang<br>KP Series Plate                              | KP8                      | X          | X    | X      | X      | X          | X     | X    | X      | X      | X             | X            | X   |      | X                      |     |
| 1-Gang<br>KP Series Bezel                              | KPIMBZ                   | X          | X    | X      | X      | X          | X     | X    | X      | X      | X             | X            | X   |      | X                      |     |
| 1-Gang Standard<br>Data Plate                          | IFP12OW                  |            | X    | X      | X      | X          |       | X    | X      | X      |               | X            |     |      | X                      |     |
| 1-Gang iSTATION<br>Plate Frame                         | IMF1OW                   |            | X    | X      | X      | X          |       | X    | X      | X      |               | X            |     |      | X                      |     |
| Style Line®<br>Data Plate                              | IFP126OW                 |            | X    | X      | X      | X          |       | X    | X      | X      |               | X            |     |      | X                      |     |
| Duplex Data Plate                                      | IFP18OW                  |            | X    | X      | X      | X          |       | X    | X      | X      |               | X            |     |      | X                      |     |
| 2-Gang iSTATION<br>Plate Frame                         | IMF2OW                   |            |      |        |        |            |       |      |        |        |               |              |     | X    |                        | X   |
| 2-Gang Standard<br>Data Plate                          | IFP29OW                  |            |      |        |        |            |       |      |        |        |               |              |     | X    |                        | X   |
| 2-Gang<br>KP Series Plate                              | KP82                     |            |      |        |        |            |       |      |        |        |               |              |     |      |                        | X   |

Note: Hubbell Office White plates and devices color match all non-metallic raceway systems.

### Physical Properties

(When tested in accordance with UL 5A)

|                   |                   |
|-------------------|-------------------|
| Impact Resistance | 5 ft. lbs.        |
| Crush Resistance  | 300 lbs.          |
| Temperature Range | -25.6° to 158° F  |
| Flame Rating      | UL94V-0           |
| Material          | UV Stabilized PVC |

### Codes/Standards

|              |                   |
|--------------|-------------------|
| EIA/TIA      | 569A              |
| UL Standard  | UL 5A             |
| Listings     | E118895 / E119190 |
| CSA Standard | C22.2 no. 62      |
| Certified    | LR87514           |

### PlugTrak Specifications

|                   |                         |
|-------------------|-------------------------|
| Receptacle Rating | NEMA 5-15R & 5-20R      |
| Wire              | #12 AWG Stranded Copper |
| Receptacle Face   | Thermoplastic           |

# Pre-Wired Raceway

## Pre-Wired Raceway Systems

Introduction

**Hubbell has been setting the standard** in the electrical industry since 1888, through innovations such as Twist-Lock®, Hospital Grade, and AUTOGUARD™ Self Test GFCI receptacles. Again, Hubbell has listened to our customers for new innovation, capacity requirements, and flexibility. We have taken raceway systems to the next level with **Pre-Wired Raceway Systems** that are manufactured to your specifications.

**Our Pre-Wired Raceway Systems** will accommodate your power and data requirements as your facility changes over time. Pre-Wired Raceways provide you with the benefit of keeping your fast track projects on schedule, and helping complete the job on time! Our Pre-Wired Raceway solutions will save up to 45% of the installation time needed for field installing component raceway parts.

### Pre-Wired Raceways are available in:

- ✓ Steel (Ivory and Gray)
- ✓ Aluminum
- ✓ Non-Metallic (Office White)



#### Quality by Design

All Hubbell Pre-Wired Raceways are UL Listed and CSA Certified. Each raceway receives a 100% quality inspection and testing prior to shipment. Pre-Wired Raceway is now available with the high quality and workmanship you have come to expect from Hubbell.



#### Labeling and Engraving

Optional labeling is available to identify branch panels and circuits at receptacle locations. Choose from adhesive labels or engraved aluminum plates.



#### Wire Identification

Wire leads are clearly labeled with corresponding circuit numbers. This aids the installer when terminating to building wiring or connecting from duct to duct. Ample wire is provided at feed locations.

## Save Time and Money, Completing the Job Quicker and On Schedule, with Hubbell...

### With Standard Raceway...



Unpack, identify and sort component parts.  
 Deliver components to work area for assembly and installation.



Measure and cut.  
 Clean and de-burr sharp edges.  
 Secure to the wall and fasten.



Pull wire.  
 Label and bundle each raceway circuit.  
 Install receptacles and test.

### With Hubbell Pre-Wired Raceway...



Pallet delivered to your worksite, labeled by room, floor area and/or building.



Unpack and install!



Installed in half the time!



### Project Support and Documentation

- ✓ A local and factory support team is there to assist in defining bills of material and project quotes, so costs can be budgeted accordingly.
- ✓ A project engineer, located at the factory, is assigned to your project as a direct point of contact.

### Manufacturing and Testing

- ✓ Precisely measured, cleanly cut, wired and assembled to your specifications.
- ✓ The wiring harness is then bundled and labeled for circuit identification for ease of installation.
- ✓ Assembly is tested for assured continuity and 100% quality inspected before kitting.



### Installs In A Snap

- ✓ Raceway ducts are kitted, labeled, and shipped by room, area or floor locations.
- ✓ Just remove raceway from the packaging and secure to the wall.
- ✓ Make power connections, snap on covers, test and you are done!



### Options:



#### Circuit Identification and Labeling:

- ✓ Adhesive Labeling
- ✓ Engraving



#### Wiring Circuits Options:

- ✓ Insulation Displacement Connectors
- ✓ Wire Nuts
- ✓ Wiring Devices




#### Kit raceway for delivery by:

- ✓ Room
- ✓ Floor
- ✓ Area
- ✓ Building

**Aluminum Pre-Wired Raceway (LINKOSITY® devices may be utilized with this Raceway Series)****HBLALU3800 Series Aluminum Raceway**

## Description

Aluminum Raceway, Single Channel,  
Satin Anodized Finish.




## Dimension

A: 2.25" (57.15)  
B: 3.00" (76.20)

**HBLALU4800 Series Aluminum Raceway**

## Description

Aluminum Raceway, Two Channel,  
Satin Anodized Finish.




A: 2.25" (57.15)  
B: 6.00" (152.40)

**HBLALU5000 Series Aluminum Raceway**

## Description

Aluminum Raceway, Two Channel,  
Satin Anodized Finish.




A: 1.75" (44.45)  
B: 5.08" (129.03)

**HBLALU7620 Series Aluminum Raceway**

## Description

Aluminum Raceway, Three Channel,  
Satin Anodized Finish.




A: 2.25" (57.15)  
B: 7.62" (193.55)

**Steel Pre-Wired Raceway (LINKOSITY® devices may be utilized with this Raceway Series)****HBL3000 Series Metal Raceway**

## Description

Steel Raceway, Single Channel,  
Ivory or Gray Finish.



A: 1.53" (38.86)  
B: 2.75" (69.85)

**HBL4750 Series Metal Raceway**

## Description

Steel Raceway, Single or  
Two Channel (with Divider),  
Ivory or Gray Finish.




A: 1.75" (44.45)  
B: 4.75" (120.65)

**HBL6750 Series Metal Raceway**

## Description

Steel Raceway, Single,  
Two Channel (with One Divider)  
or Three Channel (with Two Dividers),  
Ivory or Gray Finish.




A: 2.22" (56.39)  
B: 6.75" (171.45)

**Non-Metallic Pre-Wired Raceway****PB2 BaseTrak® Series Non-Metallic Raceway**

## Description

Non-Metallic Raceway,  
Two Channel,  
Office White Color.




A: 1.63" (41.40)  
B: 4.50" (114.30)

**PS3 Super BaseTrak® Series Non-Metallic Raceway**

## Description

Non-Metallic Raceway,  
Three Channel,  
Office White Color.



A: 1.97" (50.04)  
B: 6.70" (170.18)



Dimensions in Inches (mm)



## UL Listed Modular Pre-Wired Raceway Systems Featuring the Flexibility of LINKOSITY® Connections

Hubbell Pre-Wired Metal Raceway with LINKOSITY® connections is a Hubbell innovation providing a flexible, modular UL Listed System that allows users to relocate furniture and equipment without the need to access the internal wiring of the raceway. The inherent flexibility of this system greatly reduces the cost of installation and future end-user costs associated with re-configuring space.

The Hubbell Metal Raceway/LINKOSITY combination can be provided as a factory assembled system or by having a licensed electrician purchase and field install the required LINKOSITY components into the metal raceway.

| Features                              | Benefits                                                                                               |
|---------------------------------------|--------------------------------------------------------------------------------------------------------|
| UL Listed, NEC Compliant assemblies   | Complete code compliance minimizes design time, startup costs and building inspector acceptance.       |
| Flexible, modular terminations        | Simplifies moves, adds and changes.<br>Reduces long term total cost of ownership.                      |
| Pre-configured, factory wired         | Minimizes field wiring. Devices are custom configured to the application, tested and ready to install. |
| Cable rated TC-ER, MTW, STOOW         | One cable suitable for use in all commercial applications                                              |
| In-line 106 data/communications frame | Data/Communications may be field installed anywhere along the raceway eliminating large boxes.         |



| Device Type                                                                                                                                                                                                                                                                                                                                                                                                                                                      | Ratings                                                                                                                                                                                                                 | Wires                                                                                                                     | Conductor Colors**                                                                                                                                                                                                   | Length (FT)                                                                                                                                                                                                            |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>PH</b> = Double Ended Cable with Male/Female Straight<br><b>PM</b> = Male Single Ended Straight<br><b>PN</b> = Male Single Ended 90°<br><b>PF</b> = Female Single Ended Straight<br><b>PG</b> = Female Single Ended 90°<br><b>PQ</b> = Double Ended Cable with Female 90°<br><b>PR</b> = Double Ended Cable with Male 90°<br><b>PS</b> = Double Ended Cable with (2) 90° Connectors<br><b>RF</b> = Female Receptacle*<br><b>RM</b> = Male Receptacle (Inlet)* | <b>20</b> = 20A up to 600V<br><br><b>23</b> = 20A up to 600V<br>Specialty construction (Includes isolated ground on 6 wire and 10AWG super neutral conductor on 5 and 6 wire devices)<br><br><b>30</b> = 30A up to 600V | <b>02</b><br><b>03</b><br><b>04</b><br><b>05</b><br><br><b>03</b><br><b>04</b><br><b>05</b><br><b>06</b><br><br><b>04</b> | <b>PA</b> = Green/Yellow<br>Black (all others)<br><br><b>PB</b> = Green/Yellow<br>White<br>Black (all others)<br><br><b>PE</b> = All Blue***<br><br>**other color codes available upon request.<br>***Two wire only. | <b>001</b> = 1'<br><b>005</b> = 5'<br><b>010</b> = 10'<br><b>015</b> = 15'<br><b>020</b> = 20'<br><b>025</b> = 25'<br><b>030</b> = 30'<br><b>035</b> = 35'<br><b>040</b> = 40'<br><b>045</b> = 45'<br><b>050</b> = 50' |

\* 1/2 inch NPT rear thread

**Example:**      **PH**      **23**      **06**      **PB**      **005**



### Cable Assemblies

The LINKOSITY® cable assemblies are code compliant with the NEC and NFPA 79, and suitable for use in virtually any environment as either a permanent or temporary installation.



### Receptacles

The UL Listed LINKOSITY® male inlets or female receptacles provide the capability of interfacing directly with facility wiring by simply mounting into established fixed enclosures.



### Closure Caps

Protects unused devices from the harmful effects of harsh environments.



### Tees

| Description                                 | Catalog Number         |
|---------------------------------------------|------------------------|
| LINKOSITY® M/F/F Tee, 20A, 2P               | <b>TX2002002002T00</b> |
| LINKOSITY® M/F/F Tee, 20A, 3P               | <b>TX2003002003T00</b> |
| LINKOSITY® M/F/F Tee, 20A, 4P               | <b>TX2004002004T00</b> |
| LINKOSITY® M/F/F Tee, 20A, 5P               | <b>TX2005002005T00</b> |
| LINKOSITY® M/F/F Tee, 20A SNIG, 4P          | <b>TX2304002304T00</b> |
| LINKOSITY® M/F/F Tee, 20A SNIG, 6P          | <b>TX2306002306T00</b> |
| LINKOSITY® M/F/F Tee, 20A SNIG, A Phase Tap | <b>TX2306002304A00</b> |
| LINKOSITY® M/F/F Tee, 20A SNIG, B Phase Tap | <b>TX2306002304B00</b> |
| LINKOSITY® M/F/F Tee, 20A SNIG, C Phase Tap | <b>TX2306002304C00</b> |
| LINKOSITY® M/F/F Tee, 30A, 4P               | <b>TX3004003004T00</b> |

### Specifications

| Material         |                                                                                                                                                                           |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Raceway          | Steel, Anodized Aluminum                                                                                                                                                  |
| LINKOSITY Cables | UL 600V Type TC-ER, MTW, STOOW, polyurethane overmolded terminations                                                                                                      |
| Codes/Standards  |                                                                                                                                                                           |
| Raceway          | UL5, surface metal raceway and fittings<br>C22.2 no. 62, surface metal raceway and fittings<br>TIA/EIA 569B, commercial building standard for telecom pathways and spaces |
| LINKOSITY        | UL2238, UL50                                                                                                                                                              |