




Type K, 0.5mm Diameter Mineral Insulated thermocouple



Specifications

Sensor Type	Thermocouple type K to IEC60584
Probe material	316 stainless steel with welded tip. Mineral insulated conductors with insulated junction
Tip temperature Rating	-40°C to 1100°C
Probe termination	Pot seal, M8 x 1.0mm thread, 25mm long
Pot temperature Rating	200°C maximum
Termination lead	PTFE insulated tails, 7/0.2mm, 100mm long

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Type	Dia (mm)	Probe Length (mm)	Cable Length (mm)	Manufacturer Part No	Farnell Order #
K	0.5	250	100	MA-ISK-S05-250-P5-0.1-C2-T	424-8170
K	0.5	500	100	MA-ISK-S05-500-P5-0.1-C2-T	424-8181

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com