



Heavy Duty Thermocouple



- Type J or K thermocouple
- Stainless steel probe 4.5mm x 150mm
- 2 metres stainless steel over braided cable 7/0.2mm
- Temperature rating -60°C to +350°C
- Grounded measuring junction

Specifications:

Sensor type:	Type J or K thermocouple to IEC 584
Construction:	Stainless steel probe 4.5mm diameter x 150mm long, junction grounded to sheath at tip
Lead type:	2 metres glass fibre extension cable with stainless steel over braid, 7/0.2mm conductors
Lead termination:	Bare wire tails
Temperature range:	-60°C to +350°C

Thermocouple type	Product code	Farnell order code
Type J	FAA-GSJ-4.5-150-2.0-C4-T	707-9436
Type K	FAA-GSK-4.5-150-2.0-C4-T	707-9448

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com