

Easy Flow Gravity Hopper

Innovative system for proper lot rotation!

- Compact and space-saving vertical design
- Perfect for fasteners, assembly areas, Kanban, inventory stock, merchandise, work cells and healthcare



31625RED



31620BLUE



Hanging bins on the Floor Rack saves valuable space.



Optional bracket allows bins to hang on existing louvers panels or racks.

FEATURES


- 1 Large angled top opening for easy filling
- 2 Generous picking area provides easy access to loaded product
- 3 First-In-First-Out (FIFO) sliding divider shelf for time-sensitive inventory (for 31620 hopper only)
- 4 Rotational molded for strength and durability – LLDPE

COLORS
Red, Blue



Easy Flow Gravity Hopper		Dimensions (In.)				Capacity/Qty.			
Model No.	Description	L	W	H	D	Cu. In.	Gal.	Lbs.	Ctn. Qty.
31620 [‡]	Small Easy Flow Gravity Hopper	16	8¾	16	10	1400	6	50	1
31625	Large Easy Flow Gravity Hopper	18	10¾	19½	8	2400	10.39	75	1

When ordering 31625 specify color Red or Blue. [‡] Sliding divider shelf with 31620 hopper only.



Easy Flow Gravity Hopper Floor Rack

FEATURES

- 1 Sturdy 13-gauge steel construction
- 2 Adjustable rail heights
- 3 900 lb. weight capacity
- 4 Holds 9 large or 12 small hoppers per side
- 5 Durable powder-coated finish



30600BRACKET

- Bracket available to attach either size hopper to existing louvered panels or rail racks



30600DOLLY

- Rack can be mobilized with optional dolly
- Four swivel casters (two with brakes)



31625RACK
Shown with 31620 Easy Flow Gravity Hopper Bins

COLOR
Gray



Accessories		
Model No.	Description	Wt. Cap.
31625RACK	Easy Flow Gravity Hopper Rack 36" x 36" x 69"	900 lbs.
30600DOLLY	Easy Flow Gravity Hopper Dolly with 4" x 1½" Polyolefin Casters	900 lbs.
30600BRACKET	Easy Flow Gravity Hopper Bracket	75 lbs.



akro-mils.com

1293 South Main Street, Akron, Ohio 44301 • Tel: 800.253.2467 • Fax: 330.761.6348 • sales@akro-mils.com
In Canada: Ak-West, Inc. • Tel: 877.979.8940 • Fax: 403.225.1696 • sales@ak-westinc.com • ak-westinc.com