

PIN RECEPTACLES

FOR .032" - .046" DIAMETER PINS

<p>0359 0359-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole</p>	<p>0358 0358-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole</p>	<p>0360 0360-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole</p>	<p>0343 0343-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole</p>
<p>0356 0356-0-15-XX-34-XX-10-0 Solder mount in .102 min. mounting hole Also available on 24mm wide carrier tape: 1,100 parts per 13" reel Order as: 0356-0-57-XX-34-XX-10-0</p>	<p>6659 6659-0-15-XX-34-XX-10-0 Solder mount in .102 min. mounting hole</p>	<p>0347 0347-0-15-XX-34-XX-10-0 Solder mount in .120 min. mounting hole</p>	<p>0329 0329-0-15-XX-34-XX-10-0 Solder mount in .075 min. mounting hole. "Knock out" bottom</p>
<p>0814 0814-0-15-XX-34-XX-04-0 Solder mount in .082 min. mounting hole</p>	<p>5059 5059-0-15-XX-34-XX-04-0 Press-fit in .090 mounting hole</p>	<p>8360 8360-0-15-XX-34-XX-10-0 Press-fit in .087 mounting hole</p>	<p>9359 9359-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole</p>

SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Inches

Tolerances On: Lengths: ±.005

Diameters: ±.002

Angles: ± 2°



ORDER CODE: XXXX - X - 15 - XX - 34 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 200 μ" TIN/LEAD OVER NICKEL
- ◆ 80 200 μ" TIN OVER NICKEL (RoHS)
- ◆ 15 10 μ" GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 01 200 μ" TIN/LEAD OVER NICKEL
- ◆ 80 200 μ" TIN OVER NICKEL (RoHS)
- ◆ 27 30 μ" GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#34 CONTACT (DATA ON PAGE 258)

(For alternate contact choices, see group E on page 248)

