

EZCODE®

EZCODE® Identification Products

In this section...



EZCODE® Identification Products

Wire and Cable Marking.....	D-2-D-19
Tags	D-20-D-27
Labels.....	D-28-D-35
Signs	D-36-D-38
Warning Tapes.....	D-39-D-40

Thomas & Betts

www.tnb.com

Wire and Cable Marking

Wire and Cable Marking

Count on EZCODE® solutions for wire markers that are easy to read and stand up to the test of time. We offer printable label sheets that let you create and print your own wire markers, as well as preprinted wire marker books, cards and sleeve markers.



Sleeve Markers

- Permanently I.D. wires, cables, leads and more
- Available in a variety of sizes and materials
- A large print surface provides easy identification
- For more information, see **pages D-15–D-19**

Wire Marker Books/Cards

- Name components in seconds
- Choose the numbers or letters you need
- Carry most books and cards in your shirt pocket
- For more information, see **pages D-4–D-14**



Wire and Cable Marking

Print your own markers to meet *your* requirements!

Laser Printable Markers

- Self-laminating markers have a clear overlay of polyester that protects the legend against oils, grease, water, chemicals and foreign matter
- Markers feature a strong adhesive for maximum adhesion to the wire and are available in a variety of sizes, both as standard and specials
- 1 mil polyester (same material as WPR rolls)
- Test template included with each 25 pack
- Sizes to suit most applications



CAT. NO.	SHEET SIZE	MARKERS PER SHEET	MARKER SIZE W x L	PRINT AREA W x L	MAX. WIRE DIA.
WLP-1112	8½" x 11"	48	1" x 1½"	½" x 1"	5/16"
WLP-1214	8½" x 11"	32	1" x 2¼"	1" x ¾"	15/32"
WLP-12112	8½" x 11"	96	½" x 1½"	1/2" x 1/2"	5/16"
WLP-12214	8½" x 11"	64	½" x 2¼"	½" x ¾"	15/32"
WLP-12300	8½" x 11"	48	½" x 3"	½" x 1"	7/8"
WLP-1300	8½" x 11"	24	1" x 3"	1" x 1"	7/8"
WLP-1500	8½" x 11"	16	1" x 5"	1" x 1"	1¼"
WLP-2112	8½" x 11"	24	2" x 1½"	2½" x 2"	5/16"
WLP-2214	8½" x 11"	16	2" x 2¼"	2 x ¾"	15/32"
WLP-2300	8½" x 11"	12	2" x 3"	2" x 1"	7/8"
WLP-2500	8½" x 11"	8	2" x 5"	2" x 1"	1¼"

Order multiple 25 sheets.

Add suffix **A** for 500 sheets, **B** for 1,000 sheets.

WLP labels may be used on any standard laser printer.

Dot-Matrix Printer Labels

CAT. NO.	SHEET SIZE	MARKERS PER SHEET	MARKER SIZE W x L	PRINT AREA W x L	MAX. WIRE DIA.
WES-12112	9½" x 8"	64	½" x 1½"	½" x ½"	5/16"
WES-1112	9½" x 8"	32	1" x 1½"	1" x ½"	5/16"
WES-2112	9½" x 8"	16	2" x 1½"	2" x ½"	5/16"
WES-12214	9½" x 9"	48	½" x 2¼"	½" x ¾"	15/32"
WES-1214	9½" x 9"	24	1" x 2¼"	1" x ¾"	15/32"
WES-2214	9½" x 9"	12	2" x 2¼"	2" x ¾"	15/32"
WES-12334	9½" x 9"	32	½" x 3¾"	½" x 1"	7/8"
WES-1334	9½" x 9"	16	1" x 3¾"	1" x 1"	7/8"
WES-2334	9½" x 9"	8	2" x 3¾"	2" x 1"	7/8"
WES-2512	9½" x 12"	8	2" x 5½"	2" x 1"	1½"
WES-2128	9½" x 9"	3	2½" x 8½"	2½" x 2"	2"

Order multiple 25 sheets.

WES labels may be used on any standard dot-matrix printer.

Wire and Cable Marking

Vinyl Cloth Wire Marker Books

Standard Wire Marker Books

- Wide selection of sizes and legends
- Standard books are 3" x 5½" with 10 pages per book
- High-quality vinyl cloth material resists abrasion, oil, water and dirt
- Includes wire marker and terminal marker on one label



Standard Books

CAT. NO.	LEGENDS	NO. MARKERS PER LEGEND
WM-0 THRU 9	0 through 9; T1, T2, T3, L1, L2, L3	40 10
WM-0-9M	0 through 9 (full page each number)	46
WM-0-45	0 through 45	10
WM-46-90	46 through 90	10
WM-A-Z	A through Z, +, -, 0 through 15	10
WM-123	1, 2, 3	150
WM-ABC	A, B, C	150
WM-A-33	1 through 33, A, B, C, +, -, T1, T2, T3, L1, L2, L3	10
WM-A-90	0 through 15; 16 through 90; A through Z	6 4 2
WM-0 THRU WM-9	Any number: 0 through 9	460
WM-A, -B, -C, -D, -E, -F, -G, -L, -N, -P, -R, -S, -T, OR -X	Any letter: -A, -B, -C, -D, -E, -F, -G, -L, -N, -P, -R, -S, -T or -X	460
WM-GRD	GRD (7/16" x 2½") or GRD (7/16" x 1¼")	120 240
WMLC-1	24 house wiring and circuit breaker legends (5/8" x 1½")	20
WM-T3	T1, T2, T3	140
WM-L3	L1, L2, L3	140
WM-9T	1, 2, 3, A, B, C; T1, T2, T3; L1, L2, L3	42 28
WM-1-30	1 through 30	14
WM-12	A through Z; Blank Write-Ons; +, -	14 22 7
WM-13	+, -, AC, DC; Pos. Neg. GND; Spare, Neut., Blank Write-Ons	46 28 22
WM-0-90	0 through 45; 46 through 90	5

Order multiple 10 books for Standard Books



Compact Wire Marker Books

- Bold letters/numbers — easy to apply and read
- Convenient alphanumeric and load-center legends
- E-Z Snap feature allows removal of the entire sheet from the book more easily

Compact Books


CAT. NO.	LEGENDS	NO. MARKERS PER LEGEND
WCMB-0-9	0 through 9, A, B, C, +, - (1/4" x 1½")	128
WCMB-LC	Load Center Labels (1½" x ¾")	176

Order multiple 20 books for Compact Books

Wire and Cable Marking


Vinyl Self-Laminating Books

CAT. NO.	LEGENDS	NO. MARKERS PER LEGEND
WMSL 1-33, A-G	¼" x 1¼" – printed area ⅝"; 1 through 33 and A through G	10
WMSL-0-9	0 through 9;	40
	T1, T2, T3, L1, L2, L3	10
WMSL-0-45	0 through 45	10
WMSL-46-90	46 through 90;	10
WMSL-A-Z	A through Z; +, -, 0 through 15	10
WMSL-A-90	0 through 15;	6
	16 through 90;	4
	A through Z	2




Vinyl Self-Laminating, Blank Write-On Books

CAT. NO.	LEGENDS	NO. MARKERS PER LEGEND
WM-BW3	1" x 6" blank write-on self-laminating markers; marking area: 1" x 1"	30
WM-BW5	1" x 3" blank write-on, self laminating markers; marking area: 1" x ¾"	60
WM-BW12	½" x 1¼" blank write-on, self laminating markers; marking area: ½" x ⅝"	200
WM-BW14	¼" x 1¼" blank write-on, self-laminating markers; marking area: ¼" x ⅝"	400
WM-BW34	¾" x 1¼" blank write-on, self-laminating markers; marking area: ¾" x ½"	120



Vinyl Self-Laminating, Standard Laminator Book


CAT. NO.	LEGENDS	NO. MARKERS PER LEGEND
WM-LAM	3½" x 5" Clear Cable Laminators	50



Vinyl, Color-Coding Standard books

- Available in two sizes
- Color your wires for coding and other applications

CAT. NO.	LEGENDS	NO. MARKERS PER LEGEND
WM-COL14	¼" x 1¼" 1 page yellow and blue; 2 pages red, white, green and black	460
WM-COL1	1" x 2¼" 1 page yellow and blue; 2 pages red, white, green and black	50



Wire and Cable Marking

Make identification clean and fast! Just pull out tape, tear and wrap.

Wire Marker Dispenser

- Compact size fits in your pocket or hangs from work belt
- Unique design enables easy access to all legends during use or when refilling
- Holds 760 markers — 10 rolls of 76 markers each
- Markers are pre-cut, 1¼"-long, oil- and water-resistant polyester with acrylic adhesive

Dispenser

CAT. NO.	DESCRIPTION	STD. PKG. QTY.
WDFP-0-9	Loaded Dispenser with Legends 0 through 9	1
WDFP-NEMA	Loaded Dispenser with 10 NEMA Colors	1
WDFP	Empty Dispenser	1

Polyester Tape Refills for Dispenser

CAT. NO.	LEGEND	LABEL COLOR	ROLLS PER LEGEND
WDFPR-0	0	White	10
WDFPR-1...WDFPR-9	1, 2...9	White	10
WDFPR-0-9	0...9	White	1
WDFPR-10-19	10...19	White	1
WDFPR-A...WDFPR-Z	A, B...Z	White	10
WDFPR-L1	L1	White	10
WDFPR-L2	L2	White	10
WDFPR-L3	L3	White	10
WDFPR-T1	T1	White	10
WDFPR-T2	T2	White	10
WDFPR-T3	T3	White	10
WDFPR-MIN	-	White	10
WDFPR-PLS	+	White	10
WDFPR-YEL	BLANK	Yellow	10
WDFPR-WHT	BLANK	White	10
WDFPR-BLK	BLANK	Black	10
WDFPR-BRN	BLANK	Brown	10
WDFPR-BLU	BLANK	Blue	10
WDFPR-GRN	BLANK	Green	10
WDFPR-RED	BLANK	Red	10



Wire and Cable Marking

Vinyl Cloth Wire Marker Cards

This part number, for example, is a Wire Marker Card with a legend sequence of 1-5. Its length is 1½".


WC - 1-5 - S

Card Type
WC = Wire Marker Card
WS = Vinyl Self-Laminating


Legend
Single Character = 1, 2, 3, etc.
Sequence = 1-33, 34-66, etc.

Length
S = 1½"
D = ¾"


Numbers in Sequence




Solid Numbers on a Colored Background




Solid Letters and Numbers




Numbers in Sequence Repeated




Numbers in Sequence on a Colored Background




Voltage Markers




Solid Numbers




Solid Letters




Solid Symbols — Miscellaneous Electrical Symbols




Paired Numbers in Sequence




Letters in Sequence




Solid Machine Tool Markers




Suffix Numbers



Letters in Sequence on a Colored Background



Machine Tool Markers in Sequence



Wire and Cable Marking

Vinyl Cloth Wire Marker Cards (continued)

CAT. NO.	STYLE	LEGEND	MARKERS PER CARD OR PAIRS PER CARD		DESCRIPTION (IF NEEDED)
			1-½" (38MM)	¾" (19MM)*	
WC1-THRU-33S	Numbers in Sequence	1-33	33	66	—
WC34-THRU-66S		34-66	33	66	—
WC67-THRU-99S		67-99	33	66	—
WC100-THRU-124S		100-124	25	50	—
WC125-THRU-149S		125-149	25	50	—
WC974-THRU-999S		974-999	25	50	—
WC1-THRU-3S	Numbers in Sequence Repeated	1-3	36	72	—
WC1-THRU-4S		1-4	36	72	—
WC1-THRU-5S		1-5	35	70	—
WC0-THRU-10S		0-10	33	66	—
WC1-THRU-12S		1-12	36	72	—
WC1-THRU-18S		1-18	36	72	—
WC19-THRU-36S		19-36	36	72	—
WCZEROS	Solid Numbers	0	36	72	—
WC1S, WC2S THRU WC99S		1, 2...99	36	72	—
WC101S, 2C102S THRU WC600S		101, 102...600	25	50	—
WC1 THRU 16PS		1-16	16	32	—
WC17 THRU 32PS	Paired Numbers in Sequence	17-32	16	32	—
WC33 THRU 48PS		33-48	16	32	—
WC00S	Suffix Numbers	00	36	72	Cat. No. WC0009S has three sequences of 00...09 per card. Cat. No. WC0009D has six sequences of 00...09 per card.
WC01S, WC02S THRU WC09S		01, 02...09	36	72	
WC0009S		00...09	30	60	
WCBLZEROS	Solid Numbers on a Colored Background	0	36	72	White Legend on Blue Background
WCBL1S...WCBL50S		1...50	36	72	
WCGRZEROS		0	36	72	White Legend on Green Background
WCGR1S...WCGR50S		1...50	36	72	
WCORZEROS		0	36	72	Black Legend on Orange Background
WCOR1S...WCOR50S		1...50	36	72	
WCRDZEROS		0	36	72	White Legend on Red Background
WCRD1S...WCRD50S		1...50	36	72	
WCYLZEROS		0	36	72	Black Legend on Yellow Background
WCYL1S...WCYL50S		1...50	36	72	
WCBK1-33S	Numbers in Sequence on a Colored Background	1-33	33	66	White Legend on Black Background
WCBK34-66S		34-66	33	66	
WCBK67-99S		67-99	33	66	
WCBK100-124S		100-124	25	50	
WCBL1-33S	Numbers in Sequence on a Colored Background	1-33	33	66	White Legend on Blue Background
WCBL34-66S		34-66	33	66	
WCBL67-99S		67-99	33	66	
WCBL100-124S		100-124	25	50	
WCBR1-33S	Numbers in Sequence on a Colored Background	1-33	33	66	White Legend on Brown Background
WCBR34-66S		34-66	33	66	
WCBR67-99S		67-99	33	66	
WCBR100-124S		100-124	25	50	
WCGR1-33S	Numbers in Sequence on a Colored Background	1-33	33	66	White Legend on Green Background
WCGR34-66S		34-66	33	66	
WCGR67-99S		67-99	33	66	
WCGR100-124S		100-124	25	50	

Note: Order multiple 25 cards.

* When ¾" length markers are required, replace the last S in the catalog number with a D. For example, WC1S would become WC1D.

Wire and Cable Marking


CAT. NO.	STYLE	LEGEND	MARKERS PER CARD OR PAIRS PER CARD		DESCRIPTION (IF NEEDED)
			1-½" (38MM)	¾" (19MM)*	
WCRD1-33S	Numbers in Sequence on a Colored Background	1-33	33	66	White Legend on Red Background
WCRD34-66S		34-66	33	66	
WCRD67-99S		67-99	33	66	
WCRD100-124S		100-124	25	50	
WCOR1-33S	Numbers in Sequence on a Colored Background	1-33	33	66	Black Legend on Orange Background
WCOR34-66S		34-66	33	66	
WCOR67-99S		67-99	33	66	
WCOR100-124S		100-124	25	50	
WCYL1-33S	Numbers in Sequence on a Colored Background	1-33	33	66	Black Legend on Yellow Background
WCYL34-66S		34-66	33	66	
WCYL67-99S		67-99	33	66	
WCYL100-124S		100-124	25	50	
WCAS	Solid Letters	A	36	72	—
WCBS...WCZS		B...Z	36	72	—
WCLAS		a	36	72	—
WCLBS...WCLZS		b...z	36	72	—
WCAZAJ	Letters in Sequence	A-Z plus A-J	36	72	—
WCAZO9S		A-Z plus 0-9	36	72	—
WCLAZAJ		a-z plus a-j	36	72	—
WCBKA-ZS	Letters in Sequence on a Colored Background	A-Z plus A-J	36	72	White Legend on Black Background
WCBLA-ZS		A-Z plus A-J	36	72	White Legend on Dark Blue Background
WCBRA-ZS		A-Z plus A-J	36	72	White Legend on Brown Background
WCGRA-ZS		A-Z plus A-J	36	72	White Legend on Dark Green Background
WCRDA-ZS		A-Z plus A-J	36	72	White Legend on Red Background
WCORA-ZS		A-Z plus A-J	36	72	Black Legend on Yellow Background
WCYLA-ZS		A-Z plus A-J	36	72	Black Legend on Orange Background
WCA1S...WCA5S		Solid Letters and Numbers	A1...A5	36	72
WCB1S...WCB5S	B1...B5		36	72	—
WCC1S...WCC5S	C1...C5		36	72	—
WCD1S...WCD5S	D1...D5		36	72	—
WCE1S...WCE5S	E1...E5		36	72	—
WCF1S...WCF4S	F1...F4		36	72	—
WCG1S...WCG4S	G1...G4		36	72	—
WCH1S...WCH5S	H1...H5		36	72	—
WCJ1S...WCJ4S	J1...J4		36	72	—
WCK1S...WCK4S	K1...K4		36	72	—
WCL1S...WCL5S	L1...L5		36	72	—
WCM1S...WCM5S	M1...M5		36	72	—
WCP1S...WCP4S	P1...P4		36	72	—
WCR1S...WCR5S	R1...R5		36	72	—
WCS1S...WCS5S	S1...S5		36	72	—
WCT0S...WCT9S	T0...T9		36	72	—
WCT10S...WCT15S	T10...T15		36	72	—
WCU1S...WCU2S	U1...U2		36	72	—
WCV1S...WCV2S	V1...V2		36	72	—
WCW1S...WCW2S	W1...W2		36	72	—
WCX1S...WCX4S	X1...X4		36	72	—
WCY1S...WCY4S	Y1...Y4		36	72	—
WCZ1S...WCZ4S	Z1...Z4		36	72	—

Note: Order multiple 25 cards.

* When ¾" length markers are required, replace the last S in the catalog number with a D. For example, WC1S would become WC1D.

Wire and Cable Marking


Vinyl Cloth Wire Marker Cards (continued)

CAT. NO.	STYLE	LEGEND	MARKERS PER CARD OR PAIRS PER CARD		DESCRIPTION (IF NEEDED)
			1-½" (38MM)	¾" (19MM)*	
WC3VS	Voltage Markers	3V	36	72	—
WC6VS		6V	36	72	—
WC12VS		12V	25	50	—
WC24VS		24V	25	50	—
WC110VS		110V	22	44	—
WC115VS		115V	22	44	—
WC120VS		120V	22	44	—
WC125VS		125V	22	44	—
WC180VS		180V	22	44	—
WC220VS		220V	22	44	—
WC230VS		230V	22	44	—
WC240VS		240V	22	44	—
WC270VS		270V	22	44	—
WC280VS		280V	22	44	—
WC440VS		440V	22	44	—
WC460VS		460V	22	44	—
WC480VS		480V	22	44	—
WCPLSS		Solid Miscellaneous Electrical Symbols	+	36	72
WCMINS	-		36	72	—
WCAPLSS	A+		25	50	—
WCAMINS	A-		25	50	—
WCBPLSS	B+		25	50	—
WCBMINS	B-		25	50	—
WCPOSS	POS		25	50	—
WCNEGS	NEG		25	50	—
WCPHS	Phase		18	36	—
WCPHAS	Phase A		18	36	—
WCPHBS	Phase B		18	36	—
WCPHCS	Phase C		18	36	—
WC1PHS	1 Phase		18	36	—
WC2PHS	2 Phase		18	36	—
WC3PHS	3 Phase		18	36	—
WCINS	IN		36	72	—
WCOUTS	OUT		25	50	—
WCHOTS	HOT		25	50	—
WCGRDS	GRD		25	50	—
WCNEUTS	NEUT		22	44	—
WCLINES	LINE		22	44	—
WCLPLS	L+		25	50	—
WCLMIS	L-		25	50	—
WCLOADS	LOAD		22	44	—
WCPUS	PU		36	72	—
WCGRCS			36	72	—
WCGENS	GEN		25	50	—
WCACS	AC		36	72	—
WCDCS	DC		36	72	—
WCCOMS	COM		25	50	—
WCBATS	BAT	25	50	—	
WCBBS	BB	36	72	—	

Note: Order multiple 25 cards.

* When ¾" length markers are required, replace the last S in the catalog number with a D. For example, WC1S would become WC1D.

Wire and Cable Marking

CAT. NO.	STYLE	LEGEND	MARKERS PER CARD OR PAIRS PER CARD		DESCRIPTION (IF NEEDED)
			1-½" (38MM)	¾" (19MM)*	
WCCBS	Solid Miscellaneous Electrical Symbols	CB	36	72	—
WCCTS		CT	36	72	—
WCIGNS		IGN	25	50	—
WCSIGS		SIG	25	50	—
WCSECS		SEC	25	50	—
WCPSS		PS	36	72	—
WCPRIS		PRI	25	50	—
WCPLSS		PL	36	72	—
WCTBS		TB	36	72	—
WCSSS		SS	36	72	—
WCSPARES		SPARE	18	36	—
WCCYSS		~	36	72	—
WCGRSS			36	72	—
WCPESS		PE	36	72	—
WCPENS		PEN	25	50	—
WC1US		1U	36	72	—
WC2US		2U	36	72	—
WC1VS		1V	36	72	—
WC2VS		2V	36	72	—
WC1WS		1W	36	72	—
WC2WS	2W	36	72	—	
WC1L1S	Solid Machine Tool Markers	1L1	25	50	—
WC1L2S		1L2	25	50	—
WC1L3S		1L3	25	50	—
WC2L1S		2L1	25	50	—
WC2L2S		2L2	25	50	—
WC2L3S...WC6L1S		2L3...6L1	25	50	—
WC6L2S		6L2	25	50	—
WC6L3S		6L3	25	50	—
WC1T1S		1T1	25	50	—
WC1T2S		1T2	25	50	—
WC1T3S		1T3	25	50	—
WC2T1S		2T1	25	50	—
WC2T2S		2T2	25	50	—
WC2T3S...WC7T1S		2T3...7T1	25	50	—
WC7T2S		7T2	25	50	—
WC7T3S		7T3	25	50	—
WCLL1S		LL1	25	50	—
WCLL2S		LL2	25	50	—
WCLL3S		LL3	25	50	—
WC1T1-3T3S		Machine Tool Markers in Sequence	1T1, 1T2, 1T3, 2T1, 2T2, 2T3, 3T1, 3T2, 3T3	27	54
WC4T1-6T3S	4T1, 4T2, 4T3, 5T1, 5T2, 5T3, 6T1, 6T2, 6T3		27	54	—
WC7T1-9T3S	7T1, 7T2, 7T3, 8T1, 8T2, 8T3, 9T1, 9T2, 9T3		27	54	—
WCLL1-LL3S	LL1, LL2, LL3		27	54	—
WCA1-S2S	A1, A2, F1, F2, S1, S2		36	72	—

Note: Order multiple 25 cards.

* When ¾" length markers are required, replace the last S in the catalog number with a D. For example, WC1S would become WC1D.

Wire and Cable Marking

Identify smaller items, such as terminal blocks and small wires.


Vinyl Cloth Mini Markers

Terminal Block

CAT. NO.	LEGEND	MARKERS PER CARD
		MARKER SIZE 3/16" x 3/16"
WC1-48TM	1, 2 through 48	144
WC49-96TM	49, 50 through 96	144
WCA-ZTM	A, B through Z*	144

Order multiple 25 cards.


* A through Z legend does not include "I" or "O."



Solid Numbers and Solid Letters

CAT. NO.	LEGEND	MARKERS PER CARD
		1/2" (13MM)
Solid Numbers		
WCZEROMIN...WC99MIN	0, 1,...99	150
WC100MIN...WC250MIN	100, 101...250	99
Solid Letters		
WCAMIN	A	150
WCBMIN...WCZMIN	B,C... Z	150

Order multiple 25 cards.




Numbers in Sequence

CAT. NO.	LEGEND	MARKERS PER CARD
		1/2" (13MM)
WC0-49MIN	0, 1... 49	150
WC50-99MIN	50, 51...99	150
WC100-132MIN	100, 101...132	99
WC133-165MIN	133, 134...495	99
THRU WC463-495MIN		

Order multiple 25 cards.


Quantity of each number per card — 3.



Letters in Sequence

CAT. NO.	LEGEND	MARKERS PER CARD
		1/2" (13MM)
WCAZMIN	A, B...Z	156

Order multiple 25 cards.



Wire and Cable Marking


Identify large conductors, cables and tubing for hydraulic systems.

Vinyl Cloth Cable Markers

Solid Numbers or Letters

CAT. NO.	LEGEND	MARKERS PER CARD	
		3½" (89MM)	1¾" (45MM)*
Solid Letters			
WCCMAS	A	18	36
WCCMBS	B	18	36
WCCMCS	C	18	36
WCCMDS	D	18	36
WCCMES	E	18	36
WCCMFS	F	18	36
WCCMNS	N	18	36
Solid Numbers			
WCCM0S	0	18	36
WCCM1S, WCCM2S... WCCM9S	1, 2...9	18	36

Order multiple 25 cards.




* When 1¾" length markers are required, replace the last S in the part number with a D. e.g., WCCM1S would become WCCM1D.

Numbers or Letters in Sequence

CAT. NO.	LEGEND	MARKERS PER CARD	
		3½" (89MM)	1¾" (45MM)*
WCCM01-09S	01 through 09	2	4
WCCM1-9S	1 through 9	2	4
WCCM1-18S	1 through 18	1	2
WCCM19-36S	19 through 36	1	2
WCCM37-54S	37 through 54	1	2
WCCM55-72S	55 through 72	1	2
WCCM73-90S	73 through 90	1	2
WCCM91-99S	91 through 99	2	4
WCCMA-IS	A through I	2	4
WCCMJ-RS	J through R	2	4
WCCMS-ZS	S through Z	2	4

Order multiple 25 cards.




* When 1¾" length markers are required, replace the last S in the part number with a D. e.g., WCCM1S would become WCCM1D.

Solid NEMA Colors

CAT. NO.	COLOR	MARKERS PER CARD	
		1½" (38MM)	¾" (19MM)*
WCBLKS	Black	36	72
WCBLDS	Dark Blue	36	72
WCBLLS	Light Blue	36	72
WCBRNS	Brown	36	72
WCGRYS	Gray	36	72
WCDGRS	Dark Green	36	72
WCGRLS	Light Green	36	72
WCMARS	Maroon	36	72
WCOLIS	Olive	36	72
WCORAS	Orange	36	72
WCPINS	Pink	36	72
WCPURS	Purple	36	72
WCREDS	Red	36	72
WCTANS	Tan	36	72
WCWHIS	White	36	72
WCYELS	Yellow	36	72

Order multiple 25 cards.




* When ¾" length markers are required, replace the last S in the part number with a D. e.g., WC1S would become WC1D.

Wire and Cable Marking

Self-Laminating Vinyl Wire Marker Cards

Blank Write-On Cable Markers

CAT. NO.	OVERALL MARKER SIZE	WRITE-ON AREA W X H	MARKERS PER CARD
WSLM33	1" x 2 3/4"	1" x 3/4"	3
WSLM35	1" x 5"	1" x 1"	3
WSLM123	1 1/2" x 3"	1 1/2" x 3/4"	2
WSLM23	2" x 3"	2" x 3/4"	2
WSLM125	1 1/2" x 5"	1 1/2" x 1"	2
WSLM25	2" x 5"	2" x 1"	2
WSLM48	2" x 8"	2" x 3/4"	2
WSLM95	2 1/4" x 2 1/4"	2 1/2" x 2 1/4"	2
WSLM410	2" x 10"	2" x 4 1/2"	2
WSLM415	2" x 15"	2" x 7"	2




Solid Letters

CAT. NO.	LEGEND	MARKERS PER CARD	
		1 1/2" (38MM)	3/4" (19MM)*
WSAS	A	36	72
WSBS...WSZS	B, C...Z	36	72

Order multiple 25 cards.

* When 1 3/4" length markers are required, replace the last **S** in the part number with a **D**. e.g., WCCM1S would become WCCM1D.




Solid Numbers

CAT. NO.	LEGEND	MARKERS PER CARD	
		1 1/2" (38MM)	3/4" (19MM)*
WSZEROS	0	36	72
WS1S...WS99S	1, 2...99	36	72
WS100S	100	25	50
WS101S...WS600S	101, 102...600	25	—


Order multiple 25 cards.

* When 1 3/4" length markers are required, replace the last **S** in the part number with a **D**. e.g., WCCM1S would become WCCM1D.



Blank Write-On


CAT. NO.	WRITE-ON AREA (W X D)	MARKERS PER CARD 1 1/2" (38MM)
WSBW14X112S	1/4" x 1 1/2"	36
WSBW38X112S	3/8" x 1 1/2"	26
WSBW12X112S	1/2" x 1 1/2"	18
WSBW34X112S	3/4" x 1 1/2"	12
WSBW1X112S	1" x 1 1/2"	9
WSBW112X112S	1 1/2" x 1 1/2"	6



CAT. NO.	MARKER SIZE	MARKERS PER CARD
WCBW14X34D*	1/4" x 3/4"	72
WCBW14X112S*	1/4" x 1 1/2"	36
WCBW1132X112S*	1 1/32" x 1 1/2"	26
WCBW12X12D*	1/2" x 1 1/2"	54
WCBW12X112S*	1/2" x 1 1/2"	18
WCBW58X112S*	5/8" x 1 1/2"	14
WCBW34X12D*	3/4" x 1 1/2"	36
WCBW34X214S*	3/4" x 2 1/4"	12
WCBW1X112S*	1" x 1 1/2"	9
WCBW112X112S*	1 1/2" x 1 1/2"	6











Order multiple 25 cards.

* Not self-laminating.




Wire and Cable Marking

Sleeve Markers Features at a Glance

	SMY Series	SMC Series	SMS/SMD/SMR Series	SMO Series	SMK Series
					
SHAPE					
FOR MORE INFORMATION, SEE	p. D-16	p. D-16	p. D-17	p. D-18	p. D-18
STYLE	Closed Y-shape	Open clip-on	Closed spring-action	Closed oval	Closed slotted
APPLICATION	Install on wires before connection	Install on wires before or after connection	Install on wires before connection	Install on wires before connection or on holders	Install on holders
WIRE SIZE RANGE	#24–#20 AWG	#18–#6 AWG	#22–#5 AWG	#10–#6 AWG for direct install; any size with holder*	Any size with holder*
MARKER SIZE	.130"H x .138"W	.142"H x .146"W to .264"H x .272"W	.142"H x .138"W to .650"H x .433"W	.445"H x .169"W	.445"H
PACKAGING	Reel	Strips	Strips, disc or reel	Disc	Bag

* Holder fastens with cable ties around cable or pipe


Wire and Cable Marking



Example: The catalog number shown above is for yellow clip-on sleeve markers imprinted with the ground symbol for #12-#10 AWG wires.

SMY Series Sleeve Markers


- Closed combination marker
- Special Y-shaped profile covers a wide diameter range of small wires
- Large print surface enables excellent readability at normal reading distances



CAT. NO.	COLOR	RECOMMENDED WIRE DIAMETER (IN.)	AWG	MARKER SIZE H x W (IN.)	STD. PKG. QTY.
SMY079-4-[]	Yellow	.039-.079	#23-#20	.130 x .138	1 reel of 1,000 markers
SMY079-9-[]	White	.039-.079	#23-#20	.130 x .138	1 reel of 1,000 markers


SMC Series Clip-On Sleeve Markers

- Open marker snaps easily onto already connected wires
- Barbed design holds markers securely in place



CAT. NO.	COLOR	RECOMMENDED WIRE DIAMETER (IN.)	AWG	MARKER SIZE H x W (IN.)	STD. PKG. QTY.
SMC118-4-[]	Yellow	.094-.118	#18-#16	.142 x .146	10 strips of 20 markers
SMC118-9-[]	White	.094-.118	#18-#16	.142 x .146	10 strips of 20 markers
SMC157-4-[]	Yellow	.118-.157	#16-#14	.165 x .177	10 strips of 20 markers
SMC157-9-[]	White	.118-.157	#16-#14	.165 x .177	10 strips of 20 markers
SMC197-4-[]	Yellow	.157-.197	#12-#10	.217 x .224	10 strips of 20 markers
SMC197-9-[]	White	.157-.197	#12-#10	.217 x .224	10 strips of 20 markers
SMC244-4-[]	Yellow	.197-.244	#8-#6	.264 x .272	10 strips of 20 markers
SMC244-9-[]	White	.197-.244	#8-#6	.264 x .272	10 strips of 20 markers

Wire and Cable Marking




Example: The catalog number shown above is for white sleeve markers in strips imprinted with the number 3 for #22-#16 AWG wire.

Closed Combination Sleeve Markers


- Available in strips or bags (SMS Series), on compact disc (SMD Series) or on a reel (SMR Series)
- Permanent grip and adjustable marking sleeve for as-yet unconnected wires
- Unique profile with spring-action bellows covers wide wire diameter range
- Twist-protection for secure combination marking



SMS Series



CAT. NO.	COLOR	RECOMMENDED WIRE DIAMETER (IN.)	AWG	MARKER SIZE H x W (IN.)	STD. PKG. QTY.
SMS Series Sleeve Markers in Strips or Bags					
SMS118-4-[_]	Yellow	.051-.118	#22-#16	.142 x .138	10 strips of 25 markers
SMS118-9-[_]	White	.051-.118	#22-#16	.142 x .138	10 strips of 25 markers
SMS196-4-[_]	Yellow	.059-.197	#16-#10	.217 x .165	10 strips of 25 markers
SMS196-9-[_]	White	.059-.197	#16-#10	.217 x .165	10 strips of 25 markers
SMS394-4-[_]	Yellow	.157-.394	#13-#4	.374 x .260	10 strips of 25 markers
SMS394-9-[_]	White	.157-.394	#13-#4	.374 x .260	10 strips of 25 markers
SMS630-4-[_]	Yellow	.315-.630	#5	.650 x .433	1 bag of 20 loose markers
SMS630-9-[_]	White	.315-.630	#5	.650 x .433	1 bag of 20 loose markers
SMD Series Sleeve Markers on a Compact Disc					
SMD118-4-[_]	Yellow	.051-.118	#22-#16	.142 x .138	1 disc of 500 markers
SMD118-9-[_]	White	.051-.118	#22-#16	.142 x .138	1 disc of 500 markers
SMD196-4-[_]	Yellow	.059-.197	#16-#10	.217 x .165	1 disc of 500 markers
SMD196-9-[_]	White	.059-.197	#16-#10	.217 x .165	1 disc of 500 markers
SMD394-4-[_]	Yellow	.157-.394	#13-#4	.374 x .260	1 disc of 250 markers
SMD394-9-[_]	White	.157-.394	#13-#4	.374 x .260	1 disc of 250 markers
SMDP394-9-[_]	White	Use with RG6/RG59 coax	#12-#4	—	1 disc of 250 markers
SMR Series Sleeve Markers on a Reel					
SMR118-4-[_]	Yellow	.051-.118	#22-#16	.142 x .138	1 reel of 1,000 markers
SMR118-9-[_]	White	.051-.118	#22-#16	.142 x .138	1 reel of 1,000 markers
SMR196-4-[_]	Yellow	.059-.197	#16-#10	.217 x .165	1 reel of 1,000 markers
SMR196-9-[_]	White	.059-.197	#16-#10	.217 x .165	1 reel of 1,000 markers




SMD Series



SMR Series

Wire and Cable Marking



Example: The catalog number shown above is for yellow oval sleeve markers imprinted with the letter A for use directly on #10–#6 AWG cables or on SMOH or SMKH holders.

Combination markers for cable and pipe marking! SMO and SMK Series Sleeve Markers

- Made of cadmium-free and silicone-free rigid PVC
- SMK markers install quickly onto SMKH or SMOH holder, which fastens with cable ties around cable or pipe
- SMO markers can also be used with SMKH or SMOH holders or installed directly onto cable






SMO and SMK Markers

CAT. NO.	COLOR	RECOMMENDED WIRE DIAMETER (IN.)	AWG	MARKER SIZE H X W (IN.)	STD. PKG. QTY.
SM0256-4-[_]	Yellow	.147–.256	#10–#6	.445 x .169	1 disc of 500 markers
SM0256-9-[_]	White	.197–.256	#10–#6	.445 x .169	1 disc of 500 markers
SMK244-4-[_]	Yellow	Use with Holder	—	.445 H	1 bag of 100 markers
SMK244-9-[_]	White	Use with Holder	—	.445 H	1 bag of 100 markers

SMOH and SMKH Holders

CAT. NO.	COLOR	MAX. NO. OF SMO MARKERS	MAX. NO. OF SMK MARKERS	STD. PKG. QTY.
SMOH7-0	Black	7	8	1 bag of 100 holders
SMOH12-0	Black	12	13	1 bag of 100 holders
SMOH18-0	Black	18	19	1 bag of 100 holders
SMOH30-0	Black	30	31	1 bag of 100 holders
SMKH10-0	Black	10	10	1 bag of 100 holders
SMKH20-0*	Black	20	20	1 bag of 100 holders

* Made of Polyamide 6/6 resistant to organic solvents with limited resistance against acids and alkalis. Recommended Ty-Rap® cable tie is Cat. No. TY524MX. Other colors available on request. Contact Tech Services for availability.




Wire and Cable Marking

Sleeve Marker Magazine Dispenser

- Feeds left or right
- Sturdy polystyrene construction

This magazine dispenser features two identical lids, linked by a hinge on one side. The outer sides of the lids have grooves to hold SMS Series Sleeve Marker Strips.



CAT. NO.	DESCRIPTION	STD. PKG. QTY.
Dispenser with Application Tool Only (order sleeve markers separately)		
SMMDT118-E	Dispenser and SMAT118 Tool for SMS118 Markers	1
SMMDT196-E	Dispenser and SMAT196 Tool for SMS196 Markers	1
Dispenser with Application Tool and 20 Strips of 25 SMS Sleeve Markers*		
SMMDT118-9-0-9	Dispenser with 500 White SMS118 Sleeve Markers and SMAT118 Tool	1
SMMDT118-4-0-9	Dispenser with 500 Yellow SMS118 Sleeve Markers and SMAT118 Tool	1
SMMDT196-9-0-9	Dispenser with 500 White SMS196 Sleeve Markers and SMAT196 Tool	1
SMMDT196-4-0-9	Dispenser with 500 Yellow SMS196 Sleeve Markers and SMAT196 Tool	1

* Legend for markers included in magazine dispenser is 0-9.

For refills, order SMS118 (#22-#16 AWG) or SMS196 (#16-#10 AWG) sleeve markers (page D-17).

Sleeve Marker Application Tool

Made of Teflon® coated stainless steel, this application tool makes it easy to slide SMS Series sleeve markers onto cables.



CAT. NO.	USE WITH SLEEVE MARKER	RECOMMENDED WIRE DIAMETER (IN.)	AWG	STD. PKG. QTY.
SMAT118	SMS118	.051-.118	#22-#16	5/bag
SMAT196	SMS196	.098-.196	#16-#10	5/bag

Teflon is a trademark of DuPont.

Sleeve Marker Installation Magazine

- Complete kit for onsite marking
- Each kit includes 20 wands of 25 markers
- Marker legends include 0-9, L, R, S, T, Ground, Neutral, Blue -, Red +, Gray Neutral



CAT. NO.	DESCRIPTION	STD. PKG. QTY.
Kit with 20 Wands of 25 SMS Sleeve Markers		
SMMK118-4	Kit with 500 Yellow SMS118 Markers for #22-#16 AWG Wire	1
SMMK118-9	Kit with 500 White SMS118 Markers for #22-#16 AWG Wire	1
SMMK196-4	Kit with 500 Yellow SMS196 Markers for #16-#10 AWG Wire	1
SMMK196-9	Kit with 500 White SMS196 Markers for #16-#10 AWG Wire	1

For refills, order SMS118 (#22-#16 AWG) or SMS196 (#16-#10 AWG) sleeve markers (page D-17).

Tags

Stay safe and get into compliance — with EZCODE® Tags.

You don't need accidents happening on the job. To ensure greater workplace safety, choose the warning tags that hang tough in industrial environments and designate potential hazards. EZCODE® Tags enable easy identification and can help your facility meet OSHA regulations.

- Made of rigid vinyl with sturdy brass eyelets
- Withstand moisture, dirt and grease
- Write on with pencil, ballpoint pen or permanent marker
- Sold in packages of 25 identical tags
- Standard size is 3¼" x 6" for Accident Prevention, Lockout and Inspection and Control Tags
- Standard size is 3¼" x 5½" for Self-Laminating Tags

Accident Prevention Tags

Choose among DANGER, CAUTION or NOTICE style tags to meet OSHA regulations and help prevent personnel injury or death. They're available in English or in bilingual English/Spanish versions. All of our Accident Prevention Tags meet OSHA requirements and current ANSI Z535.5 recommendations for color and header design. They ship with heavy-duty nylon ties for fastening.



- ▲ DANGER** DANGER indicates an immediate hazard with a strong potential for death or severe injury
- ▲ CAUTION** CAUTION warns against potential hazards or unsafe practices

For more information, see pp. D-21-D-23


Inspection and Control Tags

These tags indicate equipment safety inspection and material production status at a glance with their bold headers and easily understood color-coding system. They ship with heavy-duty nylon ties for fastening.



Self-Laminating Tags

Add your own information to a pre-printed or blank tag and then seal it under a clear, protective cover. EZCODE® Self-Laminating Tags are weatherproof, moisture-resistant and tamperproof — your information can't be altered once the tag is sealed. They're made of rigid .010" plastic with a clear polyester self-laminating cover and ¼" brass eyelet.



Lockout Tags

Provide critical safety information in accordance with current OSHA regulations with Lockout Tags. Designed for repeat use, they withstand up to 80 lbs. of pulling pressure and feature brass eyelets large enough (7/16" I.D.) to accommodate most locks.



For more information, see p. D-24


Custom Tags

Need tags you don't see in this catalog? No problem — we welcome custom orders. Please refer to the form on page D-27 for guidance, and don't hesitate to contact our knowledgeable, helpful EZCODE® Technical Services representatives for ordering assistance.

Tags

Avoid peril with danger tags.

Danger Tags




CAT. NO.	TAG SIZE
APT-D5A	3/4" x 6"



CAT. NO.	TAG SIZE
APT-D6A	3/4" x 6"



CAT. NO.	TAG SIZE
APT-D8A	3/4" x 6"



CAT. NO.	TAG SIZE
APT-D12A	3/4" x 6"



CAT. NO.	TAG SIZE
APT-D15A	3/4" x 6"



CAT. NO.	TAG SIZE
APT-D16A	3/4" x 6"



CAT. NO.	TAG SIZE
APT-D19A	3/4" x 6"



CAT. NO.	TAG SIZE
APT-D20A	3/4" x 6"



CAT. NO.	TAG SIZE
APT-D27A	3/4" x 6"



CAT. NO.	TAG SIZE
APT-D28A	3/4" x 6"



CAT. NO.	TAG SIZE
APT-D34A	3/4" x 6"



CAT. NO.	TAG SIZE
APT-D48A	3/4" x 6"



Note: Order multiple 25 tags.


Tags

Give others fair warning with easy-to-see caution tags.

Caution Tags



CAT. NO.	TAG SIZE
APT-C54	3/4" x 6"




CAT. NO.	TAG SIZE
APT-C55	3/4" x 6"



CAT. NO.	TAG SIZE
APT-C56	3/4" x 6"




CAT. NO.	TAG SIZE
APT-C57	3/4" x 6"



CAT. NO.	TAG SIZE
APT-C58	3/4" x 6"



CAT. NO.	TAG SIZE
APT-C59	3/4" x 6"



CAT. NO.	TAG SIZE
APT-C60	3/4" x 6"



CAT. NO.	TAG SIZE
APT-C61	3/4" x 6"



Note: Order multiple 25 tags.

Tags

Don't let language be a barrier to safety.

Bilingual Tags



CAT. NO.	TAG SIZE
APT-BD74	3 1/4" x 6"



CAT. NO.	TAG SIZE
APT-BD75	3 1/4" x 6"



CAT. NO.	TAG SIZE
APT-BD76	3 1/4" x 6"



CAT. NO.	TAG SIZE
APT-BD79	3 1/4" x 6"



CAT. NO.	TAG SIZE
APT-BD80	3 1/4" x 6"



CAT. NO.	TAG SIZE
APT-BD81	3 1/4" x 6"



CAT. NO.	TAG SIZE
APT-BD82	3 1/4" x 6"



CAT. NO.	TAG SIZE
APT-BC77	3 1/4" x 6"



CAT. NO.	TAG SIZE
APT-BN78	3 1/4" x 6"



Note: Order multiple 25 tags.

Tags

Greatly reduce the chance of an accident.

Lockout Tags

Lockout tags meet current OSHA regulations and can prevent serious accidents from happening. When secured with nylon ties, lockout tags can withstand 80 lbs. of pulling pressure. They feature brass eyelets with an inner diameter of 7/16" — large to accommodate most locks. A write-on matte finish enables you to write on the tags with pens, pencils or permanent markers.



CAT. NO.	TAG SIZE
LT-12C	3 1/4" x 6"



CAT. NO.	TAG SIZE
LT-15C	3 1/4" x 6"



CAT. NO.	TAG SIZE
LT-16C	3 1/4" x 6"



CAT. NO.	TAG SIZE
LT-45A	3 1/4" x 6"



CAT. NO.	TAG SIZE
LT-56A	3 1/4" x 6"




CAT. NO.	TAG SIZE
LT-57A	3 1/4" x 6"



CAT. NO.	TAG SIZE
LT-58A	3 1/4" x 6"



CAT. NO.	TAG SIZE
LT-33	3 1/4" x 6"



CAT. NO.	TAG SIZE
LT-59A	3 1/4" x 6"



CAT. NO.	TAG SIZE
LT-44	3 1/4" x 6"

Note: Order multiple 25 tags.

Tags

Identify your cable bundles with permanent, Type 304 stainless steel imprinted tags applied with stainless steel cable ties.

I.D. Tagging System

- After imprinting tags, simply slip a tie through slots in the tag and fasten with a cable tie installation tool
- Works with 1/4" wide ties
- Type 304 Stainless Steel



CAT. NO.	WIDTH		LENGTH	
	IN.	MM	IN.	MM
SSID100	.75	19.05	2.0	51
SSID101	1.50	.10	2.5	63
SSID102	.75	19.05	3.5	89

Packaging Quantity: 100/box

.015" (.254mm) Thickness

Note: Customized pre-embossed tags are available. Please consult Customer Service for details.

Add suffix (316) for 316 Stainless Steel.

Imprints Thomas & Betts stainless steel I.D. tags.

I.D. Tag Imprinter

- Includes special tag holder that provides quick, accurate positioning of tag
- Comes with a 3/32" character imprinting wheel

CAT. NO.	DESCRIPTION
WTID200	I.D. Tag Imprinter
WTID281	3/32" Character Imprinting Wheel
WTID283	1/16" Character Imprinting Wheel
WTID290	1/32" Character Imprinting Wheel

Packaging Quantity: 1/box



Tags

A complete range of individual letters, numbers and symbols!

Stainless Steel I.D. Tags

- Slip these I.D. tags over carriers or strips (shown below)
- Attach to your cable or hose with a variety of Thomas & Betts Stainless Steel Cable Ties



CAT. NO.	DESCRIPTION	LENGTH	WIDTH	STD. PKG. QTY.
ER010	A	.445"	.375"	100
ER011	B	.445"	.375"	100
ER012	C	.445"	.375"	100
ER013	D	.445"	.375"	100
ER014	E	.445"	.375"	100
ER015	F	.445"	.375"	100
ER016	G	.445"	.375"	100
ER017	H	.445"	.375"	100
ER018	I	.445"	.375"	100
ER019	J	.445"	.375"	100
ER020	K	.445"	.375"	100
ER021	L	.445"	.375"	100
ER022	M	.445"	.375"	100
ER023	N	.445"	.375"	100
ER024	O	.445"	.375"	100
ER025	P	.445"	.375"	100
ER026	Q	.445"	.375"	100
ER027	R	.445"	.375"	100
ER028	S	.445"	.375"	100
ER029	T	.445"	.375"	100
ER030	U	.445"	.375"	100

CAT. NO.	DESCRIPTION	LENGTH	WIDTH	STD. PKG. QTY.
ER031	V	.445"	.375"	100
ER032	W	.445"	.375"	100
ER033	Y	.445"	.375"	100
ER034	Z	.445"	.375"	100
ER018	1	.445"	.375"	100
ER037	2	.445"	.375"	100
ER038	3	.445"	.375"	100
ER039	4	.445"	.375"	100
ER040	5	.445"	.375"	100
ER041	6	.445"	.375"	100
ER021	7	.445"	.375"	100
ER042	8	.445"	.375"	100
ER041	9	.445"	.375"	100
ER024	0	.445"	.375"	100
ER035	Minus/Hyphen	.445"	.375"	100
ER036	Blank	.445"	.375"	100
ER046	Plus +	.445"	.375"	100
ER047	Earth	.445"	.375"	100
ER048	Sine	.445"	.375"	100
ER049	Slash /	.445"	.375"	100

Character size .218"
Material .025" Type 316 Stainless Steel

Convenient and easy identification!

Stainless Steel I.D. Tag Carriers/Strips

- Select from carriers and strips
- Tag kit contains 50 of each letter, number, symbol, carrier and strip in a handy carrying case



CAT. NO.	DESCRIPTION	LENGTH	WIDTH	STD. PKG. QTY.
ER043	6 Character Carrier	3.64"	.38"	100
ER044	10 Character Carrier	5.14"	.38"	100
ER045	16 Character Carrier	7.39"	.38"	100
ER050	Short Strip	4.25"	.38"	100

CAT. NO.	DESCRIPTION	LENGTH	WIDTH	STD. PKG. QTY.
ER051	Medium Strip	5.75"	.38"	100
ER052	Long Strip	8.0"	.38"	100
ER060	I.D. Tag Kit	—	—	1

I.D. Tag Kit contains 50 of each letter, number, symbol, carrier and strip in a handy carrying case.

EZCODE®

Custom Tag Express Order Form

This Custom Tag Order Form is for the convenience of you and your authorized Thomas & Betts Distributor. To help expedite your order, please copy this form and fax a completed copy to us. For questions about ordering Custom Tags, call Tech Services at 888-862-3289.

Fax your order to 901-252-1321.







Materials and Available Sizes:

Please check the appropriate boxes for material and size.

MATERIAL	AVAILABLE SIZES	
<input type="checkbox"/> Vinyl	<input type="checkbox"/> 3¼" x 6"	<input type="checkbox"/> 3¼" x 5½"
<input type="checkbox"/> Other _____	<input type="checkbox"/> Other _____	

Tag Type:

Please check one of the options below for English or Spanish language.

<input type="checkbox"/> E <input type="checkbox"/> S  Caution	<input type="checkbox"/> E <input type="checkbox"/> S  Danger	<input type="checkbox"/> E <input type="checkbox"/> S  Lockout	Quantity: <input type="text"/> No minimum order. Orders for 50+ tags are welcome. Call for delivery and additional volume discounts.
<input type="checkbox"/> E <input type="checkbox"/> S  Inspection and Material Control	<input type="checkbox"/> E <input type="checkbox"/> S  Production Status	<input type="checkbox"/> E <input type="checkbox"/> S  Blank (No Message)	



Message, Tag Front:

Please print your message clearly in the box below.

Message, Tag Back:

If none, leave blank.

Distributor Billing Location:

Distributor Name: _____
 Distributor Address: _____
 P.O. Number: _____
 Contact Name: _____
 Phone Number: _____
 Fax Number: _____

Brass Grommets/Eyelets:

Please check the appropriate boxes for number and size.

NUMBERS	AVAILABLE SIZES
<input type="checkbox"/> 1 <input type="checkbox"/> Other _____	<input type="checkbox"/> ¼" <input type="checkbox"/> Other _____

Protective Options:

SELF-LAMINATING COVERS <input type="checkbox"/> Front <input type="checkbox"/> Back	UV PROTECTION <input type="checkbox"/>
---	--

Additional Options:

<input type="checkbox"/> Bar Codes	<input type="checkbox"/> Carbon Set	<input type="checkbox"/> Perforation	<input type="checkbox"/> Sequential Numbering
------------------------------------	-------------------------------------	--------------------------------------	---

To discuss these options, call Tech Services at 888-862-3289.

Shipping Location:

Your Name/Title: _____
 Company Name: _____
 Attn: _____
 Address: _____
 City: _____ State: _____ Zip: _____
 Phone/Fax Number: _____
 P.O. Number: _____

Labels


Stick to safety with EZCODE® Labels.

All kinds of dangers exist with high-voltage equipment and industrial machinery. Warn your employees of hazards and keep them safe with EZCODE® Labels. Place the self-adhesive labels where they need to be seen for on-the-spot identification and instruction and to help you comply with OSHA and NFPA regulations.

Arc Flash Labels

Avoid accidents and OSHA fines by clearly marking electrical equipment with potential for arc flash hazards with EZCODE® Arc Flash Labels. They're designed to meet the latest ANSI standards for safety labels and help you comply with National Electrical Code® standards.

- Made of pressure-sensitive vinyl with aggressive acrylic adhesive



Machine Warning Labels

Machine Warning Labels help you prevent injuries and reduce downtime. They also comply with ASME (ANSI Z535) and OSHA (1910.145) requirements to use safety and compliance signs to indicate hazards that may lead to accidents, injury and property damage.

▲ DANGER

DANGER indicates an immediate hazard with a strong potential for death or severe injury

▲ WARNING

WARNING indicates hazardous situations that may result in death or severe injury

▲ CAUTION

CAUTION warns against potential hazards or unsafe practices

Conduit and Voltage Markers

Positively identify voltage on conduit, load centers, circuit breakers, switches and other electrical equipment to allow faster, safer repair.

- Made from rugged, self-sticking vinyl — adheres to most surfaces
- High-contrast black type on safety-orange background for visibility
- For more information, see **p. D-29**



- Made from pressure-sensitive vinyl with polyester overlamine and permanent acrylic adhesive
- Use indoors or outdoors — temperature range of -40° F to 180° F
- 5-year durability



Electrical Safety Labels

"Mr. Ouch" NEMA Safety Labels use both words and pictures to warn children of the dangers of playing around pad-mounted transformers.

- Made from tamper-resistant film with permanent acrylic adhesive
- Weatherproof and fade-resistant
- For more information, see **p. D-30**



Write-On Control Markers

A quick and simple way to keep on-the-spot records, write-on control markers are easy to carry and dispense as needed.

- Made from pressure-sensitive, imprintable matte vinyl
- Adhere to clean, flat, dry, smooth surfaces
- Resists grease, oil and moisture
- Accepts pen, pencil, felt-tip marker, typewriter or rubber stamp
- For more information, see **pp. D-31-D-32**



Lockout Labels

Compliant with OSHA lockout/tagout requirements, EZCODE® Lockout Labels are design to help you develop, implement and update a lockout/tagout program for your facility.

- Made from pressure-sensitive vinyl with polyester overlamine
- Adhere to almost any clean, dry surface — rough or smooth
- Use in indoor or outdoor applications



Industrial Markers

Individual letters and numbers are ideal for fast, general-purpose marking of bins, shelves, poles, panels, switches and equipment.

- Made from plastic-coated vinyl cloth with high-tack adhesive
- Rated for indoor use
- Available in 4 sizes with character height ranging from 5/16" to 2"
- Reflective letters and numbers also available for high visibility in dark or dimly lit areas
- For more information, see **p. D-33**



Pictogram Labels

Use these labels featuring universal symbols to communicate hazards to anyone, regardless of literacy or language.

- Made from self-adhesive vinyl
- For more information, see **p. D-34**



Custom Labels

Need labels you don't see in this catalog? No problem — we welcome custom orders. Please refer to the form on page **D-35** for guidance, and don't hesitate to contact our knowledgeable, helpful EZCODE® Technical Services representatives for ordering assistance.

Labels


Identify electrical systems, including load centers, circuit breakers, switches and any other vital electrical equipment!

Vinyl Conduit and Voltage Markers


- Helps prevent mistakes and trial-and-error searching during electrical service work
- Manufactured from rugged, self-sticking vinyl with high-contrast black printing on safety-orange background
- OSHA compliant



STYLE A: 2 1/4" x 9"
(1 marker per card) Character Height 1 1/8"



STYLE B: 1 1/8" x 4 1/2"
(4 markers per card) Character Height 7/8"



STYLE C: 2 1/4" x 1/2"
(18 markers per card) Character Height 5/16"

STYLE A 2 1/4" X 9"	STYLE B 1 1/8" X 4 1/2"	STYLE C 2 1/4" X 1/2"	LEGEND
WJT-5010	WDT-5010	WAT-5010	110 Volts
WJT-5011	WDT-5011	WAT-5011	115 Volts
WJT-5012	WDT-5012	WAT-5012	120 Volts
WJT-5045	WDT-5045	WAT-5045	120/208 Volts
WJT-5013	WDT-5013	WAT-5013	208 Volts
WJT-5014	WDT-5014	WAT-5014	220 Volts
WJT-5015	WDT-5015	WAT-5015	230 Volts
WJT-5016	WDT-5016	WAT-5016	240 Volts
WJT-5017	WDT-5017	WAT-5017	250 Volts
WJT-5018	WDT-5018	WAT-5018	277 Volts
WJT-5046	WDT-5046	WAT-5046	277/480 Volts
WJT-5057	WDT-5057	WAT-5057	380 Volts
WJT-5044	WDT-5044	WAT-5044	415 Volts
WJT-5019	WDT-5019	WAT-5019	440 Volts
WJT-5020	WDT-5020	WAT-5020	460 Volts
WJT-5021	WDT-5021	WAT-5021	480 Volts
WJT-5022	WDT-5022	WAT-5022	550 Volts
WJT-5023	WDT-5023	WAT-5023	600 Volts
WJT-5024	WDT-5024	WAT-5024	2,200 Volts
WJT-5025	WDT-5025	WAT-5025	2,300 Volts
WJT-5026	WDT-5026	WAT-5026	2,400 Volts
WJT-5027	WDT-5027	WAT-5027	4,160 Volts
WJT-5028	WDT-5028	WAT-5028	4,800 Volts
WJT-5058	WDT-5058	WAT-5058	5,000 Volts
WJT-5029	WDT-5029	WAT-5029	6,900 Volts

Note: Order multiple 25 cards.


STYLE A 2 1/4" X 9"	STYLE B 1 1/8" X 4 1/2"	STYLE C 2 1/4" X 1/2"	LEGEND
WJT-5030	WDT-5030	WAT-5030	7,200 Volts
WJT-5059	WDT-5059	WAT-5059	12,000 Volts
WJT-5060	WDT-5060	WAT-5060	13,000 Volts
WJT-5047	WDT-5047	WAT-5047	13,200 Volts
WJT-5031	WDT-5031	WAT-5031	13,800 Volts
WJT-5032	WDT-5032	WAT-5032	AC
WJT-5043	WDT-5043	WAT-5043	Air Conditioning
WJT-5052	WDT-5052	WAT-5052	Circuit Breaker
WJT-5051	WDT-5051	WAT-5051	Circuit # ___
WJT-5038	WDT-5038	WAT-5038	DC
WJT-5050	WDT-5050	WAT-5050	Electric Out of Service
WJT-5033	WDT-5033	WAT-5033	Emergency Service
WJT-5039	WDT-5039	WAT-5039	Exit Lights
WJT-5040	WDT-5040	WAT-5040	Fire Alarm
WJT-5053	WDT-5053	WAT-5053	Fuse Box
WJT-5041	WDT-5041	WAT-5041	Heating Circuit
WJT-5037	WDT-5037	WAT-5037	Lights
WJT-5042	WDT-5042	WAT-5042	Light & Power
WJT-5048	WDT-5048	WAT-5048	On/Off
WJT-5036	WDT-5036	WAT-5036	Power
WJT-5034	WDT-5034	WAT-5034	Single Phase
WJT-5055	WDT-5055	WAT-5055	Spare
WJT-5056	WDT-5056	WAT-5056	Telephone
WJT-5035	WDT-5035	WAT-5035	Three Phase
WJT-5054	WDT-5054	WAT-5054	___ Volts

Labels


“Mr. Ouch” NEMA Safety Labels

- Use on pad-mounted transformers located in public areas
- Meets NEMA and UL standards
- Made of tamper-resistant film to prevent defacing and vandalism
- Permanent pressure-sensitive adhesive makes removal virtually impossible
- Orange WARNING label goes on outside of enclosure
- Red DANGER label goes on inside of enclosure


Note: Order multiple 25 labels.




CAT. NO.	LABEL SIZE
WUT-0368	4½" x 10¾"



CAT. NO.	LABEL SIZE
WUT-0366	4½" x 8"



CAT. NO.	LABEL SIZE
WUT-0369	4½" x 10¾"



CAT. NO.	LABEL SIZE
WUT-0367	4½" x 8"

Self-Sticking Polyester Safety Labels



CAT. NO.	LABEL SIZE
WJA-1100	2¼" x 9"
WQA-1100	5" x 14"



CAT. NO.	LABEL SIZE
WJA-0076	2¼" x 9"
WQA-0076	5" x 14"



CAT. NO.	LABEL SIZE
LB86877	3½" x 5"



CAT. NO.	LABEL SIZE
LB86871	3½" x 5"



CAT. NO.	LABEL SIZE
LB86860	3½" x 5"



CAT. NO.	LABEL SIZE
LB86861	3½" x 5"

Labels

The handy markers for frequent identification jobs.

Write-On Control Markers

- A quick and easy way to keep on-the-spot records
- Easy to carry and dispense as needed
- Made from pressure-sensitive, imprintable matte vinyl
- Adheres to clean, flat, dry, smooth surfaces
- Resists grease, oil and moisture
- Accepts marking by pen, pencil, felt-tip marker, typewriter or rubber stamp
- Standard marker size is 1½"W x ⅝"H with 14 markers per card
- Some markers available in extra-large 2½"W x 1"H size with 9 markers per card

INSPECTED	
DATE _____	INITIALS _____

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP19	1½" x ⅝"	14

CAUTION

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP6	1½" x ⅝"	14

EXTINGUISHER
CHECKED
DATE _____ BY _____

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP16	1½" x ⅝"	14

CERTIFICATION
BY _____ DATE _____
DUE _____

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP9	1½" x ⅝"	14

INVENTORY
NO. _____ DATE _____
COUNT _____ BY _____

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP20	1½" x ⅝"	14

BIN NO.

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP3	1½" x ⅝"	14

MODEL NO.

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP22	1½" x ⅝"	14

EMERGENCY
FIRE _____
POLICE _____
MEDICAL _____
MAINTENANCE _____

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP7	2½" x 1"	9

REJECTED
BY _____ DATE _____
REASON _____

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP24	2½" x 1"	9

MAINTENANCE
BY _____
DATE _____

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP21	2½" x 1"	9

ACCEPTED
BY _____ DATE _____

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP5	1½" x ⅝"	14

CALIBRATED
BY _____ DATE _____
DUE _____

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP1	1½" x ⅝"	14

CALIBRATION
BY _____ DATE _____
DUE _____

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP26	1½" x ⅝"	14

Note: Order multiple 25 cards.

Labels

Write-On Control Markers (continued)

CERTIFICATION	
BY _____	DATE _____
DUE _____	

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP2	1½" x ¾"	14

DUE FOR INSPECTION	
DO NOT REMOVE	

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP18	1½" x ¾"	14

REJECTED	
BY _____	DATE _____
REASON _____	

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP4	1½" x ¾"	14

TESTED	
DATE _____	INITIALS _____

CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP25	1½" x ¾"	14

CALIBRATION	
BY _____	DATE _____
DUE _____	


CAT. NO.	MARKERS SIZE	MARKERS PER CARD
WCMP75	2¾" x 1"	9

Note: Order multiple 25 cards.

Stay ready for quality control!

Polyolefin Pocket Pack Markers

- Easy to carry — marker books fit in shirt pocket
- Easy to use — just peel the marker from the page
- Clean and convenient — markers are tabbed so fingers never touch the adhesive



Note: Order multiple 10 books.

CAT. NO.	LEGEND	LABELS PER BOOK
WTMP-1B	CALIBRATED (black)	240
WTMP-2B	CERTIFICATION (black)	240
WTMP-3B	MAINTENANCE (blue)	240
WTMP-4B	REJECTED (red)	240
WTMP-5B	ACCEPTED (green)	240
WTMP-6B	HOLD (red)	240
WTMP-7B	RETURN TO VENDOR (orange)	240
WTMP-8B	REWORK (black)	240
WTMP-9B	HOLD FOR INSPECTION (blue)	240
WTMP-11B	CAUTION (black)	240
WTMP-16B	DATE INSTALLED (black)	240
WTMP-18B	DUE FOR INSPECTION (orange)	240
WTMP-19B	DO NOT USE AFTER (red)	240
WTMP-20B	INSPECTED (black)	240
WTMP-21B	BLANK HEADING	240
WTMP-22B	REPAIRED BY (orange)	240
WTMP-24B	SCRAPPED (orange)	240
WTMP-25B	TESTED (green)	240
WTMP-26B	CALIBRATION (green)	240
WTMP-52B	PROPERTY TAG (black)	240
WTMP-53B	SERIAL NO. (black)	240
WTMP-55B	TOOL NO. (blue)	240


15 pages per book, 16 markers per page. Each label is 1½" x ¾". Each book contains 240 identical labels.

Labels


Easy to read and available in a variety of configurations!

Numbers and Letters


- High-contrast, self-sticking, vinyl cloth markers make numbering and coding quick and easy
- Rated for indoor use
- Select character heights ranging from 5/16" to 33/4"



Series 003
78 markers per card
Marker Size: 3/8" x 1/2" Character Height: 5/16"



Series 063
32 markers per card
Marker Size: 9/16" x 3/4" Character Height: 5/8"



Series 100
10 markers per card
Marker Size: 7/8" x 1 1/2" Character Height: 1"



Series 200
10 markers per card
Marker Size: 7/8" x 2 1/4" Character Height: 2"

DESCRIPTION	LEGEND	SERIES 003	SERIES 063	SERIES 100	SERIES 200
Letters	A-Z	WCNL003A...WCNL003Z	WCNL063A...WCNL063Z	WCNL100A...WCNL100Z	WCNL200A...WCNL200Z
Numbers	0	WCNL003ZERO	WCNL063ZERO	WCNL100ZERO	WCNL200ZERO
Numbers	1-9	WCNL0031...WCNL0039	WCNL0631...WCNL0639	WCNL1001...WCNL1009	WCNL2001...WCNL2009
Letters in Sequence	A-Z	WCNL003AZ	WCNL063AZ	N/A	N/A
Letters in Sequence	A-J	N/A	N/A	WCNL100AJ	WCNL200AJ
Letters in Sequence	K-T	N/A	N/A	WCNL100KT	WCNL200KT
Letters in Sequence	U-Z	N/A	N/A	WCNL100UZ	WCNL200UZ
Numbers in Sequence	0-9	WCNL00309	WCNL06309	WCNL10009	WCNL20009

Note: Order multiple 5 cards.

Reflective Industrial Markers

- High visibility markers for use in dimly lit or dark areas
- Pressure-sensitive adhesive
- Apply at temperatures above 40° F



CAT. NO.	SIZE	CHARACTER HEIGHT	MARKER SIZE (W X H)
WRSUM*	Small	1 1/2"	1 3/8" x 1 7/8"
WRUM*	Standard	2 1/2"	1 3/4" x 2 7/8"
WRLUM*	Large	3 3/4"	2 5/8" x 4 5/16"

* Add desired letter (A-Z) or number (0-9) in place of asterisk to complete CAT. NO. Example: WRSUM1, WRSUM2, WRSUMA, etc.

Note: Order multiple 25 cards.

Labels

Don't let words get in the way of hazard information.

Pictogram Labels

- Universal symbols communicate hazards to anyone, regardless of literacy or language
- Made from self-adhesive vinyl
- Label size is 2" x 2"



CAT. NO.	LABEL SIZE
PTG-100	2" x 2"



CAT. NO.	LABEL SIZE
PTG-101	2" x 2"



CAT. NO.	LABEL SIZE
PTG-102	2" x 2"



CAT. NO.	LABEL SIZE
PTG-103	2" x 2"



CAT. NO.	LABEL SIZE
PTG-104	2" x 2"



CAT. NO.	LABEL SIZE
PTG-105	2" x 2"



CAT. NO.	LABEL SIZE
PTG-106	2" x 2"



CAT. NO.	LABEL SIZE
PTG-107	2" x 2"



CAT. NO.	LABEL SIZE
PTG-108	2" x 2"



CAT. NO.	LABEL SIZE
PTG-109	2" x 2"

Note: Order multiple 100 labels.

EZCODE®

Custom Label Express Order Form


This Custom Label Order Form is for the convenience of you and your authorized Thomas & Betts Distributor. To help expedite your order, please copy this form and fax a completed copy to us. For questions about ordering Custom Labels, call Technical Services at 888-862-3289.

Fax your order to 901-252-1321.


Label Types and Available Sizes:

Please check the appropriate boxes to choose English or Spanish and the size.




<input type="checkbox"/> E		<input type="checkbox"/> 3½" x 5"	<input type="checkbox"/> 3½" x 6"
<input type="checkbox"/> S		<input type="checkbox"/> 3½" x 10"	<input type="checkbox"/> 5" x 7"


Arc Flash

<input type="checkbox"/> E		<input type="checkbox"/> 2¼" x 4½"	<input type="checkbox"/> 2¼" x 9"	<input type="checkbox"/> 3½" x 5"
<input type="checkbox"/> S		<input type="checkbox"/> 4½" x 8"	<input type="checkbox"/> 4½" x 10¾"	<input type="checkbox"/> 5" x 14"


Electrical Safety

<input type="checkbox"/> E		<input type="checkbox"/> 2¼" x 4 ½"	<input type="checkbox"/> 3½" x 5"
<input type="checkbox"/> S			

Lockout

<input type="checkbox"/> E		<input type="checkbox"/> ¾" x 5"
<input type="checkbox"/> S		

Padlock

<input type="checkbox"/> E		<input type="checkbox"/> 3½" x 5"
<input type="checkbox"/> S		

Machine Warning

Legend

Please print your message clearly in the box below.

Materials:

Please check one box.

<input type="checkbox"/> Vinyl
<input type="checkbox"/> Other _____

Quantity:

No minimum order. Orders for 50+ labels are welcome. Call for delivery and additional volume discounts.

High-Volume Blank Printer Labels:

Please complete all portions.

Your Printer Technology

<input type="checkbox"/> TT	Thermal
<input type="checkbox"/> LP	Laser
<input type="checkbox"/> DM	Dot Matrix
<input type="checkbox"/> JT	Ink Jet
<input type="checkbox"/> EZ	Portable

Label Size

- Use fractional inches, not decimals.
- For labels on a cassette, check the C box to indicate continuous measurement in feet and indicate length next to the box.

<input type="text"/>	Width	<input type="text"/>	Height
<input type="checkbox"/> C	Length _____ft.		

Color

<input type="checkbox"/> White
<input type="checkbox"/> Yellow

Label Material

<input type="checkbox"/> SL	Self-Laminating	<input type="checkbox"/> N	Nylon
<input type="checkbox"/> C	Vinyl Cloth	<input type="checkbox"/> HS	Heat Shrink
<input type="checkbox"/> P	Polyester	<input type="checkbox"/> PM	Polyimide

Quantity:

No minimum order. Orders for 50+ labels are welcome. Call for delivery and additional volume discounts.

Distributor Billing Location:

Distributor Name: _____
 Distributor Address: _____
 P.O. Number: _____
 Contact Name: _____
 Phone Number: _____
 Fax Number: _____

Shipping Location:

Your Name/Title: _____
 Company Name: _____
 Attn: _____
 Address: _____
 City: _____ State: _____ Zip: _____
 Phone/Fax Number: _____
 P.O. Number: _____

Signs

Prevent injuries and reduce downtime with EZCODE® safety and compliance signs.

Industry Standards

ASME (ANSI Z535) and OSHA (1910.145) require the use of safety and compliance signs to indicate hazards that may lead to accidents, injury and property damage. EZCODE® signs comply with all current OSHA and ANSI standards and will help you create a safer workplace for both employees and visitors.

Guide to Headers




DANGER indicates an immediate hazard with a strong potential for death or severe injury



NOTICE provides general information to prevent confusion



CAUTION warns against potential hazards or unsafe practices



SAFETY FIRST offers information about health, housekeeping and general safety

Signs

Materials


Self-Sticking (SS)

- Made from pressure-sensitive vinyl with permanent acrylic adhesive
- Indoor and outdoor applications
- Temperature range of -40° F to 180° F
- 2- to 3-year durability




Plastic (PL)

- Made from durable linear polyethylene
- Fade- and crack-resistant
- Indoor and outdoor applications
- Temperature range of -10° F to 176° F
- 5- to 8-year durability



Aluminum (AL)

- Made from aluminum with baked finish and screen-printed graphics
- Indoor and outdoor applications
- 8- to 10-year durability



Sizes

- Most signs available in your choice of 7" x 10" or 10" x 14" sizes
- Bilingual signs available in larger 10" x 14" size only


Custom Signs

Need signs you don't see in this catalog? No problem — we welcome custom orders. Please refer to the form on page **D-38** for guidance, and don't hesitate to contact our knowledgeable, helpful EZCODE® Technical Services representatives for ordering assistance.

Custom Sign Express Order Form

This Custom Sign Order Form is for the convenience of you and your authorized Thomas & Betts Distributor. To help expedite your order, please copy this form and fax a completed copy to us. For questions about ordering Custom Signs, call Technical Services at **888-862-3289**.

Fax your order to **901-252-1321**.



Materials and Available Sizes:

Please check the appropriate box for material and size

MATERIAL	AVAILABLE SIZES
<input type="checkbox"/> Aluminum	<input type="checkbox"/> 7" x 10" <input type="checkbox"/> 10" x 14"
<input type="checkbox"/> Plastic	<input type="checkbox"/> 7" x 10" <input type="checkbox"/> 10" x 14"
<input type="checkbox"/> Self-Sticking	<input type="checkbox"/> 3" x 5" <input type="checkbox"/> 5" x 7" <input type="checkbox"/> 7" x 10" <input type="checkbox"/> 9" x 12" <input type="checkbox"/> 10" x 14"

Quantity:

No minimum order. Orders for 50+ labels are welcome. Call for delivery and additional volume discounts.

Header/Color:

Please check the appropriate box to choose English or Spanish.

<input type="checkbox"/> E ▲ DANGER	<input type="checkbox"/> E NOTICE	<input type="checkbox"/> E ▲ CAUTION	<input type="checkbox"/> E SAFETY FIRST	<input type="checkbox"/> E ▲ WARNING
<input type="checkbox"/> S ▲ PELIGRO	<input type="checkbox"/> S AVISO	<input type="checkbox"/> S ▲ PRECAUCION	<input type="checkbox"/> S SEGURIDAD PRIMERO	<input type="checkbox"/> S ▲ ADVERTENCIA
<p><input type="checkbox"/> Red and Black Header on White</p> <p><input type="checkbox"/> Blue Header on White</p> <p><input type="checkbox"/> Yellow and Black Header on White</p> <p><input type="checkbox"/> Green Header on White</p> <p><input type="checkbox"/> Orange and Black Header on White</p>				
<input type="checkbox"/> NO HEADER colors listed to the right	<input type="checkbox"/> Black on White	<input type="checkbox"/> Black on Yellow	<input type="checkbox"/> Red on White	<input type="checkbox"/> Magenta on Yellow
	<input type="checkbox"/> Black on Orange	<input type="checkbox"/> Green on White	<input type="checkbox"/> Blue on White	


Legend

Please print your message clearly in the box below.

Lay out best way Layout exactly as shown below

Pictograms:

A pictogram can be included on your custom sign, in black, at no additional charge. **Please indicate pictogram number below.**



Distributor Billing Location:

Distributor Name: _____
 Distributor Address: _____
 P.O. Number: _____
 Contact Name: _____
 Phone Number: _____
 Fax Number: _____

Shipping Location:

Your Name/Title: _____
 Company Name: _____
 Attn: _____
 Address: _____
 City: _____ State: _____ Zip: _____
 Phone/Fax Number: _____
 P.O. Number: _____

Warning Tapes

Save time and money over painting!

Color-Coded Vinyl I.D. Tape

- Effectively warns or identifies equipment, traffic and housekeeping items
- Choose from different widths
- Many colors available



1" WIDE CAT. NO.	2" WIDE CAT. NO.	3" WIDE CAT. NO.	4" WIDE CAT. NO.	COLOR
AA-1121	BA-1121	CA-1121	NA-1121	Silver
AA-1122	BA-1122	CA-1122	NA-1122	Black
AA-1123	BA-1123	CA-1123	NA-1123	Blue
AA-1124	BA-1124	CA-1124	NA-1124	Brown
AA-1125	BA-1125	CA-1125	NA-1125	Green
AA-1126	BA-1126	CA-1126	NA-1126	Orange
AA-1127	BA-1127	CA-1127	NA-1127	Purple
AA-1128	BA-1128	CA-1128	NA-1128	Red
AA-1129	BA-1129	CA-1129	NA-1129	White
AA-1130	BA-1130	CA-1130	NA-1130	Yellow
AA-1131	BA-1131	CA-1131	NA-1131	Clear

60 yards per roll

Reflective Roll Tape



2" WIDE CAT. NO.	3" WIDE CAT. NO.	4" WIDE CAT. NO.	COLOR
AZ-3108	BZ-3108	CZ-3108	Black & Yellow Stripe
AZ-3110	BZ-3110	CZ-3110	Red & White Stripe

5 yards per roll.

Self-Sticking Vinyl Cloth Tape



2" WIDE CAT. NO.	3" WIDE CAT. NO.	4" WIDE CAT. NO.	COLOR
AZ-1100	BZ-1100	CZ-1100	Black & Yellow Stripe
AZ-1102	BZ-1102	CZ-1102	Red & White Stripe
AZ-1303	BZ-1303	CZ-1303	Magenta & Yellow Stripe & Radiation Symbol

30 yards per roll.

Laminated Vinyl Tape



2" WIDE CAT. NO.	3" WIDE CAT. NO.	4" WIDE CAT. NO.	COLOR
AZ-2104	BZ-2104	CZ-2104	Black & Yellow Stripe
AZ-2106	BZ-2104	CZ-2104	Red & White Stripe

18 yards per roll.

2-Sided Foam Mounting Tape

CAT. NO.	DESCRIPTION
NA-0365	2-Sided Foam Mounting Tape

9 yards per roll.

Warning Tapes

Mark off hazardous or off-limit areas quickly and easily! Protect-A-Line™ Barricade and Burial Tapes



Barricade Tape

- Inexpensive and easy to handle
- Convenient and reusable
- For indoor and outdoor use



Buried Utility Tape

- Protect against costly dig-ins
- Place 1 to 1½ feet below the ground surface directly above the pipeline or cable below
- Bright, fade-resistant colors warn equipment operators that a vital pipeline or cable is buried below — before damage occurs
- Black text on a bright background



Foil-Backed Detectable Buried Utility Tape

- Features a metallic backing designed to be detectable under normal earthen surfaces up to 18" with common metal detectors
- Simple and fast method for relocating lines, cables and conduit for future renovation
- Black text on a bright background

CAT. NO.	LEGEND	COLOR
Surveyors Tape 1½" x 1,000'		
NA-0200	No Legend, No Printing	Yellow
NA-0201	No Legend, No Printing	Red
NA-0202	No Legend, No Printing	Green
NA-0203	No Legend, No Printing	Blue
NA-0204	No Legend, No Printing	Orange
Barricade Tape 3" x 1,000'		
NA-0250	Caution	Yellow
NA-0253	Caution Construction Area	Yellow
NA-0254	Caution Do Not Enter	Yellow
NA-0256	Caution Hard Hat Area	Yellow
NA-0257	Caution High Voltage	Yellow
NA-0258	Caution Men Working	Yellow
NA-0261	Caution Open Trench	Yellow
NA-0267	Danger, on Stripes	Red & White
Buried Utility Tape 3" x 1,000'		
NA-0600	Electric Line	Red
NA-0608	Electric Line	Yellow
NA-0601	Water Line	Blue
NA-0602	Telephone Line	Orange
NA-0603	Gas Line	Yellow
NA-0605	Sewer Line	Green
NA-0606	High Voltage Line	Red
NA-0609	Fiber Optic Cable	Orange

Note: All barricade and utility tapes are 4 MIL polyethylene and are not self sticking. All legends are printed in black. Standard package is 1 roll.

CAT. NO.	LEGEND	COLOR
Buried Utility Tape 6" x 1,000'		
NA-0700	Electric Line	Red
NA-0708	Electric Line	Yellow
NA-0701	Water Line	Blue
NA-0702	Telephone Line	Orange
NA-0703	Gas Line	Yellow
NA-0706	High Voltage Line	Red
NA-0709	Fiber Optic Cable	Orange
Foil-Backed Detectable Buried Utility Tape 3" x 1,000'		
NAF-0600	Electric Line	Red
NAF-0608	Electric Line	Yellow
NAF-0601	Water Line	Blue
NAF-0602	Telephone Line	Orange
NAF-0603	Gas Line	Yellow
NAF-0604	Oil Line	Yellow
NAF-0605	Sewer Line	Green
NAF-0606	High Voltage Line	Red
NAF-0607	Cable TV Line	Orange
NAF-0609	Fiber Optic Cable	Orange
Foil-Backed Detectable Buried Utility Tape 6" x 1,000'		
NAF-0700	Electric Line	Red
NAF-0708	Electric Line	Yellow
NAF-0701	Water Line	Blue
NAF-0702	Telephone Line	Orange
NAF-0703	Gas Line	Yellow
NAF-0704	Oil Line	Yellow
NAF-0705	Sewer Line	Green
NAF-0706	High Voltage Line	Red
NAF-0707	Cable TV Line	Orange
NAF-0709	Fiber Optic Cable	Orange