



Hex PCB Support; threaded; PCB thk. 1.6mm; M4/WS8X25.0; PA66; black

06.84.256

Type	Snap-in / screw thread
Model	Snap-in / female thread M4
Design	Without tension wings
Length	25.00 mm
Material	Nylon 66 UL94 HB
PCB Hole Dia.	4.00 mm
Chassis Hole Dia.	4.20 mm
UL Flammability	UL94 HB
Color	Black
Thread Type	M4
Board Thickness	1.60 mm
RoHS II compliant	yes
Reach/SVHC free	yes

Similar products

Hex PCB Support; threaded; PCB thk. 1.6mm; M3/WS6X25.0; PA66; black
06.53.256

Hex PCB Support; threaded; PCB thk. 2.0mm; M3/WS6X25.0; PA66; black
06.63.256

Product No. **06.84.256**

Delivery **in stock**

Price: €22.40 / 100 pcs.

Packing unit: 100 pcs.
All prices exclude VAT and shipping costs.

Log in to get lower prices for larger quantities and order items.

