

Technical Information	
Number of Screens	1
Screen Size	54.6 cm (21.5")
Screen Mode	Full HD
Response Time	5 ms
Aspect Ratio	£0.67
Horizontal Viewing Angle	90°
Vertical Viewing Angle	65°
Backlight Technology	LED
Panel Technology	Twisted Nematic Film (TN Film)
Adjustable Display Angle	Yes
Tilt Angle	-5°to25°
Swivel Angle	No
Adjustable Display Height	No
Adjustable Display Pivot	No
Video	
Maximum Resolution	1920 x 1080
Standard Refresh Rate	60 Hz
Colour Support	16.7 Million Colours
Contrast Ratio	100,000,000:1
Brightness	200 cd/m ²
Audio	
Speakers	No

Interfaces/Ports	
DVI	Yes
HDMI	Yes
VGA	Yes
Power Description	
Energy Efficiency Class	A
Energy Consumption per Year	29 kWh
Input Voltage	120 V AC
	230 V AC
Operating Power Consumption	18.10 W
Standby Power Consumption	450 mW
Off-Mode Power Consumption	350 mW
Physical Characteristics	
Colour	Black
Height	304.5 mm
Width	508 mm
Depth	52 mm
Height with Stand	390.50 mm
Width with Stand	508 mm
Depth with Stand	207 mm
Weight (Approximate)	2.70 kg
Weight with Stand (Approximate)	3.10 kg
Miscellaneous	

K222HQL Widescreen LCD Monitor

Package Contents

Power Cord

1 x VGA Cable