

## **Knockdown Economy Rack Cabinet** *REFK Series*




### **Features**

- Constructed in 16-gauge steel (body) and 10-gauge steel (rails).
- Two pairs of infinitely adjusting 19" mounting EIA-310-D compliant 10-32 tapped combination rails.
- Finished in either Black or Light Gray (RAL7035) rugged textured powder paint.
- Ships unassembled in a flat pack container for easy handling and shipping protection.
- Perfect for tight access areas or one person installations as unit is knocked down into five (5) easy to handle parts.

### **Specifications**

- Includes four (4) leveling feet.
- Rails are made of 10 gauge steel (zinc plated finish for grounding capabilities).
- Removable gland plate - over 10" (254 mm) long x 1.5" (38 mm) high opening - with knockouts on rear bottom of rack for easy cable access.
- Simple assembly using one bolt in each corner to lock the sides to the top and bottom (hardware included).
- Tested to nearly double the suggested load rating of 1,000 lbs.
- RoHS Compliant.
- Manufactured in North America.


### **Gallery**



### **Accessories**

- Universal Rack Shelf
- Rack Mount Locking Storage Drawer
- Sliding Keyboard Shelf
- Four Post Fixed Depth Shelf
- Rack Unit Label
- Horizontal Lacing Strip
- Horizontal Hinged Cable Manager
- Horizontal Steel Finger Cable Manager
- Rack Panels
- Lite Duty Caster Set
- Adjustable Depth 4-Post Rack Mount Shelf
- Four Post Mounting Sliding Shelf
- Four Post Mounting Zero Space Fixed Shelf
- Outlet Strips
- Adjustable Depth Cable Manager
- Horizontal Ring Cable Manager
- Cable Management Arm
- Mounting Hardware
- Grounding
- Medium Duty Caster Set

- 10-32 Tapped Combination Mounting Rail
- Square Hole Punched Mounting Rail



Part No. Black	Part No. Light Gray	Overall Dimensions			Usable Mounting Dimensions				Shipping Weight
		Height A	Width	Depth C	Rack Units	Height H	Depth	Depth (With Doors)	
REFK1903517BK1	REFK1903517LG1	40.19	21.34	17.50	20U	35.19	16.50	16.00	90 lb
REFK1904217BK1	REFK1904217LG1	47.19	21.34	17.50	24U	42.19	16.50	16.00	104 lb
REFK1904917BK1	REFK1904917LG1	54.19	21.34	17.50	28U	49.19	16.50	16.00	112 lb
REFK1905617BK1	REFK1905617LG1	61.19	21.34	17.50	32U	56.19	16.50	16.00	123 lb
REFK1906317BK1	REFK1906317LG1	68.19	21.34	17.50	36U	63.19	16.50	16.00	134 lb
REFK1907017BK1	REFK1907017LG1	75.19	21.34	17.50	40U	70.19	16.50	16.00	144 lb
REFK1907717BK1	REFK1907717LG1	82.19	21.34	17.50	44U	77.19	16.50	16.00	154 lb
REFK1903524BK1	REFK1903524LG1	40.19	21.34	24.50	20U	35.19	23.50	23.00	116 lb
REFK1904224BK1	REFK1904224LG1	47.19	21.34	24.50	24U	42.19	23.50	23.00	124 lb
REFK1904924BK1	REFK1904924LG1	54.19	21.34	24.50	28U	49.19	23.50	23.00	140 lb
REFK1905624BK1	REFK1905624LG1	61.19	21.34	24.50	32U	56.19	23.50	23.00	146 lb
REFK1906324BK1	REFK1906324LG1	68.19	21.34	24.50	36U	63.19	23.50	23.00	162 lb
REFK1907024BK1	REFK1907024LG1	75.19	21.34	24.50	40U	70.19	23.50	23.00	178 lb
REFK1907724BK1	REFK1907724LG1	82.19	21.34	24.50	44U	77.19	23.50	23.00	190 lb
REFK1903531BK1	REFK1903531LG1	40.19	21.34	31.50	20U	35.19	30.50	30.00	136 lb
REFK1904231BK1	REFK1904231LG1	47.19	21.34	31.50	24U	42.19	30.50	30.00	154 lb
REFK1904931BK1	REFK1904931LG1	54.19	21.34	31.50	28U	49.19	30.50	30.00	170 lb
REFK1905631BK1	REFK1905631LG1	61.19	21.34	31.50	32U	56.19	30.50	30.00	180 lb
REFK1906331BK1	REFK1906331LG1	68.19	21.34	31.50	36U	63.19	30.50	30.00	190 lb
REFK1907031BK1	REFK1907031LG1	75.19	21.34	31.50	40U	70.19	30.50	30.00	198 lb
REFK1907731BK1	REFK1907731LG1	82.19	21.34	31.50	44U	77.19	30.50	30.00	226 lb

## REFK Doors

Solid Door	Solid Door	Louvered Door	Louvered Door	Acrylic Door	Use With REFK Frame		
Part No.	Part No.	Part No.	Part No.	Part No.	Height	Rack Units	Part No.
Black	Light Gray	Black	Light Gray	Black			

<b>Solid Door</b>	<b>Solid Door</b>	<b>Louvered Door</b>	<b>Louvered Door</b>	<b>Acrylic Door</b>	<b>Use With REFK Frame</b>		
<b>Part No.</b>	<b>Part No.</b>	<b>Part No.</b>	<b>Part No.</b>	<b>Part No.</b>	<b>Height</b>	<b>Rack Units</b>	<b>Part No.</b>
<b>Black</b>	<b>Light Gray</b>	<b>Black</b>	<b>Light Gray</b>	<b>Black</b>			
<b>RSDf19035BK1</b>	<b>RSDf19035LG1</b>	<b>RSDl19035BK1</b>	<b>RSDl19035LG1</b>	<b>REDFP19035BK1</b>	35.00	20U	REFK1903524
<b>RSDf19042BK1</b>	<b>RSDf19042LG1</b>	<b>RSDl19042BK1</b>	<b>RSDl19042LG1</b>	<b>REDFP19042BK1</b>	42.00	24U	REFK1904224
<b>RSDf19049BK1</b>	<b>RSDf19049LG1</b>	<b>RSDl19049BK1</b>	<b>RSDl19049LG1</b>	<b>REDFP19049BK1</b>	49.00	28U	REFK1904924
<b>RSDf19056BK1</b>	<b>RSDf19056LG1</b>	<b>RSDl19056BK1</b>	<b>RSDl19056LG1</b>	<b>REDFP19056BK1</b>	56.00	32U	REFK1905624
<b>RSDf19063BK1</b>	<b>RSDf19063LG1</b>	<b>RSDl19063BK1</b>	<b>RSDl19063LG1</b>	<b>REDFP19063BK1</b>	63.00	36U	REFK1906324
<b>RSDf19070BK1</b>	<b>RSDf19070LG1</b>	<b>RSDl19070BK1</b>	<b>RSDl19070LG1</b>	<b>REDFP19070BK1</b>	70.00	40U	REFK1907024
<b>RSDf19077BK1</b>	<b>RSDf19077LG1</b>	<b>RSDl19077BK1</b>	<b>RSDl19077LG1</b>	<b>REDFP19077BK1</b>	77.00	44U	REFK1907724

*Data subject to change without notice*

© 2015. Hammond Manufacturing Ltd. All rights reserved.