

Filter Fan Kits *DNFF Series*

Features



- Kit includes one (1) of the following:
 - Fan
 - Plastic Filter Grill
 - Filter
 - Metal Grill
 - Wire Cord or Leads (see table)
 - Includes Mounting Hardware
- Flame retardant, ABS plastic filter fan grill is molded in a choice of four colors to match our racks & accessories.
 - "BK" (Black)
 - "GY" (ANSI 61 Gray)
 - "LG" (Light Gray - RAL7035)
 - "CG" (Gray/Beige - RAL7032)
- Fan is cooled by incoming air.
- Fan component is UL recognized to UL 507, and cUL recognized or CSA certified to CSA-C22.2 No. 113.

Part No.	Part No.	Part No.	Part No.	VAC	Fan Size	CFM	Cord Length
Black Filter Grill	ANSI 61 Gray Filter Grill	Gray/Beige Filter Grill	Light Gray Filter Grill				
DNFF080BK115	DNFF080GY115	DNFF080CG115	DNFF080LG115	115	3.15	32	11 Inch leads
DNFF120BK115	DNFF120GY115	DNFF120CG115	DNFF120LG115	115	4.70	105	24 Inch cord
DNFF254BK115	DNFF254GY115	DNFF254CG115	DNFF254LG115	115	10.00	550	24 Inch cord
DNFF080BK230	DNFF080GY230	DNFF080CG230	DNFF080LG230	230	3.15	32	11 Inch leads
DNFF120BK230	DNFF120GY230	DNFF120CG230	DNFF120LG230	230	4.70	105	24 Inch cord
DNFF254BK230	DNFF254GY230	DNFF254CG230	DNFF254LG230	230	10.00	550	24 Inch cord

Data subject to change without notice