



Standard
T&B Catalog Number:

TY525M

UPC Number:

78621080509

Status:

Active

Description:

Cable Tie 50lb 7" Natural Nylon with Stainless Steel Locking Device Distributor Pack

Features

Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulk-heads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.

The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.

Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

General

Material Nylon 6.6
 Color Natural

Dimension Information

Nominal Length (inches) 7
 Length (inches) 7.31
 Width (inches) .185
 Max. Wire Bundle Diameter (inches) 1.75

Specifications

Military Standard Part No. MS3367-1
 Temperature Rating -40°F to 185°F
 Flammability Rating UL 94 V-2

Tooling

Application Tools ERG50, WT1-TB

Packaging

T&B Order Multiple 100
 T&B Inner Pack 100
 Package in Units 1000
 Package Type Regular
 T&B Sold in UOM Each
 T&B Weight Per UOM 3.13 lbs. per 1000

Application Support

Material Selection Guide Available on Website
 Available Colors Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com