



Rigid/IMC Conduit Fittings

T&B Catalog Number:

H075GR-TB

UPC Number:

78621091367

Status:

Active

Description:

3/4 in. Zinc Grounding Hub with thermoplastic insulating throat; sealing ring-Nitrile (BUNA-N). For use with Rigid/IMC Conduit.

Application

Suitable for hazardous locations use in Class I, Division 2; Class II, Division 1&2; Class III, Division 1 & 2 per NEC 501-4(b); 502-4 (a) and 503-3 (a).

Suitable for hazardous locations use in Class II, Groups E, F, G & Class III locations per CEC 18-202; 18-252; 18-302; 18-352.

General

Trade Size (inches)	3/4
Material	Zinc

Dimension Information

Dimension A (inches)	1 21/32
Dimension B (inches)	1 19/32
Dimension C (inches)	29/32
Dimension D (inches)	3/16
Dimension E (inches)	25/32

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

T&B Inner Pack	25
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	8 lbs. per 100

Application Support

Spacing Chart	Available on Website
---------------	----------------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com