

TY153MFR

Ty-Rap®

Flame retardant ties. Body width of 0.097 in. and a length of 4.35 in. Maximum wire bundle diameter 0.625 in.



General

Type:	Cable Ties for Special Environments
Application:	Flame Retardant
Color:	White
T&B UPC:	78621097259
T&B Status:	M
Material:	Flame Retardant Nylon 6.6

Dimension Information

Body Width (in.):	0.100
Body Width (mm):	2.54
Length (in.):	4.35
Length (mm):	110.49
Marking Pad Size (in.) W x H:	.781 x 1
Tensile Strength (lb):	18
Max. Wire Bundle Dia. (in.):	0.63
Temperature Range:	-40°F to 185°F (-40°C to 85°C)