

1U Rack-Mount Console with 19-in. LCD

MODEL NUMBER: **B021-000-17**



Description

Tripp Lite's B021-000-17 1U Rackmount Console features an integrated 19" LCD panel, full 88-key keyboard, and touch pad, all in a 1U rackmountable housing. The included KVM cable kit allows for connection to a PS/2 computer or KVM, and a PS/2 to USB adapter is included, which can be used to connect to a USB computer or KVM. The unit features a USB 2.0 pass-through port for connection of a USB peripheral, such as a flash drive, CAC card reader, etc.. Your peripheral device connects to the USB type A port on the front of the unit, and your computer connects to the USB type A port on the back of the unit using a Tripp Lite [UR020-Series](#) type A M/M cable. Constructed of heavy-duty steel housing.

Features

- Space savings with 1U 19-inch, rack-mount drawer design
- Features 19-inch LCD TFT active-matrix, color panel
- Features a USB pass-through port for connection of a USB peripheral, such as a flash drive, CAC card reader, etc.
- Supports resolutions of up to 1366 x 768
- Included PS/2 to USB adapter allows for connection to a USB computer or KVM
- Sleep mode when the monitor cover is closed
- Input 120/240 VAC
- Constructed of heavy-duty steel housing

Highlights

- Control an entire network in just 1U of rack space; includes keyboard, 19" LCD screen, and touch pad
- Features a USB 2.0 pass-through port for connection of a USB peripheral, such as a flash drive, CAC card reader, etc.
- Connects to a PS/2 or USB server or KVM switch
- Supports video resolutions up to 1366 x 768
- Rackmountable in 19-inch system rack (1U), from 27" to 42" deep

Applications

- Use where rack space is at a premium, and where a Server/KVM display is needed.

System Requirements

- Computer or KVM with a VGA monitor port and USB or PS/2 keyboard/mouse ports

Package Includes

- 1- B021-000-17 1U Rackmount Console
- 1- KVM Cable Kit (HD15M to HD15M + 2 PS/2 Male)
- 1-PS/2 to USB Adapter
- 1- C13 to 5-15P Power Cord
- 1- User Manual

Specifications

General Info	
RoHS	Y
OVERVIEW	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Users	1
PC/Server Connections	VGA; USB; PS/2
Cat5 KVM Switch	No
IP Remote Access	No
Style	1U Rack Console (non-KVM)
INPUT	
Electrical Consumption	(Line Mode) 30W / (Standby Mode) 5W
PHYSICAL	
Color	Black; Green
ENVIRONMENTAL	
BTUs	(Line Mode) 102 BTU/Hr / (Standby Mode) 17.06 BTU/Hr
CONNECTIONS	
Connector A	HD15 (FEMALE)
Ports	0
CERTIFICATIONS	
Certifications	UL 60950-1 (USA), CAN/CSA (Canada), FCC Part 15 Class A, CE, IEC 60950-1.
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.