

4-Port Desktop KVM Switch

MODEL NUMBER: **B022-004-R**



Description

Tripp Lite's 4-port B022-004-R KVM Switch is the optimal solution for controlling 4 computers from one keyboard, mouse and monitor. Installation is a snap - just connect the PCs using Tripp Lite's P774-Series (PS/2) or P776-Series (USB) KVM cable kits (Not included). No software or complicated set-up procedures are required. Easily switch between computers via the front-panel push buttons or keyboard hotkey commands.

Features

- Control 4 computers from a single keyboard, mouse, and monitor
- Supports VGA, SVGA, or Multisync monitors
- Connect to PS/2 and USB computers using Tripp Lite's P774-Series (PS/2) and P776-Series (USB) KVM cable kits (Not included)
- Easy to install - no software required
- Easily select a computer via front-panel push buttons or keyboard hotkeys
- Auto Scan function to monitor computer operation
- Supports Microsoft IntelliMouse and the scrolling wheel on most mice
- Superior video quality - up to 2048x1536; DDC2B
- External power not required
- Compatible with all major operating systems except Mac and Sun

Highlights

- Control 4 computers with 1 keyboard, monitor and mouse
- Connect to PS/2 and USB computers using Tripp Lite's P774-Series (PS/2) and P776-Series (USB) KVM cable kits (Not included)
- Simple plug-and-play design
- Ultra-slim design takes up minimal space
- Compatible with all major operating systems except Mac and Sun

System Requirements

- VGA, SVGA or Multisync Monitor with an HD15 port
- PS/2 mouse
- PS/2 keyboard
- PS/2 or USB computer
- P774-Series (PS/2) and/or P776-Series (USB) KVM Cable kit(s); 1 for each connected computer
- Compatible with all major operating systems except Mac and Sun

Package Includes

- B022-004-R 4 Port KVM Switch
- PS/2 console cable kit
- Owner's manual

Specifications

General Info	
RoHS	Y
OVERVIEW	
Users	1



Console	No
Port Control	Push Buttons, Hotkeys
Max CPU	4
PC/Server Connections	PS/2
Cat5 KVM Switch	No
IP Remote Access	No
Style	Desktop
PHYSICAL	
Unit Dimensions (hwd / in.)	1 x 7.9 x 3
Unit Dimensions (hwd / cm)	2.54 x 20.07 x 7.62
Unit Weight (lbs.)	1.1
Unit Weight (kg)	0.50
Color	Silver
LCD Monitor (in.)	Not Applicable
LCD Monitor (cm)	Not Applicable
CONNECTIONS	
Ports	4
Computer/Server Ports	(x4) HD15 (Female)
Local Console Ports - Port 1	HD15 (Female)
Local Console Ports - Port 2	(x2) MiniDIN6 (Female)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.