

## 4-Port VGA/SVGA Video Splitter with Signal Booster, High Resolution Video, 350MHz, (HD15 M/4xF)

MODEL NUMBER: **B114-004-R**



### Description

Tripp Lite's 4-Port VGA/SVGA Video Splitter provides bandwidth support at 350MHZ, allowing simultaneous display of video on up to 4 monitors. In addition, a built-in booster allows a video signal (up to 2048 x 1536 @ 60Hz) to be transmitted up to 210 ft. from the source. Four standard HD15 female ports are used to connect the monitors, while a fifth HD15 male port is used to connect the CPU. The splitter can be located up to 25 ft. from the connected computer, and up to 185 ft. from the connected monitors. The number of connected monitors can be expanded by cascading up to 3 levels of B114-004-R splitters together.

### Features

- Simultaneously display video on up to 4 VGA/SVGA monitors
- Ideal for video presentations or sharing information with multiple users
- A built-in booster allows a video signal (up to 2048 x 1536 @ 60Hz) to be transmitted up to 210 ft. from the source
- The splitter can be located up to 25 ft. from the connected computer, and up to 185 ft. from the connected monitors
- 350Mhz Bandwidth Support
- Cascade up to 3 levels of B114-004-R splitters together to increase the number of connected monitors
- Rugged, fully shielded metal housing

## Specifications

General Info	
RoHS	Y
OVERVIEW	

### Highlights

- Simultaneously displays video on up to 4 VGA/SVGA monitors
- A built-in booster allows a video signal (up to 2048 x 1536 @ 60Hz) to be transmitted up to 210 ft. from the source
- The splitter can be located up to 25 ft. from the connected computer, and up to 185 ft. from the connected monitors
- 350Mhz bandwidth support

### System Requirements

- Computer with an HD15 port
- VGA/SVGA monitor
- B114-004-R can only be cascaded with other B114-004-R splitters

### Package Includes

- B114-004-R VGA/SVGA Video Splitter - 4 Port
- External power supply, 9V, 0.8A
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Chromebook Compatible	No
Display Style	Splitter
Model Type	VGA
<b>PHYSICAL</b>	
Color	Black
<b>CONNECTIONS</b>	
Connector A	HD15 (MALE)
Connector B	HD15 (FEMALE) (X4)
Ports	4
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.