

HDMI over Cat5/Cat6 Active Extender, Wallplate Remote Receiver Unit for Video and Audio, 1920x1200 at 60Hz/1080p

MODEL NUMBER: **B126-1A0-WP-1**



Description

The B126-1A0-WP-1 is a receiver unit that is used with the [B126-002](#) and [B126-004](#) transmitter units. It extends a 1080p (60Hz) signal to a monitor up to 150 ft. away using Cat5e/6 cable. To achieve maximum distance and resolution, use 24Awg Solid Wire Cat5e/6 cable. (Tripp Lite's N202-Series) It features a built-in Equalization control for adjustment of the video image, and RJ45 jacks for easy connection with Cat5e/6 patch cable. Supports 24-bit True Color (8-bits per channel), HDCP, 3D, and both stereo audio and 7.1 channel surround sound audio (*7.1 channel surround sound signal will be Multi-Channel or PCM*).

Installation is simple. Connect the transmitter unit to an HDMI source using a Tripp Lite P568-Series HDMI cable (not included). Connect the receiver unit to a display using a Tripp Lite P568-Series HDMI cable (not included).

Finally, connect the receiver to the RJ45 port on the transmitter using a single Cat5e/6 cable.

- A 1080p (60Hz) signal can be transmitted up to 150 ft.
- A 1080i (60Hz) signal can be transmitted up to 200 ft.
- A 3D signal can be transmitted up to 125 ft.

Further extend the signal range or add more displays by using a Tripp Lite [B126-110](#) Remote Repeater unit:

- Add up to three repeaters, with a receiver unit located at the end of the installation, for a total of 4 displays.
- A 1080p (60Hz) signal can be extended up to 125 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 1080p (60Hz) signal can be extended up to 500 ft..
- A 1080i (60Hz) signal can be extended up to 175 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 1080i (60Hz) signal can be extended up to 700 ft..
- A 3D signal can be extended up to 100 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 3D signal can be extended up to 400 ft..

Highlights

- For use with the [B126-002](#) and [B126-004](#) transmitter units
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p (60Hz)
- HDCP and 3D compatible
- Compatible with both stereo audio and 7.1 channel surround sound audio (*7.1 channel surround sound signal will be Multi-Channel or PCM*)
- Supports 24-bit True Color (8-bits per channel)
- Can further expand the range and number of monitors by adding repeaters
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- B126-1A0-WP-1 HDMI Over Cat5 Active Extender Remote Wallplate
- Screwdriver for adjustment of Equalization (Skew)
- Wallplate mounting hardware
- External power supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Owner's manual



Features

- For use with [B126-002](#) and [B126-004](#) transmitter units.
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p (60Hz)
- 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, is required to achieve maximum distance and resolution.
- Use Tripp Lite P568-Series HDMI cables to connect to HDMI source and monitor.
- HDCP and 3D compatible.
- Compatible with both stereo audio and 7.1 channel surround sound audio (*7.1 channel surround sound signal will be Multi-Channel or PCM*).
- Supports 24-bit True Color (8-bits per channel).
- Can further expand the range and number of monitors by adding [B126-110](#) repeaters.
- Connect up to three repeaters, with a receiver unit located at the end of the installation, for a total of 4 displays.
- A 1080p (60Hz) signal can be extended up to 125 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 1080p (60Hz) signal can be extended up to 500 ft..
- A 1080i (60Hz) signal can be extended up to 175 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 1080i (60Hz) signal can be extended up to 700 ft..
- A 3D signal can be extended up to 100 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 3D signal can be extended up to 400 ft..
- Features a built-in Equalization control for adjustment of the video image.
- Features RJ45 jacks for easy connection with Cat5e/6 patch cable. 110 punchdown not required.
- Compatible with all operating systems.
- Plug and play; No drivers required.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Specifications

General Info	
RoHS	Y
OVERVIEW	
Chromebook Compatible	Yes
Display Style	Extender
Model Type	HDMI
Cable Types	CAT5/CAT5E
PHYSICAL	
Unit Dimensions (hwd / cm)	4.5 x 2.75 x 1
Included Mounting Accessories	Yes
Color	White
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
CONNECTIONS	
Connector A	HDMI (FEMALE)
Connector B	RJ45 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.